


TV Outlets



Description

This uniquely shaped range of TV outlets is easy to install, with clear bold terminal markings and is supplied in individual protective bags suitable for display.

Features

- Contemporary designed profile
- Only one size 4mm screwdriver needed
- Loop-in/loop-out braiding clamps on VC1264
- Diplexer & Triplexer plates are fully screened and suitable for DAB (Digital Audio Broadcasting)
- Fixing screws & screw caps supplied
- Individually bagged
- 2-year guarantee

Range

Single co-axial isolated	VP1264
TV/FM (DAB) diplexer	VP1265
TV/F type	VP1266
TV/FM (DAB) Satellite triplexer	VP1340

Technical Specification

Size	86 x 86 x 7mm (H x W x D)
Front plate material	Urea formaldehyde
Urea flammability classification	UL94 grade V-C
No user serviceable parts	

Back Boxes

Minimum recommended depth

	Metal Flush 25mm	Dry lining 35mm	Surface	
			25mm	33mm*
1g	DB162	DB2540	VP1221	VP1222
2g	DB163	DB2541	VP1223	VP1224

*A deeper surface box is required for VP1265 & VP1340

Standards

- BS EN 50083-2