

M18 FLAG230XPDB-121C

M18 FUEL™ 230 MM LARGE BRAKING GRINDER WITH PADDLE SWITCH

The world's first single 18V battery operated large angle grinder that delivers the power to grind, lighter than corded tools and makes up to 68 cuts per charge in 42 mm stainless steel pipe

The HIGH OUTPUT™ system of tools elevates the M18 FUEL™ technologies to a new level and delivers extended performance and extended run time. These tools are designed to maximise the partnership with HIGH OUTPUT™ and FORGE™ batteries

Disc brake slows the disc down faster for improved user protection

Non-lockable safety paddle switch with line-lock-out function to prevent automatic start up

Keyless guard for great cutting capacity and fast guard adjustment without using a key

FIXTEC™ nut for tool-free disc change

Anti-vibration side handle for lower vibration

Removable dust screen to prevent debris entrance, prolonging motor life

-



REDLITHIUM™



No load speed (rpm)	6,600
Brake	Yes
Anti kickback protection	Yes
Switch type	Paddle (Deadman) switch
FIXTEC™	Yes
Kit included	1 x M18 FB12 Battery pack, M12-18 FC Charger, Kitbox
Article number	4933499241