

TERTIARY SERVICES



250 KG

Ultra-light plastic tray trolleys. Easy to maintain, they are particularly popular with laboratories and canteens.

- Meticulous finishes. Phthalate-free, non-toxic, suitable for food contact. Resistant to temperatures ranging from -20°C to +140°C. Easy to clean.
- Extruded reinforced aluminium uprights.
- Reinforced trays, 16 mm thick, in polypropylene and fibreglass, with 30 mm rim.
- Plastic handles integrated into the top tray.
- 4 castor wheels, 2 of which have brakes, EN 1757 standard. Heavy-duty, ball-bearing, steel frame and non-staining TPE tyres. Low starting resistance, quiet running, swivels 360° on the spot.

Models with single trays :

- 30 mm rim.

Model with trays + 2 drawers :

- Integrated, lockable, non-protruding drawers mounted on roller runners with quick-return system. Integrated grab bar.
Top drawer dimensions: Width 600 × Depth 400 × Height 45 mm.
Bottom drawer dimensions: Length 600 × Depth 400 × Height 70 mm.
- Delivered unassembled. Easy to assemble.



885 007 668 - 2 trays simple



885 007 672 - Trays + 2 drawers

Reference	Model	Capacity kg	Number of trays	Capacity upper/intermediate tray kg	Tray dimensions mm	Tray spacing mm	Overall dimensions mm	Wheels	Weight kg
885 007 668	Single trays	250	2	150	680 x 450	553	850 x 480 x 950	Ø 100 TPE bandage	9
885 007 669			3			275	850 x 480 x 1000		11,5
885 007 671			2		915 x 520	553	1100 x 520 x 950		12,5
885 007 670			3			275	1100 x 520 x 1020		16,5
885 007 672	Trays + 2 drawers		2		680 x 450	448	850 x 480 x 950		20,5



PRODUCT ZOOM



885 007 669 - 3 single trays



885 007 671 - 2 single trays



885 007 670 - 3 single trays

OTHER MODELS AVAILABLE



Compact sideboard with 2 shelves



Sideboard with 100mm tray, 2 or 3 shelves



Assembly instructions