

KERN 366-87

Individual weight, OIML Class M3, 10 kg, Block, cast iron lacquered

KERN

Category

Brand	KERN
Product category	Individual weight
Product group	OIML M3
Product family	366

Measuring System

Test weight - nominal value	10 kg
Test weight - volume uncertainty (cm ³)	119,024
Weight OIML class	M3
Conformity assessment possible	no
Test weight - volume (cm ³)	1408,4507
Permissible tolerance according to OIML (+/-)	5 g
OIML-compliant	✓
Test weight - Density [Min] (OIML)	1500
Test weight - Density (kg/m ³)	7100
Test weight - Density uncertainty (kg/m ³)	600

Construction

Shape weight	Block
Dimensions weight (W×D×H)	190×95×109 mm
Material	cast iron lacquered
Adjustment method	Adjusting cavity - Seal

Services (optional)

Article number for DAkkS calibration	962-644
--------------------------------------	---------

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	190×95×109 mm
Shipping method	Parcel service
Net weight approx.	10 kg
Gross weight approx.	10 kg
Shipping weight	10 kg
Shipping volume weight	0,4 kg

Optional cases

Case - Aluminium article number	346-070-600
---------------------------------	-------------

Product information

GTIN/EAN number	4045761012004
Trade number	84239090
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

