

SAUTER AHBD-01

3 hardness comparison plates for Shore D, tolerance up to ± 2 HD

KERN

REACH classification

no prohibited substances

Pictograms

STANDARD



Category

Brand	Sauter
Product category	Measurementtechnology
Product group	Hardness test block

Construction

Dimension housing (W×D×H)	50×50×7 mm
Dimensions completely mounted (W×D×H)	50×50×7 mm
Material	plastic
Material housing	plastic

Environmental conditions

Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

Services (optional)

Article number for factory calibration	961-170
--	---------

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	173×94×61 mm
Shipping method	Parcel service
Net weight approx.	0,05 kg
Gross weight approx.	0,30 kg
Shipping weight	0,3 kg
Shipping volume weight	0,2 kg

Product information

GTIN/EAN number	4045761123700
Trade number	90249000