

# M18 F2BPB-124

## M18 FUEL™ DUAL BATTERY BACKPACK BLOWER

High constant clearing force with a consistent blowing force of 20.5 N over the entire battery discharge

2 x 18V dedicated backpack blower with a padded back pad and padded adjustable straps for extreme comfort

Up to four battery slots for extended run time

Up to 18.5 m³/min of air volume at 250 km/h to clear leaves, gravel and debris

Optimised balance and ergonomics with a 3-mode select, variable speed lever, tool-free handle adjustment and telescoping adjustable nozzle

Achieves full throttle in under 1 second

Easy to transport thanks to hook for vertical nozzle storage and carry handle

Interchangeable nozzle attachments to optimise the blowing pattern for various applications

The DNA of our FUEL™ platform redefines the balance of cordless technologies. MILWAUKEE®'s POWERSTATE™ brushless motor, REDLITHIUM™ battery pack and REDLINK PLUS™ electronic intelligence delivering outstanding power, run time and durability

Flexible battery system: works with all MILWAUKEE® M18™ batteries



**REDLITHIUM™**



|                                      |                                                                        |
|--------------------------------------|------------------------------------------------------------------------|
| Air speed [km per hour]              | 0 - 250                                                                |
| Air volume (m³ per minute)           | 0 - 18.5                                                               |
| Clearing force [N]                   | 20.5                                                                   |
| Cruise control                       | Yes                                                                    |
| Weight with battery pack (EPTA) (kg) | 11.4 (2x M18 HB12)                                                     |
| Kit included                         | 4 x M18 FB12 Battery packs, M18 PC6 Charger, No kitbox or bag supplied |
| Article number                       | 4933499231                                                             |