


162003 DPZ-10-40-P-A-KF Twin cylinder - Series: All



162003 DPZ-10-40-P-A-KF Twin cylinder - Series: All

Pos.	Part no.	Type	Note	Qty.	Unit
A	383820	DPZ - 10-P-A Set of wearing parts	Spare parts: 3, 10, 11, 14, 15, 19, 20	1	PC
1	343440	DPZ- 10- P-A Grooved nut	Tightening torque 2.2 Nm / 1.6 lbf ft Use locking compound. See position 20	2	PC
2	343424	DPZ- 10- P-A End plate		1	PC
3	660770	DPZ-10/16-... Buffer		1	PC
4	235674	ISO 4017-M4X18-8.8 Hexagon head screw		1	PC
5	212996	DIN 439-B-M4-04 Hex nut		1	PC
6	249024	DIN 988-5X10X1-A2 Shim		2	PC
7	683523	JV-12 Retaining ring		4	PC
8	353418	6X12X19:LM6UU Ball bushing		2	PC
9		DPZ-10-...-KF Retaining	Not available	2	PC
10	200926	B-10X1-N-NBR75 O-ring ISO3601	Grease using during assembly. See position 19	4	PC
11	200880	RIFC1-6X10X3-NBR Rod seal	Grease using during assembly. See position 19	2	PC
12	353071	ARA-06-S0093,6-DHS Piston rod	Tightening torque 1.4 Nm / 1.0 lbf ft Use locking compound. See position 20	2	PC
13		DPZ-10-40-P-A-KF Housing	Not available	1	PC
14	343445	5,8X8,6X1,5 DPZ- 10 Cushioning ring		2	PC
15	245750	LEFC2-10X6X2,55-TPE-U Lip seal	Grease using during assembly. See position 19	4	PC
16	121001	DSNU- 10- PA Piston magnet		2	PC
17	203973	DSN- 10 Cushioning ring		2	PC
18		DPZ-10-KF End cap	Not available	2	PC
19	684474	LUB-KC1 SILIKONFREI 20ML Lubricating grease		1	PC
20	8181256	CYBERBOND TM44 TB1ML Adhesive bonding agent		1	PC