

Features

- Excellent abrasion resistance
- High degree of flexibility
- Provides excellent resistance to chemicals
- Operating temperature between -60°C to +160°C
- Flame retardant
- Flammability rating UL-94-V2

RS PRO PA66

RS Stock No.: 0848973



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

RS PRO PA66 braided sleeving is manufactured from a Nylon™ 6.6 monofilament yarn that provides exceptional resistance against abrasion, whilst maintaining a high degree of flexibility. The material also provides excellent resistance to many chemicals.

General Specifications

Material	Polyamide 6.6
Colour	Black & Grey
Braided	Yes
Expandable	Yes
Fire Behaviour	Flame Retardant
Applications	Most commonly used to protect wire harnesses and cable assemblies against abrasion in automotive, aerospace and military applications. The material is also ideal for the protection of fluid pipes and air conditioning conduits.

Approvals

Compliance/Certifications	RoHS
Standards Met	UL-94-V2

Specifications

Part Number	Product Description	Nominal Size (mm)	Bundle DIA Min(mm)	Bundle DIA Max(mm)
	0848973	12.0	8.0	24.0