

M12 BPS-421X

M12™ SUB COMPACT POLISHER / SANDER

Variable 2 speed selection (0-2800 / 0-8300 RPM) for both polishing and sanding applications

REDLINK™ overload protection electronics in tool and battery pack deliver best in class system durability

Large capacity of 76 mm polishing sponge and 50 mm sanding pad size for fast job completion

Long run time allows frequent task completion with one battery charge

Compact design with only 130 mm allows access to hard areas

Spindle lock allows fast, tool free accessory change

Detachable 2 position side handle

Individual battery cell monitoring optimises tool run time and ensures long term pack durability

REDLITHIUM™ battery pack provides superior pack construction, electronics and fade-free performance to deliver more run time and more work over pack life

Flexible battery system: works with all MILWAUKEE® M12™ batteries

Supplied with polishing pad, sanding pad, polishing sponge white, polishing sponge yellow, lambswool, side handle



REDLITHIUM™



No load speed [rpm]	Calculated 0 - 2,800/ 0 - 8,300
Disc diameter (mm)	76
Spindle size	M9 x 0.75
Weight with battery pack (EPTA) (kg)	1.0 (M12 B2)
Standard equipment	Polishing pad, sanding pad, polishing sponge white, polishing sponge yellow, lambswool, side handle
Kit included	1 x M12 B4, 1 x M12 B2 Battery packs, C12 C Charger, HD Box
Article Number	4933447802