

HD18 CS-402B

M18™ 55 MM CIRCULAR SAW FOR WOOD AND PLASTIC

Powerful 3500 rpm motor easily cuts most timber construction materials

REDLINK™ overload protection electronics in tool and battery pack deliver best in class system durability

Large 50° bevel facility

Magnesium upper guard provide best in class durability for impact resistance

Excellent visibility of cutting line

Electronic motor brake, saw blade stops within seconds

Individual battery cell monitoring optimises tool run time and ensures long term pack durability

Fuel gauge displays remaining charge

REDLITHIUM™ battery pack provides superior pack construction, electronics and fade-free performance to deliver more run time and more work over pack life

Flexible battery system: works with all MILWAUKEE® M18™ batteries

Supplied with 24 tooth saw blade, parallel guide, dust port and allen key



REDLITHIUM™

No load speed (rpm)	3,500
Max. cutting depth 90° (mm)	55
Max. cutting depth 45° (mm)	39
Blade diameter (mm)	165
Bore size (mm)	15.87
Kit included	2 x M18 B4 Battery packs, M12-18 C Charger, Tool bag
Article Number	4933441403

