



M18 FTR-0X

M18 FUEL™ TRIM ROUTER

POWERSTATE™ brushless motor delivers the power of AC trim routers, max. 31,000 rpm for powerful, smooth cutting

Variable speed dial allows users to adjust the speed between 10,000 and 31,000 rpm to choose the best control for the application at hand

All day run time on a single charge of an M18™ 5.0 Ah battery (up to 115 m)

Innovative height adjustment system incorporating a 0.4 mm micro adjustment

Active brake stops the router bit quickly

Included plunge base features 3 stop pins for multiple pass mortising

Dual LED lights to illuminate the work surface

Compatible with the dust collection shroud (DEK 26)

Supplied with 2 x dust extraction attachments, 146 mm sub-baseplate which accepts 31.75 mm guide bushings, 6 mm and 6.35 mm collets, plunge base, 2 x side fences

Integrates three MILWAUKEE®-exclusive technologies - the POWERSTATE™ brushless motor, REDLITHIUM™ battery pack and REDLINK PLUS™ intelligence hardware and software - which deliver outstanding power, run time and durability on the jobsite

Flexible battery system: works with all MILWAUKEE® M18™ batteries



REDLITHIUM™



Collet capacity (mm)	6/ 6.35
Plunge capacity (mm)	50
No load speed (rpm)	10,000 - 31,000
Speed settings	6
Weight with battery pack (EPTA) (kg)	2.1 (M18 B5)
Kit included	No batteries supplied, No charger supplied, HD Box
Article Number	4933471604