



6-DRAWER TROLLEY COMPOSITION OF 302 TOOLS IN FOAM MODULES FOR TROLLEYS **CPP-302MM**

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:59:30





DESCRIPTION

6-DRAWER TROLLEY COMPOSITION OF 302 TOOLS IN FOAM MODULES FOR TROLLEYS

Composition of 302 foam module tools for 41 series tool chest or others.

SPECIFIC DATA

Designation	SERVI 30N - 6 DRAWERS - RED - 302 TOOLS
Sales reference	CPP-302MM
Weight (kg)	90

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:59:30



Guarantee

O | SAM TOOL guarantee.

Guarantee applied

O | SAM TOOL guarantee.

Guarantee without time limit on the tools used under normal conditions.

>> [Find out more](#)

Toolset



x 1

6-drawer tool trolley
SERVI-630N



x 1

Selection of tightening tools - foam module 3/3
CP-138PM



x 1

Screw driving bits ph + hex
E-900J10
Ref : E-900J10



x 1

Screw driving bits pz +tx
E-910J10
Ref : E-910J10



x 1

Screw driving bits fte +txr
E-920J10
Ref : E-920J10



x 1

3/8" sliding handle
J-120
Ref : J-120



x 1

1/2" site ratchet with lever reversion
J-157B
Ref : J-157B



x 2

Straight 3/8" extensions
J-2...
Ref : J-208 - J-210



x 1

3/8" joint
J-240
Ref : J-240



x 17

3/8" short hexagonal sockets in mm
JH-...
Ref : 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 20 - 21 - 22

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:59:30



	x 2	LONG SOCKET 6-FLAT 3/8" 28 MM JHL-... Ref : 16 - 21
	x 5	3/8" sockets for Torx® head JTX-... Ref : 10 - 11 - 12 - 14 - 16
	x 15	1/4" short hexagonal key socket (mm) R-...Douilles_1/4_MM Ref : 3,5 - 4 - 4,5 - 5 - 5,5 - 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 - 14 - 15
	x 1	1/4" sliding handle R-120 Ref : R-120
	x 1	Site 1/4" ratchet R-157B Ref : R-157B
	x 2	Straight 1/4" extensions R-21... Ref : R-210 - R-211
	x 1	Flexible 1/4" extension R-220 Ref : R-220
	x 1	Fitted 1/4" extension R-225 Ref : R-225
	x 1	1/4" joint R-240 Ref : R-240
	x 1	1/4" bit holder socket RD-1 Ref : RD-1
	x 6	1/4" single-piece screwdriver sockets for hollow hexagonal screws RS-... Ref : 3 - 4 - 5 - 6 - 7 - 8
	x 1	Sets of 6 screwdriver sockets 1/4" for 6-flat socket head screws on storage rack RS-J6R Ref : RS-J6R
	x 1	Set of 8 screwdriver sockets 1/4" for Torx® imprint on storage rack RT-J8R Ref : RT-J8R
	x 5	1/4" sockets for Torx® head RTX-... Ref : 4 - 5 - 6 - 7 - 8

 x 1
1/2" sliding locking handle
S-120
Ref : S-120

 x 1
1/2" site ratchet with lever reversion
S-157B
Ref : S-157B

 x 1
Straight 1/2" extensions
S-2...
Ref : S-215

 x 1
1/2" joint
S-240
Ref : S-240

 x 18
1/2" short hexagonal sockets in mm
SH-...
Ref : 10 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 20 - 21 - 22 - 23 - 24 - 27 - 30 - 32

 x 5
1/2" long bi-hexagonal sockets in mm
SL-...Douilles_MM
Ref : 14 - 15 - 17 - 19 - 22

 x 3
1/2" sockets for Torx® head
STX-...
Ref : 18 - 20 - 24



x 1

3/3 FOAM MODULE 12 PLIERS
CP-12MM

 x 1
Polished chrome-plated universal pliers with spring
204-R...G
Ref : 204-R18G

 x 1
Mechanic's diagonal chrome-plated cutting pliers with spring
232-R...G
Ref : 232-R18G

 x 1
Straight half-round nose pliers, polished chrome-plate
237-...G
Ref : 237-20G

 x 1
Polished chrome-plated angled half-round nose pliers with spring
239-R20G

 x 1
Mat chrome-plated straight nose outer circlips pliers
195-...A
Ref : 195-17A

 x 1
Mat chrome-plated 90° elbowed nose outer circlips pliers
196-...A
Ref : 196-17A



x 1

 x 1
Burnished finish straight nose inner circlips pliers
190-...A
Ref : 190-17A

 x 1
Mat chrome-plated 90° elbowed nose inner circlips pliers
191-...A
Ref : 191-17A

 x 1
High-capacity lock grip pliers
212-25

 x 1
Crimping pliers
241-42

 x 1
Polished chrome-plated stacked-branch multigrip pliers
209-25B

 x 1
Mechanic's end nippers
229-...
Ref : 229-25

MODM 3/3 88 SCREWDRIVER+WRENCHES MA.
CP-88MM

 x 1
Flexible screwdriver 6 mm
23-...
Ref : 7 mm

 x 1
Ratchet telescopic screwdriver with magnetic bit holder
T-PE

 x 9
Rack of 9 male 6-flat keys with spherical head in mm
67-AR9A
Ref : 1,5 - 2 - 2,5 - 3 - 4 - 5 - 6 - 8 - 10 mm

 x 9
Rack of 9 Torx® male keys
66-R9A
Ref : T8 - T9 - T10 - T15 - T20 - T25 - T27 - T30 - T40

 x 9
Torx® S1 round blade screwdriver
T-...X
Ref : T8 - T9 - T10 - T15 - T20 - T25 - T27 - T30 - T40

 x 2
Testing screwdriver
268-...
Ref : 6-24V et 100-500V

 x 3
SCREWDRIVER ELECTRICIAN INSULATED 1000V
ZTC-...E
Ref : N°2 - N°3 - N°4

	x 2	SCREWDRIVER PHILLIPS® INSULATED 1000V ZTC-...P Ref : N°1 - N°2
	x 1	Electrician's S1 round blade slotted head screwdriver T-...E Ref : 4x100 mm
	x 3	Mechanic's S1 round blade slotted head screwdriver T-...M Ref : 5,5x100 - 6,5x100 - 8x150 mm
	x 3	Phillips® S1 round blade screwdriver T-...P Ref : N°1 - N°2 - N°3
	x 1	Phillips® S1 round blade tom thumb screwdriver T-...P_Tom_pouce Ref : N°2
	x 1	Electrician's S1 round blade tom thumb slotted head screwdriver T-...E_Tom_pouce Ref : 6,5x35 mm
	x 30	31-piece screwdriver bit set E900-J30B



x 1

3/3 FOAM MOD 24 STRIK TOOLS
CP-24MM

	x 1	SAMSOPLUS® riveting hammer, three-material handle 310-...TM Ref : 32 mm
	x 1	Mallets with interchangeable tips 320-...D Ref : 32 mm
	x 1	Short tape measures with two-material casings UB-...N Ref : 2 m
	x 1	Slide callipers with 1/2"0 mm precision 710-P-8
	x 1	Plastic body scriber 665-11
	x 6	Short drift punches 7-C...A Ref : 1,9 - 2,9 - 3,9 - 4,9 - 5,9 - 7,9 mm

 x 1 **Knife with retractable blade**
378-7

 x 5 **Set of 5 helix pullers**
761-C-5

 x 1 **Fitted flat hand file**
LPM-...E
Ref : 250 mm

 x 1 **Fitted round files**
LR-...-E
Ref : 250 mm

 x 1 **Fitted half-round files**
LDR-...-E
Ref : 250 mm

 x 2 **Constant section chisels with comfortable handle**
3-...-G
Ref : 175 - 200 mm

 x 1 **Punch 10 mm**
8N-...A
Ref : 8 mm



x 1

3/3 FOAM MOD 40 WRENCHES
CP-40MM

 x 19 **Extra-thin combination wrench**
50N-...
Ref : 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 20 - 21 - 22 - 23 - 24 mm

 x 9 **Set of 9 multi-nut inch / metric ratchet combination spanners**
50-HCJ9
Ref : 10 - 11 - 12 - 13 - 14 - 16 - 17 - 18 - 19 mm

 x 8 **Set of 8 offset ring wrenches in mm**
105-J8D

 x 4 **Torx® polygonal straight wrench**
9T-...
Ref : E6xE8 - E10xE12 - E14xE18 - E20xE24 mm