



M18 FUEL™

M18 ONEFHIWF1-O

M18 FUEL™ ONE-KEY™ 1" HIGH TORQUE IMPACT WRENCH WITH FRICTION RING

The M18 FUEL™ 1" T-handle high torque impact wrench has the power to replace AC, petrol or pneumatic solutions

Delivering up to 2033 Nm of fastening torque at half the size and weight of AC, petrol or pneumatic solutions

Packed with 2400 Nm of nut busting torque meaning those rusted stubborn old bolts wont stand a chance

The 4 -Mode DRIVE CONTROL allows the user to shift into four different speed and torque settings to maximise application versatility

The integrated blow counting sensor enhances the consistent repeatability of the chosen torque setting

ONE-KEY™ tool tracking & security offers a free of charge cloud-based tracking network and inventory management platform for your tools.

ONE-KEY™ also features a remote locking functionality. Customisation function allows for precise tool adjustment to application

The HIGH OUTPUT™ system of tools elevates the M18 FUEL™ technologies to a new level and delivers extended performance and extended run time. These tools are designed to maximise the partnership with HIGH OUTPUT™ and FORGE™ batteries



REDLITHIUM™

Name	M18 ONEFHIWF1-O
No load speed (rpm)	0-950/ 0-1080/ 0-1370/ 0-1670
Impact rate (ipm)	1350/ 1650/ 2100/ 0-2500
Max. torque (Nm)	
Nut-busting torque (Nm)	2400
Weight with battery pack (EPTA) (kg)	5.9 (M18 FB8)
Kit included	, , No kitbox or bag supplied
Article Number	4933499162