

**Universal programmer / copier
for serial EEPROMs 24xx / 25xx / 93xx, Spi FLASH 25xx / 26xx, DataFlash 45xx, Microwire, NorFlash
On USB-C port, ZIF28 socket + ICSP cable**



FlyPro-SP20P



Introduction:

FLYPRO-SP20B supports more than 16800 Serial EEPROMs and Serial FLASHs. Its library contains most of EEPROMs i2C memory and most of ISP FLASHs memory. It supports also DataFlash memory. Thanks to its USB port, this programmer does not require any external power supply. It has also a mass production mode, as well as a stand-alone mode with an OLED display, Run button and 512 MB internal memory. It is possible to program the components on its ZIF28 socket or through its HE10 connector with the ICSP cable provided, for on-board chip (such as the computer motherboard BIOS that leads to the SPI interface), it can be directly wired. This programmer is very practical to use with a laptop computer at the office or on a business trip. Support for Windows 7 / 8 / 10 / 11 (32 and 64 bits) and higher.

Features:

Programmer with mass production mode, stand-alone mode with an OLED display, Run button and 512MB internal memory. Read / Write / Blank-Check Write / Verify / Blank-Check / Erase / Duplicate functions. Support low voltage devices 1,7V to 5,0V, until 1GB. System of over-current detection and short circuit protection. Automatically detects whether the chips are placed well and then automatically starts programming. Support online high-speed mass production until 8 programmers simultaneously on PC. Supports Windows 7 / Windows8 / Windows10 / Windows 11 (32bit and 64bit) and higher.

Hardware & Electrical specifications:

Dimensions product : 108 x 76 x 21 mm. Weight : 100g.
Dimensions package : 126 x 90 x 60mm. Weight : 190g.
Power supply on USB port.
Interface : connect to laptop or PC through USB port (USB 1.1, 2.0 or higher).

Item includes:

Programmer with ZIF28 socket.
Cable type USB-A to USB-C.
ICSP-HE10 cable with 10 wires.
Software on CD-ROM.
User manual in English and French.



↓ **Devices list programmed below** ↓

www.seeit.fr



DEVICES LIST FLYPRO-SP20B / SP20P

Push "CTRL + F" keys to find a component

EEPROM / FLASH ICSP universal programmer

Total manufacturers : 122

Total devices : 1849

Version : 1.51

Devices list:

ABLIC INC. - SPI EEPROM			
Device Model	Package Type	Adapter module	Remark
S-25A010A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-25A020A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-25A040A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-25A080A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-25A080B	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-25A160A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-25A160B	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-25A320A	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
	---	ISP	
S-25A320B	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-25A640A	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
	---	ISP	
S-25A640B	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-25A128B	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-25A256B	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
	---	ISP	
S-25C010A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-25C020A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-25C040A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-25C080A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-25C160A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-25C320A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-25C640A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	

	---	ISP	
S-25C128A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-25C256A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-25C512A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-25CM01A	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
ABLIC INC. - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
S-24C01C	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-24C02C	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-24C02D	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
S-24C04D	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
S-24C08C	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-24C08D	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
S-24C16C	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-24C16D	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
S-24C32C	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-24C64C	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-24C128C	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-24C256C	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-24C512C	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-24CM01C	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
S-24CS01A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-24CS02A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-24CS04A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	

	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
S-24CS08A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-24CS16A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
S-24CS64A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
ABLIC INC. - Microwire EEPROM			
Device Model	Package Type	Adapter Module	Remark
S-93A46A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-93A46B	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-93A56A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-93A56B	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-93A66A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-93A66B	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-93A76B	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-93A86A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-93A86B	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-93C46A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-93C46B	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-93C46CD	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-93C46CR	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
S-93C56A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-93C56B	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-93C56CD	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-93C56CR	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
S-93C66A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	

S-93C66B	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-93C66CD	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-93C66CR	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
S-93C76A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
S-93C76CD	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-93C76CR	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
S-93C86B	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-93C86CD	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-93C86CR	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	

ACE Technology - SPI Flash

Device Model	Package Type	Adapter Module	Remark
ACE25C512G	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
ACE25C100G	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
ACE25C400G	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
ACE25C800G	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	---	ISP	
ACE25C160G	DIP8		
	SOP8 / 208mil	SF-SOP8-200A	
	---	ISP	
ACE25C320G	DIP8		
	SOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
ACE25QC320G	DIP8		OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
ACE25QC640G	DIP8		OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
ACE25QC128G	DIP8		OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	

ACE Technology - I2C EEPROM

Device Model	Package Type	Adapter Module	Remark
ACE24AC02A1	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	

ACE24AC02A3C	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
ACE24AC04	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
ACE24AC08	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
ACE24AC16	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
ACE24AC64	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
ACE24AC128	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	DIP8		
ACE24AC256	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
	DIP8		
ACE24AC512	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
ACE24AC1024D	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
	DIP8		
ACE24C02	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
	DIP8		
ACE24C04	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
	DIP8		
ACE24C04A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
	DIP8		
ACE24C08	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
	DIP8		
ACE24C08A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
	DIP8		
ACE24C16	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
	DIP8		
ACE24C32	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
	DIP8		
ACE24C32A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		

	---	ISP	
ACE24C64	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
ACE24C128	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
ACE24C256	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
ACE24C256C	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
ACE24C512C	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
ACE24LA02	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
ACE24LA04	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
ACE24LA08	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
ACE24LA16	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
ACE24LA64	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
ACE24LA128	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
ACE24LA256	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
ACE24LA512	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
ACE24LC02	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
ACE24LC04	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
ACE24LC08	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	

	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
ACE24LC16	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
ACE Technology - Microwire EEPROM			
Device Model	Package Type	Adapter Module	Remark
ACE93C46	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
ACE93C56	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
ACE93C66	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
Actrans - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
AC25LV512	SO8 / 150mil	SF-SOP8-150A	
AC25LV010	SO8 / 150mil	SF-SOP8-150A	
Adesto - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
AT25DF256	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AT25DF512C	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AT25DF011	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AT25DF021	SOIC8 / 150mil	SF-SOP8-150A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
AT25DF021A	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
AT25DF041A	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
AT25DF041B	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
AT25DF081	SOIC8 / 150mil	SF-SOP8-150A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
AT25DF081A	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
AT25DF161	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
AT25DF321	SOIC8 / 200mil	SF-SOP8-200A	
	SOIC16 / 300mil	SF-SO16-300A	
	---	ISP	
AT25DF321A	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	

	---	ISP	
AT25DF641	DFN8 / 5x6mm	SF-QFN8-6X5A	
	SOIC16 / 300mil	SF-SO16-300A	
	---	ISP	
AT25DF641A	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
AT25DL081	SOIC8 / 150mil	SF-SOP8-150A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
AT25DL161	SOIC8 / 150mil	SF-SOP8-150A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
AT25DN256	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AT25DN512C	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AT25DN011	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AT25FF041A	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	UDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
AT25FF081A	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	UDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
AT25FF161A	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	UDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
AT25FF321A	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	UDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
AT25PE20	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
AT25PE40	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
AT25PE80	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
AT25PE16	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
AT25SF041	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
AT25SF041B	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	

	---	ISP	
AT25SF081	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
AT25SF081B	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
AT25SF161	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
AT25SF161B	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
AT25SF321	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
AT25SF321B	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
AT25SF641	SOIC8 / 208mil	SF-SOP8-200A	
	UDFN8 / 5x6mm	SF-QFN8-6X5A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
AT25SF641B	SOIC8 / 208mil	SF-SOP8-200A	OTP
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
AT25SF128A	SOIC8 / 208mil	SF-SOP8-200A	OTP
	UDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
AT25QF641	SOIC8 / 208mil	SF-SOP8-200A	OTP
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
AT25QF641B	SOIC8 / 208mil	SF-SOP8-200A	OTP
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
AT25QF128A	SOIC8 / 208mil	SF-SOP8-200A	OTP
	UDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
AT25XE512C	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AT25XE011	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AT25XE021A	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
AT25XE041B	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
AT25XE041D	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	

AT25XE081D	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AT25XE161D	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	UDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
AT25XE321D	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	UDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
AT25XV021A	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
AT25XV041B	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
AT25SL321	SOIC8 / 208mil	SF-SOP8-200A	
	UDFN8 / 5x6mm	SF-QFN8-6X5A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
AT25SL641	SOIC8 / 208mil	SF-SOP8-200A	
	UDFN8 / 5x6mm	SF-QFN8-6X5A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
AT25SL128A	SOIC8 / 208mil	SF-SOP8-200A	
	UDFN8 / 5x6mm	SF-QFN8-6X5A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
AT25QL128A	SOIC8 / 208mil	SF-SOP8-200A	
	UDFN8 / 5x6mm	SF-QFN8-6X5A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
AT45DB021E(P264)	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
AT45DB021E(P256)	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
AT45DB041E(P264)	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
AT45DB041E(P256)	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
AT45DB081E(P264)	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
AT45DB081E(P256)	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
AT45DB161E(P528)	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
AT45DB161E(P512)	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
AT45DB321E(P528)	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
AT45DB321E(P512)	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
AT45DB641E(P264)	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	

AT45DB641E(P256)	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
Adesto - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
RM24C32C	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
RM24C64C	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
RM24C128C	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
RM24C256C	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
RM24C512C	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
AiT - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
A25S40	SOP8 / 150mil	SF-SOP8-150A	
A25S80	SOP8 / 150mil	SF-SOP8-150A	
A25S16	SOP8 / 150mil	SF-SOP8-150A	
A25S32	SOP8 / 150mil	SF-SOP8-150A	
AiT - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
A24C02	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
A24C04	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
A24C08	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
A24C16	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
A24C32	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
A24C64	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
A24C128	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
A24C256	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
A24C512	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
A24C1024	SOP8 / 150mil	SF-SOP8-150A	

	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
AiT - Microwire EEPROM			
Device Model	Package Type	Adapter Module	Remark
A93C46	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
A93C56	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
A93C66	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
AMIC Technology - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
A25L512	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 209mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	WSOP8 / 6x5mm	SF-QFN8-6X5A	
A25L512A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 209mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	WSOP8 / 6x5mm	SF-QFN8-6X5A	
A25L010	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 209mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
A25L010A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USOP8 / 3x2mm	SF-QFN8-2X3A	
A25L020	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 209mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
A25L020C	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 209mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
A25L040	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 209mil	SF-SOP8-200A	
A25L040A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 209mil	SF-SOP8-200A	
A25L040B	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 209mil	SF-SOP8-200A	
	USOP8 / 3x2mm	SF-QFN8-2X3A	
A25L080	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 209mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
A25L016	DIP8		
	SOP8 / 209mil	SF-SOP8-200A	
	SOP16 / 300mil	SF-SO16-300A	
A25LQ080	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 209mil	SF-SOP8-200A	
A25LQ080A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 209mil	SF-SOP8-200A	

	USON8 / 3x2mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
A25LQ16	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 209mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
A25LQ16A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 209mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
A25LQ32A	DIP8		
	SOP8 / 209mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
A25LQ64	SOP8 / 209mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
A25LQ64M-FE	SOP8 / 209mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
A25LQ256	WSON8 / 6x8mm	SF-QFN8-8X6A	OTP
A25LQ512	WSON8 / 6x8mm	SF-QFN8-8X6A	OTP
Anachip - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
AM24LC02	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
AM24LC04	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
AM24LC08	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
AM24LC16	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
AM24LC21	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
AM24LC21B	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
Anachip - Microwire EEPROM			
Device Model	Package Type	Adapter Module	Remark
AM93LC46	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
AM93LC46G	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
AM93LC56	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
AM93LC56G	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
AM93LC66	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
AM93LC66G	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
AM93LC86	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
APLUS - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
AF24BC01	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
AF24BC02	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	

AF24BC04	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
AF24BC08	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
AF24BC16	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
AF24BC32	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
AF24BC64	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
AF24BC128	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
AF24BC256	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
APLUS - Microwire EEPROM			
Device Model	Package Type	Adapter Module	Remark
AF93BC46	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
AF93BC56	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
AF93BC66	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
AF93BC86	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
Artschip - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
24LC01B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
24LC02B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
24LC04B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
24LC08B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
24LC16B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
24LC32B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
24LC64B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
24AA64	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	

	---	ISP	
24LC64	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
24AA128	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	---	ISP	
24LC128	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	---	ISP	
24AA256	DIP8		
	SOIC8 / 208mil	SF-SOP8-200A	
	---	ISP	
24LC256	DIP8		
	SOIC8 / 208mil	SF-SOP8-200A	
	---	ISP	

ATC - I2C EEPROM

Device Model	Package Type	Adapter Module	Remark
24C02	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
24C02W	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
24C04	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
24C04P	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
24C08	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
24LC02	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
24LC02W	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
24LC04	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
24LC08	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	

ATC - Microwire EEPROM

Device Model	Package Type	Adapter Module	Remark
93C46	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
93C56	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
93C66	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
AM93LC46	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
AM93LC56	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
AM93LC56G	SOP8 / 150mil	SF-SOP8-150A	
AM93LC66	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
AM93LC66G	SOP8 / 150mil	SF-SOP8-150A	

ATMEL - SPI Flash

Device Model	Package Type	Adapter Module	Remark
--------------	--------------	----------------	--------

AT25DF256	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
AT25DF512C	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
AT25DF011	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
AT25DF021	SOIC8 / 150mil	SF-SOP8-150A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
AT25DF021A	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
AT25DF041A	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
AT25DF041B	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
AT25DF081	SOIC8 / 150mil	SF-SOP8-150A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
AT25DF081A	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
AT25DF161	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
AT25DF321	SOIC8 / 200mil	SF-SOP8-200A	
	SOIC16 / 300mil	SF-SO16-300A	
AT25DF321A	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
AT25DF641	DFN8 / 5x6mm	SF-QFN8-6X5A	
	SOIC16 / 300mil	SF-SO16-300A	
AT25DF641A	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
AT25F512	SOIC8 / 150mil	SF-SOP8-150A	
AT25F512A	SOIC8 / 150mil	SF-SOP8-150A	
AT25F512B	SOIC8 / 150mil	SF-SOP8-150A	
AT25F1024	SOIC8 / 150mil	SF-SOP8-150A	
AT25F1024A	SOIC8 / 150mil	SF-SOP8-150A	
AT25F2048	SOIC8 / 150mil	SF-SOP8-150A	
AT25F4096	SOIC8 / 150mil	SF-SOP8-150A	
AT26DF081A	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 200mil	SF-SOP8-200A	
AT26DF161	SOIC8 / 200mil	SF-SOP8-200A	
AT26DF161A	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	MLF8 / 5x6mm	SF-QFN8-6X5A	
AT26DF321	SOIC8 / 200mil	SF-SOP8-200A	
AT45DB011B	SOIC8 / 209mil	SF-SOP8-200A	
AT45DB011D(P264)	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 209mil	SF-SOP8-200A	
	MLF8 / 5x6mm	SF-QFN8-6X5A	
AT45DB011D(P256)	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 209mil	SF-SOP8-200A	
	MLF8 / 5x6mm	SF-QFN8-6X5A	
AT45DB021B	SOIC8 / 209mil	SF-SOP8-200A	
AT45DB021D(P264)	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 209mil	SF-SOP8-200A	
	MLF8 / 5x6mm	SF-QFN8-6X5A	
AT45DB021D(P256)	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 209mil	SF-SOP8-200A	
	MLF8 / 5x6mm	SF-QFN8-6X5A	
AT45DB041B	SOIC8 / 209mil	SF-SOP8-200A	
AT45DB041D(P264)	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 209mil	SF-SOP8-200A	
	MLF8 / 5x6mm	SF-QFN8-6X5A	
AT45DB041D(P256)	SOIC8 / 150mil	SF-SOP8-150A	

AT45DB081D(P264)	SOIC8 / 209mil	SF-SOP8-200A	
	MLF8 / 5x6mm	SF-QFN8-6X5A	
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 209mil	SF-SOP8-200A	
AT45DB081D(P256)	MLF8 / 5x6mm	SF-QFN8-6X5A	
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 209mil	SF-SOP8-200A	
	MLF8 / 5x6mm	SF-QFN8-6X5A	
AT45DB161D(P528)	SOIC8 / 209mil	SF-SOP8-200A	
	MLF8 / 5x6mm	SF-QFN8-6X5A	
AT45DB161D(P512)	SOIC8 / 209mil	SF-SOP8-200A	
	MLF8 / 5x6mm	SF-QFN8-6X5A	
AT45DB321D(P528)	SOIC8 / 209mil	SF-SOP8-200A	
	MLF8 / 5x6mm	SF-QFN8-6X5A	
	MLF8 / 8x6mm	SF-QFN8-8X6A	
AT45DB321D(P512)	SOIC8 / 209mil	SF-SOP8-200A	
	MLF8 / 5x6mm	SF-QFN8-6X5A	
	MLF8 / 8x6mm	SF-QFN8-8X6A	
AT45DB642D(P1024)	WSON8 / 8x6mm	SF-QFN8-8X6A	
AT45DB642D(P1056)	WSON8 / 8x6mm	SF-QFN8-8X6A	
ATMEL - SPI EEPROM			
Device Model	Package Type	Adapter Module	Remark
AT25010	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
AT25010A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AT25010B	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AT25020	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
AT25020A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AT25020B	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AT25040	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
AT25040A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AT25040B	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AT25080	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
AT25080A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AT25080B	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AT25160	DIP8		

AT25160A	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
	DIP8		
AT25160B	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AT25320	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AT25320A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
AT25320B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AT25640	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AT25640A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
AT25640B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AT25128	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AT25128A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
AT25128B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AT25256	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AT25256A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
AT25256B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AT25512	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AT25M01	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	---	ISP	
AT25M02	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
AT25HP256	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	

AT25HP512	SOIC8 / 200mil	SF-SOP8-200A	
	---	ISP	
ATMEL - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
AT24C01	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
AT24C01A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
AT24C01B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
AT24C01C	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
---	ISP		
AT24C01D	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
---	ISP		
AT24C02	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
AT24C02A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
AT24C02B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
AT24C02C	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
---	ISP		
AT24C02D	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
---	ISP		
AT24C04	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	SOT23-5	SF-SOT23-6A	
---	ISP		
AT24C04A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
AT24C04B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	SOT23-5	SF-SOT23-6A	

	---	ISP	
AT24C04C	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
AT24C04D	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
AT24C08	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
AT24C08A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
AT24C08B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
AT24C08C	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
AT24C08D	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
AT24C16	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
AT24C164	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
AT24C16A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
AT24C16B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	SOT23-5	SF-SOT23-6A	
AT24C16C	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
AT24C16D	SOT23-5	SF-SOT23-6A	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
AT24C21	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
AT24C32	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	

	---	ISP	
AT24C32A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
AT24C32B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
AT24C32C	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
AT24C32D	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
AT24C32E	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
AT24C64	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
AT24C64A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
AT24C64B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
AT24C64C	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
AT24C64D	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AT24C128	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 200mil	SF-SOP8-200A	
	---	ISP	
AT24C128B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
AT24C128C	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AT24C256	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 200mil	SF-SOP8-200A	
	---	ISP	
AT24C256B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
AT24C256C	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AT24C512	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	

	SOIC8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
AT24C512B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
AT24C512C	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AT24C1024	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
AT24C1024B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
AT24CM01	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
AT24CM02	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
AT24CS01	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
AT24CS02	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
AT24CS04	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
AT24CS08	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
AT24CS16	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
AT24CS32	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
AT24CS64	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AT24HC02B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
AT24HC02C	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	

AT24HC04C	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
AT34C02C	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AT34C02D	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AT34C04	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
ATMEL - Microwire EEPROM			
Device Model	Package Type	Adapter Module	Remark
AT93C46A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
AT93C46B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
AT93C46C	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
AT93C46D	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AT93C46E	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
AT93C56	---	ISP	
AT93C56R	---	ISP	
AT93C56A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
AT93C56B	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AT93C57	---	ISP	
AT93C66	---	ISP	
AT93C66A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
AT93C66B	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AT93C86	---	ISP	
AT93C86A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
Axelite - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
AX24C02A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	

AX24C04A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
AX24C08A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
AX24C16A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AX24C32A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AX24C64A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
AX24C128A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
AX24C256A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	

Belling - SPI EEPROM

Device Model	Package Type	Adapter Module	Remark
BL25C02A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
BL25C04A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
BL25C08A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
BL25C16A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
BL25C32A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
BL25C64A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
BL25C128A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
BL25C256A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
BL25CM1A	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
BL25CM2A	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	

Belling - I2C EEPROM

Device Model	Package Type	Adapter Module	Remark
BL24C02	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	

	---	ISP	
BL24C02A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	TSOT23-5	SF-SOT23-6A	
	---	ISP	
BL24C02B	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	TSOT23-5	SF-SOT23-6A	
	---	ISP	
BL24C02F	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	TSOT23-5	SF-SOT23-6A	
	---	ISP	
BL24C02P	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
BL24C04	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
BL24C04A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	TSOT23-5	SF-SOT23-6A	
	---	ISP	
BL24C04B	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	TSOT23-5	SF-SOT23-6A	
	---	ISP	
BL24C04F	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	TSOT23-5	SF-SOT23-6A	
	---	ISP	
BL24C08	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
BL24C08A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	TSOT23-5	SF-SOT23-6A	
	---	ISP	
BL24C08B	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	TSOT23-5	SF-SOT23-6A	
	---	ISP	
BL24C08F	DIP8		

	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	TSOT23-5	SF-SOT23-6A	
	---	ISP	
BL24C16	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
BL24C16A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	TSOT23-5	SF-SOT23-6A	
BL24C16B	---	ISP	
	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
BL24C16F	TSOT23-5	SF-SOT23-6A	
	---	ISP	
	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
BL24C32	SOT23-5	SF-SOT23-6A	
	TSOT23-5	SF-SOT23-6A	
	---	ISP	
	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
BL24C32A	---	ISP	
	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
BL24C32F	TSOT23-5	SF-SOT23-6A	
	---	ISP	
	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
BL24C64	SOT23-5	SF-SOT23-6A	
	TSOT23-5	SF-SOT23-6A	
	---	ISP	
	DIP8		
BL24C64A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
BL24C64F	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	TSOT23-5	SF-SOT23-6A	
BL24C128	---	ISP	
	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
BL24C128A	---	ISP	
	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	

	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	TSOT23-5	SF-SOT23-6A	
	---	ISP	
BL24C128F	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	TSOT23-5	SF-SOT23-6A	
BL24C256	---	ISP	
	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
BL24C256A	---	ISP	
	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	TSOT23-5	SF-SOT23-6A	
BL24C256F	---	ISP	
	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
BL24C512A	TSOT23-5	SF-SOT23-6A	
	---	ISP	
	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
BL24C512B	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	TSOT23-5	SF-SOT23-6A	
	---	ISP	
BL24C512F	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	TSOT23-5	SF-SOT23-6A	
BL24CM1A	---	ISP	
	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
BL24CM2A	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
BL24SA64	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
BL34C04A	UDFN8 / 2x3mm	SF-QFN8-2X3A	
Belling - Microwire EEPROM			
Device Model	Package Type	Adapter Module	Remark
BL93C46	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
BL93C46A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
BL93C56	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	

	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
BL93C56A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
BL93C66	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
BL93C66A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
BL93C76A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
BL93C86A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
Bestow Mascot - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
BM24C02D	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
BM24C02E	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
BM24C04D	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
BM24C04E	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
BM24C08D	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
BM24C08E	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
BM24C16D	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
BM24C16E	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	

BM24C32D	---	ISP	
	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
BM24C32E	---	ISP	
	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
BM24C64D	---	ISP	
	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
BM24C64E	---	ISP	
	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
BM24C128D	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
	BM24C128E	DIP8	
SOP8 / 150mil		SF-SOP8-150A	
TSSOP8 / 173mil		SF-TSP8-170A	
DFN8 / 2x3mm		SF-QFN8-2X3A	
---		ISP	
BM24C256D		DIP8	
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
	BM24C256E	DIP8	
SOP8 / 150mil		SF-SOP8-150A	
TSSOP8 / 173mil		SF-TSP8-170A	
DFN8 / 2x3mm		SF-QFN8-2X3A	
---		ISP	
BM24C512D		DIP8	
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
	BM24C512E	DIP8	
SOP8 / 150mil		SF-SOP8-150A	
TSSOP8 / 173mil		SF-TSP8-170A	
DFN8 / 2x3mm		SF-QFN8-2X3A	
---		ISP	
BM24CM01D		DIP8	
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
	Bestow Mascot - Microwire EEPROM		
Device Model	Package Type	Adapter Module	Remark
BM93C46	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
	BM93C56	DIP8	
SOP8 / 150mil		SF-SOP8-150A	
TSSOP8 / 173mil		SF-TSP8-170A	
DFN8 / 2x3mm		SF-QFN8-2X3A	
---		ISP	

BM93C66	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
Bookly - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
24C02	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
24C04	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
24C08	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
24C16	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
24C32	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
24C64	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
Boya Microelectronics - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
BY25D05AS	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
BY25D05ES	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
BY25D10AS	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
BY25D10ES	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
BY25D20AS	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
BY25D20ES	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
BY25D20FS	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	

	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
BY25D20EW	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
BY25D40AS	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
BY25D40ES	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
BY25D80AS	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
BY25D16AS	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
BY25FQ16EL	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
BY25FQ16ES	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
BY25FQ32EL	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
BY25FQ64EL	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
BY25FQ64ES	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	DFN8 / 4x3mm	SF-QFN8-4X3B	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
BY25FQ128EL	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	DFN8 / 4x3mm	SF-QFN8-4X3B	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
BY25FQ256EL	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 6x8mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
BY25FQ256ES	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 6x8mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
BY25FQM512ES	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 6x8mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
BY25FQM1GES	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 6x8mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
BY25Q512AS	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
BY25Q10AS	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	

	---	ISP	
BY25Q20AS	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
BY25Q20AW	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
BY25Q20BL	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
BY25Q40AL	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
BY25Q40AS	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
BY25Q40AV	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
BY25Q40AW	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
BY25Q40BL	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
BY25Q40GV	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
BY25Q80AL	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
BY25Q80AS	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	---	ISP	
BY25Q80AW	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
BY25Q80BS	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	DFN8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
BY25Q80ES	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 6x8mm	SF-QFN8-8X6A	

	---	ISP	
BY25Q16AL	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
BY25Q16AS	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	DFN8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
BY25Q16AW	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
BY25Q16BL	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
BY25Q16BS	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	DFN8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
BY25Q16ES	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 6x8mm	SF-QFN8-8X6A	
	---	ISP	
BY25Q16EV	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 6x8mm	SF-QFN8-8X6A	
	---	ISP	
BY25Q32AL	VSOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
BY25Q32AS	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
BY25Q32BS	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
BY25Q32CS	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
BY25Q32EL	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 6x8mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
BY25Q32ES	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 6x8mm	SF-QFN8-8X6A	
	---	ISP	
BY25Q64AL	VSOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
BY25Q64AS	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
BY25Q64ES	SOP8 / 150mil	SF-SOP8-150A	OTP

	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 6x8mm	SF-QFN8-8X6A	
	---	ISP	
BY25Q64FS	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	DFN8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
BY25Q128AL	VSOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
BY25Q128AS	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
BY25Q128BL	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 6x8mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
BY25Q128EL	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 6x8mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
BY25Q128ES	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 6x8mm	SF-QFN8-8X6A	
	---	ISP	
BY25Q128FS	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	---	ISP	
BY25Q256FS	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 6x8mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
BY25QM512FS	WSON8 / 6x8mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
BY25QM1GFS	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
BSH - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
BH25HD-20A	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
BH25LD-20A	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
BH25UD-20A	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
BH25HQ-20A	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
BH25LQ-20A	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
BH25UQ-20A	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	

BH25HQ-40A	WS0N8 / 6x5mm	SF-QFN8-6X5A	OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	US0N8 / 2x3mm	SF-QFN8-2X3A	
	WS0N8 / 6x5mm	SF-QFN8-6X5A	
BH25LQ-40A	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	US0N8 / 2x3mm	SF-QFN8-2X3A	
	WS0N8 / 6x5mm	SF-QFN8-6X5A	
BH25UQ-40A	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	US0N8 / 2x3mm	SF-QFN8-2X3A	
	WS0N8 / 6x5mm	SF-QFN8-6X5A	
BH25LE-20A	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	US0N8 / 2x3mm	SF-QFN8-2X3A	
	WS0N8 / 6x5mm	SF-QFN8-6X5A	
BH25LE-40A	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	US0N8 / 2x3mm	SF-QFN8-2X3A	
	WS0N8 / 6x5mm	SF-QFN8-6X5A	

Catalyst (CSI) - SPI EEPROM

Device Model	Package Type	Adapter Module	Remark
CAT25C01	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
CAT25C02	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
CAT25C04	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CAT25C08	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CAT25C16	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CAT25C32	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT25C64	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT25C33	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT25C65	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT25C128	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT25C256	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT25C11	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	

CAT25C03	MSOP8	SF-MSP8-3X3A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
	DIP8		
CAT25C05	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
	DIP8		
CAT25C09	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
	DIP8		
CAT25C17	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
	DIP8		
CAT25010	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
	DIP8		
CAT25020	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
	DIP8		
CAT25040	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
	DIP8		
CAT25080	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
	DIP8		
CAT25160	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
	DIP8		
CAT25320	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
	DIP8		
CAT25640	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
CAT25128	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
	DIP8		
CAT25256	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
	DIP8		
Catalyst (CS1) - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
CAT24AA01	SOIC8 / 150mil	SF-SOP8-150A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
CAT24AA02	SOIC8 / 150mil	SF-SOP8-150A	

CAT24AA04	SOT23-5	SF-SOT23-6A	
	---	ISP	
	SOIC8 / 150mil	SF-SOP8-150A	
	SOT23-5	SF-SOT23-6A	
CAT24AA08	---	ISP	
	SOIC8 / 150mil	SF-SOP8-150A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
CAT24AA16	SOIC8 / 150mil	SF-SOP8-150A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
	---	ISP	
CAT24C01	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
	---	ISP	
CAT24C02	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
	---	ISP	
CAT24C03	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
CAT24C04	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
	---	ISP	
CAT24C05	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
CAT24C08	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
	---	ISP	
CAT24C16	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
	---	ISP	
CAT24C32	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
CAT24C64	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
CAT24C128	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	

CAT24C256	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT24AC128	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 200mil	SF-SOP8-200A	
	---	ISP	
CAT24C21	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
CAT24FC01	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
CAT24FC02	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
CAT24FC16	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
CAT24FC17	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
CAT24FC32	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
CAT24FC32A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CAT24FC64	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
CAT24FC65	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
CAT24FC66	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
CAT24FC256	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	---	ISP	
CAT24WC01	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	

CAT24WC02	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
CAT24WC03	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CAT24WC04	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
CAT24WC05	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT24WC08	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT24WC09	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT24WC16	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT24WC17	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT24WC32	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT24WC33	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT24WC64	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT24WC65	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT24WC66	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT24WC128	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT24WC129	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT24WC256	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT24WC257	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT34C02	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
Catalyst (CS1) - Microwire EEPROM			
Device Model	Package Type	Adapter Module	Remark
CAT93C46	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CAT93C46J	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT93C46W	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT93C56	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	

	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CAT93C56J	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT93C56W	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT93C57	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CAT93C57J	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT93C57W	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT93C66	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CAT93C66J	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT93C66W	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT93C76	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CAT93C86	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT93C86J	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT93C86W	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	

CBC Microelectr - I2C EEPROM

Device Model	Package Type	Adapter Module	Remark
MC24C02	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
MC24C04	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
MC24C08	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
MC24C16	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
MC24C32	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
MC24C64	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
MC24C128	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
MC24C256	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
MC24LC02	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	

MC24LC04	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
MC24LC08	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
MC24LC16	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
CBC Microelectr - Microwire EEPROM			
Device Model	Package Type	Adapter Module	Remark
MC93C46	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
MC93C56	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
MC93C66	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
Ceramate - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
24LC02	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
24LC04	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
24LC08	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
24LC16	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
24LLC02	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
24LLC04	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
24LLC08	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
24LLC16	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
Ceramate - Microwire EEPROM			
Device Model	Package Type	Adapter Module	Remark
93LC46	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
93LC46G	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
CFX - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
GM25Q64A	DIP8		OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
GM25Q128A	DIP8		OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	

	WSON8 / 8x6mm	SF-QFN8-8X6A	
CF(China Flash) - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
TJ25Q08MA	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
Chingis - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
Pm25LV512	SOIC8 / 150mil	SF-SOP8-150A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
Pm25LV512A	SOIC8 / 150mil	SF-SOP8-150A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
Pm25LV010	SOIC8 / 150mil	SF-SOP8-150A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
Pm25LV010A	SOIC8 / 150mil	SF-SOP8-150A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
Pm25LV020	SOIC8 / 150mil	SF-SOP8-150A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
Pm25LV040	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
Pm25LV080B	SOIC8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
Pm25LV016B	SOIC8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
Pm25LD256C	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
Pm25LD512C	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
Pm25LD512	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
Pm25LD010	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
Pm25LD010C	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
Pm25LD020	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
Pm25LD020C	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
Pm25LD040	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
Pm25LD040C	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
Pm25LQ512B	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
Pm25LQ010B	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
Pm25LQ020B	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
Pm25LQ040B	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
Pm25LQ080C	SOIC8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
Pm25LQ016	SOIC8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	

	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
Pm25LQ016C	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
Pm25LQ032C	SOIC8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
Chipswinner - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
CW24C02	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
CW24C02A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	TSOT23-5	SF-SOT23-6A	
---	ISP		
CW24C04	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
CW24C04A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	TSOT23-5	SF-SOT23-6A	
---	ISP		
CW24C08	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
CW24C08A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	TSOT23-5	SF-SOT23-6A	
---	ISP		
CW24C16	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
CW24C32	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
CW24C32A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	TSOT23-5	SF-SOT23-6A	
---	ISP		
CW24C64	DIP8		

	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
CW24C64A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	TSOT23-5	SF-SOT23-6A	
CW24C128	---	ISP	
	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
CW24C128A	---	ISP	
	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	TSOT23-5	SF-SOT23-6A	
CW24C256	---	ISP	
	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
CW24C256A	---	ISP	
	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	TSOT23-5	SF-SOT23-6A	
CW24C512A	---	ISP	
	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	TSOT23-5	SF-SOT23-6A	
	---	ISP	

Chrontel - I2C EEPROM

Device Model	Package Type	Adapter Module	Remark
CH9904	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	

Coreriver - I2C EEPROM

Device Model	Package Type	Adapter Module	Remark
CR24C01	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
CR24C02	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
CR24C04	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
CR24C08	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
CR24C16	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
CR24C32	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
CR24C64	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
CR24C128	DIP8		

CR24C256	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
Coreriver - Microwire EEPROM			
Device Model	Package Type	Adapter Module	Remark
CR93C46	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
CR93C46W	SOIC8 / 150mil	SF-SOP8-150A	
CR93C56	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
CR93C56W	SOIC8 / 150mil	SF-SOP8-150A	
CR93C66	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
CR93C66W	SOIC8 / 150mil	SF-SOP8-150A	
CR93C76	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
CR93C86	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
CYPRESS - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
S25FL004A	SO8 / 208mil	SF-SOP8-200A	
	USON8 / 5x6mm	SF-QFN8-6X5A	
S25FL004K	SO8 / 150mil	SF-SOP8-150A	
	SO8 / 208mil	SF-SOP8-200A	
S25FL008A	SO8 / 208mil	SF-SOP8-200A	
	USON8 / 5x6mm	SF-QFN8-6X5A	
S25FL008K	SO8 / 150mil	SF-SOP8-150A	
	SO8 / 208mil	SF-SOP8-200A	
S25FL016A	SO8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x8mm	SF-QFN8-8X6A	
	SO16 / 300mil	SF-SO16-300A	
S25FL016K	SO8 / 150mil	SF-SOP8-150A	
	SO8 / 208mil	SF-SOP8-200A	
S25FL032A	SO16 / 300mil	SF-SO16-300A	
S25FL032K	SO8 / 208mil	SF-SOP8-200A	
S25FL064A	SO16 / 300mil	SF-SO16-300A	
S25FL064K	SO8 / 208mil	SF-SOP8-200A	
	SO16 / 300mil	SF-SO16-300A	
S25FL116K	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSON8 / 5x6mm	SF-QFN8-6X5A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
S25FL132K	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSON8 / 5x6mm	SF-QFN8-6X5A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
S25FL164K	SOIC8 / 208mil	SF-SOP8-200A	
	WSON8 / 5x6mm	SF-QFN8-6X5A	
	SOIC16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
S25FL127S	SOIC8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
S25FL128P	WSON8 / 6x8mm	SF-QFN8-8X6A	
	SO16 / 300mil	SF-SO16-300A	
S25FL129P	WSON8 / 6x8mm	SF-QFN8-8X6A	
	SO16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
S25FL128S	WSON8 / 6x8mm	SF-QFN8-8X6A	

	SOIC16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
S25FL256S	WSON8 / 6x8mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	SO8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x8mm	SF-QFN8-8X6A	
S25FL512S	SO16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
S25FL204K	SO8 / 150mil	SF-SOP8-150A	
	SO8 / 208mil	SF-SOP8-200A	
S25FL208K	SO8 / 150mil	SF-SOP8-150A	
	SO8 / 208mil	SF-SOP8-200A	
S25FL216K	SO8 / 150mil	SF-SOP8-150A	
	SO8 / 208mil	SF-SOP8-200A	
S25FS064S	SO8 / 208mil	SF-SOP8-200A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
S25FS128S	SO8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	WSON8 / 6x8mm	SF-QFN8-8X6A	
	SO16 / 300mil	SF-SO16-300A	
S25FS256S	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	WSON8 / 6x8mm	SF-QFN8-8X6A	
S25FS512S	SO16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	WSON8 / 6x8mm	SF-QFN8-8X6A	
S70FL256P	SO16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	

CYPRESS - SPI EEPROM

Device Model	Package Type	Adapter Module	Remark
CY15B128Q	SOIC8 / 150mil	SF-SOP8-150A	
CY15B256Q	SOIC8 / 150mil	SF-SOP8-150A	
CY15B102Q	SOIC8 / 150mil	SF-SOP8-150A	
CY15B104Q	SOIC8 / 150mil	SF-SOP8-150A	
CY15B104QI	SOIC8 / 150mil	SF-SOP8-150A	
FM25040	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM25040A	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM25040B	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM25640	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM25640B	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM25640C	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM25256	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM25256B	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM25C160	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM25C160B	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM25CL04	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM25CL64	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM25CL64B	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM25H20	SOIC8 / 200mil	SF-SOP8-200A	
	---	ISP	
FM25L04	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM25L04B	SOIC8 / 150mil	SF-SOP8-150A	

	---	ISP	
FM25L16	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM25L16B	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM25L256	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM25L256B	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM25L512	TDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
FM25V01	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM25V02	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM25V05	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM25V10	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM25V20	SOIC8 / 200mil	SF-SOP8-200A	
	TDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
FM25V20A	SOIC8 / 200mil	SF-SOP8-200A	
	TDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
FM25VN02	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM25VN05	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM25VN10	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM25W256	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	

CYPRESS - I2C EEPROM

Device Model	Package Type	Adapter Module	Remark
CY24C01	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CY24C02	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CY24C04	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CY24C08	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CY24C16	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
FM24C04	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM24C04A	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM24C04B	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM24C16	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM24C16A	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM24C16B	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM24C64	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM24C64B	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM24C256	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM24C512	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM24CL04	SOIC8 / 150mil	SF-SOP8-150A	

	---	ISP	
FM24CL04B	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM24CL16	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM24CL16A	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM24CL16B	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM24CL64	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM24CL64B	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM24V01	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM24V01A	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM24V02	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM24V02A	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM24V05	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM24V10	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM24VN05	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM24VN10	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
FM24W256	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	

CYPRESS - Microwire EEPROM

Device Model	Package Type	Adapter Module	Remark
CY93C01	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CY93C02	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CY93C04	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CY93C08	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CY93C16	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	

Dosilicon - SPI Flash

Device Model	Package Type	Adapter Module	Remark
DS25M64E	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
DS25M4AB	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
DS25M4AE	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
DS25M4BA	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
DS25M4CA	SOP16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
DS25M4CB	WSO8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
DS25M4DM	SOP16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
DS25M4DN	WSO8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
DS25Q64A	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
DS25Q4AA	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
FM25M04A	DIP8		

	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
FM25M08A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
FM25M16A	SOIC16 / 300mil	SF-SO16-300A	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
FM25M32A	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOIC16 / 300mil	SF-SO16-300A	
	DIP8		
	SOIC8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
FM25M64A	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOIC16 / 300mil	SF-SO16-300A	
	DIP8		
	SOIC8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
FM25M64C	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	VSOP8 / 208mil	SF-SOP8-200A	
	SOP8 / 208mil	SF-SOP8-200A	
FM25M4AA	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	VSOP8 / 200mil	SF-SOP8-200A	
	SOP8 / 200mil	SF-SOP8-200A	
FM25Q08	SOIC16 / 300mil	SF-SO16-300A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOIC8 / 208mil	SF-SOP8-200A	
	SOIC8 / 150mil	SF-SOP8-150A	
	DIP8		
FM25Q08A	SOIC16 / 300mil	SF-SO16-300A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOIC8 / 208mil	SF-SOP8-200A	
	SOIC8 / 150mil	SF-SOP8-150A	
	DIP8		
FM25Q16	SOIC16 / 300mil	SF-SO16-300A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOIC8 / 208mil	SF-SOP8-200A	
	SOIC8 / 150mil	SF-SOP8-150A	
	DIP8		
FM25Q16A	SOIC16 / 300mil	SF-SO16-300A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	VSOP8 / 208mil	SF-SOP8-200A	
	SOIC8 / 208mil	SF-SOP8-200A	
	SOIC8 / 150mil	SF-SOP8-150A	
FM25Q16B	SOIC16 / 300mil	SF-SO16-300A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	VSOP8 / 208mil	SF-SOP8-200A	
	SOIC8 / 208mil	SF-SOP8-200A	
	SOIC8 / 150mil	SF-SOP8-150A	
FM25Q32	SOIC16 / 300mil	SF-SO16-300A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOIC8 / 208mil	SF-SOP8-200A	
	SOIC8 / 150mil	SF-SOP8-150A	
	DIP8		
FM25Q32A	SOIC8 / 208mil	SF-SOP8-200A	
	DIP8		

	VSOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOIC16 / 300mil	SF-SO16-300A	
FM25Q64	DIP8		
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
FM25Q64A	SOIC16 / 300mil	SF-SO16-300A	
	SOP8 / 200mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
DOUQI - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
DQ25Q40AL	VSOP8 / 208mil	SF-SOP8-200A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
DQ25Q32AS	SOP8 / 208mil	SF-SOP8-200A	
	USO8 / 4x3mm	SF-QFN8-4X3B	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
DQ25Q64AS	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	SOP8 / 208mil	SF-SOP8-200A	
	USO8 / 4x3mm	SF-QFN8-4X3B	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
DQ25Q128AS	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	VSOP8 / 208mil	SF-SOP8-200A	
DQ25Q128AL	WSO8 / 6x5mm	SF-QFN8-6X5A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
E-CMOS - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
EC24C02	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
EC24C02A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
EC24C04	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
EC24C04A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
EC24C08	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
EC24C08A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
EC24C16	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
EC24C16A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
EC24C32	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
EC24C32A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
EC24C64	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
EC24C64A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
EC24C128	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	

EC24C128A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
EC24C256A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
E-CMOS - Microwire EEPROM			
Device Model	Package Type	Adapter Module	Remark
EC93C46	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
EC93C56	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
EC93C66	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
EC93C86	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
Ehiway - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
E25Q64A	DIP8		
	SOIC8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
EON(cFeon) - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
EN25B05	SOP8 / 150mil	SF-SOP8-150A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25B10	SOP8 / 150mil	SF-SOP8-150A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25B20	SOP8 / 150mil	SF-SOP8-150A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25B40	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25B80	DIP8		
	SOP8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25B16	SOP8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
EN25B32	SOP8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
EN25B64	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
EN25D80	DIP8		
	SOP8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25D16	DIP8		
	SOP8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
EN25E10A	SOP8 / 150mil	SF-SOP8-150A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
EN25E40A	SOP8 / 150mil	SF-SOP8-150A	
	USON8 / 3x2mm	SF-QFN8-2X3A	

	---	ISP	
EN25F05	SOP8 / 150mil	SF-SOP8-150A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25F05A	SOP8 / 150mil	SF-SOP8-150A	
	VSOP8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25F10	SOP8 / 150mil	SF-SOP8-150A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25F10A	SOP8 / 150mil	SF-SOP8-150A	
	VSOP8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25F20	SOP8 / 150mil	SF-SOP8-150A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25F20A	SOP8 / 150mil	SF-SOP8-150A	
	VSOP8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25F20A(2N)	SOP8 / 150mil	SF-SOP8-150A	
	VSOP8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25F40	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25F40A	SOP8 / 150mil	SF-SOP8-150A	
	VSOP8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25F80	DIP8		
	SOP8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25F16	DIP8		
	SOP8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SQ16-300A	
	---	ISP	
EN25F32	DIP8		
	SOP8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SQ16-300A	
	---	ISP	
EN25F64	DIP8		
	SOP8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	VDFN8 / 6x8mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SQ16-300A	
	---	ISP	
EN25LF05	SOP8 / 150mil	SF-SOP8-150A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25LF10	SOP8 / 150mil	SF-SOP8-150A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25LF20	SOP8 / 150mil	SF-SOP8-150A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25LF40	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	

	SOP8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25P05	SOP8 / 150mil	SF-SOP8-150A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25P10	SOP8 / 150mil	SF-SOP8-150A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25P20	SOP8 / 150mil	SF-SOP8-150A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25P40	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25P80	SOP8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25P16	SOP8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
EN25P32	SOP8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
EN25P64	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
EN25Q40	SOP8 / 150mil	SF-SOP8-150A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25Q40A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	VSOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25Q40B	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	VSOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25Q80A	DIP8		OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25Q80B	DIP8		OTP
	SOP8 / 150mil	SF-SOP8-150A	
	VSOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
EN25Q80C	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	VSOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
EN25Q80C(OTP)	DIP8		OTP
	SOP8 / 150mil	SF-SOP8-150A	
	VSOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	

	USON8 / 2x3mm	SF-QFN8-2X3A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
EN25Q16	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
EN25Q16A	---	ISP	OTP
	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
EN25Q16B	VDFN8 / 5x6mm	SF-QFN8-6X5A	OTP
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
EN25Q32A	---	ISP	OTP
	DIP8		
	SOP8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
EN25Q32B	---	ISP	OTP
	DIP8		
	SOP8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
EN25Q32B(OTP)	SOP16 / 300mil	SF-SO16-300A	OTP
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
	DIP8		
EN25Q32C	SOP8 / 200mil	SF-SOP8-200A	OTP
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
EN25Q32C(OTP)	DIP8		OTP
	SOP8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
EN25Q32C(2B)	---	ISP	OTP
	DIP8		
	SOP8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
EN25Q64	SOP16 / 300mil	SF-SO16-300A	OTP
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
	VDFN8 / 6x8mm	SF-QFN8-8X6A	
EN25Q128	VDFN8 / 5x6mm	SF-QFN8-6X5A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
EN25QA32A	SOP8 / 200mil	SF-SOP8-200A	OTP
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
	SOP8 / 200mil	SF-SOP8-200A	
EN25QA64A	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	OTP
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
EN25QE16A	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	

EN25QE32A	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
EN25QH16	DIP8		OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
EN25QH16A	DIP8		OTP
	SOP8 / 150mil	SF-SOP8-150A	
	VSOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
EN25QH16B	DIP8		OTP
	SOP8 / 150mil	SF-SOP8-150A	
	VSOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
EN25QH16B(OTP)	DIP8		OTP
	SOP8 / 150mil	SF-SOP8-150A	
	VSOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
EN25QH32	DIP8		OTP
	SOP8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
EN25QH32A	DIP8		OTP
	SOP8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
EN25QH32B	---	ISP	OTP
	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
EN25QH64	SOP16 / 300mil	SF-SO16-300A	OTP
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
	DIP8		
	SOP8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
EN25QH64A	VDFN8 / 6x8mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
	DIP8		
	SOP8 / 200mil	SF-SOP8-200A	
EN25QH128	VDFN8 / 5x6mm	SF-QFN8-6X5A	OTP
	VDFN8 / 6x8mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
EN25QH128A	DIP8		OTP
	SOP8 / 200mil	SF-SOP8-200A	

	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
EN25QH256	VDFN8 / 6x8mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
EN25QH256A	VDFN8 / 6x8mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
EN25QX64A	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	VDFN8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
EN25QX128A	SOP8 / 208mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	VDFN8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
EN25QX256A	SOP8 / 208mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	VDFN8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
EN25QX512A	SOP8 / 208mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	VDFN8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
EN25S10	SOP8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
EN25S10A	SOP8 / 150mil	SF-SOP8-150A	
	VSOP8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
EN25S20	SOP8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25S20A	SOP8 / 150mil	SF-SOP8-150A	
	VSOP8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25S40	SOP8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25S40A	SOP8 / 150mil	SF-SOP8-150A	
	VSOP8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25S80	SOP8 / 150mil	SF-SOP8-150A	
	VSOP8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25S80A	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	VSOP8 / 200mil	SF-SOP8-200A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25S16	SOP8 / 150mil	SF-SOP8-150A	
	VSOP8 / 200mil	SF-SOP8-200A	

	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25S16B	SOP8 / 150mil	SF-SOP8-150A	OTP
	VSOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25S16B(OTP)	SOP8 / 150mil	SF-SOP8-150A	OTP
	VSOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25S32	VSOP8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25S64	VSOP8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25S64A	DIP8		
	SOP8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25SX64A	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25SX128A	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	VDFN8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
EN25SX256A	SOP8 / 208mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	VDFN8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
EN25T80	DIP8		
	SOP8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EN25T16	DIP8		
	SOP8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
EN25T16A	DIP8		OTP
	SOP8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	

Eorex - I2C EEPROM

Device Model	Package Type	Adapter Module	Remark
EM24LC02	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	

Eorex - Microwire EEPROM

Device Model	Package Type	Adapter Module	Remark
EM93LC46	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
EM93LC56	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
EM93LC57	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
EM93LC66	DIP8		

EM93LC86	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
Estek - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
24C02	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
24C04	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
24C08	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
24C16	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
24C32	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
24C64	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
Everspin - SPI EEPROM			
Device Model	Package Type	Adapter Module	Remark
MR25H256A	DFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
MR25H10	DFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
EXCELSEMI - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
ES25P40	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
ES25P80	SOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
ES25P16	SOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
ES25M40	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
ES25M40A	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
ES25M80	SOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
ES25M80A	SOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
ES25M16	SOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
ES25M16A	SOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
EXEL - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
XL24C01A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
XL24C02	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
XL24C04	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
XL24C08	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
XL24C16	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	

XL24C164	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
EXEL - Microwire EEPROM			
Device Model	Package Type	Adapter Module	Remark
XL93C46	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
XL93C46J	SOIC8 / 150mil	SF-SOP8-150A	
XL93C46A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
XL93C46AJ	SOIC8 / 150mil	SF-SOP8-150A	
XL93C66	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
XL93C66J	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
XL93LC46B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
XL93LC46BY	SOIC8 / 150mil	SF-SOP8-150A	
XL93LC56	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
XL93LC56Y	SOIC8 / 150mil	SF-SOP8-150A	
XL93LC56A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
XL93LC56AY	SOIC8 / 150mil	SF-SOP8-150A	
XL93LC56B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
XL93LC56BY	SOIC8 / 150mil	SF-SOP8-150A	
XL93LC66	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
XL93LC66Y	SOIC8 / 150mil	SF-SOP8-150A	
XL93LC66A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
XL93LC66AY	SOIC8 / 150mil	SF-SOP8-150A	
XL93LC66B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
XL93LC66BY	SOIC8 / 150mil	SF-SOP8-150A	
Fairchild - SPI EEPROM			
Device Model	Package Type	Adapter Module	Remark
FM25C020U	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FM25C020UL	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FM25C040U	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FM25C041U	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FM25C040UL	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FM25C160U	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FM25C160UL	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FM25C320U	DIP8		

FM25C320UL	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
FM25C640U	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
NM25C020	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
NM25C04	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
NM25C040	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
NM25C041	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
NM25C160	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
NM25C640	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
Fairchild - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
FM24C02U	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
FM24C02UF	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
FM24C03U	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
FM24C03UF	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
FM24C04U	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
FM24C04UF	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
FM24C05U	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
FM24C05UF	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
FM24C08U	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
FM24C08UF	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
FM24C09U	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
FM24C09UF	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
FM24C16U	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
FM24C16UF	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
FM24C17U	DIP8		

FM24C17UF	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
FM24C32U	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
FM24C32UF	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
FM24C64	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
FM24C64F	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
FM24C128	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
FM24C128F	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
FM24C256	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
FM24C256F	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
NM24C02	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
NM24C02F	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
NM24C02U	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
NM24C03	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
NM24C03F	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
NM24C03U	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
NM24C04	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
NM24C04F	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
NM24C05	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
NM24C05F	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
NM24C05U	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
NM24C08	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
NM24C08F	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
NM24C08U	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		

NM24C09	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM24C09F	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM24C09U	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM24C16	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM24C16F	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM24C16U	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM24C16UF	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM24C17	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM24C17F	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM24C17U	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM24C17UF	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM24C32	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM24C32F	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM24C32U	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM24C65	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM24C65F	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM24C65U	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM24C65UF	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM24W02	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM24W04	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM24W08	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM24W16	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
Fairchild - Microwire EEPROM			
Device Model	Package Type	Adapter Module	Remark
FM93C46	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	

FM93C46T	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FM93C46A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FM93C46AT	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FM93C56	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FM93C56A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FM93C66	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FM93C66A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FM93C86A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FM93CS46	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FM93CS46T	SOIC8 / 150mil	SF-SOP8-150A	
NM93C46	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM93C46A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM93C46AL	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM93C46L	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM93C46LZ	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM93C46T	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM93C56	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM93C56A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM93C56AL	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM93C56L	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM93C56LZ	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM93C56T	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM93C66	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM93C66A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM93C66AL	DIP8		

NM93C66L	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
NM93C66LZ	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM93C66T	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM93C86A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM93C86AL	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
Fidelix - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
FM25M04A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
FM25M08A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOIC16 / 300mil	SF-SO16-300A	
FM25M16A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOIC16 / 300mil	SF-SO16-300A	
FM25M32A	DIP8		
	SOIC8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOIC16 / 300mil	SF-SO16-300A	
FM25M64A	DIP8		
	SOIC8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOIC16 / 300mil	SF-SO16-300A	
FM25M64C	SOP8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
FM25M4AA	SOP8 / 200mil	SF-SOP8-200A	
	VSOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
FM25Q08	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOIC16 / 300mil	SF-SO16-300A	
FM25Q08A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOIC16 / 300mil	SF-SO16-300A	
FM25Q16	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	

FM25Q16A	SOIC16 / 300mil	SF-SO16-300A	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOIC16 / 300mil	SF-SO16-300A	
FM25Q16B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOIC16 / 300mil	SF-SO16-300A	
FM25Q32	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOIC16 / 300mil	SF-SO16-300A	
FM25Q32A	DIP8		
	SOIC8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOIC16 / 300mil	SF-SO16-300A	
FM25Q64	DIP8		
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOIC16 / 300mil	SF-SO16-300A	
FM25Q64A	SOP8 / 200mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	

First Rank - SPI Flash

Device Model	Package Type	Adapter Module	Remark
T25S40	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	---	ISP	
T25S80	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	---	ISP	
T25S16	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	---	ISP	
T25S32	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	USO8 / 4x3mm	SF-QFN8-4X3B	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
T25S64	SOP8 / 200mil	SF-SOP8-200A	
	---	ISP	

First Rank - I2C EEPROM

Device Model	Package Type	Adapter Module	Remark
T24C02	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
T24C02A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
T24C04	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
T24C04A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	

	---	ISP	
T24C08	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
T24C08A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
T24C16	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
T24C16A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
T24C32	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
T24C32A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
T24C64	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
T24C64A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
T24C128	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
T24C128A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
T24C256	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
T24C256A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
T24C512A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	

First Rank - Microwire EEPROM

Device Model	Package Type	Adapter Module	Remark
T93C46	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
T93C46A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
T93C56	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
T93C56A	DIP8		

	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
T93C66	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
T93C66A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
Force Technologies - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
FT24C01	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FT24C01A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FT24C02	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FT24C02A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FT24C04	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FT24C04A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FT24C08	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FT24C08A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FT24C16	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FT24C16A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FT24C32	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FT24C32A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FT24C64	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FT24C64A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FT24C128	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FT24C128A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FT24C256	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FT24C256A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FT24C256B	DIP8		

	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FORESEE - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
FS25Q004	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
FS25Q008	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
FS25Q016	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
FS25Q032	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TDFN8 / 5x6mm	SF-QFN8-6X5A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
FS25Q064	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TDFN8 / 5x6mm	SF-QFN8-6X5A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
FS25Q128	SOP8 / 208mil	SF-SOP8-200A	
	TDFN8 / 8x6mm	SF-QFN8-8X6A	
FS25SQA032M	SOP8 / 150mil	SF-SOP8-150A	
Forward - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
24LC01	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
24LC02	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
24LC04	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
24LC08	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
24LC16	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
24LC32	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
24LC64	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
Fremont - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
FT25H04	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
FT25H08	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
FT25H16	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
FT25H32	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
FT25H64	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
FT25L08	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	

Fremont - SPI EEPROM			
Device Model	Package Type	Adapter Module	Remark
FT25C08A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
FT25C16A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
FT25C32A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
FT25C64A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
Fremont - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
FT24C02A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	TSOT23-5	SF-SOT23-6A	
	---	ISP	
FT24C04A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	TSOT23-5	SF-SOT23-6A	
	---	ISP	
FT24C08A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	TSOT23-5	SF-SOT23-6A	
	---	ISP	
FT24C16A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	TSOT23-5	SF-SOT23-6A	
	---	ISP	
FT24C32A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	TSOT23-5	SF-SOT23-6A	
	---	ISP	
FT24C64A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	TSOT23-5	SF-SOT23-6A	

	---	ISP	
FT24C128A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
FT24C256A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FT24C512A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FT24C1024A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
FT34C04A	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
Fremont - Microwire EEPROM			
Device Model	Package Type	Adapter Module	Remark
FT93C46	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FT93C46-R	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
FT93C46A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FT93C46A-R	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
FT93C56	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FT93C56-R	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
FT93C56A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FT93C56A-R	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
FT93C66	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FT93C66-R	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
FT93C66A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FT93C66A-R	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
Fudan Microelect - SPI Flash			

Device Model	Package Type	Adapter Module	Remark
AB25WD02	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
FM25F005	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FM25F005A	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FM25F005B	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
FM25F005C	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
FM25F01	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FM25F01A	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FM25F01B	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
FM25F01C	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
FM25F02	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FM25F02A	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FM25F02C	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
FM25F04	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FM25F04A	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FM25LQ16I3	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
FM25LQ32I3	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
FM25LQ128I3	SOP8 / 208mil	SF-SOP8-200A	OTP
	TDFN8 / 5x6mm	SF-QFN8-6X5A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
FM25Q02	SOP8 / 150mil	SF-SOP8-150A	OTP

	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FM25Q02B	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
FM25Q04	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FM25Q04B	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FM25Q08	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
FM25Q08A	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FM25Q08B	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FM25Q16	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
FM25Q16A	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FM25Q16B	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
FM25Q32	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
FM25Q32A	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TDFN8 / 5x6mm	SF-QFN8-6X5A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
FM25Q32BI3	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
FM25Q64	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TDFN8 / 5x6mm	SF-QFN8-6X5A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
FM25Q64AI3	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	TDFN8 / 5x6mm	SF-QFN8-6X5A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
FM25Q128	SOP8 / 208mil	SF-SOP8-200A	OTP
	TDFN8 / 8x6mm	SF-QFN8-8X6A	
	---	ISP	

FM25Q128A	SOP8 / 208mil	SF-SOP8-200A	OTP
	TDFN8 / 5x6mm	SF-QFN8-6X5A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
FM25Q128AI3	SOP8 / 208mil	SF-SOP8-200A	OTP
	TDFN8 / 5x6mm	SF-QFN8-6X5A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
FM25Q256I3	SOP8 / 208mil	SF-SOP8-200A	OTP
	TDFN8 / 5x6mm	SF-QFN8-6X5A	
	TDFN8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
FM25W01	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FM25W02	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FM25W02H	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
FM25W04	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FM25W08	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FM25W16	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
FM25W16A	SOP8 / 150mil	SF-SOP8-150A	OTP
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FM25W32	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
FM25W32AI3	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
FM25W128	SOP8 / 208mil	SF-SOP8-200A	OTP
	TDFN8 / 5x6mm	SF-QFN8-6X5A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
FM25WD02	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
Fudan Microelect - SPI EEPROM			
Device Model	Package Type	Adapter Module	Remark
FM25080	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FM25160	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	

FM25320	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FM25640	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FM25128	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FM25128S	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FM25256	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FM25256S	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FM25512	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FM25512S	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	

Fudan Microelect - I2C EEPROM

Device Model	Package Type	Adapter Module	Remark
FM24C02	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
FM24C02A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
FM24C02B	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	SOT23-5	SF-SOT23-6A	
FM24C02C	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
FM24C02F	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
FM24C02G	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
FM24C04	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
FM24C04A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	

FM24C04B	DIP8		OTP
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
FM24C04D	DIP8		OTP
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
FM24C04F	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
FM24C08	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
FM24C08A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
FM24C08B	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	SOT23-5	SF-SOT23-6A	
FM24C08D	DIP8		OTP
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
FM24C08F	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
FM24C16	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
FM24C16A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
FM24C16B	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	SOT23-5	SF-SOT23-6A	
FM24C16D	DIP8		OTP
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
FM24C32A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
FM24C32D	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FM24C64A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	

FM24C64D	DIP8		OTP
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FM24C128A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
FM24C128D	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FM24C256A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
FM24C256E	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FM24C512A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
FM24C512D	DIP8		OTP
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FM24C1024A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
FM24F32D	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FM24LN64I3	DIP8		OTP
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FM24LN128I3	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
FM34C04D	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	

Fudan Microelect - Microwire EEPROM

Device Model	Package Type	Adapter Module	Remark
FM93C46	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-6	SF-SOT23-6A	
	---	ISP	
FM93C56	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-6	SF-SOT23-6A	
	---	ISP	
FM93C66	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-6	SF-SOT23-6A	
	---	ISP	

Fujitsu - SPI EEPROM			
Device Model	Package Type	Adapter Module	Remark
MB85RS16	SOP8 / 150mil	SF-SOP8-150A	
MB85RS64	SOP8 / 150mil	SF-SOP8-150A	
MB85RS64V	SOP8 / 150mil	SF-SOP8-150A	
MB85RS128B	SOP8 / 150mil	SF-SOP8-150A	
MB85RS256B	SOP8 / 150mil	SF-SOP8-150A	
MB85RS1MT	SOP8 / 150mil	SF-SOP8-150A	
MB85RS2MT	SOP8 / 150mil	SF-SOP8-150A	
MB85RS4MT	SOP8 / 150mil	SF-SOP8-150A	
Fujitsu - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
MB85RC04V	SOP8 / 150mil	SF-SOP8-150A	
MB85RC16	SOP8 / 150mil	SF-SOP8-150A	
MB85RC16V	SOP8 / 150mil	SF-SOP8-150A	
MB85RC64	SOP8 / 150mil	SF-SOP8-150A	
MB85RC64A	SOP8 / 150mil	SF-SOP8-150A	
MB85RC64V	SOP8 / 150mil	SF-SOP8-150A	
MB85RC128	SOP8 / 150mil	SF-SOP8-150A	
MB85RC128A	SOP8 / 150mil	SF-SOP8-150A	
MB85RC256V	SOP8 / 150mil	SF-SOP8-150A	
Gatelevel - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
GM24LC02B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
GM24LC04B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
GM24LC08B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
GM24LC16B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
Generalplus - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
GPR25L1603E	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
GPR25L3203F	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
GPR25L6403F	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
Giantec - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
GT25D20E	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GT25Q05C	SOIC8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GT25Q10C	SOIC8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GT25Q20C	SOIC8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GT25Q20F	SOIC8 / 150mil	SF-SOP8-150A	OTP

	TSSOP8 / 173mil	SF-TSP8-170A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GT25Q40C	SOIC8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GT25Q40D	SOIC8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GT25Q80A	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GT25Q16A	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GT25Q16B	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GT25Q32A	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GT25Q32B-L	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GT25Q64A-S	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
Giantec - SPI EEPROM			
Device Model	Package Type	Adapter Module	Remark
GT25C01	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
GT25C02	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
GT25C04	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
GT25C08	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
GT25C16	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	

GT25C32	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
GT25C32A	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
GT25C64	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
GT25C128	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
GT25C256	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
GT25C512	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
Giantec - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
GT24C01	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
GT24C02	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
GT24C02A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
GT24C02B	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
GT24C04	SOT23-5	SF-SOT23-6A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
GT24C04A	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
GT24C08	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	

GT24C08A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
GT24C08B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
GT24C16	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
GT24C16A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
GT24C16B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
GT24C32	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
GT24C32A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
GT24C32B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
GT24C32D	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
GT24C64	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
GT24C64A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	

	---	ISP	
GT24C128	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
GT24C128A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
GT24C128B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
GT24C128D	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
GT24C256	SOT23-5	SF-SOT23-6A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
GT24C256A	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
GT24C256C	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
GT24C512	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
GT24C512A	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
GT24C512B	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
GT24C1024	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
GT24C2048H	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	

	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
GT34C02A	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
GT34C02B	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
GT34C04	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
Giantec - Microwire EEPROM			
Device Model	Package Type	Adapter Module	Remark
GT93C46	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
GT93C46A	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
GT93C56	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
GT93C56A	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
GT93C66	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
GT93C66A	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
GT93C76	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
GT93C86	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
GigaDevice - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
GD25B16C	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	---	ISP	
GD25B16E	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25B32E	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
GD25B64E	SOP8 / 208mil	SF-SOP8-200A	OTP
	USON8 / 3x4mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	

GD25B32C	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
	DIP8		
	SOP8 / 208mil	SF-SOP8-200A	
GD25B64B	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
	DIP8		
	SOP8 / 208mil	SF-SOP8-200A	
GD25B64C	WSO8 / 6x5mm	SF-QFN8-6X5A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
	DIP8		
GD25B64H	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
GD25B127D	SOP8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
GD25B128C	SOP16 / 300mil	SF-SO16-300A	OTP
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
	DIP8		
GD25B128E	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	---	ISP	
GD25B128H	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	---	ISP	
GD25B256D	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
GD25B256E	SOP16 / 300mil	SF-SO16-300A	OTP
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
	DIP8		
GD25B512ME	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	---	ISP	
GD25B512MF	SOP16 / 300mil	SF-SO16-300A	OTP
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
	DIP8		
GD25D05B	SOP8 / 208mil	SF-SOP8-200A	
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USO8 / 3x2mm	SF-QFN8-2X3A	
GD25D05C	---	ISP	
	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	

	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
GD25D05E	SOP8 / 150mil	SF-SOP8-150A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
GD25D10B	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
GD25D10C	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
GD25D10E	SOP8 / 150mil	SF-SOP8-150A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
GD25D20C	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
GD25D20E	SOP8 / 150mil	SF-SOP8-150A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
GD25D40	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	---	ISP	
GD25D40C	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
GD25D40E	SOP8 / 150mil	SF-SOP8-150A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
GD25D80	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	---	ISP	
GD25D80C	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
GD25D80E	SOP8 / 150mil	SF-SOP8-150A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
GD25E32E	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25F40	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	---	ISP	
GD25F80	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	---	ISP	
GD25F64F	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25F128E	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SQ16-300A	

	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
GD25F128F	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
GD25F128J	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
GD25F256F	WSON8 / 6x5mm	SF-QFN8-6X5A	OTP
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
GD25F512MF	WSON8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
GD25LB16E	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LB32E	SOP8 / 208mil	SF-SOP8-200A	OTP
	USON8 / 3x2mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LB64C	SOP8 / 208mil	SF-SOP8-200A	OTP
	VSOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LB64E	SOP8 / 208mil	SF-SOP8-200A	OTP
	VSOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LB128C	SOP8 / 208mil	SF-SOP8-200A	OTP
	VSOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LB128D	SOP8 / 208mil	SF-SOP8-200A	OTP
	VSOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LB128E	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
GD25LB256E	WSON8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
GD25LB256F	WSON8 / 6x5mm	SF-QFN8-6X5A	OTP
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
GD25LB512ME	WSON8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
GD25LB512MF	WSON8 / 6x5mm	SF-QFN8-6X5A	OTP
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	

	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
GD25LD05C	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
GD25LD10C	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
GD25LD10E	SOP8 / 150mil	SF-SOP8-150A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
GD25LD20C	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LD20E	SOP8 / 150mil	SF-SOP8-150A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
GD25LD40C	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LD40E	SOP8 / 150mil	SF-SOP8-150A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
GD25LD80C	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LD80E	SOP8 / 150mil	SF-SOP8-150A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
GD25LE05C	SOP8 / 150mil	SF-SOP8-150A	OTP
	VSOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LE10C	SOP8 / 150mil	SF-SOP8-150A	OTP
	VSOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LE20C	SOP8 / 150mil	SF-SOP8-150A	OTP
	VSOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	

GD25LE40C	SOP8 / 150mil	SF-SOP8-150A	OTP
	VSOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LE40E	SOP8 / 150mil	SF-SOP8-150A	OTP
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	---	ISP	
GD25LE80C	SOP8 / 150mil	SF-SOP8-150A	OTP
	VSOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LE80E	SOP8 / 208mil	SF-SOP8-200A	OTP
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
GD25LE16E	SOP8 / 208mil	SF-SOP8-200A	OTP
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
GD25LE32E	SOP8 / 208mil	SF-SOP8-200A	OTP
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	---	ISP	
GD25LE16C	SOP8 / 150mil	SF-SOP8-150A	OTP
	VSOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LE32D	SOP8 / 208mil	SF-SOP8-200A	OTP
	VSOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LE64C	SOP8 / 208mil	SF-SOP8-200A	OTP
	VSOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LE64E	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LE128D	SOP8 / 208mil	SF-SOP8-200A	OTP
	VSOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	---	ISP	
GD25LE128E	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
GD25LE255E	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LE256D	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
GD25LE256H	WSON8 / 6x5mm	SF-QFN8-6X5A	OTP
	---	ISP	
GD25LF80E	SOP8 / 208mil	SF-SOP8-200A	OTP

	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	---	ISP	
GD25LF16E	SOP8 / 208mil	SF-SOP8-200A	OTP
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	---	ISP	
GD25LF32E	SOP8 / 208mil	SF-SOP8-200A	OTP
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LF64E	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LF128E	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
GD25LF128J	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
GD25LF255E	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LF256F	WSON8 / 6x5mm	SF-QFN8-6X5A	OTP
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
GD25LF256H	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LF512MF	WSON8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
GD25LH05C	SOP8 / 150mil	SF-SOP8-150A	OTP
	VSOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LH10C	SOP8 / 150mil	SF-SOP8-150A	OTP
	VSOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LH20C	SOP8 / 150mil	SF-SOP8-150A	OTP
	VSOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LH40C	SOP8 / 150mil	SF-SOP8-150A	OTP
	VSOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	

	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LH80C	SOP8 / 150mil	SF-SOP8-150A	OTP
	VSOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	USO8 / 3x2mm	SF-QFN8-2X3A	
	USO8 / 3x4mm	SF-QFN8-4X3B	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LH80E	SOP8 / 150mil	SF-SOP8-150A	OTP
	VSOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	USO8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
GD25LH16C	SOP8 / 150mil	SF-SOP8-150A	OTP
	VSOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	USO8 / 3x4mm	SF-QFN8-4X3B	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LH16E	SOP8 / 150mil	SF-SOP8-150A	OTP
	VSOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	USO8 / 3x4mm	SF-QFN8-4X3B	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LH32D	SOP8 / 208mil	SF-SOP8-200A	OTP
	VSOP8 / 208mil	SF-SOP8-200A	
	USO8 / 3x4mm	SF-QFN8-4X3B	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LH32E	SOP8 / 208mil	SF-SOP8-200A	OTP
	USO8 / 3x2mm	SF-QFN8-2X3A	
	USO8 / 3x4mm	SF-QFN8-4X3B	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LQ05B	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USO8 / 3x2mm	SF-QFN8-2X3A	
	USO8 / 4x3mm	SF-QFN8-4X3B	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LQ10B	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USO8 / 3x2mm	SF-QFN8-2X3A	
	USO8 / 4x3mm	SF-QFN8-4X3B	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LQ20B	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USO8 / 3x2mm	SF-QFN8-2X3A	
	USO8 / 4x3mm	SF-QFN8-4X3B	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LQ05C	SOP8 / 150mil	SF-SOP8-150A	OTP
	VSOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	USO8 / 3x2mm	SF-QFN8-2X3A	
	USO8 / 4x3mm	SF-QFN8-4X3B	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LQ10C	SOP8 / 150mil	SF-SOP8-150A	OTP
	VSOP8 / 150mil	SF-SOP8-150A	

	SOP8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LQ20C	SOP8 / 150mil	SF-SOP8-150A	OTP
	VSOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
GD25LQ20E	WSON8 / 6x5mm	SF-QFN8-6X5A	OTP
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
GD25LQ40	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LQ40B	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LQ40C	SOP8 / 150mil	SF-SOP8-150A	OTP
	VSOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
GD25LQ40E	WSON8 / 6x5mm	SF-QFN8-6X5A	OTP
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
GD25LQ80	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	OTP
GD25LQ80B	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	OTP
GD25LQ80C	VSOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	OTP
GD25LQ80E	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
GD25LQ16	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
GD25LQ16C			OTP

	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LQ16E	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LQ32	VSOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LQ32C	SOP8 / 208mil	SF-SOP8-200A	OTP
	VSOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LQ32D	SOP8 / 208mil	SF-SOP8-200A	OTP
	VSOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LQ32E	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LQ64B	VSOP8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LQ64C	SOP8 / 208mil	SF-SOP8-200A	OTP
	VSOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LQ64E	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LQ128C	SOP8 / 208mil	SF-SOP8-200A	OTP
	VSOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25LQ128D	SOP8 / 208mil	SF-SOP8-200A	OTP
	VSOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
	SOP8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
GD25LQ128E	WSON8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
	SOP8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
GD25LQ255E	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
GD25LQ256C	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
GD25LQ256D	---	ISP	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	

GD25LQ256H	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	---	ISP	
GD25LR64E	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
GD25LR128D	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
GD25LR128E	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
GD25LR256E	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
GD25LR256F	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
GD25LR512ME	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
GD25LR512MF	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
GD25LT256E	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
GD25LT512ME	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
GD25LX128J	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
GD25LX256E	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
GD25LX512ME	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
GD25M21B	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
GD25M41B	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
GD25Q512	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USO8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
GD25Q10	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	

	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
GD25Q20B	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
GD25Q20C	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
GD25Q20E	---	ISP	OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
GD25Q21B	---	ISP	OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
GD25Q40B	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
GD25Q40C	DIP8		OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
GD25Q40E	---	ISP	OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
GD25Q41B	---	ISP	OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
GD25Q80B	---	ISP	OTP
	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
GD25Q80C	---	ISP	OTP
	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
GD25Q80E	WSO8 / 6x5mm	SF-QFN8-6X5A	OTP
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
GD25Q16B	WSO8 / 6x5mm	SF-QFN8-6X5A	OTP
	---	ISP	
	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
GD25Q16C	---	ISP	OTP
	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	

	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
GD25Q16E	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
GD25Q32B	---	ISP	OTP
	DIP8		
	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
GD25Q32C	---	ISP	OTP
	DIP8		
	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
GD25Q32E	---	ISP	OTP
	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
GD25Q64B	USON8 / 3x4mm	SF-QFN8-4X3B	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
	DIP8		
GD25Q64C	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
GD25Q64E	---	ISP	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
GD25Q64F	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	OTP
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
GD25Q64H	---	ISP	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
GD25Q127C	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	OTP
	---	ISP	
	DIP8		
	SOP8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
GD25Q128B	WSON8 / 6x5mm	SF-QFN8-6X5A	OTP
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
	WSON8 / 8x6mm	SF-QFN8-8X6A	

	---	ISP	
GD25Q128C	DIP8		OTP
	SOP8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
GD25Q128E	DIP8		OTP
	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
GD25Q128F	---	ISP	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
GD25Q128H	---	ISP	OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
GD25Q256C	---	ISP	OTP
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
GD25Q256D	---	ISP	OTP
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
GD25Q256E	SOP16 / 300mil	SF-SO16-300A	OTP
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
GD25Q257D	WSON8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
GD25Q512MC	SOP16 / 300mil	SF-SO16-300A	OTP
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
GD25R64C	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25R64E	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	---	ISP	
GD25R127D	DIP8		
	SOP8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
GD25R128E	---	ISP	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
GD25R256D	---	ISP	
	WSON8 / 6x5mm	SF-QFN8-6X5A	

	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
GD25R256E	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
GD25R512ME	WSO8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
GD25R512MF	WSO8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
GD25S512MD	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
GD25S513MD	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
GD25T512ME	WSO8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
GD25VQ21B	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USO8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
GD25VQ40C	DIP8		OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	USO8 / 3x2mm	SF-QFN8-2X3A	
	USO8 / 3x4mm	SF-QFN8-4X3B	
	---	ISP	
GD25VQ80C	DIP8		OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	USO8 / 3x2mm	SF-QFN8-2X3A	
	USO8 / 3x4mm	SF-QFN8-4X3B	
	---	ISP	
GD25VQ32C	DIP8		OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	USO8 / 4x3mm	SF-QFN8-4X3B	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
GD25VQ41B	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USO8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
GD25VQ16C	DIP8		OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	USO8 / 3x2mm	SF-QFN8-2X3A	
	USO8 / 4x3mm	SF-QFN8-4X3B	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
GD25WB256E	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	

	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
GD25WD05C	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
GD25WD10C	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
GD25WD10E	SOP8 / 150mil	SF-SOP8-150A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
GD25WD20C	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
GD25WD20E	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
GD25WD40C	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
GD25WD40E	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
GD25WD80C	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
GD25WD80E	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
GD25WQ20E	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
GD25WQ40E	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
GD25WQ80E	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	---	ISP	
GD25WQ16E	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	---	ISP	
GD25WQ32E	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
GD25WQ64E	SOP8 / 208mil	SF-SOP8-200A	OTP
	USON8 / 3x4mm	SF-QFN8-4X3B	

	WSO8 / 6x5mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
GD25WQ64H	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	USO8 / 3x4mm	SF-QFN8-4X3B	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
GD25WQ128E	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
GD25WQ128H	---	ISP	OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	USO8 / 3x4mm	SF-QFN8-4X3B	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
GD25WR256E	---	ISP	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
GD25X512ME	---	ISP	OTP
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
GD55B512ME	---	ISP	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
GD55B01GE	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	OTP
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
GD55B01GF	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
GD55F256F	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
GD55F01GF	SOP8 / 200mil	SF-SOP8-200A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
GD55LB512MF	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
GD55LB01GE	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
GD55LB01GF	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
GD55LE511ME	SOP16 / 300mil	SF-SO16-300A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
GD55LF511ME	WSO8 / 8x6mm	SF-QFN8-8X6A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
GD55LF01GF	WSO8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
GD55LR512MF	SOP16 / 300mil	SF-SO16-300A	OTP
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
GD55LT01GE	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
GD55LX512WE	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	OTP
	SOP16 / 300mil	SF-SO16-300A	
GD55LX01GE	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
GD55R512ME	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	SOP16 / 300mil	SF-SO16-300A	
GD55T01GE	WSO8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	

	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
GD55WB512ME	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
GD55WR512ME	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
GD55X01GE	SOP16 / 300mil	SF-SO16-300A	OTP
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
MD25D05	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
MD25D10	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
MD25D20	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
MD25D20E	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
MD25D40	---	ISP	
	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
MD25D40E	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
MD25D80	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	---	ISP	
MD25D80D	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
MD25D80E	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	---	ISP	
MD25LQ16E	SOP8 / 150mil	SF-SOP8-150A	OTP
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
XD25LD40E	SOP8 / 150mil	SF-SOP8-150A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
MD25Q80C	DIP8		OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
MD25Q16C	DIP8		OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
MD25Q32C	DIP8		OTP
	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
MD25Q64C	DIP8		OTP

	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
MD25Q128(old)	DIP8		OTP
	SOP8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MD25Q128	DIP8		OTP
	SOP8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
Green Engine - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
GE24C01	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
GE24C02	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
GE24BC04	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
HangShun - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
HK24C02	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
HK24C04	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
HK24C08	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
HK24C16	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
HK24C32	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
HK24C64	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
HK24C128	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
HK24C256	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	

HK24C512	---	ISP	
	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
HeYang Tek. - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
HY25D04U	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
HY25D08U	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
HY25D16U	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
HY25Q32U	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
HY25Q64U	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
HY25Q128U	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
HY25Q256U	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 6x8mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
HY25Q512U	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
HIKSEMI - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
HSERCD64A	DIP8		OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
HSERCD128A	DIP8		OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
HOLTEK - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
HT24LC01	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
HT24LC02	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
HT24LC04	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
HT24LC08	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
HT24LC16	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
HT24LC32	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
HT24LC64	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
HT24LC256	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	

	---	ISP	
HOLTEK - Microwire EEPROM			
Device Model	Package Type	Adapter Module	Remark
HT93LC46-A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
HT93LC46-B	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
HT93LC56-A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
HT93LC56-B	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
HT93LC56-C	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
HT93LC56-D	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
HT93LC66-A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
HT93LC66-B	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
HT93LC76	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
HT93LC86-A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
HT93LC86-B	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
Hopefind - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
HM24LC01	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
HM24LC02	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
HM24LC04	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
HM24LC08	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
HM24LC16	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
HM24LC32	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
HM24LC64	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
HuaHong ZealCore - SPI Flash			

Device Model	Package Type	Adapter Module	Remark
BH25D05AS	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
BH25D05BS	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
BH25D10AS	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
BH25D10BS	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
BH25D20AS	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
BH25D40AS	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
BH25D80AS	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
BH25D16AS	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
BH25Q20BW	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
BH25Q40GW	SOIC8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
BH25Q80DW	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
BH25Q16BS	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
BH25Q16DW	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
BH25Q32AS	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
BH25Q32BS	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
BH25Q32DW	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
BH25Q64BS	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	

BH25Q128AS	SOP8 / 208mil	SF-SOP8-200A	
H25S40	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
H25S80	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
H25S16	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
H25S32	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
H25S64	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
H25S128	SOP8 / 208mil	SF-SOP8-200A	
HF25QH64AE	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	TDFN8 / 5x6mm	SF-QFN8-6X5A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
HF25QH128AE	SOP8 / 208mil	SF-SOP8-200A	OTP
	TDFN8 / 5x6mm	SF-QFN8-6X5A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
HF25QW128AE	SOP8 / 208mil	SF-SOP8-200A	OTP
	TDFN8 / 5x6mm	SF-QFN8-6X5A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	

HuaHong ZealCore - I2C EEPROM

Device Model	Package Type	Adapter Module	Remark
HE24C02	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
HE24C04	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
HE24C08	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
HE24C16	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
HE24C32	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
HE24C64	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
HE24C128	DIP8		

	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
HE24C256	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
HE24C512	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
IK Semiconductor - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
IN24LC02B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
IN24LC04B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
IN24LC08B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
IN24LC16B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
Infineon - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
SLA24C01	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
SLA24C02	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
SLA24C04	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
SLA24C08	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
SLA24C16	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
SLA24C164	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
SLA24C32	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
SLA24C64	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
SLE24C01	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
SLE24C02	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
SLE24C04	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
SLE24C08	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
SLE24C16	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
SLE24C164	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
SLE24C32	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	

SLE24C64	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
InnoMem - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
IM25RWQ10	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
IM25RWQ20	SOP8 / 150mil	SF-SOP8-150A	OTP
	USON8 / 3x2mm	SF-QFN8-2X3A	
IM25RWQ40	SOP8 / 150mil	SF-SOP8-150A	OTP
	USON8 / 3x2mm	SF-QFN8-2X3A	
IM25RWQ80	SOP8 / 150mil	SF-SOP8-150A	OTP
	USON8 / 3x2mm	SF-QFN8-2X3A	
Intel - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
QB25F016S33B	SOP8 / 150mil	SF-SOP8-150A	
QB25F016S33T	SOP8 / 150mil	SF-SOP8-150A	
QB25F160S33B	SOP16 / 300mil	SF-SO16-300A	
QB25F160S33T	SOP16 / 300mil	SF-SO16-300A	
QB25F320S33B	SOP16 / 300mil	SF-SO16-300A	
QB25F320S33T	SOP16 / 300mil	SF-SO16-300A	
QB25F640S33B	SOP16 / 300mil	SF-SO16-300A	
QB25F640S33T	SOP16 / 300mil	SF-SO16-300A	
QH25F016S33B	SOP8 / 150mil	SF-SOP8-150A	
QH25F016S33T	SOP8 / 150mil	SF-SOP8-150A	
QH25F160S33B	SOP16 / 300mil	SF-SO16-300A	
QH25F160S33T	SOP16 / 300mil	SF-SO16-300A	
QH25F320S33B	SOP16 / 300mil	SF-SO16-300A	
QH25F640S33B	SOP16 / 300mil	SF-SO16-300A	
QH25F640S33T	SOP16 / 300mil	SF-SO16-300A	
ISSI - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
IS25CQ032	SOIC8 / 208mil	SF-SOP8-200A	
	---	ISP	
IS25LE128E	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
IS25LE256E	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
IS25LE512M	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
IS25LE01G	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
IS25LP025E	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
IS25LP512E	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
IS25LP010E	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	

	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
IS25LP020E	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
IS25LP040E	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
IS25LP080D	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	---	ISP	
IS25LP016D	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	---	ISP	
IS25LP032	SOIC8 / 208mil	SF-SOP8-200A	OTP
	VSOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
IS25LP032A	---	ISP	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
IS25LP032D	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
IS25LP064	SOIC8 / 208mil	SF-SOP8-200A	OTP
	VSOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
IS25LP064A	---	ISP	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
IS25LP064D	SOIC8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	

	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
IS25LP128	SOIC8 / 208mil	SF-SOP8-200A	OTP
	VSOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
IS25LP128F	SOIC8 / 208mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
IS25LP256D	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
IS25LP256E	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
IS25LP256H	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
IS25LP512M	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
IS25LP512MG	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
IS25LP01GG	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
IS25LQ025B	SOIC8 / 150mil	SF-SOP8-150A	
	VVSOP8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USO8 / 2x3mm	SF-QFN8-2X3A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
IS25LQ512A	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
IS25LQ512B	SOIC8 / 150mil	SF-SOP8-150A	
	VVSOP8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USO8 / 2x3mm	SF-QFN8-2X3A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
IS25LQ010A	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
IS25LQ010B	SOIC8 / 150mil	SF-SOP8-150A	
	VVSOP8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USO8 / 2x3mm	SF-QFN8-2X3A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
IS25LQ020A	SOIC8 / 150mil	SF-SOP8-150A	

	VVSOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
IS25LQ020B	SOIC8 / 150mil	SF-SOP8-150A	
	VVSOP8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
IS25LQ040B	SOIC8 / 150mil	SF-SOP8-150A	
	VVSOP8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
IS25LQ080	SOIC8 / 150mil	SF-SOP8-150A	
	VVSOP8 / 150mil	SF-SOP8-150A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
IS25LQ080B	SOIC8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
IS25LQ016B	SOIC8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
IS25LQ032B	SOIC8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
IS25WE128E	---	ISP	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
IS25WE256E	---	ISP	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
IS25WE512M	---	ISP	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
IS25WE01G	---	ISP	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
IS25WJ016F	---	ISP	OTP
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
IS25WJ032F	---	ISP	OTP
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
IS25WJ064F	---	ISP	OTP
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	USON8 / 4x3mm	SF-QFN8-4X3B	

	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
IS25WJ128F	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
IS25WP025E	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USO8 / 2x3mm	SF-QFN8-2X3A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
IS25WP512E	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USO8 / 2x3mm	SF-QFN8-2X3A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
IS25WP010E	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USO8 / 2x3mm	SF-QFN8-2X3A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
IS25WP020E	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USO8 / 2x3mm	SF-QFN8-2X3A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
IS25WP040E	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USO8 / 2x3mm	SF-QFN8-2X3A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
IS25WP020D	SOIC8 / 150mil	SF-SOP8-150A	
	USO8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
IS25WP040D	SOIC8 / 150mil	SF-SOP8-150A	
	USO8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
IS25WP080D	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	USO8 / 2x3mm	SF-QFN8-2X3A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
IS25WP016D	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	USO8 / 2x3mm	SF-QFN8-2X3A	
	USO8 / 4x3mm	SF-QFN8-4X3B	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	---	ISP	
IS25WP032D	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	USO8 / 4x3mm	SF-QFN8-4X3B	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
IS25WP064A	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	

	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
IS25WP064D	SOIC8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
IS25WP128F	SOIC8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
IS25WP256D	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
IS25WP256E	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
IS25WP256H	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
IS25WP512M	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
IS25WP512MG	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
IS25WP01GG	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
IS25WQ020	SOIC8 / 150mil	SF-SOP8-150A	
	VVSOP8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
IS25WQ040	SOIC8 / 150mil	SF-SOP8-150A	
	VVSOP8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
Pm25LQ512B	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
Pm25LQ010B	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
Pm25LQ020B	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
Pm25LQ040B	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
ISSI - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
IS24C01	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	

IS24C01B	MSOP8	SF-MSP8-3X3A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
IS24C01C	MSOP8	SF-MSP8-3X3A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
IS24C02	MSOP8	SF-MSP8-3X3A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
IS24C02A	MSOP8	SF-MSP8-3X3A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
IS24C02B	MSOP8	SF-MSP8-3X3A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
IS24C02C	MSOP8	SF-MSP8-3X3A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
IS24C02D	MSOP8	SF-MSP8-3X3A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
IS24C02E	MSOP8	SF-MSP8-3X3A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
IS24C04	MSOP8	SF-MSP8-3X3A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
IS24C04A	MSOP8	SF-MSP8-3X3A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
IS24C04B	MSOP8	SF-MSP8-3X3A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
IS24C08	MSOP8	SF-MSP8-3X3A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
IS24C08A	MSOP8	SF-MSP8-3X3A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
IS24C08B	MSOP8	SF-MSP8-3X3A	

	---	ISP	
IS24C16	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
IS24C16A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
IS24C16B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
IS24C32	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
IS24C32A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
IS24C32B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
IS24C32C	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
IS24C64	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
IS24C64A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
IS24C64B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
IS24C64C	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
IS24C128	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
IS24C128A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
IS24C256A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	

IS24C128B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
IS24C256	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
IS24C256B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
JUYANG - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
JY25VQ64A	SOP8 / 200mil	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
KHIC - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
KH25L512	SOP8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
KH25L512E	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
KH25L5121E	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
KH25L1005	SOP8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
KH25L1006E	SOP8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
KH25L1021E	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
KH25L2005	SOP8 / 150mil	SF-SOP8-150A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25L2006E	SOP8 / 150mil	SF-SOP8-150A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25L2026E	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
KH25L4005A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25L4006E	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25L4026E	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
KH25L8005	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25L8006E	DIP8		OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25L8008E	SOP8 / 200mil	SF-SOP8-200A	

	---	ISP	
KH25L8035E	SOP8 / 200mil	SF-SOP8-200A	OTP
	---	ISP	
KH25L8073E	SOP8 / 200mil	SF-SOP8-200A	OTP
	---	ISP	
KH25L1605A	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
KH25L1605D	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
KH25L1606E	DIP8		OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
KH25L1633E	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25L1635D	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
KH25L1673E	SOP8 / 200mil	SF-SOP8-200A	OTP
	---	ISP	
KH25L1691E	SOP8 / 200mil	SF-SOP8-200A	OTP
	---	ISP	
KH25L3205D	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
KH25L3206E	DIP8		OTP
	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
KH25L3208E	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25L3233F	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
KH25L3235E	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
KH25L3236F	SOP8 / 200mil	SF-SOP8-200A	OTP
	---	ISP	
KH25L3239E	SOP8 / 200mil	SF-SOP8-200A	OTP
	VSOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25L3255E	SOP8 / 200mil	SF-SOP8-200A	OTP
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
KH25L3273E	SOP8 / 200mil	SF-SOP8-200A	OTP
	VSOP8 / 200mil	SF-SOP8-200A	
	---	ISP	
KH25L3291E	SOP8 / 200mil	SF-SOP8-200A	OTP
	---	ISP	
KH25L3296F	SOP8 / 200mil	SF-SOP8-200A	OTP
	---	ISP	

KH25L32356	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25L6405D	WSON8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
KH25L6406E	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
KH25L6408E	SOP8 / 200mil	SF-SOP8-200A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
KH25L6433F	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
KH25L6435E	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
KH25L6436F	SOP8 / 200mil	SF-SOP8-200A	OTP
	---	ISP	
KH25L6439E	SOP8 / 200mil	SF-SOP8-200A	OTP
	VSOP8 / 200mil	SF-SOP8-200A	
	---	ISP	
KH25L6455E	WSON8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
KH25L6455F	WSON8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
KH25L6473E	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25L64356	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
KH25L12833F	SOP8 / 200mil	SF-SOP8-200A	OTP
	---	ISP	
KH25L12835F	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
KH25L12845E	WSON8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
KH25L12845G	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
KH25L12873F	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
KH25L25635F	WSON8 / 6x5mm	SF-QFN8-6X5A	OTP
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	

	---	ISP	
KH25L25645G	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
KH25U5121E	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
KH25U4033E	SOP8 / 150mil	SF-SOP8-150A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25U8033E	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25U8035E	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25U1639E	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25U3239E	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25U6439F	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25U6473F	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25U12832F	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
KH25U12839F	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25U25645G	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
KH25V4035F	SOP8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
KH25V40066	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
KH25V80066	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
KH25V8035F	SOP8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
KH25V1635F	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25V16066	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	---	ISP	
Kodenshi - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark

KK24C02B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
KK24C04	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
KK24C04B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
KK24C08	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
KK24C08B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
KK24C16	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
KK24C16B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	

LinkSmart - I2C EEPROM

Device Model	Package Type	Adapter Module	Remark
L24C02	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
L24C04	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
L24M04	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
L24M08	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
L24W02	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
L24W04	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
L24W08	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
L24W16	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
L24W32	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
L24W64	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	

Litao - I2C EEPROM

Device Model	Package Type	Adapter Module	Remark
LT24C01	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
LT24C02	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
LT24C04	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
LT24C08	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
LT24C16	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	

Lize - I2C EEPROM

Device Model	Package Type	Adapter Module	Remark
L24C02	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
L24C04	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
L24C08	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
L24C16	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
LRC - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
LR25D40S	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
LR25D80S	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
LR25D16S	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
LR25Q32S	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
LR25Q64S	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
LR25Q128S	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
Lyontek - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
LY24C02	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
LY24C04	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
LY24C08	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
LY24C16	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
Macronix(MXIC) - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
KH25L512	SOP8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
KH25L512E	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
KH25L5121E	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
KH25L1005	SOP8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
KH25L1006E	SOP8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
KH25L1021E	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
KH25L2005	SOP8 / 150mil	SF-SOP8-150A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25L2006E	SOP8 / 150mil	SF-SOP8-150A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	

KH25L2026E	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
KH25L4005A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25L4006E	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25L4026E	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
KH25L8005	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25L8006E	DIP8		OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25L8008E	SOP8 / 200mil	SF-SOP8-200A	
	---	ISP	
KH25L8035E	SOP8 / 200mil	SF-SOP8-200A	OTP
	---	ISP	
KH25L8073E	SOP8 / 200mil	SF-SOP8-200A	OTP
	---	ISP	
KH25L1605A	SOP8 / 200mil	SF-SOP8-200A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
KH25L1605D	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
KH25L1606E	DIP8		OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
KH25L1633E	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25L1635D	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
KH25L1673E	SOP8 / 200mil	SF-SOP8-200A	OTP
	---	ISP	
KH25L1691E	SOP8 / 200mil	SF-SOP8-200A	OTP
	---	ISP	
KH25L3205D	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
KH25L3206E	DIP8		OTP
	SOP8 / 200mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
KH25L3208E	SOP8 / 200mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25L3233F	SOP8 / 150mil	SF-SOP8-150A	OTP

	SOP8 / 200mil	SF-SOP8-200A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SQ16-300A	
	---	ISP	
KH25L3235E	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SQ16-300A	
	---	ISP	
KH25L3236F	SOP8 / 200mil	SF-SOP8-200A	OTP
	---	ISP	
KH25L3239E	SOP8 / 200mil	SF-SOP8-200A	OTP
	VSOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25L3255E	SOP8 / 200mil	SF-SOP8-200A	OTP
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
KH25L3273E	SOP8 / 200mil	SF-SOP8-200A	OTP
	VSOP8 / 200mil	SF-SOP8-200A	
	---	ISP	
KH25L3291E	SOP8 / 200mil	SF-SOP8-200A	OTP
	---	ISP	
KH25L3296F	SOP8 / 200mil	SF-SOP8-200A	OTP
	---	ISP	
KH25L32356	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25L32366	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25L6405D	WSON8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SQ16-300A	
	---	ISP	
KH25L6406E	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SQ16-300A	
	---	ISP	
KH25L6408E	SOP8 / 200mil	SF-SOP8-200A	
	SOP16 / 300mil	SF-SQ16-300A	
	---	ISP	
KH25L6433F	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SQ16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
KH25L6435E	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SQ16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
KH25L6436F	SOP8 / 200mil	SF-SOP8-200A	OTP
	---	ISP	
KH25L6439E	SOP8 / 200mil	SF-SOP8-200A	OTP
	VSOP8 / 200mil	SF-SOP8-200A	
	---	ISP	
KH25L6455E	WSON8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SQ16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
KH25L6455F	WSON8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SQ16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
KH25L6473E	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	

KH25L64356	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
KH25L64366	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25L12833F	SOP8 / 200mil	SF-SOP8-200A	OTP
	---	ISP	
KH25L12835F	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
KH25L12845E	WSON8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
KH25L12845G	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
KH25L12872F	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25L12873F	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
KH25L128356	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
KH25L25635F	WSON8 / 6x5mm	SF-QFN8-6X5A	OTP
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
KH25L25645G	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
KH25U5121E	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
KH25U4033E	SOP8 / 150mil	SF-SOP8-150A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25U8033E	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25U8035E	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25U1639E	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25U3239E	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25U6439F	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25U6473F	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	

	---	ISP	
KH25U12832F	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SQ16-300A	
	---	ISP	
KH25U12839F	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25U25645G	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SQ16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
KH25V4035F	SOP8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
KH25V40066	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
KH25V80066	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
KH25V8035F	SOP8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
KH25V1635F	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
KH25V16066	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	---	ISP	
MX25L512	SOP8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
MX25L512C	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
MX25L512E	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
MX25L5121E	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
MX25L1005	SOP8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
MX25L1005A	SOP8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
MX25L1005C	SOP8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
MX25L1006E	SOP8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
MX25L1006F	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
MX25L1021E	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
MX25L1025C	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	

MX25L1026E	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
MX25L2005	SOP8 / 150mil	SF-SOP8-150A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
MX25L2005C	SOP8 / 150mil	SF-SOP8-150A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
MX25L2006E	SOP8 / 150mil	SF-SOP8-150A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
MX25L2025C	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
MX25L2026C	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
MX25L2026E	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
MX25L4005A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
MX25L4005C	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
MX25L4006E	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
MX25L4025C	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
MX25L4026E	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
MX25L8005	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
MX25L8006E	DIP8		OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
MX25L8008E	SOP8 / 200mil	SF-SOP8-200A	
	---	ISP	
MX25L8035E	SOP8 / 200mil	SF-SOP8-200A	OTP
	---	ISP	
MX25L8036E	SOP8 / 200mil	SF-SOP8-200A	OTP
	---	ISP	
MX25L8073E	SOP8 / 200mil	SF-SOP8-200A	OTP
	---	ISP	
MX25L8075E	SOP8 / 200mil	SF-SOP8-200A	OTP
	---	ISP	
MX25L1605A	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SQ16-300A	
	---	ISP	
MX25L1605D	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SQ16-300A	
	---	ISP	
MX25L1606E	DIP8		OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SQ16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	

	---	ISP	
MX25L1608D	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25L1608E	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	---	ISP	
MX25L1633E	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
MX25L1635D	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25L1635E	SOP8 / 200mil	SF-SOP8-200A	OTP
	---	ISP	
MX25L1636D	SOP8 / 200mil	SF-SOP8-200A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25L1636E	SOP8 / 200mil	SF-SOP8-200A	OTP
	---	ISP	
MX25L1655D	SOP8 / 200mil	SF-SOP8-200A	OTP
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
MX25L1673E	SOP8 / 200mil	SF-SOP8-200A	OTP
	---	ISP	
MX25L1675E	SOP8 / 200mil	SF-SOP8-200A	OTP
	---	ISP	
MX25L3205D	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25L3206E	DIP8		OTP
	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
MX25L3208D	DIP8		
	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25L3208E	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
MX25L3225D	SOP8 / 200mil	SF-SOP8-200A	OTP
	---	ISP	
MX25L3233F	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25L3235D	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25L3235E	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25L3236D	SOP8 / 200mil	SF-SOP8-200A	OTP
	---	ISP	
MX25L3236F	SOP8 / 200mil	SF-SOP8-200A	OTP
	---	ISP	
MX25L3239E	SOP8 / 200mil	SF-SOP8-200A	OTP

	VSOP8 / 200mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
MX25L3255D	SOP8 / 200mil	SF-SOP8-200A	OTP
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
MX25L3255E	SOP8 / 200mil	SF-SOP8-200A	OTP
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
MX25L3273E	SOP8 / 200mil	SF-SOP8-200A	OTP
	VSOP8 / 200mil	SF-SOP8-200A	
	---	ISP	
MX25L3273F	SOP8 / 200mil	SF-SOP8-200A	OTP
	---	ISP	
MX25L3275E	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25L32356	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	USO8 / 4x3mm	SF-QFN8-4X3B	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
MX25L32366	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
MX25L6406E	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25L6408D	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25L6408E	SOP8 / 200mil	SF-SOP8-200A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25L6433F	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
MX25L6435E	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
MX25L6436E	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25L6436F	SOP8 / 200mil	SF-SOP8-200A	OTP
	---	ISP	
MX25L6439E	SOP8 / 200mil	SF-SOP8-200A	OTP
	VSOP8 / 200mil	SF-SOP8-200A	
	---	ISP	
MX25L6445E	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25L6465E	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25L6473E	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
MX25L6473F	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25L6475E	SOP8 / 200mil	SF-SOP8-200A	OTP

	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25L64356	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25L64736	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
MX25L12833F	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25L12835F	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25L12845E	WSO8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25L12845G	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
MX25L12855E	SOP16 / 300mil	SF-SO16-300A	OTP
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
MX25L12855F	SOP16 / 300mil	SF-SO16-300A	OTP
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
MX25L12865F	SOP16 / 300mil	SF-SO16-300A	OTP
	---	ISP	
MX25L12872F	SOP8 / 200mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
MX25L12873F	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25L12875F	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25L128356	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25L128736	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25L25633F	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25L25635E	WSO8 / 6x5mm	SF-QFN8-6X5A	OTP
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25L25635F	WSO8 / 6x5mm	SF-QFN8-6X5A	OTP

	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25L25645G	SOP8 / 200mil	SF-SOP8-200A	OTP
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
MX25L25655E	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
MX25L25672F	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25L25673G	SOP8 / 200mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25L25733F	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25L25735E	WSO8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25L25735F	WSO8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25L25745G	WSO8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25L25773G	WSO8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25L51237G	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25L51243G	WSO8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
MX25L51243J	WSO8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
MX25L51245G	WSO8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
MX25L51245J	WSO8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
MX25L51265G	WSO8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
MX25L51273G	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25R512F	SOP8 / 150mil	SF-SOP8-150A	OTP
	USO8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
MX25R1035F	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	USO8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
MX25R2035F	SOP8 / 150mil	SF-SOP8-150A	OTP
	USO8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
MX25R4035F	SOP8 / 150mil	SF-SOP8-150A	OTP

MX25R8035F	USON8 / 2x3mm	SF-QFN8-2X3A	OTP
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
MX25R1635F	---	ISP	OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
MX25R3235F	SOP8 / 200mil	SF-SOP8-200A	OTP
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
	SOP8 / 200mil	SF-SOP8-200A	
MX25R6435F	WSO8 / 6x5mm	SF-QFN8-6X5A	OTP
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
MX25U5121E	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
MX25U1001E	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
MX25U2032E	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	VSOP8 / 150mil	SF-SOP8-150A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
MX25U2033E	SOP8 / 150mil	SF-SOP8-150A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	VSOP8 / 150mil	SF-SOP8-150A	
MX25U4032E	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	VSOP8 / 150mil	SF-SOP8-150A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
MX25U4033E	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
MX25U4035	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
MX25U4035F	SOP8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	VSOP8 / 150mil	SF-SOP8-150A	
MX25U8032E	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	VSOP8 / 150mil	SF-SOP8-150A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
MX25U8033E	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
MX25U8035	SOP8 / 150mil	SF-SOP8-150A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	VSOP8 / 150mil	SF-SOP8-150A	
MX25U8035E	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
MX25U8035F	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
MX25U1632F	SOP8 / 200mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
MX25U1633F	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	

MX25U1635E	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
MX25U1635F	SOP8 / 200mil	SF-SOP8-200A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
MX25U16356	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
MX25U3232F	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
MX25U3235E	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
MX25U3235F	SOP8 / 200mil	SF-SOP8-200A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
MX25U32356	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
MX25U6432F	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
MX25U6433F	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
	---	ISP	
MX25U6435E	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
MX25U6435F	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
MX25U6472F	SOP8 / 200mil	SF-SOP8-200A	
	---	ISP	
MX25U6473F	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
MX25U64736	SOP8 / 200mil	SF-SOP8-200A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
MX25U12832F	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25U12835F	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25U12843G	SOP8 / 200mil	SF-SOP8-200A	
	---	ISP	
MX25U12845G	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
MX25U12872F	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
MX25U12873F	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	

MX25U12892F	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
MX25U25635F	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
MX25U25641G	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
MX25U25643G	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
MX25U25645G	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
MX25U25671G	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
MX25U25672G	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
MX25U25673G	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
MX25U25691G	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
MX25U51241G	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
MX25U51245G	WSON8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
MX25U51271G	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
MX25U51279G	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
MX25U51293G	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
MX25UR51245G	SOP16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
MX25V512F	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
MX25V5126F	SOP8 / 150mil	SF-SOP8-150A	

	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
MX25V1006F	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
MX25V1035F	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
MX25V2006E	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
MX25V2033F	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
MX25V2035F	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
MX25V4006E	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
MX25V4035F	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
MX25V8006E	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
MX25V8033F	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
MX25V8035F	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
MX25V1606F	SOP8 / 200mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
MX25V1635F	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
MX25V6433F	USON8 / 2x3mm	SF-QFN8-2X3A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
MX25V20066	---	ISP	
	SOP8 / 200mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
MX25V40066	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
MX25V80066	SOP8 / 200mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
MX25V16066	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	

	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
MX66L51235F	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
MX66L1G43J	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
MX66L1G45G	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
MX66L1G45J	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
MX66L1G55G	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
MX66L1G65G	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
MX66U51235F	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
MX66U1G45G	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
MX66U1G93G	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
MX77L6450F	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
MX77L12850F	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
MX77L25650F	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
MX77L25655G	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
MX77L51255G	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
MX77U12851F	SOP8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
MX77U25650F	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
MX77U25655F	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
MX77U25655G	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
MX77U51250F	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
MX77U51255F	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
MX77U51255G	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
MX77U1G55G	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	

Maxcom - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
MAX24A02	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
MAX24A04	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
MAX24A08	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
MAX24A16	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
Maxcom - Microwire EEPROM			
Device Model	Package Type	Adapter Module	Remark
MAX93LC46	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
MengXW - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
ME25L10D	SOP8 / 150mil	SF-SOP8-150A	
ME25L40E	SOP8 / 150mil	SF-SOP8-150A	
ME25L80E	SOP8 / 150mil	SF-SOP8-150A	
ME25L16E	SOP8 / 150mil	SF-SOP8-150A	
ME25L32E	SOP8 / 150mil	SF-SOP8-150A	
ME25L64E	SOP8 / 208mil	SF-SOP8-200A	
ME25L128C	SOP8 / 208mil	SF-SOP8-200A	
Microchip - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
SST25LF020A	SOIC8 / 150mil	SF-SOP8-150A	
	WSO8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
SST25LF040A	SOIC8 / 200mil	SF-SOP8-200A	
	WSO8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
SST25LF080A	SOIC8 / 200mil	SF-SOP8-200A	
	---	ISP	
SST25VF512	SOIC8 / 150mil	SF-SOP8-150A	
	WSO8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
SST25VF512A	SOIC8 / 150mil	SF-SOP8-150A	
	WSO8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
SST25VF010	SOIC8 / 150mil	SF-SOP8-150A	
	WSO8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
SST25VF010A	SOIC8 / 150mil	SF-SOP8-150A	
	WSO8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
SST25VF020	SOIC8 / 150mil	SF-SOP8-150A	
	WSO8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
SST25VF020B	SOIC8 / 150mil	SF-SOP8-150A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
SST25VF040	SOIC8 / 200mil	SF-SOP8-200A	
	WSO8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
SST25VF040B	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 200mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
SST25VF080	SOIC8 / 200mil	SF-SOP8-200A	
	---	ISP	
SST25VF080B	DIP8		
	SOIC8 / 200mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
SST25VF016B	SOIC8 / 200mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	

	---	ISP	
SST25VF032B	SOIC8 / 200mil	SF-SOP8-200A	
	WSON8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
SST25VF064C	SOIC8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x8mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
SST25WF512	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
SST25WF010	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
SST25WF020	SOIC8 / 150mil	SF-SOP8-150A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
SST25WF020A	SOIC8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
SST25WF040	SOIC8 / 150mil	SF-SOP8-150A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
SST25WF040B	SOIC8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
SST25WF080	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
SST25WF080B	SOIC8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
SST26VF016	SOIC8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
SST26VF016B	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 200mil	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
SST26VF032	SOIC8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
SST26VF032B	SOIC8 / 200mil	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
SST26VF064B	SOIC8 / 200mil	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	SOIC16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
SST26WF016B	SOIC8 / 150mil	SF-SOP8-150A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
SST26WF032	SOIC8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
SST26WF064C	SOIC8 / 200mil	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	SOIC16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
Microchip - SPI EEPROM			
Device Model	Package Type	Adapter Module	Remark
25AA010A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-6	SF-SOT23-6A	
	---	ISP	
25AA020A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	

	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-6	SF-SOT23-6A	
	---	ISP	
25AA040	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
25AA040A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-6	SF-SOT23-6A	
	---	ISP	
25AA080	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
25AA080A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
25AA080B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
25AA080C	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
25AA080D	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
25AA160	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
25AA160A	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
25AA160B	MSOP8	SF-MSP8-3X3A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
25AA160C	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
25AA160D	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
25AA320	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	

	---	ISP	
25AA320A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
25AA640	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
25AA640A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
25AA128	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
25AA256	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
25AA512	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
25AA1024	DIP8		
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
25C040	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
25C040A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
25C080	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
25C160	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
25C320	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
25C640	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
25LC010A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-6	SF-SOT23-6A	
	---	ISP	
25LC020A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	

	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-6	SF-SOT23-6A	
	---	ISP	
25LC040	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
25LC040A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-6	SF-SOT23-6A	
25LC080	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
25LC080A	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
25LC080B	MSOP8	SF-MSP8-3X3A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
25LC080C	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
	DIP8		
25LC080D	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
25LC160	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
25LC160A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
25LC160B	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
25LC160C	MSOP8	SF-MSP8-3X3A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
25LC160D	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
	DIP8		
25LC320	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
	DIP8		
25LC320A	DIP8		

	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
25LC640	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
25LC640A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
25LC128	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
25LC256	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
25LC512	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
25LC1024	DIP8		
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
Microchip - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
24AA00	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
24AA01	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
24AA014	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-6	SF-SOT23-6A	
24AA014H	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
24AA01H	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	

	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
24AA02	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
24AA024	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-6	SF-SOT23-6A	
	---	ISP	
24AA024H	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
24AA025	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-6	SF-SOT23-6A	
24AA025E48	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-6	SF-SOT23-6A	
24AA02H	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
24AA04	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
24AA04H	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
24AA08	SOT23-5	SF-SOT23-6A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	

24AA08H	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
24AA16	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
24AA16H	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
24AA32A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
24AA32AF	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
24AA64	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
24AA64F	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
24AA65	DIP8		
	SOIC8 / 208mil	SF-SOP8-200A	
	---	ISP	
24AA128	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
24AA256	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
24AA256	---	ISP	

24AA512	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
24AA1025	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	---	ISP	
24AA1026	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	---	ISP	
24FC128	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
24FC256	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	SOT23-5	SF-SOT23-6A	
24FC512	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	SOT23-5	SF-SOT23-6A	
24FC1025	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	---	ISP	
24FC1026	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	---	ISP	
24LC00	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
24LC014	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-6	SF-SOT23-6A	
	---	ISP	
24LC014H	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
24LC01B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	

	SOT23-5	SF-SOT23-6A	
	---	ISP	
24LC01BH	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
24LC024	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-6	SF-SOT23-6A	
24LC024H	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
24LC025	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-6	SF-SOT23-6A	
24LC02B	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
24LC02BH	SOT23-5	SF-SOT23-6A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
24LC04B	SOT23-5	SF-SOT23-6A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
24LC04BH	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
24LC08B	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
24LC08BH	MSOP8	SF-MSP8-3X3A	
	SOIC8 / 150mil	SF-SOP8-150A	

	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
24LC16B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
24LC16BH	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
24LC21	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
24LC22A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
24LC32A	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
24LC32AF	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
24LC64	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
24LC64F	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
	DIP8		
24LC65	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
	DIP8		
24LC128	SOIC8 / 208mil	SF-SOP8-200A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
24LC256	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	

	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
24LC512	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
24LC1025	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	---	ISP	
24LC1026	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	---	ISP	
24LCS21	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
24LCS21A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
24LCS22A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
34AA02	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
34AA04	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
34LC02	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	

Microchip - Microwire EEPROM

Device Model	Package Type	Adapter Module	Remark
93AA46	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
93AA46A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-6	SF-SOT23-6A	
	---	ISP	
93AA46B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-6	SF-SOT23-6A	
	---	ISP	
93AA46C	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
93AA46X	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	

93AA46AX	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
93AA46BX	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
93AA46CX	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
93LC46	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
93LC46A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-6	SF-SOT23-6A	
	---	ISP	
93LC46B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-6	SF-SOT23-6A	
	---	ISP	
93LC46C	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
93LC46X	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
93LC46AX	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
93LC46BX	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
93LC46CX	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
93AA56	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
93AA56A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-6	SF-SOT23-6A	
	---	ISP	
93AA56B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-6	SF-SOT23-6A	
	---	ISP	
93AA56C	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
93AA56X	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
93AA56AX	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
93AA56BX	SOIC8 / 150mil	SF-SOP8-150A	

	---	ISP	
93AA56CX	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
93LC56	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
93LC56A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-6	SF-SOT23-6A	
	---	ISP	
93LC56B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-6	SF-SOT23-6A	
	---	ISP	
93LC56C	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
93LC56X	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
93LC56AX	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
93LC56BX	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
93LC56CX	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
93AA66	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
93AA66A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-6	SF-SOT23-6A	
	---	ISP	
93AA66B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-6	SF-SOT23-6A	
	---	ISP	
93AA66C	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
93AA66X	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
93AA66AX	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
93AA66BX	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
93AA66CX	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	

93LC66	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
93LC66A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-6	SF-SOT23-6A	
	---	ISP	
93LC66B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-6	SF-SOT23-6A	
	---	ISP	
93LC66C	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
93LC66X	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
93LC66AX	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
93LC66BX	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
93LC66CX	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
93AA76	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
93AA76A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	SOT23-6	SF-SOT23-6A	
93AA76B	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
93AA76C	SOT23-6	SF-SOT23-6A	
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
93LC76	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
	DIP8		
93LC76A	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
93LC76B	SOT23-6	SF-SOT23-6A	
	---	ISP	
	DIP8		
93LC76	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	SOT23-6	SF-SOT23-6A	
	---	ISP	

93LC76C	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
93AA86	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
93AA86A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	SOT23-6	SF-SOT23-6A	
	---	ISP	
93AA86B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	SOT23-6	SF-SOT23-6A	
	---	ISP	
93AA86C	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
93LC86	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
93LC86A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	SOT23-6	SF-SOT23-6A	
	---	ISP	
93LC86B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	SOT23-6	SF-SOT23-6A	
	---	ISP	
93LC86C	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	

Micron - SPI Flash

Device Model	Package Type	Adapter Module	Remark
M25P05	SO8 / 150mil	SF-SOP8-150A	
M25P05-A	SO8 / 150mil	SF-SOP8-150A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M25P10	SO8 / 150mil	SF-SOP8-150A	
M25P10-A	SO8 / 150mil	SF-SOP8-150A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M25P20	SO8 / 150mil	SF-SOP8-150A	
M25P40	SO8 / 150mil	SF-SOP8-150A	
M25P80	SO8W	SF-SOP8-200A	
M25P16	SO8N	SF-SOP8-150A	
	SO8W	SF-SOP8-200A	
	MLP8 / 8x6mm	SF-QFN8-8X6A	
	SO16 / 300mil	SF-SO16-300A	
M25P32	SO8N	SF-SOP8-150A	
	SO8W	SF-SOP8-200A	
	MLP8 / 8x6mm	SF-QFN8-8X6A	
	SO16 / 300mil	SF-SO16-300A	
M25P64	SO8W	SF-SOP8-200A	

M25P128	MLP8 / 8x6mm	SF-QFN8-8X6A	
	SO16 / 300mil	SF-SO16-300A	
	SO8W	SF-SOP8-200A	
	MLP8 / 8x6mm	SF-QFN8-8X6A	
	SO16 / 300mil	SF-SO16-300A	
M25PE10(T7X)	SO8N	SF-SOP8-150A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M25PE20(T7X)	SO8N	SF-SOP8-150A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M25PE40(T7X)	SO8N	SF-SOP8-150A	
	SO8W	SF-SOP8-200A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M25PE80(T7X)	SO8N	SF-SOP8-150A	
	SO8W	SF-SOP8-200A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M25PE10(T9HX)	SO8N	SF-SOP8-150A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M25PE20(T9HX)	SO8N	SF-SOP8-150A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M25PE40(T9HX)	SO8N	SF-SOP8-150A	
	SO8W	SF-SOP8-200A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M25PE80(T9HX)	SO8N	SF-SOP8-150A	
	SO8W	SF-SOP8-200A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M25PE16	SO8N	SF-SOP8-150A	
	SO8W	SF-SOP8-200A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M25PX80	SO8N	SF-SOP8-150A	
	SO8W	SF-SOP8-200A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M25PX16	SO8N	SF-SOP8-150A	
	SO8W	SF-SOP8-200A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M25PX32	SO8W	SF-SOP8-200A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
	SO16W / 300mil	SF-SO16-300A	
M25PX64	SO8W	SF-SOP8-200A	
	MLP8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
MT25QL128ABA	SO8W	SF-SOP8-200A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
	MLP8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
MT25QL128ABB	SO8W	SF-SOP8-200A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
	MLP8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
MT25QL256ABA	MLP8 / 6x5mm	SF-QFN8-6X5A	
	MLP8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
MT25QL512ABA	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
MT25QL512ABB	SO8W	SF-SOP8-200A	
	MLP8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
MT25QL01GBBB	MLP8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
MT25QU128ABA	SO8W	SF-SOP8-200A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
	MLP8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	

	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
MT25QU256ABA	MLP8 / 6x5mm	SF-QFN8-6X5A	
	MLP8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
MT25QU512ABB	MLP8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
MT25QU01GBBB	MLP8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q032A11E	SO8W	SF-SOP8-200A	
	DFN8 / 4x3mm	SF-QFN8-4X3B	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q032A21E	SO8W	SF-SOP8-200A	
	DFN8 / 4x3mm	SF-QFN8-4X3B	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q032A31E	SO8W	SF-SOP8-200A	
	DFN8 / 4x3mm	SF-QFN8-4X3B	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q032A41E	SO8W	SF-SOP8-200A	
	DFN8 / 4x3mm	SF-QFN8-4X3B	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q032A13E	SO8N	SF-SOP8-150A	
	SO8W	SF-SOP8-200A	
	DFN8 / 4x3mm	SF-QFN8-4X3B	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q032A23E	SO8N	SF-SOP8-150A	
	SO8W	SF-SOP8-200A	
	DFN8 / 4x3mm	SF-QFN8-4X3B	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
N25Q032A33E	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	SO8N	SF-SOP8-150A	
	SO8W	SF-SOP8-200A	
	DFN8 / 4x3mm	SF-QFN8-4X3B	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
N25Q032A43E	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	SO8N	SF-SOP8-150A	
	SO8W	SF-SOP8-200A	
	DFN8 / 4x3mm	SF-QFN8-4X3B	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
N25Q064A11E	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	SO8W	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
N25Q064A21E	SO8W	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	

N25Q064A31E	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	SO8W	SF-SOP8-200A	
N25Q064A41E	DFN8 / 6x5mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	SO8W	SF-SOP8-200A	
N25Q064A13E	DFN8 / 6x5mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	SO8W	SF-SOP8-200A	
N25Q064A23E	DFN8 / 6x5mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	SO8W	SF-SOP8-200A	
N25Q064A33E	DFN8 / 6x5mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	SO8W	SF-SOP8-200A	
N25Q064A43E	DFN8 / 6x5mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	SO8W	SF-SOP8-200A	
N25Q128A11E	DFN8 / 6x5mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	SO8W	SF-SOP8-200A	
N25Q128A21E	DFN8 / 6x5mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	SO8W	SF-SOP8-200A	
N25Q128A31E	DFN8 / 6x5mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	SO8W	SF-SOP8-200A	
N25Q128A41E	DFN8 / 6x5mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	SO8W	SF-SOP8-200A	
N25Q128A13E	DFN8 / 6x5mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q128A23E	DFN8 / 6x5mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q128A33E	DFN8 / 6x5mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	

N25Q128A43E	SO8W	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q256A11E	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q256A21E	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q256A31E	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q256A41E	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q256A71E	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q256A81E	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q256A13E	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q256A23E	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q256A33E	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q256A43E	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q256A73E	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q256A83E	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q512A11G	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q512A21G	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q512A31G	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q512A41G	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q512A71G	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q512A81G	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q512A13G	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q512A23G	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q512A33G	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q512A43G	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	

N25Q512A73G	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q512A83G	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q00AA13G	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q00AA23G	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q00AA33G	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q00AA43G	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q00AA73G	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25W032A11E	SO8W	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
N25W064A11E	SO8W	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
N25W128A11E	SO8W	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	

MSHINE Technology - SPI Flash

Device Model	Package Type	Adapter Module	Remark
MS25X512	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
MS25X10	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
MS25X20	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
MS25X40	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 209mil	SF-SOP8-200A	
MS25X80	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 209mil	SF-SOP8-200A	
MS25X16	DIP8		
	SOP8 / 209mil	SF-SOP8-200A	
	SOP16 / 300mil	SF-SO16-300A	

My-MS - I2C EEPROM

Device Model	Package Type	Adapter Module	Remark
MM24C01-3	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
MM24C02-3	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
MM24C04-3	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
MM24C08-2/3	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
MM24C16-2/3	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
MM24C32-2/3	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
MM24C64-2/3	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	

My-MS - Microwire EEPROM

Device Model	Package Type	Adapter Module	Remark
MM93C46-3	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
MM93C46-3G	SOIC8 / 150mil	SF-SOP8-150A	
MM93C46-3GR	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
MM93C56-3	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
MM93C56-3G	SOIC8 / 150mil	SF-SOP8-150A	
MM93C56-3GR	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
MM93C66-3	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
MM93C66-3G	SOIC8 / 150mil	SF-SOP8-150A	
MM93C66-3GR	SOIC8 / 150mil	SF-SOP8-150A	
MySON - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
MTV24C08	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
MTV24LC08	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
MTV24C16	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
MTV24LC16	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
Nantronics - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
N25S10	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
N25S20	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
N25S40	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
N25S80	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
N25S16	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
NeuMem - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
NM25Q16A	DIP8		OTP
	SOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
NM25Q32A	DIP8		OTP
	SOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
NM25Q64A	DIP8		OTP
	SOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	

NM25Q128A	DIP8		OTP
	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
NEXFLASH - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
NX25P10	SOIC8 / 150mil	SF-SOP8-150A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
NX25P20	SOIC8 / 150mil	SF-SOP8-150A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
NX25P40	SOIC8 / 150mil	SF-SOP8-150A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
NX25P80	SOIC8 / 200mil	SF-SOP8-200A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
NX25P16	SOIC8 / 200mil	SF-SOP8-200A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
	SOIC16 / 300mil	SF-SO16-300A	
NX25P32	SOIC8 / 200mil	SF-SOP8-200A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
	SOIC16 / 300mil	SF-SO16-300A	
National Semiconductor (NS) - SPI EEPROM			
Device Model	Package Type	Adapter Module	Remark
FM25C020U	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FM25C020UL	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FM25C040U	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FM25C040UL	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FM25C160U	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FM25C160UL	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FM25C320U	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
FM25C320UL	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM25C020	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM25C04	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM25C040	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM25C041	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM25C160	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM25C640	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
National Semiconductor (NS) - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
NM24C02	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	

NM24C03	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM24C04	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM24C05	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM24C08	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM24C09	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM24C16	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM24C17	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM24C32	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM24C65	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	

National Semiconductor (NS) - Microwire EEPROM

Device Model	Package Type	Adapter Module	Remark
NM93C46	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM93C46A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM93C46AL	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM93C46L	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM93C46LZ	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM93C46T	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM93C56	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM93C56A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM93C56AL	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM93C56L	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM93C56LZ	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM93C56T	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM93C66	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM93C66A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	

NM93C66AL	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM93C66L	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM93C66LZ	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM93C66T	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM93C86A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
NM93C86AL	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	

Numonyx - SPI Flash

Device Model	Package Type	Adapter Module	Remark
M25P05	SO8 / 150mil	SF-SOP8-150A	
M25P05-A	SO8 / 150mil	SF-SOP8-150A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M25P10	SO8 / 150mil	SF-SOP8-150A	
M25P10-A	SO8 / 150mil	SF-SOP8-150A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M25P20	SO8 / 150mil	SF-SOP8-150A	
M25P40	SO8 / 150mil	SF-SOP8-150A	
M25P80	SO8W	SF-SOP8-200A	
M25P16	SO8N	SF-SOP8-150A	
	SO8W	SF-SOP8-200A	
	MLP8 / 8x6mm	SF-QFN8-8X6A	
	SO16 / 300mil	SF-SO16-300A	
M25P32	SO8N	SF-SOP8-150A	
	SO8W	SF-SOP8-200A	
	MLP8 / 8x6mm	SF-QFN8-8X6A	
	SO16 / 300mil	SF-SO16-300A	
M25P64	SO8W	SF-SOP8-200A	
	MLP8 / 8x6mm	SF-QFN8-8X6A	
	SO16 / 300mil	SF-SO16-300A	
M25P128	SO8W	SF-SOP8-200A	
	MLP8 / 8x6mm	SF-QFN8-8X6A	
	SO16 / 300mil	SF-SO16-300A	
M25PE10(T7X)	SO8N	SF-SOP8-150A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M25PE20(T7X)	SO8N	SF-SOP8-150A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M25PE40(T7X)	SO8N	SF-SOP8-150A	
	SO8W	SF-SOP8-200A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M25PE80(T7X)	SO8N	SF-SOP8-150A	
	SO8W	SF-SOP8-200A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M25PE10(T9HX)	SO8N	SF-SOP8-150A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M25PE20(T9HX)	SO8N	SF-SOP8-150A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M25PE40(T9HX)	SO8N	SF-SOP8-150A	
	SO8W	SF-SOP8-200A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M25PE80(T9HX)	SO8N	SF-SOP8-150A	
	SO8W	SF-SOP8-200A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M25PE16	SO8N	SF-SOP8-150A	
	SO8W	SF-SOP8-200A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M25PX80	SO8N	SF-SOP8-150A	
	SO8W	SF-SOP8-200A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M25PX16	SO8N	SF-SOP8-150A	
	SO8W	SF-SOP8-200A	

	MLP8 / 6x5mm	SF-QFN8-6X5A	
M25PX32	SO8W	SF-SOP8-200A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
	SO16W / 300mil	SF-SO16-300A	
M25PX64	SO8W	SF-SOP8-200A	
	MLP8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
N25Q032A13E	SO8N	SF-SOP8-150A	
	SO8W	SF-SOP8-200A	
	DFN8 / 4x3mm	SF-QFN8-4X3B	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q032A23E	SO8N	SF-SOP8-150A	
	SO8W	SF-SOP8-200A	
	DFN8 / 4x3mm	SF-QFN8-4X3B	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q032A33E	SO8N	SF-SOP8-150A	
	SO8W	SF-SOP8-200A	
	DFN8 / 4x3mm	SF-QFN8-4X3B	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q032A43E	SO8N	SF-SOP8-150A	
	SO8W	SF-SOP8-200A	
	DFN8 / 4x3mm	SF-QFN8-4X3B	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q064A13E	SO8W	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q064A23E	SO8W	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q064A33E	SO8W	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q064A43E	SO8W	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q128A13E	SO8W	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q128A23E	SO8W	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
N25Q128A33E	SO8W	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	

N25Q128A43E	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	SO8W	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
ON Semiconductor - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
LE25S20	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
LE25S40	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
LE25S81A	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
LE25S161	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
LE25U20A	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
LE25U40C	SOIC8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	---	ISP	
LE25U40PCMC	SOIC8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	---	ISP	
LE25W81QE	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
ON Semiconductor - SPI EEPROM			
Device Model	Package Type	Adapter Module	Remark
CAT25010	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
CAT25020	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
CAT25040	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
CAT25080	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
CAT25160	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
CAT25320	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
CAT25640	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
CAT25128	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
CAT25256	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
CAT25512	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	

	---	ISP	
CAT25M01	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CAT25M02	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAV25010	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CAV25020	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CAV25040	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CAV25080	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CAV25160	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CAV25320	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CAV25640	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
CAV25128	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CAV25256	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CAV25512	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CAV25M01	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	

ON Semiconductor - I2C EEPROM

Device Model	Package Type	Adapter Module	Remark
CAT24AA01	SOIC8 / 150mil	SF-SOP8-150A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
CAT24AA02	SOIC8 / 150mil	SF-SOP8-150A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
CAT24AA04	SOIC8 / 150mil	SF-SOP8-150A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
CAT24AA08	SOIC8 / 150mil	SF-SOP8-150A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
CAT24AA16	SOIC8 / 150mil	SF-SOP8-150A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
CAT24C01	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
CAT24C02	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
CAT24C03	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	

	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
CAT24C04	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
CAT24C05	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
CAT24C08	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
CAT24C16	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
CAT24C32	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
CAT24C64	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
CAT24C128	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
CAT24C256	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
CAT24C512	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
CAT24M01	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
CAT24C21	---	ISP	
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
CAV24C02	MSOP8	SF-MSP8-3X3A	
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	

	---	ISP	
CAV24C04	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CAV24C08	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CAV24C16	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CAV24C32	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CAV24C64	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CAV24C128	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CAV24C256	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CAV24C512	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
CAV24M01	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CAT34C02	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	

ON Semiconductor - Microwire EEPROM

Device Model	Package Type	Adapter Module	Remark
CAT93C46	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CAT93C46J	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT93C46W	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT93C56	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CAT93C56J	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT93C56W	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT93C57	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CAT93C57J	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT93C57W	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT93C66	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CAT93C66J	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT93C66W	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT93C76	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CAT93C86	DIP8		

	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT93C86J	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAT93C86W	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
CAV93C46	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CAV93C56	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CAV93C66	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CAV93C76	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
CAV93C86	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
PCT - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
PCT25LF020A	SOIC8 / 150mil	SF-SOP8-150A	
	WSON8 / 5x6mm	SF-QFN8-6X5A	
PCT25LF040A	SOIC8 / 200mil	SF-SOP8-200A	
	WSON8 / 5x6mm	SF-QFN8-6X5A	
PCT25LF080A	SOIC8 / 200mil	SF-SOP8-200A	
PCT25VF512	SOIC8 / 150mil	SF-SOP8-150A	
	WSON8 / 5x6mm	SF-QFN8-6X5A	
PCT25VF512A	SOIC8 / 150mil	SF-SOP8-150A	
	WSON8 / 5x6mm	SF-QFN8-6X5A	
PCT25VF010	SOIC8 / 150mil	SF-SOP8-150A	
	WSON8 / 5x6mm	SF-QFN8-6X5A	
PCT25VF010A	SOIC8 / 150mil	SF-SOP8-150A	
	WSON8 / 5x6mm	SF-QFN8-6X5A	
PCT25VF020	SOIC8 / 150mil	SF-SOP8-150A	
	WSON8 / 5x6mm	SF-QFN8-6X5A	
PCT25VF020B	SOIC8 / 150mil	SF-SOP8-150A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
PCT25VF040	SOIC8 / 200mil	SF-SOP8-200A	
	WSON8 / 5x6mm	SF-QFN8-6X5A	
PCT25VF040B	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
PCT25VF080	SOIC8 / 200mil	SF-SOP8-200A	
PCT25VF080B	DIP8		
	SOIC8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
PCT25VF016B	SOIC8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
PCT25VF032B	SOIC8 / 200mil	SF-SOP8-200A	
	WSON8 / 5x6mm	SF-QFN8-6X5A	
PMC - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
Pm25LV512	SOIC8 / 150mil	SF-SOP8-150A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
Pm25LV512A	SOIC8 / 150mil	SF-SOP8-150A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
Pm25LV010	SOIC8 / 150mil	SF-SOP8-150A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
Pm25LV010A	SOIC8 / 150mil	SF-SOP8-150A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
Pm25LV020	SOIC8 / 150mil	SF-SOP8-150A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
Pm25LV040	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
Pm25LV080B	SOIC8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	

Pm25LV016B	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
Pm25LD256C	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
Pm25LD512C	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
Pm25LD512	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
Pm25LD010	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
Pm25LD010C	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
Pm25LD020	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
Pm25LD020C	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
Pm25LD040	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
Pm25LD040C	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
Pm25LQ512B	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
Pm25LQ010B	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
Pm25LQ020B	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
Pm25LQ040B	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
Pm25LQ080C	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
Pm25LQ016	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
Pm25LQ016C	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
Pm25LQ032C	SOIC8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	

Puya Semiconductor - SPI Flash

Device Model	Package Type	Adapter Module	Remark
P25D05H	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
P25D05L	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
P25D09H	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USO8 / 3x2mm	SF-QFN8-2X3A	

P25D09U	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
P25D10H	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
P25D10L	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
P25D10U	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
P25D20H	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
P25D20L	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
P25D20U	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
P25D22H	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
P25D22L	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
P25D24L	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
P25D24H	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
P25D40H	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
P25D40L	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
P25D40U	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
P25D40SH	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
P25D80H	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	

P25D80L	USON8 / 2x3mm	SF-QFN8-2X3A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
P25D80U	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
P25D80SH	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
P25D80SL	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
P25D16H	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
P25D16L	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
P25D16U	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
P25D16SH	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
P25D32H	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
P25D32L	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
P25D32U	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
P25D32SH	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
P25D64H	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
P25D64L	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
P25D64U	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
P25D64SH	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
P25D128H	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	

P25Q05H	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
P25Q05L	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
P25Q05SH	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
P25Q06H	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
P25Q06L	WSON8 / 6x5mm	SF-QFN8-6X5A	OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
P25Q06U	USON8 / 3x4mm	SF-QFN8-4X3B	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
P25Q10H	USON8 / 3x2mm	SF-QFN8-2X3A	OTP
	USON8 / 3x4mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
P25Q10L	TSSOP8 / 173mil	SF-TSP8-170A	OTP
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
P25Q10SH	TSSOP8 / 173mil	SF-TSP8-170A	OTP
	USON8 / 3x2mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
P25Q11H	TSSOP8 / 173mil	SF-TSP8-170A	OTP
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP8 / 150mil	SF-SOP8-150A	
P25Q11L	SOP8 / 208mil	SF-SOP8-200A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
P25Q11U	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
P25Q20H	WSON8 / 6x5mm	SF-QFN8-6X5A	OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	

P25Q20L	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
P25Q20U	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
P25Q20SH	WSON8 / 6x5mm	SF-QFN8-6X5A	OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
P25Q21H	WSON8 / 6x5mm	SF-QFN8-6X5A	OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
P25Q21L	USON8 / 3x4mm	SF-QFN8-4X3B	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
P25Q21U	USON8 / 3x2mm	SF-QFN8-2X3A	OTP
	USON8 / 3x4mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
P25Q23L	TSSOP8 / 173mil	SF-TSP8-170A	OTP
	USON8 / 3x2mm	SF-QFN8-2X3A	
P25Q40H	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
P25Q40L	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
P25Q40U	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
P25Q40M	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
P25Q40SH	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
P25Q40SL	WSON8 / 6x5mm	SF-QFN8-6X5A	OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
P25Q40SU	USON8 / 3x4mm	SF-QFN8-4X3B	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	

P25Q42L	SOP8 / 150mil	SF-SOP8-150A	OTP
	USON8 / 3x2mm	SF-QFN8-2X3A	
P25Q80H	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
P25Q80L	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
P25Q80U	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
P25Q80SH	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
P25Q80SL	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
P25Q16H	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
P25Q16L	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
P25Q16U	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
P25Q16SH	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
P25Q16SL	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
P25Q16SU	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
P25Q16SLE	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
P25Q32H	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
P25Q32L	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	

	WSO8 / 6x5mm	SF-QFN8-6X5A	
P25Q32U	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USO8 / 2x3mm	SF-QFN8-2X3A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
P25Q32SH	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USO8 / 2x3mm	SF-QFN8-2X3A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
P25Q32SL	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USO8 / 2x3mm	SF-QFN8-2X3A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
P25Q32SU	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USO8 / 2x3mm	SF-QFN8-2X3A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
P25Q64H	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
P25Q64L	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
P25Q64U	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
P25Q64LB	SOP8 / 208mil	SF-SOP8-200A	OTP
	VSOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
P25Q64SH	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	USO8 / 3x2mm	SF-QFN8-2X3A	
	USO8 / 4x3mm	SF-QFN8-4X3B	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
P25Q64SL	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	USO8 / 3x2mm	SF-QFN8-2X3A	
	USO8 / 4x3mm	SF-QFN8-4X3B	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
P25Q64SU	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	USO8 / 3x2mm	SF-QFN8-2X3A	
	USO8 / 4x3mm	SF-QFN8-4X3B	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
P25Q128H	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
P25Q128L	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
P25Q128U	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
P25Q32SN	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USO8 / 3x2mm	SF-QFN8-2X3A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
P25Q64SN	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
P25Q128SN	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
P25R05H	SOP8 / 150mil	SF-SOP8-150A	

	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
P25R05L	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
P25R05U	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
P25R10H	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
P25R10L	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP8 / 150mil	SF-SOP8-150A	
P25R10U	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
P25R20H	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
P25R20L	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
P25R20U	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
P25R40H	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP8 / 150mil	SF-SOP8-150A	
P25R40L	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
P25R40U	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
P25T12H	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
P25T12L	USON8 / 3x2mm	SF-QFN8-2X3A	
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
P25T22H	USON8 / 3x2mm	SF-QFN8-2X3A	
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	

P25T22L	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
P25T22U	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
P25X05	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
P25X10	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
P25X20	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
P25X40	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
PY25D40HB	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
PY25D80HB	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
PY25D16HB	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
PY25D32HB	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
PY25D64HA	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
PY25F64HA	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
PY25F128HA	SOP8 / 208mil	SF-SOP8-200A	OTP
	VSOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
PY25F128LA	SOP8 / 208mil	SF-SOP8-200A	OTP
	VSOP8 / 208mil	SF-SOP8-200A	

	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
PY25F256HB	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
PY25F256LC	WSO8 / 6x5mm	SF-QFN8-6X5A	OTP
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
PY25F512HB	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
PY25F512LC	WSO8 / 6x5mm	SF-QFN8-6X5A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
PY25Q40HB	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USO8 / 2x3mm	SF-QFN8-2X3A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
PY25Q80HB	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USO8 / 2x3mm	SF-QFN8-2X3A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
PY25Q16HB	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USO8 / 2x3mm	SF-QFN8-2X3A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
PY25Q16LB	SOP8 / 150mil	SF-SOP8-150A	OTP
	USO8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
PY25Q32HB	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USO8 / 2x3mm	SF-QFN8-2X3A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
PY25Q32LB	SOP8 / 150mil	SF-SOP8-150A	OTP
	USO8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
PY25Q32LC	SOP8 / 150mil	SF-SOP8-150A	OTP
	USO8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
PY25Q64HA	SOP8 / 208mil	SF-SOP8-200A	OTP
	VSOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
PY25Q64LB	SOP8 / 208mil	SF-SOP8-200A	OTP
	VSOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
PY25Q128HA	SOP8 / 208mil	SF-SOP8-200A	OTP
	VSOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	

	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
PY25Q128LA(old)	SOP8 / 208mil	SF-SOP8-200A	OTP
	VSOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
PY25Q128LA	SOP8 / 208mil	SF-SOP8-200A	OTP
	VSOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
PY25Q256HB	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
PY25Q256LC	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
PY25Q512HB	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
PY25Q512LC	WSO8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
PY25Q01GHB	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
PY25Q01GLC	WSO8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
PY25R32LB	SOP8 / 150mil	SF-SOP8-150A	OTP
	USO8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
PY25R128HA	SOP8 / 208mil	SF-SOP8-200A	OTP
	VSOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
PY25R128LA	SOP8 / 208mil	SF-SOP8-200A	OTP
	VSOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
PY25R256HB	WSO8 / 6x5mm	SF-QFN8-6X5A	OTP
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
PY25R256LC	WSO8 / 6x5mm	SF-QFN8-6X5A	OTP
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
PY25R512LC	WSO8 / 6x5mm	SF-QFN8-6X5A	OTP
	SOP16 / 300mil	SF-SO16-300A	

	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
Puya Semiconductor - SPI EEPROM			
Device Model	Package Type	Adapter Module	Remark
P25C08H	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
P25C16H	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
P25C32H	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
P25C64F	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
P25C64H	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
P25C128F	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
P25C128H	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
P25C256F	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
P25C256H	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
P25C512F	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
P25C512H	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
P25CM01H	USON8 / 3x2mm	SF-QFN8-2X3A	
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
P25CM02F	SOP8 / 150mil	SF-SOP8-150A	
Puya Semiconductor - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
P24C02A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
P24C02C	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
P24C04C	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
P24C08C	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
P24C08D	DIP8		OTP
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	

	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
P24C16C	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
P24C16D	DIP8		OTP
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
P24C32C	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
P24C64B	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
P24C64C	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
P24C64G	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
P24C64H	DIP8		OTP
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
P24C128	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
P24C128B	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
P24C128D	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
P24C128F	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
P24C256	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
P24C256B	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
P24C256F	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	

P24C512	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
P24C512B	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
P24C512F	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
P24C512H	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
P24CM01B	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
P24CM01H	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
P24CM02F	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
P24CM02Z	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	

Ramtron - SPI EEPROM

Device Model	Package Type	Adapter Module	Remark
FM25040	SOIC8 / 150mil	SF-SOP8-150A	
FM25040A	SOIC8 / 150mil	SF-SOP8-150A	
FM25040B	SOIC8 / 150mil	SF-SOP8-150A	
FM25640	SOIC8 / 150mil	SF-SOP8-150A	
FM25640B	SOIC8 / 150mil	SF-SOP8-150A	
FM25640C	SOIC8 / 150mil	SF-SOP8-150A	
FM25256	SOIC8 / 150mil	SF-SOP8-150A	
FM25256B	SOIC8 / 150mil	SF-SOP8-150A	
FM25C160	SOIC8 / 150mil	SF-SOP8-150A	
FM25C160B	SOIC8 / 150mil	SF-SOP8-150A	
FM25CL04	SOIC8 / 150mil	SF-SOP8-150A	
FM25CL64	SOIC8 / 150mil	SF-SOP8-150A	
FM25CL64B	SOIC8 / 150mil	SF-SOP8-150A	
FM25H20	SOIC8 / 200mil	SF-SOP8-200A	
FM25L04	SOIC8 / 150mil	SF-SOP8-150A	
FM25L04B	SOIC8 / 150mil	SF-SOP8-150A	
FM25L16	SOIC8 / 150mil	SF-SOP8-150A	
FM25L16B	SOIC8 / 150mil	SF-SOP8-150A	
FM25L256	SOIC8 / 150mil	SF-SOP8-150A	
FM25L256B	SOIC8 / 150mil	SF-SOP8-150A	
FM25L512	TDFN8 / 5x6mm	SF-QFN8-6X5A	
FM25V01	SOIC8 / 150mil	SF-SOP8-150A	
FM25V02	SOIC8 / 150mil	SF-SOP8-150A	
FM25V05	SOIC8 / 150mil	SF-SOP8-150A	
FM25V10	SOIC8 / 150mil	SF-SOP8-150A	
FM25V20	SOIC8 / 200mil	SF-SOP8-200A	
	TDFN8 / 5x6mm	SF-QFN8-6X5A	
FM25V20A	SOIC8 / 200mil	SF-SOP8-200A	
	TDFN8 / 5x6mm	SF-QFN8-6X5A	
FM25VN02	SOIC8 / 150mil	SF-SOP8-150A	
FM25VN05	SOIC8 / 150mil	SF-SOP8-150A	
FM25VN10	SOIC8 / 150mil	SF-SOP8-150A	
FM25W256	SOIC8 / 150mil	SF-SOP8-150A	

Ramtron - I2C EEPROM

Device Model	Package Type	Adapter Module	Remark
--------------	--------------	----------------	--------

FM24C04	SOIC8 / 150mil	SF-SOP8-150A	
FM24C04A	SOIC8 / 150mil	SF-SOP8-150A	
FM24C16	SOIC8 / 150mil	SF-SOP8-150A	
FM24C16A	SOIC8 / 150mil	SF-SOP8-150A	
FM24C64	SOIC8 / 150mil	SF-SOP8-150A	
FM24C256	SOIC8 / 150mil	SF-SOP8-150A	
FM24C512	SOIC8 / 150mil	SF-SOP8-150A	
FM24CL04	SOIC8 / 150mil	SF-SOP8-150A	
FM24CL04B	SOIC8 / 150mil	SF-SOP8-150A	
FM24CL16	SOIC8 / 150mil	SF-SOP8-150A	
FM24CL16A	SOIC8 / 150mil	SF-SOP8-150A	
FM24CL16B	SOIC8 / 150mil	SF-SOP8-150A	
FM24CL64	SOIC8 / 150mil	SF-SOP8-150A	
FM24CL64B	SOIC8 / 150mil	SF-SOP8-150A	
FM24V01	SOIC8 / 150mil	SF-SOP8-150A	
FM24V01A	SOIC8 / 150mil	SF-SOP8-150A	
FM24V02	SOIC8 / 150mil	SF-SOP8-150A	
FM24V02A	SOIC8 / 150mil	SF-SOP8-150A	
FM24V05	SOIC8 / 150mil	SF-SOP8-150A	
FM24V10	SOIC8 / 150mil	SF-SOP8-150A	
FM24VN05	SOIC8 / 150mil	SF-SOP8-150A	
FM24VN10	SOIC8 / 150mil	SF-SOP8-150A	
Rato - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
RT24A02	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
Rato - Microwire EEPROM			
Device Model	Package Type	Adapter Module	Remark
RT93LC46	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
Raydium - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
RM24C02	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
RM24C16	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
RM24C32	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
RM24C64	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
Reliance - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
RT25LD20A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
RT25LQ40A	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
RT25VD20A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
RT25VQ40A	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
Renesas - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
AT25EU0011A	SOIC8 / 150mil	SF-SOP8-150A	OTP
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
AT25EU0021A	SOIC8 / 150mil	SF-SOP8-150A	OTP
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
AT25EU0041A	SOIC8 / 150mil	SF-SOP8-150A	OTP
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
AT25EU0081A	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	

AT25EU0161A	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
AT25DF256	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
AT25DF011	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
AT25DF021A	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
AT25DF041B	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
AT25DF081A	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
AT25DF321A	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
AT25DF641A	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
AT25DL081	SOIC8 / 150mil	SF-SOP8-150A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
AT25DL161	SOIC8 / 150mil	SF-SOP8-150A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
AT25DN256	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
AT25DN512C	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
AT25DN011	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
AT25FF041A	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	UDFN8 / 5x6mm	SF-QFN8-6X5A	
AT25FF081A	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	UDFN8 / 5x6mm	SF-QFN8-6X5A	
AT25FF161A	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	UDFN8 / 5x6mm	SF-QFN8-6X5A	
AT25FF321A	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	UDFN8 / 5x6mm	SF-QFN8-6X5A	
AT25PE20	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
AT25PE40	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
AT25PE80	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
AT25PE16	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
AT25SF041B	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
AT25SF081B	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	

	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
AT25SF161B	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
AT25SF321B	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
AT25SF641B	SOIC8 / 208mil	SF-SOP8-200A	OTP
	DFN8 / 5x6mm	SF-QFN8-6X5A	
AT25SF128A	SOIC8 / 208mil	SF-SOP8-200A	OTP
	UDFN8 / 5x6mm	SF-QFN8-6X5A	
AT25SF2561C	SOIC8 / 208mil	SF-SOP8-200A	OTP
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SQ16-300A	
AT25QF641B	SOIC8 / 208mil	SF-SOP8-200A	OTP
	DFN8 / 6x5mm	SF-QFN8-6X5A	
AT25QF128A	SOIC8 / 208mil	SF-SOP8-200A	OTP
	UDFN8 / 5x6mm	SF-QFN8-6X5A	
AT25XE512C	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
AT25XE011	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
AT25XE021A	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
AT25XE041B	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
AT25XE041D	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
AT25XE081D	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
AT25XE161D	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	UDFN8 / 5x6mm	SF-QFN8-6X5A	
AT25XE321D	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	UDFN8 / 5x6mm	SF-QFN8-6X5A	
AT25XV021A	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
AT25XV041B	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
AT25SL321	SOIC8 / 208mil	SF-SOP8-200A	
	UDFN8 / 5x6mm	SF-QFN8-6X5A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
AT25SL641	SOIC8 / 208mil	SF-SOP8-200A	
	UDFN8 / 5x6mm	SF-QFN8-6X5A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
AT25SL128A	SOIC8 / 208mil	SF-SOP8-200A	
	UDFN8 / 5x6mm	SF-QFN8-6X5A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
AT25QL128A	SOIC8 / 208mil	SF-SOP8-200A	
	UDFN8 / 5x6mm	SF-QFN8-6X5A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
AT45DB021E(P264)	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	

	DFN8 / 6x5mm	SF-QFN8-6X5A	
AT45DB021E(P256)	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
AT45DB041E(P264)	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
AT45DB041E(P256)	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
AT45DB081E(P264)	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
AT45DB081E(P256)	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
AT45DB161E(P528)	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
AT45DB161E(P512)	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
AT45DB321E(P528)	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
AT45DB321E(P512)	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
AT45DB641E(P264)	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
AT45DB641E(P256)	SOIC8 / 208mil	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	

ROHM - SPI EEPROM

Device Model	Package Type	Adapter Module	Remark
BR25A256	SOP-J8	SF-SOP8-150A	
	TSSOP-B8	SF-TSP8-170A	
	---	ISP	
BR25A512	SOP-J8	SF-SOP8-150A	
	TSSOP-B8	SF-TSP8-170A	
	---	ISP	
BR25A1M	SOP-J8	SF-SOP8-150A	
	TSSOP-B8	SF-TSP8-170A	
	---	ISP	
BR25G320	SOP-J8	SF-SOP8-150A	
	TSSOP-B8	SF-TSP8-170A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR25G640	SOP-J8	SF-SOP8-150A	
	TSSOP-B8	SF-TSP8-170A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR25G128	SOP-J8	SF-SOP8-150A	
	TSSOP-B8	SF-TSP8-170A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR25G256	SOP-J8	SF-SOP8-150A	
	TSSOP-B8	SF-TSP8-170A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR25G512	SOP-J8	SF-SOP8-150A	
	TSSOP-B8	SF-TSP8-170A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR25G1M	SOP-J8	SF-SOP8-150A	
	TSSOP-B8	SF-TSP8-170A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR25H010	SOP-J8	SF-SOP8-150A	
	TSSOP-B8	SF-TSP8-170A	
	---	ISP	
BR25H020	SOP-J8	SF-SOP8-150A	

	TSSOP-B8	SF-TSP8-170A	
	---	ISP	
BR25H040	SOP-J8	SF-SOP8-150A	
	TSSOP-B8	SF-TSP8-170A	
	---	ISP	
BR25H080	SOP-J8	SF-SOP8-150A	
	TSSOP-B8	SF-TSP8-170A	
	---	ISP	
BR25H160	SOP-J8	SF-SOP8-150A	
	TSSOP-B8	SF-TSP8-170A	
	---	ISP	
BR25H320	SOP-J8	SF-SOP8-150A	
	TSSOP-B8	SF-TSP8-170A	
	---	ISP	
BR25H640	SOP-J8	SF-SOP8-150A	
	TSSOP-B8	SF-TSP8-170A	
	---	ISP	
BR25H128	SOP-J8	SF-SOP8-150A	
	TSSOP-B8	SF-TSP8-170A	
	---	ISP	
BR25H256	SOP-J8	SF-SOP8-150A	
	TSSOP-B8	SF-TSP8-170A	
	---	ISP	
BR25L010	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	---	ISP	
BR25L020	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	---	ISP	
BR25L040	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	---	ISP	
BR25L080	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	---	ISP	
BR25L160	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	---	ISP	
BR25L320	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	---	ISP	
BR25L640	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	---	ISP	
BR25S320F	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	TSSOP-B8J	SF-MSP8-3X3A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR25S640F	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	TSSOP-B8J	SF-MSP8-3X3A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR25S128F	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	TSSOP-B8J	SF-MSP8-3X3A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR25S256F	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	

	TSSOP-B8	SF-TSP8-170A	
	TSSOP-B8J	SF-MSP8-3X3A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
ROHM - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
BR24A01A	SOP-J8	SF-SOP8-150A	
	---	ISP	
BR24A02	SOP-J8	SF-SOP8-150A	
	---	ISP	
BR24A04	SOP-J8	SF-SOP8-150A	
	---	ISP	
BR24A08	SOP-J8	SF-SOP8-150A	
	---	ISP	
BR24A16	SOP-J8	SF-SOP8-150A	
	---	ISP	
BR24A32	SOP-J8	SF-SOP8-150A	
	---	ISP	
BR24A64	SOP-J8	SF-SOP8-150A	
	---	ISP	
BR24H01ANUX	---	ISP	
BR24H01F	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
BR24H01FJ	SOP-J8	SF-SOP8-150A	
	---	ISP	
BR24H01FVM	MSOP8	SF-MSP8-3X3A	
	---	ISP	
BR24H01FVT	TSSOP-B8	SF-TSP8-170A	
	---	ISP	
BR24H02ANUX	---	ISP	
BR24H02F	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
BR24H02FJ	SOP-J8	SF-SOP8-150A	
	---	ISP	
BR24H02FVM	MSOP8	SF-MSP8-3X3A	
	---	ISP	
BR24H02FVT	TSSOP-B8	SF-TSP8-170A	
	---	ISP	
BR24H04ANUX	---	ISP	
BR24H04F	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
BR24H04FJ	SOP-J8	SF-SOP8-150A	
	---	ISP	
BR24H04FVM	MSOP8	SF-MSP8-3X3A	
	---	ISP	
BR24H04FVT	TSSOP-B8	SF-TSP8-170A	
	---	ISP	
BR24H08ANUX	---	ISP	
BR24H08F	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
BR24H08FJ	SOP-J8	SF-SOP8-150A	
	---	ISP	
BR24H08FVM	MSOP8	SF-MSP8-3X3A	
	---	ISP	
BR24H08FVT	TSSOP-B8	SF-TSP8-170A	
	---	ISP	
BR24H16ANUX	---	ISP	
BR24H16F	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
BR24H16FJ	SOP-J8	SF-SOP8-150A	
	---	ISP	
BR24H16FVM	MSOP8	SF-MSP8-3X3A	
	---	ISP	
BR24H16FVT	TSSOP-B8	SF-TSP8-170A	
	---	ISP	
BR24H32ANUX	---	ISP	
BR24H32F	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
BR24H32FJ	SOP-J8	SF-SOP8-150A	
	---	ISP	
BR24H32FVM	MSOP8	SF-MSP8-3X3A	

	---	ISP	
BR24H32FVT	TSSOP-B8	SF-TSP8-170A	
	---	ISP	
BR24H32NUX	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR24H64ANUX	---	ISP	
BR24H64F	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
BR24H64FJ	SOP-J8	SF-SOP8-150A	
	---	ISP	
BR24H64FVM	MSOP8	SF-MSP8-3X3A	
	---	ISP	
BR24H64FVT	TSSOP-B8	SF-TSP8-170A	
	---	ISP	
BR24H64NUX	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR24H128F	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
BR24H128FJ	SOP-J8	SF-SOP8-150A	
	---	ISP	
BR24H128FVM	MSOP8	SF-MSP8-3X3A	
	---	ISP	
BR24H128FVT	TSSOP-B8	SF-TSP8-170A	
	---	ISP	
BR24H128NUX	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR24H256F	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
BR24H256FJ	SOP-J8	SF-SOP8-150A	
	---	ISP	
BR24H256FVM	MSOP8	SF-MSP8-3X3A	
	---	ISP	
BR24H256FVT	TSSOP-B8	SF-TSP8-170A	
	---	ISP	
BR24H256NUX	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR24H512F	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
BR24H512FJ	SOP-J8	SF-SOP8-150A	
	---	ISP	
BR24H512FVM	MSOP8	SF-MSP8-3X3A	
	---	ISP	
BR24H512FVT	TSSOP-B8	SF-TSP8-170A	
	---	ISP	
BR24H1MF	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
BR24H1MFJ	SOP-J8	SF-SOP8-150A	
	---	ISP	
BR24H1MFVT	TSSOP-B8	SF-TSP8-170A	
	---	ISP	
BR24G01	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	TSSOP-B8J	SF-MSP8-3X3A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR24G02	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	TSSOP-B8J	SF-MSP8-3X3A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR24G04	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	TSSOP-B8J	SF-MSP8-3X3A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR24G08	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	

	TSSOP-B8J	SF-MSP8-3X3A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR24G16	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	TSSOP-B8J	SF-MSP8-3X3A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR24G32	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	TSSOP-B8J	SF-MSP8-3X3A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR24G64	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	TSSOP-B8J	SF-MSP8-3X3A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR24G128	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	TSSOP-B8J	SF-MSP8-3X3A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR24G256	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	---	ISP	
BR24G512	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	---	ISP	
BR24G1M	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	---	ISP	
BR24L01	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	TSSOP-B8J	SF-MSP8-3X3A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR24L02	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	TSSOP-B8J	SF-MSP8-3X3A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR24L04	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	TSSOP-B8J	SF-MSP8-3X3A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR24L08	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	TSSOP-B8J	SF-MSP8-3X3A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR24L16	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	TSSOP-B8J	SF-MSP8-3X3A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR24L32	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	

	TSSOP-B8	SF-TSP8-170A	
	TSSOP-B8J	SF-MSP8-3X3A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR24L64	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	TSSOP-B8J	SF-MSP8-3X3A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR24S01	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	TSSOP-B8J	SF-MSP8-3X3A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR24S02	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	TSSOP-B8J	SF-MSP8-3X3A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR24S04	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	TSSOP-B8J	SF-MSP8-3X3A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR24S08	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	TSSOP-B8J	SF-MSP8-3X3A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR24S16	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	TSSOP-B8J	SF-MSP8-3X3A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR24S32	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	TSSOP-B8J	SF-MSP8-3X3A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR24S64	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	TSSOP-B8J	SF-MSP8-3X3A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR24S128	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	TSSOP-B8J	SF-MSP8-3X3A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR24S256	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	---	ISP	
BR24T01	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	TSSOP-B8J	SF-MSP8-3X3A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR24T02	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	

	TSSOP-B8J	SF-MSP8-3X3A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR24T04	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	TSSOP-B8J	SF-MSP8-3X3A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR24T08	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	TSSOP-B8J	SF-MSP8-3X3A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR24T16	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	TSSOP-B8J	SF-MSP8-3X3A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR24T32	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	TSSOP-B8J	SF-MSP8-3X3A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR24T64	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	TSSOP-B8J	SF-MSP8-3X3A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR24T128	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	TSSOP-B8J	SF-MSP8-3X3A	
	VSON008X2030	SF-QFN8-3X2A	
	---	ISP	
BR24T256	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	---	ISP	
BR24T512	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	---	ISP	
BR24T1M	SOP-J8	SF-SOP8-150A	
	SSOP-B8	SF-TSP8-170A	
	TSSOP-B8	SF-TSP8-170A	
	---	ISP	

ROHM - Microwire EEPROM

Device Model	Package Type	Adapter Module	Remark
BR93A46FJ-WM	SOP-J8	SF-SOP8-150A	
BR93A46RFJ-WM	SOP-J8	SF-SOP8-150A	
BR93A46RFVT-WM	TSSOP-B8	SF-TSP8-170A	
BR93A56FJ-WM	SOP-J8	SF-SOP8-150A	
BR93A56RFJ-WM	SOP-J8	SF-SOP8-150A	
BR93A56RFVT-WM	TSSOP-B8	SF-TSP8-170A	
BR93A66FJ-WM	SOP-J8	SF-SOP8-150A	
BR93A66RFJ-WM	SOP-J8	SF-SOP8-150A	
BR93A66RFVT-WM	TSSOP-B8	SF-TSP8-170A	
BR93A76FJ-WM	SOP-J8	SF-SOP8-150A	
BR93A76RFJ-WM	SOP-J8	SF-SOP8-150A	
BR93A76RFVT-WM	TSSOP-B8	SF-TSP8-170A	
BR93A86FJ-WM	SOP-J8	SF-SOP8-150A	
BR93A86RFJ-WM	SOP-J8	SF-SOP8-150A	
BR93A86RFVT-WM	TSSOP-B8	SF-TSP8-170A	
BR93G46-3	DIP8		
BR93G46FJ-3	SOP-J8	SF-SOP8-150A	
BR93G46FV-3	SSOP-B8	SF-TSP8-170A	

BR93G46FVJ-3	TSSOP-B8J	SF-MSP8-3X3A	
BR93G46FVT-3	TSSOP-B8	SF-TSP8-170A	
BR93G46NUX-3	VSON008X2030	SF-QFN8-3X2A	
BR93G46-3A	DIP8		
BR93G46FJ-3A	SOP-J8	SF-SOP8-150A	
BR93G46FV-3A	SSOP-B8	SF-TSP8-170A	
BR93G46FVJ-3A	TSSOP-B8J	SF-MSP8-3X3A	
BR93G46FVT-3A	TSSOP-B8	SF-TSP8-170A	
BR93G46NUX-3A	VSON008X2030	SF-QFN8-3X2A	
BR93G46-3B	DIP8		
BR93G46FJ-3B	SOP-J8	SF-SOP8-150A	
BR93G46FV-3B	SSOP-B8	SF-TSP8-170A	
BR93G46FVJ-3B	TSSOP-B8J	SF-MSP8-3X3A	
BR93G46FVT-3B	TSSOP-B8	SF-TSP8-170A	
BR93G46NUX-3B	VSON008X2030	SF-QFN8-3X2A	
BR93G56-3	DIP8		
BR93G56FJ-3	SOP-J8	SF-SOP8-150A	
BR93G56FV-3	SSOP-B8	SF-TSP8-170A	
BR93G56FVJ-3	TSSOP-B8J	SF-MSP8-3X3A	
BR93G56FVT-3	TSSOP-B8	SF-TSP8-170A	
BR93G56NUX-3	VSON008X2030	SF-QFN8-3X2A	
BR93G56-3A	DIP8		
BR93G56FJ-3A	SOP-J8	SF-SOP8-150A	
BR93G56FV-3A	SSOP-B8	SF-TSP8-170A	
BR93G56FVJ-3A	TSSOP-B8J	SF-MSP8-3X3A	
BR93G56FVT-3A	TSSOP-B8	SF-TSP8-170A	
BR93G56NUX-3A	VSON008X2030	SF-QFN8-3X2A	
BR93G56-3B	DIP8		
BR93G56FJ-3B	SOP-J8	SF-SOP8-150A	
BR93G56FV-3B	SSOP-B8	SF-TSP8-170A	
BR93G56FVJ-3B	TSSOP-B8J	SF-MSP8-3X3A	
BR93G56FVT-3B	TSSOP-B8	SF-TSP8-170A	
BR93G56NUX-3B	VSON008X2030	SF-QFN8-3X2A	
BR93G66-3	DIP8		
BR93G66FJ-3	SOP-J8	SF-SOP8-150A	
BR93G66FV-3	SSOP-B8	SF-TSP8-170A	
BR93G66FVJ-3	TSSOP-B8J	SF-MSP8-3X3A	
BR93G66FVT-3	TSSOP-B8	SF-TSP8-170A	
BR93G66NUX-3	VSON008X2030	SF-QFN8-3X2A	
BR93G66-3A	DIP8		
BR93G66FJ-3A	SOP-J8	SF-SOP8-150A	
BR93G66FV-3A	SSOP-B8	SF-TSP8-170A	
BR93G66FVJ-3A	TSSOP-B8J	SF-MSP8-3X3A	
BR93G66FVT-3A	TSSOP-B8	SF-TSP8-170A	
BR93G66NUX-3A	VSON008X2030	SF-QFN8-3X2A	
BR93G66-3B	DIP8		
BR93G66FJ-3B	SOP-J8	SF-SOP8-150A	
BR93G66FV-3B	SSOP-B8	SF-TSP8-170A	
BR93G66FVJ-3B	TSSOP-B8J	SF-MSP8-3X3A	
BR93G66FVT-3B	TSSOP-B8	SF-TSP8-170A	
BR93G66NUX-3B	VSON008X2030	SF-QFN8-3X2A	
BR93G76-3	DIP8		
BR93G76FJ-3	SOP-J8	SF-SOP8-150A	
BR93G76FV-3	SSOP-B8	SF-TSP8-170A	
BR93G76FVJ-3	TSSOP-B8J	SF-MSP8-3X3A	
BR93G76FVT-3	TSSOP-B8	SF-TSP8-170A	
BR93G76NUX-3	VSON008X2030	SF-QFN8-3X2A	
BR93G76-3A	DIP8		
BR93G76FJ-3A	SOP-J8	SF-SOP8-150A	
BR93G76FV-3A	SSOP-B8	SF-TSP8-170A	
BR93G76FVJ-3A	TSSOP-B8J	SF-MSP8-3X3A	
BR93G76FVT-3A	TSSOP-B8	SF-TSP8-170A	
BR93G76NUX-3A	VSON008X2030	SF-QFN8-3X2A	
BR93G76-3B	DIP8		
BR93G76FJ-3B	SOP-J8	SF-SOP8-150A	
BR93G76FV-3B	SSOP-B8	SF-TSP8-170A	
BR93G76FVJ-3B	TSSOP-B8J	SF-MSP8-3X3A	
BR93G76FVT-3B	TSSOP-B8	SF-TSP8-170A	
BR93G76NUX-3B	VSON008X2030	SF-QFN8-3X2A	
BR93G86-3	DIP8		
BR93G86FJ-3	SOP-J8	SF-SOP8-150A	

BR93G86FV-3	SSOP-B8	SF-TSP8-170A	
BR93G86FVJ-3	TSSOP-B8J	SF-MSP8-3X3A	
BR93G86FVT-3	TSSOP-B8	SF-TSP8-170A	
BR93G86NUX-3	VSON008X2030	SF-QFN8-3X2A	
BR93G86-3A	DIP8		
BR93G86FJ-3A	SOP-J8	SF-SOP8-150A	
BR93G86FV-3A	SSOP-B8	SF-TSP8-170A	
BR93G86FVJ-3A	TSSOP-B8J	SF-MSP8-3X3A	
BR93G86FVT-3A	TSSOP-B8	SF-TSP8-170A	
BR93G86NUX-3A	VSON008X2030	SF-QFN8-3X2A	
BR93G86-3B	DIP8		
BR93G86FJ-3B	SOP-J8	SF-SOP8-150A	
BR93G86FV-3B	SSOP-B8	SF-TSP8-170A	
BR93G86FVJ-3B	TSSOP-B8J	SF-MSP8-3X3A	
BR93G86FVT-3B	TSSOP-B8	SF-TSP8-170A	
BR93G86NUX-3B	VSON008X2030	SF-QFN8-3X2A	
BR93H46RFJ-2C	SOP-J8	SF-SOP8-150A	
BR93H46RFVT-2C	TSSOP-B8	SF-TSP8-170A	
BR93H56RFJ-2C	SOP-J8	SF-SOP8-150A	
BR93H56RFVT-2C	TSSOP-B8	SF-TSP8-170A	
BR93H56RFJ-WC	SOP-J8	SF-SOP8-150A	
BR93H66RFJ-2C	SOP-J8	SF-SOP8-150A	
BR93H66RFVT-2C	TSSOP-B8	SF-TSP8-170A	
BR93H66RFJ-WC	SOP-J8	SF-SOP8-150A	
BR93H76RFJ-2C	SOP-J8	SF-SOP8-150A	
BR93H76RFVT-2C	TSSOP-B8	SF-TSP8-170A	
BR93H76RFJ-WC	SOP-J8	SF-SOP8-150A	
BR93H86RFJ-2C	SOP-J8	SF-SOP8-150A	
BR93H86RFVT-2C	TSSOP-B8	SF-TSP8-170A	
BR93H86RFJ-WC	SOP-J8	SF-SOP8-150A	
BR93L46-W	DIP8		
BR93L46FJ-W	SOP-J8	SF-SOP8-150A	
BR93L46FV-W	SSOP-B8	SF-TSP8-170A	
BR93L46FVT-W	TSSOP-B8	SF-TSP8-170A	
BR93L46RFJ-W	SOP-J8	SF-SOP8-150A	
BR93L46RFV-W	SSOP-B8	SF-TSP8-170A	
BR93L46RFVJ-W	TSSOP-B8J	SF-MSP8-3X3A	
BR93L46RFVT-W	TSSOP-B8	SF-TSP8-170A	
BR93L56-W	DIP8		
BR93L56FJ-W	SOP-J8	SF-SOP8-150A	
BR93L56FV-W	SSOP-B8	SF-TSP8-170A	
BR93L56FVT-W	TSSOP-B8	SF-TSP8-170A	
BR93L56RFJ-W	SOP-J8	SF-SOP8-150A	
BR93L56RFV-W	SSOP-B8	SF-TSP8-170A	
BR93L56RFVJ-W	TSSOP-B8J	SF-MSP8-3X3A	
BR93L56RFVT-W	TSSOP-B8	SF-TSP8-170A	
BR93L66-W	DIP8		
BR93L66FJ-W	SOP-J8	SF-SOP8-150A	
BR93L66FV-W	SSOP-B8	SF-TSP8-170A	
BR93L66FVT-W	TSSOP-B8	SF-TSP8-170A	
BR93L66RFJ-W	SOP-J8	SF-SOP8-150A	
BR93L66RFV-W	SSOP-B8	SF-TSP8-170A	
BR93L66RFVJ-W	TSSOP-B8J	SF-MSP8-3X3A	
BR93L66RFVT-W	TSSOP-B8	SF-TSP8-170A	
BR93L76-W	DIP8		
BR93L76FJ-W	SOP-J8	SF-SOP8-150A	
BR93L76RFJ-W	SOP-J8	SF-SOP8-150A	
BR93L76RFV-W	SSOP-B8	SF-TSP8-170A	
BR93L76RFVJ-W	TSSOP-B8J	SF-MSP8-3X3A	
BR93L76RFVT-W	TSSOP-B8	SF-TSP8-170A	
BR93L86-W	DIP8		
BR93L86FJ-W	SOP-J8	SF-SOP8-150A	
BR93L86RFJ-W	SOP-J8	SF-SOP8-150A	
BR93L86RFV-W	SSOP-B8	SF-TSP8-170A	
BR93L86RFVJ-W	TSSOP-B8J	SF-MSP8-3X3A	
BR93L86RFVT-W	TSSOP-B8	SF-TSP8-170A	
ROHM - Other			
Device Model	Package Type	Adapter Module	Remark
BR9010	DIP8		
BR9010F	SOP8 / 150mil	SF-SOP8-150A	
BR9010FV	SOP8 / 150mil	SF-SOP8-150A	

BR9020	DIP8		
BR9020F	SOP8 / 150mil	SF-SOP8-150A	
BR9040	DIP8		
BR9040F	SOP8 / 150mil	SF-SOP8-150A	
BR9080	DIP8		
BR9080F	SOP8 / 150mil	SF-SOP8-150A	
BR9080RFV	SOP8 / 150mil	SF-SOP8-150A	
BR9080AF	SOP8 / 150mil	SF-SOP8-150A	
BR9080ARFV	SOP8 / 150mil	SF-SOP8-150A	
BR9080ARFVM	MSOP8	SF-MSP8-3X3A	
BR9016	DIP8		
BR9016F	SOP8 / 150mil	SF-SOP8-150A	
BR9016RFV	SOP8 / 150mil	SF-SOP8-150A	
BR9016AF	SOP8 / 150mil	SF-SOP8-150A	
BR9016ARFV	SOP8 / 150mil	SF-SOP8-150A	
BR9016ARFVM	MSOP8	SF-MSP8-3X3A	

SANXIA - SPI Flash

Device Model	Package Type	Adapter Module	Remark
SX25Q64A	DIP8		
	SOIC8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
SX25Q128B	DIP8		
	SOIC8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	

SEIKO - SPI EEPROM

Device Model	Package Type	Adapter Module	Remark
S-25A010A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-25A020A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-25A040A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-25A080A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-25A080B	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-25A160A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-25A160B	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-25A320A	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
S-25A320B	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-25A640A	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
S-25A640B	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-25A128B	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-25A256B	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
S-25C010A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-25C020A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	

	---	ISP	
S-25C040A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-25C080A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-25C160A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-25C320A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-25C640A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-25C128A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-25C256A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-25C512A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-25CM01A	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	

SEIKO - I2C EEPROM

Device Model	Package Type	Adapter Module	Remark
S-24C01C	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-24C02C	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-24C02D	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
S-24C04D	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
S-24C08C	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-24C08D	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
S-24C16C	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-24C16D	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
S-24C32C	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-24C64C	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-24C128C	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-24C256C	SOP8 / 150mil	SF-SOP8-150A	

S-24C512C	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
S-24CM01C	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
S-24CS01A	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
S-24CS02A	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
S-24CS04A	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
S-24CS08A	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
S-24CS16A	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
S-24CS64A	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	

SEIKO - Microwire EEPROM

Device Model	Package Type	Adapter Module	Remark
S-93A46A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-93A46B	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-93A56A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-93A56B	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-93A66A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-93A66B	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-93A76B	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-93A86A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-93A86B	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
S-93C46A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
S-93C46B	---	ISP	
	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
S-93C46CD	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
S-93C46CR	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
S-93C56A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	

S-93C56B	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
S-93C56CD	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
S-93C56CR	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
	DIP8		
S-93C66A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
	DIP8		
S-93C66B	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
	DIP8		
S-93C66CD	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
S-93C66CR	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
	DIP8		
S-93C76A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
S-93C76CD	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
S-93C76CR	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
	DIP8		
S-93C86B	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
	DIP8		
S-93C86CD	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
	DIP8		
S-93C86CR	SOP8 / 150mil	SF-SOP8-150A	
	---	ISP	
	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	

Siemens - I2C EEPROM

Device Model	Package Type	Adapter Module	Remark
SLA24C01	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
SLA24C02	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
SLA24C04	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
SLA24C08	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
SLA24C16	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
SLA24C164	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
SLA24C32	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
SLA24C64	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
SLE24C01	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
SLE24C02	DIP8		

SLE24C04	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
SLE24C08	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
SLE24C16	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
SLE24C164	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
SLE24C32	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
SLE24C64	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
Silicon Kaiser - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
SK25P128-x1Bxx	SOIC8 / 208mil	SF-SOP8-200A	OTP
SK25P128-xBxx	SOIC8 / 208mil	SF-SOP8-200A	OTP
SK25LP128-x1Bxx	SOIC8 / 208mil	SF-SOP8-200A	OTP
SK25LP128-xBxx	SOIC8 / 208mil	SF-SOP8-200A	OTP
SK25LP128-xKxx	WSO8 / 6x5mm	SF-QFN8-6X5A	OTP
SPANSION - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
S25FL004A	SO8 / 208mil	SF-SOP8-200A	
	USO8 / 5x6mm	SF-QFN8-6X5A	
S25FL004K	SO8 / 150mil	SF-SOP8-150A	
	SO8 / 208mil	SF-SOP8-200A	
S25FL008A	SO8 / 208mil	SF-SOP8-200A	
	USO8 / 5x6mm	SF-QFN8-6X5A	
S25FL008K	SO8 / 150mil	SF-SOP8-150A	
	SO8 / 208mil	SF-SOP8-200A	
S25FL016A	SO8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x8mm	SF-QFN8-8X6A	
	SO16 / 300mil	SF-SO16-300A	
S25FL016K	SO8 / 150mil	SF-SOP8-150A	
	SO8 / 208mil	SF-SOP8-200A	
S25FL032A	SO16 / 300mil	SF-SO16-300A	
S25FL032K	SO8 / 208mil	SF-SOP8-200A	
S25FL032P	SO8 / 208mil	SF-SOP8-200A	
	USO8 / 5x6mm	SF-QFN8-6X5A	
	WSO8 / 6x8mm	SF-QFN8-8X6A	
	SO16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
S25FL064A	SO16 / 300mil	SF-SO16-300A	
S25FL064K	SO8 / 208mil	SF-SOP8-200A	
	SO16 / 300mil	SF-SO16-300A	
S25FL064P	WSO8 / 6x8mm	SF-QFN8-8X6A	
	SO16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
S25FL064L	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 5x6mm	SF-QFN8-6X5A	
	SOIC16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
S25FL116K	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 5x6mm	SF-QFN8-6X5A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
S25FL132K	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 5x6mm	SF-QFN8-6X5A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	

	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
S25FL164K	SOIC8 / 208mil	SF-SOP8-200A	
	WSON8 / 5x6mm	SF-QFN8-6X5A	
	SOIC16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
S25FL127S	SOIC8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
S25FL128L	SOIC8 / 208mil	SF-SOP8-200A	
	WSON8 / 5x6mm	SF-QFN8-6X5A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
S25FL128P	WSON8 / 6x8mm	SF-QFN8-8X6A	
	SO16 / 300mil	SF-SO16-300A	
S25FL129P	WSON8 / 6x8mm	SF-QFN8-8X6A	
	SO16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
S25FL128S	WSON8 / 6x8mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
S25FL256L	WSON8 / 6x8mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
S25FL256S	WSON8 / 6x8mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
S25FL512S	SO8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x8mm	SF-QFN8-8X6A	
	SO16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
S25FL204K	SO8 / 150mil	SF-SOP8-150A	
	SO8 / 208mil	SF-SOP8-200A	
S25FL208K	SO8 / 150mil	SF-SOP8-150A	
	SO8 / 208mil	SF-SOP8-200A	
S25FL216K	SO8 / 150mil	SF-SOP8-150A	
	SO8 / 208mil	SF-SOP8-200A	
S25FS064S	SO8 / 208mil	SF-SOP8-200A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
S25FS128S	SO8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
S25FS256S	WSON8 / 6x8mm	SF-QFN8-8X6A	
	SO16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
S25FS512S	WSON8 / 6x8mm	SF-QFN8-8X6A	
	SO16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
S25HL256T	WSON8 / 6x8mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
S25HL512T	WSON8 / 6x8mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
S25HL01GT	SOIC16 / 300mil	SF-SO16-300A	
S25HS256T	WSON8 / 6x8mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
S25HS512T	WSON8 / 6x8mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
S25HS01GT	SOIC16 / 300mil	SF-SO16-300A	
S70FL256P	SO16 / 300mil	SF-SO16-300A	

	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
SST - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
SST25LF020A	SOIC8 / 150mil	SF-SOP8-150A	
	WSO8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
SST25LF040A	SOIC8 / 200mil	SF-SOP8-200A	
	WSO8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
SST25LF080A	SOIC8 / 200mil	SF-SOP8-200A	
	---	ISP	
SST25PF020B	SOIC8 / 150mil	SF-SOP8-150A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
SST25PF040C	SOIC8 / 150mil	SF-SOP8-150A	
	USO8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
SST25VF512	SOIC8 / 150mil	SF-SOP8-150A	
	WSO8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
SST25VF512A	SOIC8 / 150mil	SF-SOP8-150A	
	WSO8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
SST25VF010	SOIC8 / 150mil	SF-SOP8-150A	
	WSO8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
SST25VF010A	SOIC8 / 150mil	SF-SOP8-150A	
	WSO8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
SST25VF020	SOIC8 / 150mil	SF-SOP8-150A	
	WSO8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
SST25VF020B	SOIC8 / 150mil	SF-SOP8-150A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
SST25VF040	SOIC8 / 200mil	SF-SOP8-200A	
	WSO8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
SST25VF040B	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 200mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
SST25VF080	SOIC8 / 200mil	SF-SOP8-200A	
	---	ISP	
SST25VF080B	DIP8		
	SOIC8 / 200mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
SST25VF016B	SOIC8 / 200mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
SST25VF032B	SOIC8 / 200mil	SF-SOP8-200A	
	WSO8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
SST25VF064C	SOIC8 / 200mil	SF-SOP8-200A	
	WSO8 / 6x8mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
SST25WF512	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
SST25WF010	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
SST25WF020	SOIC8 / 150mil	SF-SOP8-150A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
SST25WF020A	SOIC8 / 150mil	SF-SOP8-150A	
	USO8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
SST25WF040	SOIC8 / 150mil	SF-SOP8-150A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	

SST25WF040B	SOIC8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
SST25WF080	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
SST25WF080B	SOIC8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
SST26VF016	SOIC8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
SST26VF016B	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 200mil	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
SST26VF032	SOIC8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
SST26VF032B	SOIC8 / 200mil	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
SST26VF064B	SOIC8 / 200mil	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	SOIC16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
SST26WF016B	SOIC8 / 150mil	SF-SOP8-150A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
SST26WF032	SOIC8 / 200mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
SST26WF064C	SOIC8 / 200mil	SF-SOP8-200A	
	DFN8 / 6x5mm	SF-QFN8-6X5A	
	SOIC16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	

ST - SPI Flash

Device Model	Package Type	Adapter Module	Remark
M25P05	SO8 / 150mil	SF-SOP8-150A	
M25P05-A	SO8 / 150mil	SF-SOP8-150A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M25P10	SO8 / 150mil	SF-SOP8-150A	
M25P10-A	SO8 / 150mil	SF-SOP8-150A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M25P20	SO8 / 150mil	SF-SOP8-150A	
M25P40	SO8 / 150mil	SF-SOP8-150A	
M25P80	SO8W	SF-SOP8-200A	
M25P16	SO8N	SF-SOP8-150A	
	SO8W	SF-SOP8-200A	
	MLP8 / 8x6mm	SF-QFN8-8X6A	
	SO16 / 300mil	SF-SO16-300A	
M25P32	SO8N	SF-SOP8-150A	
	SO8W	SF-SOP8-200A	
	MLP8 / 8x6mm	SF-QFN8-8X6A	
	SO16 / 300mil	SF-SO16-300A	
M25P64	SO8W	SF-SOP8-200A	
	MLP8 / 8x6mm	SF-QFN8-8X6A	
	SO16 / 300mil	SF-SO16-300A	
M25P128	SO8W	SF-SOP8-200A	
	MLP8 / 8x6mm	SF-QFN8-8X6A	
	SO16 / 300mil	SF-SO16-300A	
M25PE10(T7X)	SO8N	SF-SOP8-150A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M25PE20(T7X)	SO8N	SF-SOP8-150A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M25PE40(T7X)	SO8N	SF-SOP8-150A	
	SO8W	SF-SOP8-200A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M25PE80(T7X)	SO8N	SF-SOP8-150A	

	SO8W	SF-SOP8-200A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M25PE10(T9HX)	SO8N	SF-SOP8-150A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M25PE20(T9HX)	SO8N	SF-SOP8-150A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M25PE40(T9HX)	SO8N	SF-SOP8-150A	
	SO8W	SF-SOP8-200A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M25PE80(T9HX)	SO8N	SF-SOP8-150A	
	SO8W	SF-SOP8-200A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M25PE16	SO8N	SF-SOP8-150A	
	SO8W	SF-SOP8-200A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M25PX80	SO8N	SF-SOP8-150A	
	SO8W	SF-SOP8-200A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M25PX16	SO8N	SF-SOP8-150A	
	SO8W	SF-SOP8-200A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M25PX32	SO8W	SF-SOP8-200A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
	SO16W / 300mil	SF-SO16-300A	
M25PX64	SO8W	SF-SOP8-200A	
	MLP8 / 8x6mm	SF-QFN8-8X6A	
	SO16W / 300mil	SF-SO16-300A	
M45PE10	SO8 / 150mil	SF-SOP8-150A	
M45PE20	SO8 / 150mil	SF-SOP8-150A	
M45PE40	SO8N	SF-SOP8-150A	
	SO8W	SF-SOP8-200A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M45PE80	SO8N	SF-SOP8-150A	
	SO8W	SF-SOP8-200A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
M45PE16	SO8W	SF-SOP8-200A	
	MLP8 / 6x5mm	SF-QFN8-6X5A	
ST - SPI EEPROM			
Device Model	Package Type	Adapter Module	Remark
M95010-R	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M95010-W	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M95020-R	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	UFDFPN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
M95020-W	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M95040-DF	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M95040-DRE	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M95040-R	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	UFDFPN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
M95040-W	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M95080-DF	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M95080-DRE	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M95080-R	SO8 / 150mil	SF-SOP8-150A	

	TSSOP8 / 169mil	SF-TSP8-170A	
	UFDFPN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
M95080-W	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	UFDFPN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
M95160-DF	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	UFDFPN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
M95160-DRE	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M95160-R	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	UFDFPN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
M95160-W	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M95320-DF	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	UFDFPN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
M95320-DRE	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M95320-R	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	UFDFPN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
M95320-W	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M95640-DF	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	UFDFPN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
M95640-DRE	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M95640-R	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	UFDFPN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
M95640-W	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M95128-DF	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	UFDFPN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
M95128-DRE	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M95128-R	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	UFDFPN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
M95128-W	SO8 / 150mil	SF-SOP8-150A	
	---	ISP	
M95256-DF	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	UFDFPN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
M95256-DRE	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M95256-R	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	

M95256-W	UFD8FN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
M95512-DF	---	ISP	
	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	UFD8FN8 / 2x3mm	SF-QFN8-2X3A	
M95512-DRE	---	ISP	
	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M95512-R	---	ISP	
	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M95512-W	---	ISP	
	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M95M01-DF	---	ISP	
	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M95M01-R	---	ISP	
	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M95M02-DR	---	ISP	
	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	
M95M04-DR	---	ISP	
	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	---	ISP	

ST - 12C EEPROM

Device Model	Package Type	Adapter Module	Remark
M24C01-R	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
	---	ISP	
M24C01-W	DIP8		
	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M24C02-DRE	---	ISP	
	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M24C02-F	---	ISP	
	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	UFD8FN8 / 2x3mm	SF-QFN8-2X3A	
M24C02-R	---	ISP	
	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	UFD8FN8 / 2x3mm	SF-QFN8-2X3A	
M24C02-W	---	ISP	
	DIP8		
	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
M24C04-DRE	---	ISP	
	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M24C04-F	---	ISP	
	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	UFD8FN8 / 2x3mm	SF-QFN8-2X3A	
M24C04-R	---	ISP	
	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	UFD8FN8 / 2x3mm	SF-QFN8-2X3A	
M24C04-W	---	ISP	
	DIP8		
	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
M24C08-DRE	---	ISP	
	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	

	---	ISP	
M24C08-F	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	UFDFPN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
M24C08-R	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	UFDFPN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
M24C08-W	DIP8		
	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M24C16-DRE	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M24C16-F	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	UFDFPN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
M24C16-R	DIP8		
	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	UFDFPN8 / 2x3mm	SF-QFN8-2X3A	
M24C16-W	DIP8		
	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M24C32-DF	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	UFDFPN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
M24C32-DRE	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M24C32-F	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	UFDFPN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
M24C32-R	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M24C32-W	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M24C32-X	TSSOP8 / 169mil	SF-TSP8-170A	
	UFDFPN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
M24C64-DF	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	UFDFPN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
M24C64-DRE	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M24C64-F	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	UFDFPN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
M24C64-R	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M24C64-W	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M24128-BF	UFDFPN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
M24128-BR	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	

M24128-BW	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M24128-DF	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	UFD8FN8 / 2x3mm	SF-QFN8-2X3A	
M24128-DRE	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M24256-BF	TSSOP8 / 169mil	SF-TSP8-170A	
	UFD8FN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
M24256-BR	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M24256-BW	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M24256-DF	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	UFD8FN8 / 2x3mm	SF-QFN8-2X3A	
M24256-DR	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M24256-DRE	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M24512-DF	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	UFD8FN8 / 2x3mm	SF-QFN8-2X3A	
M24512-DRE	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M24512-R	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M24512-W	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M24M01-DF	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M24M01-R	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M24M02-DR	SO8 / 150mil	SF-SOP8-150A	
	---	ISP	
	---	ISP	
M34E02	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
M34E04	DFN8 / 2x3mm	SF-QFN8-2X3A	
M34E04B	DFN8 / 2x3mm	SF-QFN8-2X3A	

ST - Microwire EEPROM

Device Model	Package Type	Adapter Module	Remark
M93C46-DRE	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M93C46-R	DIP8		
	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
M93C46-W	DIP8		
	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
M93C56-DRE	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M93C56-R	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	

	---	ISP	
M93C56-W	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M93C66-DRE	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M93C66-R	UFDFPN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
M93C66-W	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M93C76-DRE	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M93C76-R	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M93C76-W	SO8 / 150mil	SF-SOP8-150A	
	---	ISP	
M93C86-DRE	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M93C86-R	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	UFDFPN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
M93C86-W	DIP8		
	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
	---	ISP	
M93S46	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
M93S46-R	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
M93S46-W	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
M93S56	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
M93S56-R	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
M93S56-W	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
M93S66	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
M93S66-R	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
M93S66-W	SO8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 169mil	SF-TSP8-170A	
Sunmoon - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
SM24C02	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
TearDevices - SPI EEPROM			
Device Model	Package Type	Adapter Module	Remark
TD25C128	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
TD25C256	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
TD25C512	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
TD25CM01	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	

TD25CM02	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
TearDevices - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
TD24C02	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
TD24C04	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
TD24C08	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
TD24C16	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
TD24C32	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
TD24C64	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
TD24C128	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
TD24C256	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
TD24C512	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
TD34C02	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
TD34C04	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
TERACHIP - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
T25Q128FV	SOP8 / 208mil	SF-SOP8-200A	OTP
	VSOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
TMC - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
TMC24A01	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
TMC24A02	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
TMC24A04	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
TMC24A08	DIP8		

	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
TMC24A16	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
TMC - Microwire EEPROM			
Device Model	Package Type	Adapter Module	Remark
TMC93LC46	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
TMC93LC56	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
TMC93LC57	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
TMC93LC66	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
TMC93LC86	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
TsingTeng - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
NH25D32HA	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
NH25D64HA	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
NH25D128HA	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
TH25D-20HA	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
TH25D-20LA	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
TH25D-20UA	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
TH25D20UB	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
TH25D-40HA	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
TH25D-40LA	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
TH25D-40UA	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
TH25D-40HB	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
TH25D40UC	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	

	USON8 / 3x2mm	SF-QFN8-2X3A	
TH25Q-40HA	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSOP8 / 6x5mm	SF-QFN8-6X5A	
TH25Q-40LA	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSOP8 / 6x5mm	SF-QFN8-6X5A	
TH25Q-40UA	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSOP8 / 6x5mm	SF-QFN8-6X5A	
TH25Q-80HA	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSOP8 / 6x5mm	SF-QFN8-6X5A	
TH25Q-80HB	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSOP8 / 6x5mm	SF-QFN8-6X5A	
TH25Q-80LA	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSOP8 / 6x5mm	SF-QFN8-6X5A	
TH25Q-80UA	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSOP8 / 6x5mm	SF-QFN8-6X5A	
TH25Q-16HB	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	WSOP8 / 6x5mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
TH25Q-16UA	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	WSOP8 / 6x5mm	SF-QFN8-6X5A	
TH25Q-16UB	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	WSOP8 / 6x5mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
TH25Q-32HA	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	WSOP8 / 6x5mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
TH25Q80UC	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
TH25Q16UC	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
TH25Q64HA	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	WSOP8 / 6x5mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
TH25Q128HA	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	WSOP8 / 6x5mm	SF-QFN8-6X5A	

	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
TsingTeng - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
TH24C-128UA	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	MSOP8	SF-MSP8-3X3A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
Turbo_IC - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
TU24C01B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
TU24C02B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
TU24C04B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
TU24C08B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
TU24C16B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
TU24C32	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
TU24C64B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
TU24C128	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
TU24C256	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
Turbo_IC - Microwire EEPROM			
Device Model	Package Type	Adapter Module	Remark
TU93C46	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
TU93C56	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
TU93C66	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
UCUN Technology - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
UC25HD40B	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
UC25HQ40	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
UC25HQ80	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
UC25HQ80B	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
UC25HQ16	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
UC25HQ32	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	

UC25HQ64	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
UC25IQ64	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
UC25IQ128	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
UC25WD10	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
UC25WD20	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
UC25WD40IB	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
UC25WQ80	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	

Unigen - I2C EEPROM

Device Model	Package Type	Adapter Module	Remark
UG24C01	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
UG24C02	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
UG24C04	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
UG24C08	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
UG24C16	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	

Unigen - Microwire EEPROM

Device Model	Package Type	Adapter Module	Remark
UG93C46-A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
UG93C46-B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
UG93C56-A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
UG93C56-B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
UG93C56-C	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
UG93C66-A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
UG93C66-B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	

Wave Systems - I2C EEPROM

Device Model	Package Type	Adapter Module	Remark
24CW01	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
24CW02	DIP8		

24CW03	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
24CW04	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
24CW05	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
24CW08	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
24CW09	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
24CW16	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
24CW17	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
24CW32	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
24CW33	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
24CW64	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
24CW65	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
24CW128	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
24CW129	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
24CW256	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		
24CW257	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DIP8		

Wave Systems - Microwire EEPROM

Device Model	Package Type	Adapter Module	Remark
W93C46	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
W93C46B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
W93C56	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
W93C56B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
W93C66	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
W93C66B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
W93C86	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
W93C86B	DIP8		

	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
Westberry - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
WB25HQ40	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
WB25HQ80	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
WB25WQ40	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
WB25WQ80	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
WB25WQ16	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
Westberry - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
WB24C01	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
WB24C02	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
WB24C04	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
WB24C08	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
WB24C16	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
WB24C32	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
WB24C64	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
WB24C128	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
WB24C256	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
WB24C512	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	

WB24CM01	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
WB24CM02	SOP8 / 150mil	SF-SOP8-150A	OTP
	---	ISP	
WB34C02	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
WB34C04	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
Winbond - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
W25H256JVxxM	WSO8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
W25H512JVxxM	WSO8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
W25H512NWxxM	WSO8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
W25H01NW	WSO8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
W25Q10EW	SOIC8 / 150mil	SF-SOP8-150A	OTP
	VSOP8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
W25Q10RL	SOIC8 / 150mil	SF-SOP8-150A	OTP
	VSOP8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
W25Q20BW	SOIC8 / 150mil	SF-SOP8-150A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
W25Q20CL	SOIC8 / 150mil	SF-SOP8-150A	
	VSOP8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
W25Q20EW	SOIC8 / 150mil	SF-SOP8-150A	OTP
	VSOP8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
W25Q20RL	SOIC8 / 150mil	SF-SOP8-150A	OTP
	VSOP8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
W25Q40BL	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
W25Q40BV	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
W25Q40BW	SOIC8 / 150mil	SF-SOP8-150A	OTP
	VSOP8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
W25Q40CL	SOIC8 / 208mil	SF-SOP8-200A	OTP
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	

W25Q40CV	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
W25Q40EW	SOIC8 / 150mil	SF-SOP8-150A	OTP
	VSOP8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
W25Q40RVxxxQ	---	ISP	OTP
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
W25Q40RL	---	ISP	OTP
	SOIC8 / 150mil	SF-SOP8-150A	
	VSOP8 / 150mil	SF-SOP8-150A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
W25Q41EW	SOIC8 / 150mil	SF-SOP8-150A	OTP
	USON8 / 2x3mm	SF-QFN8-2X3A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
W25Q80BL	DIP8		OTP
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
W25Q80BV	---	ISP	OTP
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
W25Q80BW	---	ISP	OTP
	SOIC8 / 150mil	SF-SOP8-150A	
	VSOP8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
W25Q80DV	WSON8 / 6x5mm	SF-QFN8-6X5A	OTP
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
W25Q80EW	---	ISP	OTP
	SOIC8 / 150mil	SF-SOP8-150A	
	VSOP8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
W25Q81EW	WSON8 / 6x5mm	SF-QFN8-6X5A	OTP
	---	ISP	
	SOIC8 / 150mil	SF-SOP8-150A	
	VSOP8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
W25Q80JVxxxQ	USON8 / 2x3mm	SF-QFN8-2X3A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
	SOIC8 / 150mil	SF-SOP8-150A	
	VSOP8 / 150mil	SF-SOP8-150A	
W25Q80RVxxxQ	SOIC8 / 208mil	SF-SOP8-200A	OTP
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
	SOIC8 / 150mil	SF-SOP8-150A	
W25Q16V	SOIC8 / 208mil	SF-SOP8-200A	

	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOIC16 / 300mil	SF-SO16-300A	
	---	ISP	
W25Q16BV	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOIC16 / 300mil	SF-SO16-300A	
	---	ISP	
W25Q16CL	DIP8		OTP
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOIC16 / 300mil	SF-SO16-300A	
	---	ISP	
W25Q16CV	DIP8		OTP
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
W25Q16DV	DIP8		OTP
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
W25Q16DW	---	ISP	OTP
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOIC16 / 300mil	SF-SO16-300A	
	---	ISP	
W25Q16FW	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	USO8 / 2x3mm	SF-QFN8-2X3A	
	USO8 / 4x3mm	SF-QFN8-4X3B	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
W25Q16JL	SOIC8 / 150mil	SF-SOP8-150A	OTP
	VSOP8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	USO8 / 2x3mm	SF-QFN8-2X3A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
W25Q16JVxxxQ	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	USO8 / 2x3mm	SF-QFN8-2X3A	
	USO8 / 4x3mm	SF-QFN8-4X3B	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
W25Q16JVxxxM	SOIC8 / 150mil	SF-SOP8-150A	OTP
	VSOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
W25Q16JWxxxQ	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	USO8 / 4x3mm	SF-QFN8-4X3B	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
W25Q16JWxxxM	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	USO8 / 4x3mm	SF-QFN8-4X3B	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	

W25Q16RVxxxQ	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	OTP
	---	ISP	
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
W25Q32V	WSO8 / 6x5mm	SF-QFN8-6X5A	OTP
	---	ISP	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOIC16 / 300mil	SF-SO16-300A	
W25Q32BV	---	ISP	OTP
	DIP8		
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
W25Q32FV	SOIC16 / 300mil	SF-SO16-300A	OTP
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
	DIP8		
W25Q32DW	SOIC8 / 208mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	---	ISP	
W25Q32FW	SOIC8 / 208mil	SF-SOP8-200A	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	---	ISP	
W25Q32JVxxxQ	DIP8		OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOIC16 / 300mil	SF-SO16-300A	
W25Q32JVxxxM	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	OTP
	---	ISP	
	SOIC8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
W25Q32JWxxxQ	---	ISP	OTP
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
W25Q32JWxxxM	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	OTP
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
W25Q32RVxxxQ	VSOP8 / 208mil	SF-SOP8-200A	OTP
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
W25Q64BV	---	ISP	OTP
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
W25Q32RVxxxQ	---	ISP	OTP
	DIP8		
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	

	---	ISP	
W25Q64CV	DIP8		OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
W25Q64DW	SOIC8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	---	ISP	
W25Q64FVxxxF	DIP8		OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
W25Q64FVxxxG	DIP8		OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
W25Q64FVxxxQ	DIP8		OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
W25Q64JVxxxQ	DIP8		OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
W25Q64JVxxxM	DIP8		OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	---	ISP	
W25Q64FW	SOIC8 / 208mil	SF-SOP8-200A	OTP
	VSOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	---	ISP	
W25Q64JWxxxQ	SOIC8 / 208mil	SF-SOP8-200A	OTP
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
W25Q64JWxxxM	SOIC8 / 208mil	SF-SOP8-200A	OTP
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
W25Q128BV	WSON8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
W25Q128FVxxG	DIP8		OTP
	SOIC8 / 208mil	SF-SOP8-200A	

	WS0N8 / 6x5mm	SF-QFN8-6X5A	
	WS0N8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
W25Q128FVxxP	DIP8		OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	WS0N8 / 6x5mm	SF-QFN8-6X5A	
	WS0N8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
W25Q128FVxxQ	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	OTP
	---	ISP	
	DIP8		
	SOIC8 / 208mil	SF-SOP8-200A	
	WS0N8 / 6x5mm	SF-QFN8-6X5A	
	WS0N8 / 8x6mm	SF-QFN8-8X6A	
W25Q128FW	SOIC16 / 300mil	SF-SO16-300A	OTP
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
	SOIC8 / 208mil	SF-SOP8-200A	
	WS0N8 / 6x5mm	SF-QFN8-6X5A	
W25Q128JVxxQ	WS0N8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
	SOIC8 / 208mil	SF-SOP8-200A	
W25Q128JVxxM	WS0N8 / 6x5mm	SF-QFN8-6X5A	OTP
	WS0N8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
W25Q128JWxxQ	SOIC8 / 208mil	SF-SOP8-200A	OTP
	WS0N8 / 6x5mm	SF-QFN8-6X5A	
	WS0N8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
W25Q128JWxxM	---	ISP	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	WS0N8 / 6x5mm	SF-QFN8-6X5A	
	WS0N8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
W25Q12PWxxQ	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	OTP
	---	ISP	
	SOIC8 / 208mil	SF-SOP8-200A	
	WS0N8 / 6x5mm	SF-QFN8-6X5A	
	WS0N8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
W25Q12PWxxM	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	OTP
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
	SOIC8 / 208mil	SF-SOP8-200A	
	WS0N8 / 6x5mm	SF-QFN8-6X5A	
	WS0N8 / 8x6mm	SF-QFN8-8X6A	
W25Q256FVxxF	SOIC16 / 300mil	SF-SO16-300A	OTP
	WS0N8 / 8x6mm	SF-QFN8-8X6A	

	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
W25Q256FVxxG	WSON8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
W25Q256FVxxQ	WSON8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
W25Q256JVxxQ	WSON8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
W25Q256JVxxM	WSON8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
W25Q256JVxxN	WSON8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
W25Q256JWxxQ	WSON8 / 6x5mm	SF-QFN8-6X5A	OTP
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
W25Q256JWxxM	WSON8 / 6x5mm	SF-QFN8-6X5A	OTP
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
W25Q257FV	WSON8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOIC16 / 300mil	SF-SO16-300A	
	---	ISP	
W25Q257JVxxQ	WSON8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOIC16 / 300mil	SF-SO16-300A	
	---	ISP	
W25Q512JVxxQ	WSON8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
W25Q512JVxxM	WSON8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
W25Q512NWxxQ	WSON8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
W25Q512NWxxM	WSON8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
W25Q512NWxxN	WSON8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
W25Q01JVxxQ	WSON8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	

W25Q01JVxxM	WS08 / 8x6mm	SF-QFN8-8X6A	OTP
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
W25Q01JVxxN	WS08 / 8x6mm	SF-QFN8-8X6A	OTP
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
W25Q01NWxxQ	WS08 / 8x6mm	SF-QFN8-8X6A	OTP
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
W25Q01NWxxM	WS08 / 8x6mm	SF-QFN8-8X6A	OTP
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
W25M512JVxxQ	WS08 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
W25M512JWxxQ	WS08 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
W25R64FV	DIP8		OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	WS08 / 6x5mm	SF-QFN8-6X5A	
	WS08 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
W25R64JVxxxQ	DIP8		OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	WS08 / 6x5mm	SF-QFN8-6X5A	
	WS08 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
W25R64JVxxxN	DIP8		OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	WS08 / 6x5mm	SF-QFN8-6X5A	
	WS08 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
W25R64JW	DIP8		OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	WS08 / 6x5mm	SF-QFN8-6X5A	
	WS08 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
W25R128FV	DIP8		OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WS08 / 6x5mm	SF-QFN8-6X5A	
	WS08 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
W25R128JV	SOIC8 / 208mil	SF-SOP8-200A	OTP
	WS08 / 6x5mm	SF-QFN8-6X5A	
	WS08 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
W25R128JW	DIP8		OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WS08 / 6x5mm	SF-QFN8-6X5A	
	WS08 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	

W25R256JV	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	OTP
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
W25R256JW	---	ISP	OTP
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
W25R512JV	WSO8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOIC16 / 300mil	SF-SO16-300A	
	---	ISP	
W25R512NW	WSO8 / 8x6mm	SF-QFN8-8X6A	OTP
	---	ISP	
W25X05CL	SOIC8 / 150mil	SF-SOP8-150A	
	VSOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USO8 / 2x3mm	SF-QFN8-2X3A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
W25X10V	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
W25X10L	SOIC8 / 150mil	SF-SOP8-150A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
W25X10AL	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
W25X10A(V)	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
W25X10BL	SOIC8 / 150mil	SF-SOP8-150A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
W25X10BV	SOIC8 / 150mil	SF-SOP8-150A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
W25X10CL	SOIC8 / 150mil	SF-SOP8-150A	
	VSOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USO8 / 2x3mm	SF-QFN8-2X3A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
W25X20V	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
W25X20L	SOIC8 / 150mil	SF-SOP8-150A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
W25X20AL	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
W25X20A(V)	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
W25X20BL	SOIC8 / 150mil	SF-SOP8-150A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
W25X20BV	SOIC8 / 150mil	SF-SOP8-150A	

	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
W25X20CL	SOIC8 / 150mil	SF-SOP8-150A	
	VSOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USO8 / 2x3mm	SF-QFN8-2X3A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
W25X20CV	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	USO8 / 2x3mm	SF-QFN8-2X3A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
W25X21CL	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
W25X40L	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
W25X40V	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
W25X40A(V)	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
W25X40AL	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
W25X40BL	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
W25X40BV	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
W25X40CV	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	VSOP8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	USO8 / 2x3mm	SF-QFN8-2X3A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
W25X40CL	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	VSOP8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	USO8 / 2x3mm	SF-QFN8-2X3A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
W25X41CL	---	ISP	
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
W25X80L	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
W25X80V	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
W25X80AL	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	

	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
W25X80A(V)	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
W25X16V	DIP8		
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOIC16 / 300mil	SF-SO16-300A	
	---	ISP	
W25X16AV	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOIC16 / 300mil	SF-SO16-300A	
	---	ISP	
W25X16AL	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOIC16 / 300mil	SF-SO16-300A	
	---	ISP	
W25X16BV	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOIC16 / 300mil	SF-SO16-300A	
	---	ISP	
W25X32AV	DIP8		
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	SOIC16 / 300mil	SF-SO16-300A	
W25X32BV	---	ISP	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
W25X32V	---	ISP	
	DIP8		
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
W25X64BV	---	ISP	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
W25X64V	---	ISP	
	DIP8		
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
W25M121AV-NOR	---	ISP	OTP
W35T51NW	WSO8 / 8x6mm	SF-QFN8-8X6A	
W74M64FV	SOIC16 / 300mil	SF-SO16-300A	OTP
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	DIP8		
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
W74M12FV	SOIC16 / 300mil	SF-SO16-300A	OTP
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
	DIP8		
	SOIC8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	

W74M12JV	SOIC8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
W74M12JW	SOIC8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
W74M25FV	WSON8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
W74M25JV	WSON8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
W74M25JW	WSON8 / 6x5mm	SF-QFN8-6X5A	OTP
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOIC16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
W77Q64JWxxQ	SOIC8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	

Wing Shing - I2C EEPROM

Device Model	Package Type	Adapter Module	Remark
WS24C02	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
WS24W02	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
WS24W04	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
WS24W08	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
WS24W16	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
WS24W32	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
WS24W64	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	

XICOR - SPI EEPROM

Device Model	Package Type	Adapter Module	Remark
X25020	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
X25040	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
X25041	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
X25043	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
X25045	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
X25080	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
X25160	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	

X25320	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
X25640	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
X25642	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
X25650	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
X25128	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
X25138	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	---	ISP	
X5043	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
X5045	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	MSOP8	SF-MSP8-3X3A	
	---	ISP	
XMC - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
XM25EH512DxxT	WSO8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
XM25LU32CxxG	SOP8 / 208mil	SF-SOP8-200A	OTP
	USO8 / 2x3mm	SF-QFN8-2X3A	
	USO8 / 4x3mm	SF-QFN8-4X3B	
	WSO8 / 5x6mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
XM25LU32CxxQ	SOP8 / 208mil	SF-SOP8-200A	OTP
	USO8 / 2x3mm	SF-QFN8-2X3A	
	USO8 / 4x3mm	SF-QFN8-4X3B	
	WSO8 / 5x6mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
XM25LU64CxxG	SOP8 / 208mil	SF-SOP8-200A	OTP
	USO8 / 4x3mm	SF-QFN8-4X3B	
	WSO8 / 5x6mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
XM25LU64CxxQ	SOP8 / 208mil	SF-SOP8-200A	OTP
	USO8 / 4x3mm	SF-QFN8-4X3B	
	WSO8 / 5x6mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
XM25LU128C	SOP8 / 208mil	SF-SOP8-200A	OTP
	USO8 / 4x3mm	SF-QFN8-4X3B	
	WSO8 / 5x6mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
XM25QE16B	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	USO8 / 2x3mm	SF-QFN8-2X3A	
	USO8 / 4x3mm	SF-QFN8-4X3B	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
XM25QE32C	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	

	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 5x6mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
XM25QH10B	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
XM25QH20B	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
XM25QH40B	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
XM25QH80B	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
XM25QH16B	DIP8		OTP
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
XM25QH16C	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 5x6mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
XM25QH32B	SOIC8 / 208mil	SF-SOP8-200A	OTP
	---	ISP	
XM25QH32C	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
XM25QH32DxxG	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 5x6mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
XM25QH32DxxQ	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 5x6mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
XM25QH64A	DIP8		OTP
	SOP8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	VDFN8 / 6x8mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
XM25QH64BxxG	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 5x6mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	

XM25QH64BxxQ	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 5x6mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
XM25QH64CxxG	SOP8 / 208mil	SF-SOP8-200A	OTP
	VSOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 5x6mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
XM25QH64CxxQ	SOP8 / 208mil	SF-SOP8-200A	OTP
	VSOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 5x6mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
XM25QH64DxxG	SOP8 / 208mil	SF-SOP8-200A	OTP
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 5x6mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
XM25QH64DxxQ	SOP8 / 208mil	SF-SOP8-200A	OTP
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 5x6mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
XM25QH128A	SOP8 / 208mil	SF-SOP8-200A	OTP
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 5x6mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
XM25QH128BxxG	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 5x6mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
XM25QH128BxxQ	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 5x6mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
XM25QH128C	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
XM25QH128DxxG	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 5x6mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
XM25QH128DxxQ	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 5x6mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
XM25QH256B	WSON8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 5x6mm	SF-QFN8-6X5A	
	WSON8 / 6x8mm	SF-QFN8-8X6A	
XM25QH256CxxQ	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 5x6mm	SF-QFN8-6X5A	
	WSON8 / 6x8mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	SOP8 / 208mil	SF-SOP8-200A	

XM25QH512CxxQ	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	OTP
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	WSON8 / 6x8mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SOP16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
XM25QH256DxxQ	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	OTP
	WSON8 / 5x6mm	SF-QFN8-6X5A	
	WSON8 / 6x8mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SOP16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
XM25QH512D	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	OTP
	WSON8 / 6x8mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SOP16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
XM25QH01D	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	OTP
	WSON8 / 6x8mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SOP16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
XM25QU20B	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	OTP
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
XM25QU40B	---	ISP	OTP
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
XM25QU80B	---	ISP	OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
XM25QU16B	---	ISP	OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
XM25QU16C	---	ISP	OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 5x6mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
XM25QU32C	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	OTP
	---	ISP	
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	USON8 / 4x3mm	SF-QFN8-4X3B	
XM25QU64A	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
XM25QU64BxxG	DIP8		
	SOP8 / 200mil	SF-SOP8-200A	
	VSON8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	---	ISP	
XM25QU64BxxQ	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 5x6mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
XM25QU64CxxG	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 5x6mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
XM25QU64CxxG	SOP8 / 208mil	SF-SOP8-200A	OTP
	VSON8 / 208mil	SF-SOP8-200A	

	WSO8 / 5x6mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
XM25QU64CxxQ	SOP8 / 208mil	SF-SOP8-200A	OTP
	VSOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 5x6mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
XM25QU128BxxG	SOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 5x6mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
XM25QU128BxxQ	SOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 5x6mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
XM25QU128C	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	USO8 / 4x3mm	SF-QFN8-4X3B	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
XM25QU256B	WSO8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
XM25QU256CxxQ	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSO8 / 5x6mm	SF-QFN8-6X5A	
	WSO8 / 6x8mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
XM25QU512CxxQ	WSO8 / 5x6mm	SF-QFN8-6X5A	OTP
	WSO8 / 6x8mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
XM25QU512DxxQ	WSO8 / 6x8mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
XM25QU01DxxQ	WSO8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
XM25QW16C	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	USO8 / 2x3mm	SF-QFN8-2X3A	
	USO8 / 4x3mm	SF-QFN8-4X3B	
	WSO8 / 5x6mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
XM25QW32C	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	USO8 / 2x3mm	SF-QFN8-2X3A	
	USO8 / 4x3mm	SF-QFN8-4X3B	
	WSO8 / 5x6mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
XM25QW64C	---	ISP	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 5x6mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
XM25QW128C	---	ISP	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	

	WS0N8 / 5x6mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
XM25RH64CxxQ	SOP8 / 208mil	SF-SOP8-200A	OTP
	VSOP8 / 208mil	SF-SOP8-200A	
	US0N8 / 4x3mm	SF-QFN8-4X3B	
	WS0N8 / 5x6mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
XM25RH128CxxQ	SOP8 / 208mil	SF-SOP8-200A	OTP
	WS0N8 / 5x6mm	SF-QFN8-6X5A	
	WS0N8 / 6x8mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
XM25RH256CxxQ	SOP8 / 208mil	SF-SOP8-200A	OTP
	WS0N8 / 5x6mm	SF-QFN8-6X5A	
	WS0N8 / 6x8mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
XM25RH512CxxQ	WS0N8 / 6x8mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
XM25RU128CxxQ	SOP8 / 208mil	SF-SOP8-200A	OTP
	WS0N8 / 5x6mm	SF-QFN8-6X5A	
	WS0N8 / 6x8mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
XM25RU256CxxQ	SOP8 / 208mil	SF-SOP8-200A	OTP
	WS0N8 / 5x6mm	SF-QFN8-6X5A	
	WS0N8 / 6x8mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
XM25RU512CxxQ	WS0N8 / 6x8mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
XM25UH16C	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	US0N8 / 2x3mm	SF-QFN8-2X3A	
	US0N8 / 4x3mm	SF-QFN8-4X3B	
	WS0N8 / 5x6mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
XM25UH32C	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	US0N8 / 4x3mm	SF-QFN8-4X3B	
	WS0N8 / 5x6mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
XM25UH128C	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	US0N8 / 4x3mm	SF-QFN8-4X3B	
	WS0N8 / 6x5mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
XTX - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
BN25F04A	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
PN25F04A	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
PN25F04C	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
PN25F08	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
PN25F08B	SOP8 / 150mil	SF-SOP8-150A	

	SOP8 / 208mil	SF-SOP8-200A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
PN25F16	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
PN25F16B	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
PN25F32	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
PN25F64B	DIP8		OTP
	SOP8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	VDFN8 / 6x8mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
PN25F128B	SOP8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
XT25BF128F	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	---	ISP	
XT25BQ64D	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
XT25BQ128D	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
XT25F01B	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	VSOP8 / 200mil	SF-SOP8-200A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
XT25F01C	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
XT25F01D	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
XT25F02B	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	VSOP8 / 200mil	SF-SOP8-200A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
XT25F02C	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
XT25F02D	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
XT25F02E	SOP8 / 150mil	SF-SOP8-150A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	

XT25F04B	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	VSOP8 / 200mil	SF-SOP8-200A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
XT25F04C	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
XT25F04D	SOP8 / 150mil	SF-SOP8-150A	OTP
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
XT25F08B	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
XT25F08F	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
XT25F16B	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
XT25F16F	SOP8 / 150mil	SF-SOP8-150A	OTP
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
XT25F32B	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 200mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	DFN8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
XT25F32E	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	USON8 / 3x4mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
XT25F32F(3*1024)	SOP8 / 150mil	SF-SOP8-150A	OTP
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
XT25F32F(2*1024)	SOP8 / 150mil	SF-SOP8-150A	OTP
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
XT25F64B	SOP8 / 208mil	SF-SOP8-200A	OTP
	VSOP8 / 208mil	SF-SOP8-200A	
	DFN8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
XT25F64F	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
XT25F128A	DIP8		
	SOP8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	VDFN8 / 6x8mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SQ16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
XT25F128B	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	

XT25F128F	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	OTP
	---	ISP	
	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
XT25F256B	WSON8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
	SOP8 / 8x6mm	SF-QFN8-8X6A	
XT25BF256B	SOP16 / 300mil	SF-SO16-300A	OTP
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
XT25Q01B	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
XT25Q01D	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN6(1.2*1.2)	SF-DFN6-1212A	
XT25Q02B	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
XT25Q02D	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
XT25Q04B	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
XT25Q04C	SOP8 / 200mil	SF-SOP8-200A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
XT25Q08B	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
XT25Q08D	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
XT25Q16C	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
XT25Q16D	DFN8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
XT25Q32B	DFN8 / 2x3mm	SF-QFN8-2X3A	OTP
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
XT25Q32F	VSOP8 / 208mil	SF-SOP8-200A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	OTP
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 150mil	SF-SOP8-150A	

	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
XT25Q64B	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	DFN8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
XT25Q64D	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
XT25Q64F	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
XT25Q128B	SOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
XT25Q128D	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
XT25Q128F	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
XT25Q256F	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
XT25Q512F	WSON8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	BGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
XT25W01D	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
XT25W02D	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
XT25W02E	SOP8 / 150mil	SF-SOP8-150A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN6(1.2*1.2)	SF-DFN6-1212A	
	---	ISP	
XT25W04D	SOP8 / 150mil	SF-SOP8-150A	OTP
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
XT25W08B	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
XT25W16C	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
XT25W32B	---	ISP	OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	

	DFN8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
XT25W32F	SOP8 / 150mil	SF-SOP8-150A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
XT25W64B	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	DFN8 / 4x3mm	SF-QFN8-4X3B	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
XT25W512B	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
XT25W1GB	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
FT25H08	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FT25H16	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
FT25H32	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	---	ISP	
FT25H64	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	---	ISP	
FT25L08	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
YMC - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
Y24LC02	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
Y24LC04	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
Y24LC08	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
Y24LC16	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
YMC - Microwire EEPROM			
Device Model	Package Type	Adapter Module	Remark
Y93LC46-A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
Y93LC46-B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
Y93LC66	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
Zbit Semiconductor - SPI Flash			
Device Model	Package Type	Adapter Module	Remark
HS25LQ64A	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	

	---	ISP	
HS25Q32D	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
HS25Q64D	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	---	ISP	
ZB25D20A	SOP8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
ZB25D40	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
ZB25D40B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
ZB25D40C	---	ISP	OTP
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
ZB25D80	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
ZB25D80B	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
ZB25D80C	---	ISP	OTP
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
ZB25D16	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
ZB25F256A	---	ISP	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SQ16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
ZB25LD20A	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN6(1.2*1.2)	SF-DFN6-1212A	
ZB25LD40B	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
ZB25LQ40C	---	ISP	OTP
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	

	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
ZB25LQ80A	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
ZB25LQ16A	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
ZB25LQ16B	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 4x3mm	SF-QFN8-4X3B	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
ZB25LQ32A	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
ZB25LQ32B	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
ZB25LQ64A	SOP8 / 208mil	SF-SOP8-200A	OTP
	DFN8 / 4x3mm	SF-QFN8-4X3B	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
ZB25LQ128A	SOP8 / 208mil	SF-SOP8-200A	OTP
	VSOP8 / 208mil	SF-SOP8-200A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
ZB25LQ128C	SOP8 / 208mil	SF-SOP8-200A	OTP
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
ZB25Q16B	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 4x3mm	SF-QFN8-4X3B	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
ZB25Q64D	---	ISP	
	DIP8		
	SOP8 / 200mil	SF-SOP8-200A	
	VDFN8 / 5x6mm	SF-QFN8-6X5A	
	VDFN8 / 6x8mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	

ZB25Q256A	SOP8 / 208mil	SF-SOP8-200A	OTP
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SQ16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
ZB25S512A	DFN8 / 5x6mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SQ16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
ZB25VF64C	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	DFN8 / 4x3mm	SF-QFN8-4X3B	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SQ16-300A	
	---	ISP	
ZB25VF128D	SOP8 / 208mil	SF-SOP8-200A	OTP
	VSOP8 / 208mil	SF-SOP8-200A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SQ16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
ZB25VQ40	---	ISP	OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
ZB25VQ40A	---	ISP	OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
ZB25VQ40B	---	ISP	OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 4x3mm	SF-QFN8-4X3B	
ZB25VQ80A	---	ISP	OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
ZB25VQ80B	---	ISP	OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 4x3mm	SF-QFN8-4X3B	
ZB25VQ16A	---	ISP	OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
ZB25VQ16C	---	ISP	OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 4x3mm	SF-QFN8-4X3B	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	

	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
ZB25VQ16E	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 4x3mm	SF-QFN8-4X3B	
	---	ISP	
ZB25VQ32B	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 4x3mm	SF-QFN8-4X3B	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
ZB25VQ32D	---	ISP	OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 4x3mm	SF-QFN8-4X3B	
ZB25VQ64A	---	ISP	OTP
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
ZB25VQ64C	---	ISP	OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	DFN8 / 4x3mm	SF-QFN8-4X3B	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
ZB25VQ64D	---	ISP	OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	DFN8 / 4x3mm	SF-QFN8-4X3B	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
ZB25VQ128A	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	OTP
	---	ISP	
	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
ZB25VQ128D	WSON8 / 6x5mm	SF-QFN8-6X5A	OTP
	---	ISP	
	SOP8 / 208mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
ZB25VQ128D(DTR)	DFN8 / 8x6mm	SF-QFN8-8X6A	OTP
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
	SOP8 / 208mil	SF-SOP8-200A	
ZB25WD20A	VSOP8 / 208mil	SF-SOP8-200A	
	DFN8 / 5x6mm	SF-QFN8-6X5A	
	DFN8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
ZB25WD40A	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	

	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	
ZB25WD40C	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
ZB25WD80B	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
ZB25WD80C	---	ISP	OTP
	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
ZB25WQ40A	---	ISP	OTP
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 4x3mm	SF-QFN8-4X3B	
ZB25WQ80A	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 4x3mm	SF-QFN8-4X3B	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
ZB25WQ16A	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	OTP
	---	ISP	
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	DFN8 / 2x3mm	SF-QFN8-2X3A	
	DFN8 / 4x3mm	SF-QFN8-4X3B	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	TFBGA24 / 8x6mm (ball 5x5)	SF-BGA24-B55A	
	---	ISP	

ZemPro Electronic - SPI Flash

Device Model	Package Type	Adapter Module	Remark
TS25L512A	SOP8 / 150mil	SF-SOP8-150A	
TS25L010A	SOP8 / 150mil	SF-SOP8-150A	
TS25L020A	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
TS25L80P	SO8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
TS25L16P	SO8 / 150mil	SF-SOP8-150A	
	SOP8 / 200mil	SF-SOP8-200A	
TS25L16AP	SOP8 / 208mil	SF-SOP8-200A	
TS25L16BP	SOP8 / 208mil	SF-SOP8-200A	

Zetta - SPI Flash

Device Model	Package Type	Adapter Module	Remark
ZD25D20	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
ZD25D40	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
ZD25D40B	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	

	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
ZD25D40C	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USO8 / 3x2mm	SF-QFN8-2X3A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
ZD25D80	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	USO8 / 3x2mm	SF-QFN8-2X3A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
ZD25D16	DIP8		
	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
ZD25LD40B	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USO8 / 3x2mm	SF-QFN8-2X3A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
ZD25LQ64A	SOP8 / 200mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
ZD25LQ128A	SOP8 / 200mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	WSO8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
ZD25Q40A	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USO8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
ZD25Q80C	SOIC8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	USO8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
ZD25Q16A	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USO8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
ZD25Q16B	SOP8 / 150mil	SF-SOP8-150A	
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
ZD25Q16C	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USO8 / 2x3mm	SF-QFN8-2X3A	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
ZD25Q32A	SOIC8 / 150mil	SF-SOP8-150A	
	SOIC8 / 208mil	SF-SOP8-200A	
	USO8 / 3x4mm	SF-QFN8-4X3B	
	WSO8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
ZD25Q32C	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	

	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
ZD25Q64A	SOIC8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
ZD25Q64B	SOP8 / 200mil	SF-SOP8-200A	
	VSOP8 / 208mil	SF-SOP8-200A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 8x6mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	TFBGA24 / 8x6mm (ball 6x4)	SF-BGA24-B64A	
	---	ISP	
ZD25Q64C	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
ZD25Q128C	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
ZD25Q256A	SOP8 / 208mil	SF-SOP8-200A	OTP
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	WSON8 / 6x8mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
ZD25Q512A	WSON8 / 6x8mm	SF-QFN8-8X6A	
	SOP16 / 300mil	SF-SO16-300A	
	---	ISP	
ZD25WD20B	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
ZD25WD20C	SOP8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	---	ISP	
ZD25WD40B	SOP8 / 150mil	SF-SOP8-150A	OTP
	SOP8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 3x2mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
ZD25WQ80B	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
ZD25WQ80C	SOIC8 / 150mil	SF-SOP8-150A	OTP
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
ZD25WQ16A	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
ZD25WQ16B	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
ZD25WQ16C	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
ZD25WQ32C	SOIC8 / 150mil	SF-SOP8-150A	OTP
	SOIC8 / 208mil	SF-SOP8-200A	

	TSSOP8 / 173mil	SF-TSP8-170A	
	USON8 / 2x3mm	SF-QFN8-2X3A	
	WSON8 / 6x5mm	SF-QFN8-6X5A	
	---	ISP	
Zetta - I2C EEPROM			
Device Model	Package Type	Adapter Module	Remark
ZD24C02A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
ZD24C02B	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
ZD24C04A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
ZD24C08A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
ZD24C32A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
ZD24C64A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
ZD24C128A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
ZD24C256A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	SOT23-5	SF-SOT23-6A	
	---	ISP	
ZD24C512A	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	
ZD24C1MA	DIP8		
	SOIC8 / 150mil	SF-SOP8-150A	
	TSSOP8 / 173mil	SF-TSP8-170A	
	UDFN8 / 2x3mm	SF-QFN8-2X3A	
	---	ISP	