


159821 DPZ-32-80-P-A Twin cylinder - Series: All



159821 DPZ-32-80-P-A Twin cylinder - Series: All

Pos.	Part no.	Type	Note	Qty.	Unit
A	383825	DPZ - 32-P-A Set of wearing parts	Spare parts: 3, 5, 7, 9, 12	1	PC
1	343459	DPZ- 32- P-A Grooved nut	Tightening torque 23 Nm / 17.0 lbf ft Use locking compound 8181256 CYBERBOND TM44	2	PC
2	343455	DPZ-32 End plate		1	PC
3		DPZ-20/25/32-... Buffer element	Not available separately, see position A	1	PC
4	348265	J-33 Retaining ring		4	PC
5	338266	WIFC4-16X23X4,8-TPE-U Wiper seal	Lubricate with 684474 LUB-KC1 during assembly	2	PC
6	348242	ARA-16-S0129,8-B Piston rod	Use locking compound 8181256 CYBERBOND TM44 Tightening torque 17 Nm / 12.5 lbf ft	2	PC
7		B-30X1,5-N-NBR75 O-ring ISO3601	Not available separately, see position A Lubricate with 684474 LUB-KC1 during assembly	4	PC
8	354372	DPZ- 32- P-A Bearing		2	PC
9		DPZ/DPZJ-32 Piston seal	Not available separately, see position A Lubricate with 684474 LUB-KC1 during assembly	4	PC
10	348268	DPZ-32 Piston magnet		2	PC
11	348080	29,2X23,5X4,1 Ring magnet		2	PC
12		B-10X1,5-N-NBR75 O-ring ISO3601	Not available separately, see position A Lubricate with 684474 LUB-KC1 during assembly	2	PC
13	348266	DPZ-32 Piston		2	PC
14	348267	10,4X18X4-1.0715 Ring		2	PC
15		ISO 8675-M10X1-04 Hex nut	Not available Use locking compound 8181256 CYBERBOND TM44	2	PC
16	210977	ISO 4017-M6X20-8.8 Hexagon head screw	Tightening torque 23 Nm / 17.0 lbf ft	1	PC
17	200601	DIN 439-B-M6-04 Hex nut		1	PC
18			Not available	1	PC
19	343457	DPZ-32 End cap		1	PC