


623390124040

Power relay 16 A



This image is for illustrative purposes only and therefore may not represent the exact product code. Colours may vary.

Technical Description:

High Power relay, Plug-in socket version, 3 pole, CO (nPDT), 16 A, AgSnO2, DC coil, 12 V, operating from 9.6 to 13.2 V, rated power 1.3 W, resistance 110 Ω, consumption 109 mA, holding voltage 7.2 V, must drop-out voltage 1.2 V, option: Lockable test button + mechanical indicator, ambient temperature from -40 to +70 °C

[BROWSE PRODUCT PAGE](#)

Technical Features:

Commercial Description:	16 A power relay, 3 CO or NO contacts (NO contact gap ≥ 3 mm), socket mounting (92 Series) or directly via Faston 187 (4.8 x 0.5 mm). Equipped with AC or DC coil, LED, lockable test button and standard mechanical indicator. Reinforced insulation between coil and contacts according to EN 60335-1; clearance/creepage separation 6/8 mm.
Supply:	DC coil
Nominal voltage DC:	12 V
Rated power DC:	1.3 W
Operating range DC:	9.6 ... 13.2 V
Contact configuration:	3 pole, CO (nPDT)
Rated current (contacts):	16
Rated contact voltage:	250 V AC
Electrical life:	100000 cycles
Insulation coil/contacts:	6 kV
Ambient temperature range:	-40 ... 70 °C
Dimensions:	49.1x35.8x38.2 mm
Certifications and quality approvals (according to type):	       

The information, technical details, data and features contained in this document are subject to change or modification at any time.\nIt is for information purposes only and does not form\nthe basis of a contract.

Need more information?
[Contact our sales](#) [Find a dealer](#)