

ALBS 200/20K

Heavy duty wheel, with Blickle Besthane® Soft polyurethane tread, with aluminium wheel centre

EAN 4047526694531

ID 694539

Customs tariff number 87169090



Tread:

- high-quality polyurethane elastomer Blickle Besthane® Soft, hardness 75 Shore A
- extra-thick elastic tread for excellent operational comfort
- very good floor preservation, low-noise operation
- very low rolling resistance
- **high dynamic load capacity**
- high abrasion resistance
- high cut and tear propagation resistance
- colour blue, non-marking, non-staining
- excellent chemical connection with the wheel centre

Wheel centre:

- die-cast aluminium

Other features:

- high chemical resistance to many aggressive substances
- operating temperature: -20 °C to +70 °C, temporarily up to +90 °C, reduced load capacity over +40 °C

Technical data:

Wheel Ø (D)	⊕	200 mm
Wheel width	⊥	50 mm
Load capacity at 4 km/h	⊞	750 kg
Load capacity at 6 km/h	⊞	520 kg
Load capacity at 10 km/h	⊞	370 kg
Load capacity at 16 km/h	⊞	300 kg
Load capacity (static)	⊞	1,875 kg
Bearing type	⊙	ball bearing
Axle bore Ø (d)		20 mm
Hub keyway (T1)	⊕	60 mm
Temperature resistance min		-20 °C
Temperature resistance max		70 °C
Tread and tyre hardness		75 Shore A
Unit weight	⊞	1.6 kg
Non-marking		✓
Non-staining		✓
Antistatic	⊞	×
ESD		×
Electrically conductive	⊞	×
Corrosion-resistant		×
Heat-resistant	⊞	×
Tread hydrolysis-resistant		✓
Suitable for autoclaves		×



Tread and tyre hardness

■ ■ ■ ■ □ □ 75 Shore A

Rolling resistance

■ ■ ■ ■ ■ ■ excellent

Wear resistance

■ ■ ■ ■ ■ □ very good

Operating noise / floor surface preservation

■ ■ ■ ■ ■ □ very good

