





## **Contact Us**

**United Kingdom** sales@nightsearcher.co.uk Tel. +44 023 9238 9774 www.nightsearcher.co.uk Export Enquiries

exportsales@nightsearcher.com Tel. +48 616 242 998 www.nightsearcher.com



## NightSearcher



Rotational light heads





30m Beam



1.5 to 4.5hrs **Runtime** 



**1m Impact** Resistance



**IPX4 Rated** 

Can be used continuously when plugged into **AC Mains** 



## **SPECIFICATIONS**

**Battery** 

**LED** 








**Cool Light / Warm Light** 





**Magnetic base** 



**Water and dust resistance - IPX4** 



Mode High Medium **AC Mains** Low **Lumen Output** 2000lm 1200lm 700lm 1200lm 4.5h 2.5h 1.5h **Runtime** Continuous 25m 25m **Beam Distance** 15m 30m

Charger

**Material Quality** 

**Product Code: NSTOWERPRO-2K** 

7.4V-2000mAh

Cool Light + Warm Light

Weight: 1.8kg

8.4V-1.5A

Aluminium + ABS