

Hook Clip w/ 4 mm Banana (female) Jack (socket)



Specification

Electrical protection	1000 V CAT IV , reinforced insulation, pollution degree 1, 2 or 3 , 20 A
Operating Temperature Range	-20 °C...+80 °C

RND Part Nr.	Colour
RND 350-00115	Black
RND 350-00116	Red

