

KERN 336-37

Individual weight, OIML Class F2, 10 kg, Block, stainless steel

KERN

Category

Brand	KERN
Product category	Individual weight
Product group	OIML F2
Product family	336

Measuring System

Test weight - nominal value	10 kg
Weight OIML class	F2
Permissible tolerance according to OIML (+/-)	160 mg
OIML-compliant	✓
Test weight - Density [Min] (OIML)	6400
Test weight - Density [Max] (OIML)	10700

Construction

Shape weight	Block
Dimensions weight (W×D×H)	193×96×117 mm
Material	stainless steel
Adjustment method	Adjusting cavity - Seal

Services (optional)

Article number for DAkkS calibration	962-444
Article number for guaranteed plus-deviation	921-444

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	193×96×117 mm
Shipping method	Parcel service
Net weight approx.	10 kg

Gross weight approx.	10 kg
Shipping weight	10 kg
Shipping volume weight	0,4 kg

Optional cases

Case - Plastic article number	nicht verfügbar
Case - Aluminium article number	346-070-600
Case - Wood article number	nicht verfügbar

Product information

GTIN/EAN number	4045761232815
Trade number	84239090
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

