

KERN 367-07

KERN

Individual weight, OIML Class M3, 100 g, Knob, stainless steel fine turned



Category

Brand	KERN
Product category	Individual weight
Product group	OIML M3
Product family	367

Measuring System

Test weight - nominal value	100 g
Test weight - volume uncertainty (cm ³)	0,2409
Weight OIML class	M3
Conformity assessment possible	no
Test weight - volume (cm ³)	11,9048
Permissible tolerance according to OIML (+/-)	50 mg
OIML-compliant	✓
Test weight - Density [Min] (OIML)	1500
Test weight - Density (kg/m ³)	7950
Test weight - Density uncertainty (kg/m ³)	140

Construction

Shape weight	Knob
Dimensions (Ø×H)	22×37 mm
Material	stainless steel fine turned
Adjustment method	Adjusting cavity - Seal

Services (optional)

Article number for DAkkS calibration	962-637
--------------------------------------	---------

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	22×22×37 mm
Shipping method	Parcel service
Net weight approx.	0,10 kg
Gross weight approx.	0,10 kg
Shipping weight	0,1 kg
Shipping volume weight	0,1 kg

Optional cases

Case - Plastic article number	347-070-400
Case - Aluminium article number	317-070-600
Case - Wood article number	337-070-200

Product information

GTIN/EAN number	4045761257269
Trade number	84239090
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

