

Features

- Hardened stainless steel frame and measuring jaws
- Thumb roll adjustment
- Knurled locking screw
- Depth rod
- Clear LCD Display
- Large 11mm digits
- Inch/Metric conversion Origin setting
- Resolution: 0.01mm / 0.0005"
- Repeatability: 0.01mm / 0.0005"
- 4 Way measurement: Individual serial numbers
- Power: 1 x Silver oxide battery LR44 - 1.55v
- Operating temperature: 5 - 40°C
- Relative humidity: Maximum 80%

RS PRO Digital Calliper 300mm, 0.01mm Resolution, Metric/Imperial

RS Stock No.: 905806



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Electronic Digital Vernier Calliper with LCD Display

RS PRO stainless steel digital calliper is with a 4-way measurement. This electronic vernier is proficient at measuring component parts' outside, inside, step and depth during test & measurement applications.

Our electronic calliper has a measurement range between 0 mm and 300 mm and a resolution of 0.0005 in, 0.01 mm. It uses a linear encoder to measure internal and external distances, it's highly accurate and much easier to use than traditional analogue devices.

The conversion scale can be changed from inches to millimetres at the touch of a button and the floating zero feature allows you to read the increments without calculation. This reading is then shown on an LCD display with 11 mm digits making it easy to read.

The RS PRO calliper is a great tool packed with features that make it a joy to use. This measuring device is a must-have accessory for your toolbox. Calibration options are available.

Key Features

- Hardened stainless steel frame and measuring jaws
- Thumb roll adjustment
- Knurled locking screw
- Depth rod
- Clear LCD Display
- Large 11mm digits
- Inch/Metric conversion Origin setting
- Resolution: 0.01mm / 0.0005"
- Repeatability: 0.01mm / 0.0005"
- 4 Way measurement: Individual serial numbers
- Power: 1 x Silver oxide battery LR44 - 1.55v
- Operating temperature: 5 - 40°C
- Relative humidity: Maximum 80%

General Specifications

Product Type	Calliper
Imperial/Metric	Metric, Imperial
Display Type	Digital
Accuracy	$\pm 0.02\text{mm}$ ($\leq 100\text{mm}$) $\pm 0.03\text{mm}$ ($\leq 200\text{mm}$) $\pm 0.04\text{mm}$ ($\leq 300\text{mm}$)
Resolution	0.01 mm
Measurement Capacity	300mm
Calliper Type	Digital
Standards/Approvals	No

Approvals

Declarations	REACH DoC
Standards Met	CE

Similar Products

Stock No.	Brand	Product Name	Meas. Capacity	Resolution	Imperial/Metric
XXX-XXXX 905803	RS PRO	Digital Calliper	150mm	0.01mm	Metric, Imperial
XXX-XXXX 905805	RS PRO	Digital Calliper	200mm	0.01mm	Metric, Imperial
XXX-XXXX 905806	RS PRO	Digital Calliper	300mm	0.01mm	Metric, Imperial
243-6615	RS PRO	Digital Calliper	150mm	0.01mm	Metric, Imperial
243-6617	RS PRO	Digital Calliper	200mm	0.01mm	Metric, Imperial
243-6801	RS PRO	Digital Calliper, UKAS	150mm	0.01mm	Metric, Imperial
243-6828	RS PRO	Digital Calliper, UKAS	300mm	0.01mm	Metric, Imperial
841-2518	RS PRO	Digital Calliper	150mm	0.01mm	Metric, Imperial
243-6620	RS PRO	Digital Calliper	300mm	0.01mm	Metric, Imperial
877-1788	RS PRO	Digital Calliper	600mm	0.01mm	Metric, Imperial
243-6815	RS PRO	Digital Calliper, UKAS	200mm	0.01mm	Metric, Imperial
243-6808	RS PRO	Digital Calliper, UKAS	150mm	0.01mm	Metric, Imperial
243-6821	RS PRO	Digital Calliper, UKAS	200mm	0.01mm	Metric, Imperial

Stock No.	Brand	Product Name	Meas. Capacity	Resolution	Imperial/Metric
243-6618	RS PRO	Digital Calliper	200mm	0.01mm	Metric, Imperial
243-6616	RS PRO	Digital Calliper	150mm	0.01mm	Metric, Imperial
247-161	RS PRO	Digital Calliper	150mm	0.01mm	Metric, Imperial
123-0916	RS PRO	Digital Calliper	1m	0.01mm	Metric, Imperial
480-699	RS PRO	Digital Calliper, UKAS	150mm	0.01mm	Metric, Imperial
247-206	RS PRO	Digital Calliper	150mm	0.03mm	Metric, Imperial
136-8102	RS PRO	Digital Calliper	150mm	0.01mm	Metric, Imperial
243-6621	RS PRO	Digital Calliper	300mm	0.01mm	Metric, Imperial
243-6835	RS PRO	Digital Calliper, UKAS	300mm	0.01mm	Metric, Imperial
192-5872	RS PRO	Digital Calliper, UKAS	150mm	0.01mm	Metric, Imperial