

Features

- Ø24mm cutout
- Metal body
- Solder contacts

RS PRO Panel Mount 4 Way Metal XLR Connector

RS Stock No.: 885307, 885308, 885921, 885922



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

These professional, high quality XLR audio connectors are can be used in numerous applications including professional and consumer audio, broadcast and industrial uses.

They feature a robust metal body and gold plated contacts. There is a male and female version. The female model has a locking latch.

They are panel mounting and fit a standard Ø24mm panel hole.

General Specifications

Mounting Type	Panel Mounting
Body Orientation	Straight
No of Contacts	4
Type of Contact	Solder

Mechanical Specifications

Body Material	Zinc Alloy
Contact Material	Brass
Contact Plating	Gold Plated
Insertion Life	>2000 insertions
Insertion force	10-80N

Electrical Specifications

Contact Resistance	$\leq 7\text{m}\Omega$
Insulation Resistance	$\geq 5000\text{M}\Omega$
Withstand Voltage	1400V

Approvals

Standards Met	RoHS
---------------	------

Similar Products

Stock No.	Brand	Product Name	Gender
885307, 885308	RS PRO	4 Pin XLR connector	Female
885921, 885922	RS PRO	4 Pin XLR connector	Male

