



Connectors > Terminal Blocks & Strips > Terminal Block & Strip Accessories > Terminal Block & Strip Mounting & Retention Accessories



Mounting & Retention Accessory Type: Rail

Product Length: 914.4 mm [36 in]

Features

Body Features

Primary Product Material	Steel
Mounting & Retention Accessory Type	Rail

Dimensions

Product Length	914.4 mm[36 in]
----------------	-----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUN 2020 (209) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits



as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought




TE Part #2-1416010-7
RE034024



TE Part #CAT-104MTA-NGPNR
Nylon Gold Plated Receptacle: 2.54 mm, no Mating Alignment



TE Part #2-1416010-6
RE034012



TE Part #2-1879666-0
H8 210K 0.1% 15PPM



TE Part #NB20274001
VERSAFIT-3/16-0-SP



TE Part #1-1825002-3
ADF0804=DIP SWT,FLUSH,THRU/HL



TE Part #2-1676914-4
YR1 0.1% 402R



TE Part #3-111196-3
80 RCPT SYSTEM 50 30 DPLX



TE Part #6-104068-6
80 SYSTEM 50 HDR DRST SHRD

Documents

- CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1437381-8_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1437381-8_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1437381-8_A.3d_stp.zip](#)

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

BUCHANAN NEMA Terminal Blocks - Catalogue

English

BUCHANAN TERMINAL BLOCKS CATALOG - BARRIER STRIPS

English