

Features

- Unique 4-hole slider hasp engineered for superior safety and functionality.
- **Ultra-Thin 3 mm Shackle** – Designed specifically for small and tight electrical isolation points.
- **Non-Conductive Construction** – Hard nylon shackle and ABS body ensure full di-electric protection.
- **Support Up to 4 Padlocks** – Allows multi-user lockout for group maintenance and compliance.
- **Spark-Proof & Lightweight** – Ideal for electrical environments where metal hasps are unsuitable.

RS PRO Di-Electric Slider Hasp for 4 Locks with 3mm shackle

RS Stock No.: 0750824



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- *Di-Electric 4-Hole Slider Hasp features a 3 mm thin, spark-proof shackle designed to secure electrical panel enclosures with small isolation points.*
- *Engineered for tight-clearance applications such as electrical panels, MCBs, and compact electrical switchgear.*
- *Built using hard nylon (shackle) and ABS (body) to ensure complete non-conductivity and safe handling.*
- *Can accommodate up to 4 LOTO padlocks, making it suitable for multi-person lockout operations.*
- *Available in red colour for easy identification and visual safety management.*

General Specifications

Type	Lockout Hasp
Material	Nylon Shackle & ABS Body
Colour	Red
Padlock holes	04
Package	BOPP

Mechanical Specifications

Dia (Jaw Size)	24 / 44 mm
Body - Width	61mm
Body - Height	105mm
Shackle Dia	3mm
Weight	36 Grams

Operation Environment Specifications

Withstand temperature	-20 °C to +80 °C
-----------------------	------------------