

KERN YKA-03N

Mains adapter 100 V - 240 V, 50 / 60 Hz, EURO UK US CH

KERN



Category

Brand	KERN
Product category	Balance
Product group	Power adapter

Construction

Design	rectangular
Dimension (W×D×H)	59×41×34,5 mm
Material	plastic
Cable length	1,8 m

Power Supply

Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	9 V, 300 mA
Power socket for mains adapter	Hollow plug, inside minus, Ø inside 2,1 mm, Ø outside 5,5 mm, long 12 mm

Environmental conditions

Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Approval

CE mark	✓
---------	---

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	90×70×70 mm

Shipping method	Parcel service
Net weight approx.	0,15 kg
Gross weight approx.	0,15 kg
Shipping weight	0,133 kg
Shipping volume weight	0,1 kg

Product information

GTIN/EAN number	4045761362871
Trade number	85044095
REACH classification	no prohibited substances

Pictograms

STANDARD

