



**CABLE CUTTER INSULATED 1000V 80
MM**

Z-324-80

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:51:46





DESCRIPTION

CABLE CUTTER INSULATED 1000V 80 MM

USE

For cutting all LV network cables.

FEATURES

Tool can be locked/unlocked using a simple dial.

Worn blades can be replaced.

Cutting capacities indicated on the tool.

Cutting capacity:

- Flexible copper cables: 630 mm²
- Multi-strand copper/aluminium cables: 840 mm²
- Multi-strand copper power cables: 3 x 240 mm²
- Multi-strand aluminium power cables: 4 x 240 mm²

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:51:46



STANDARDS / DIRECTIVES

CEI 60900, NF EN 60900

SPECIFIC DATA

Designation	CABLE CUTTER INSULATED 1000V 80 MM
Sales reference	Z-324-80
L (mm)	590
Weight (g)	3700
C1 (mm²)	840
C2 (mm²)	1000
C3 (mm²)	70
A1 (mm²)	Ã~ 80
A2 (mm²)	
Guarantee	O SAM TOOL guarantee.

Guarantee applied

O | SAM TOOL guarantee.

Guarantee without time limit on the tools used under normal conditions.

[>> Find out more](#)

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:51:46

