

VLEA 530/5

Heavy duty hub fitting wheel with super-elastic solid rubber tyres and pressed steel rim

EAN 4047526264130

ID 264135

Customs tariff number 87169090



Tyre:

- super-elastic solid rubber, steel-wire reinforced, hardness 70 Shore A
- 3-component tyre, highly-elastic cushion layer, abrasion-resistant tread
- very good operational comfort
- very good floor preservation, low-noise operation
- colour black

Rim:

- heavy pressed steel
- centre piece with a central hole and fitting holes
- fitting holes with domed anchor recesses
- zinc-plated, blue-passivated, Cr6-free

Other features:

- fitted using domed anchor nuts and bolts in accordance with DIN 74361
- chemical resistance to many aggressive substances, except oils
- operating temperature: -30 °C to +80 °C, temporarily up to +100 °C, reduced load capacity over +60 °C
- The wheel and tyre dimensions provided here apply to new tyres that are not bearing a load. The dimensions may change when they are in use.

Technical data:

Wheel Ø (D)	☉	525 mm
Wheel width	⊥	140 mm
Tyre dimensions		6.00-9
Rim dimension		4.00E-9
Load capacity at 4 km/h	⚖	1,885 kg
Load capacity at 6 km/h	⚖	1,885 kg
Load capacity at 25 km/h	⚖	1,450 kg
Load capacity (static)	⚖	4,712 kg
Bearing type	☉	hub fitting
Number of fixing holes	⊗	5
Fixing hole Ø		16.5 mm
Central hole Ø (d)	☉	110 mm
PCD (d1)	☉	145 mm
Temperature resistance min		-30 °C
Temperature resistance max		80 °C
Tread and tyre hardness		70 Shore A
Unit weight	⚖	32 kg
Non-marking		×
Non-staining		×
Antistatic	⚡	×
ESD		×
Electrically conductive	⚡	×
Corrosion-resistant		×



Tread and tyre hardness

■ ■ ■ □ □ □ 70 Shore A

Rolling resistance


■ ■ ■ □ □ good

Wear resistance

■ ■ ■ □ □ good

Operating noise / floor surface preservation

■ ■ ■ ■ □ very good



Heat-resistant	✖	✖
Suitable for autoclaves		✖