

590 - 592

chiavi dinamometriche a lettura diretta serraggi destrorsi e sinistrorsi Toll. $\pm 3\%$

UNI EN ISO 6789



	art.	Nm	Kgfm	lbf.in	■	A mm	L mm	kg	لبا
005900001	590	0,8÷4	0,08÷0,4	7÷35	1/4	60	253	0,52	0,1
005900003	590/1	2,5÷12,5	0,25÷1,25	21÷110	1/4	60	253	0,52	0,5
005920005	592/3	5÷25	0,5÷2,5	44÷220	3/8	70	253	0,52	1,0
005920007	592/4	8÷40	0,8÷4	72÷360	3/8	70	253	0,52	1,0