



Published on April 23, 2026

Sales Management Section 2, Sales Management Department

E-Series-PMX Compact DC Regulated Power Supply  
Sales start announcement

We would like to express our sincere gratitude for your continued support. We wish your company continued prosperity. Dear Sir/Madam

We have started selling the E-PMX series of compact DC regulated power supplies.

A DC power supply with a series dropper design. CC (constant current/constant voltage), high-performance constant voltage, compact, series E-PMX

It comes standard with C232RS, USB, LAN, and other essential communication interfaces for system upgrades, while being low noise.

Monitoring is possible. Control is available via browser, including smartphones such as tablets, and via a PC or LAN connection.

It ensures high versatility. It is also equipped with memory functions, various protection functions, monitor output, analog external control, and more.

Sincerely,

member

Main Features

- Memory sequencing function •
- Bleeder circuit selection function, output off timer •
- Anomaly detection is possible with the Ctrl external function, Watchdog•
- Interface standard equipped C232RS / USB / LAN (LAN•
- External analog remote control •
- Comprehensive protection features •
- (Equipped on the V35 system, V18 system (with sensing function and remote control)

Lineup •



E Series - PMX

| 仕様<br>形名    | 標準価格     |          | 出力      |         | リップル・ノイズ    |             | 電源変動     |          | 負荷変動     |          | 入力 (AC)       |            | 質量<br>(約)<br>kg |
|-------------|----------|----------|---------|---------|-------------|-------------|----------|----------|----------|----------|---------------|------------|-----------------|
|             | 税抜       | 税込       | CV<br>V | CC<br>A | CV<br>mVrms | CC<br>mArms | CV<br>mV | CC<br>mA | CV<br>mV | CC<br>mA | 電圧<br>V ± 10% | 電力<br>約 VA |                 |
| PMX18-2E    | ¥ 72,000 | ¥ 79,200 | 0 ~ 18  | 0 ~ 2   | 0.5         | 1           | ± 1      | ± 5      | ± 2      | ± 5      | 100           | 150        | 5               |
| PMX18-5E    | ¥ 78,000 | ¥ 85,800 | 0 ~ 18  | 0 ~ 5   | 0.5         | 2           | ± 1      | ± 5      | ± 5      | ± 5      | 100           | 310        | 6               |
| PMX35-1E    | ¥ 72,000 | ¥ 79,200 | 0 ~ 35  | 0 ~ 1   | 0.5         | 1           | ± 3      | ± 5      | ± 3      | ± 5      | 100           | 150        | 5               |
| PMX35-3E    | ¥ 78,000 | ¥ 85,800 | 0 ~ 35  | 0 ~ 3   | 0.5         | 1           | ± 3      | ± 5      | ± 4      | ± 5      | 100           | 310        | 6               |
| PMX70-1E    | ¥ 80,000 | ¥ 88,000 | 0 ~ 70  | 0 ~ 1   | 1           | 1           | ± 5      | ± 2      | ± 5      | ± 5      | 100           | 230        | 6               |
| PMX110-0.6E | ¥ 85,000 | ¥ 93,500 | 0 ~ 110 | 0 ~ 0.6 | 2           | 1           | ± 7      | ± 2      | ± 7      | ± 5      | 100           | 210        | 6               |

Thank you for your cooperation. If you have any questions, please contact our sales office.

That's all.

