

KERN YKA-40

Power adapter (EURO UK CH)

KERN



Category

Brand	KERN
Product category	Balance
Product group	Power adapter

Construction

Material	plastic
----------	---------

Functions

IP protection - complete device	-
---------------------------------	---

Power Supply

Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO UK CH
Input voltage power supply / power [Max]	100 - 240 V AC 50/60 Hz 0.5 A
Input voltage device / power [Max]	9 V, 600 mA
Power socket for mains adapter	Hollow plug, inside plus, Ø outside 5,5 mm, Ø inside 2,1 mm, long 10,5 mm

Environmental conditions

Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Approval

CE mark	✓
---------	---

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	93×67×70 mm

Shipping method	Parcel service
Net weight approx.	0,15 kg
Gross weight approx.	0,20 kg
Shipping weight	0,16 kg
Shipping volume weight	0,1 kg

Product information

GTIN/EAN number	4045761259041
Trade number	85044095
REACH classification	no prohibited substances

Pictograms

STANDARD

