


RNA2205-2RSR [🔗](#)

Galet de roulement

Yoke type track rollers RNA22...-2RSR, single row needle roller bearings with particularly thick-walled outer ring, needle roller and cage assembly, without inner ring, without axial guidance of the outer ring, lip seal radial sealing action on both sides, inner ring can be mounted separately

Information technique



Votre alternative produit actuelle

joint	2RSR	Joint frottant des deux côtés
profile bague extérieure	R500	Diamètre extérieur sphérique (Standard)

dimensions principale & données de performance

D	52 mm	Diamètre extérieur
F _w	30 mm	Diamètre sous rouleaux
C	17,8 mm	Largeur, bague extérieure
C _{r w}	14.500 N	Charge dyn. de base, radiale
C _{0r w}	20.300 N	Charge stat. de base, radiale
C _{ur w}	2.950 N	Limite à la fatigue, radiale
n _{D G}	1.800 1/min	Vitesse pour une lubrification à la graisse
≈m	166,2 g	Poids

Dimensions

D _{1 min}	38 mm	Dimension de montage minimum
r _{min}	1 mm	Dimension minimum de chanfrein
R	500 mm	Rayon bague extérieure profile externe



Caractéristiques



Effort radial



Lubrification à vie, sans entretien



Lubrification à la graisse



Étanche des 2 côtés