

KERN 326-05

KERN

Individual weight, OIML Class F1, 20 g, Eco Shape, stainless steel polished



Dimensions packaging (W×D×H)	13×13×22 mm
Shipping method	Parcel service
Net weight approx.	0,05 kg
Gross weight approx.	0,05 kg
Shipping weight	0,1 kg
Shipping volume weight	0,1 kg

Optional cases

Case - Plastic article number	347-050-400
Case - Aluminium article number	317-050-600
Case - Wood article number	317-050-100

Product information

GTIN/EAN number	4045761223707
Trade number	84239090
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION



Category

Brand	KERN
Product category	Individual weight
Product group	OIML F1
Product family	326

Measuring System

Test weight - nominal value	20 g
Weight OIML class	F1
Permissible tolerance according to OIML (+/-)	0,25 mg
OIML-compliant	✓
Test weight - Density [Min] (OIML)	6600
Test weight - Density [Max] (OIML)	10100
Test weight - Density (kg/m ³)	7950
Test weight - Density uncertainty (kg/m ³)	140

Construction

Shape weight	Eco Shape
Dimensions (Ø×H)	13×22 mm
Material	stainless steel polished
Adjustment method	Polishing

Services (optional)

Article number for DAkkS calibration	962-435
Article number for guaranteed plus-deviation	921-435

Packing & Shipping

Delivery time	1 d
---------------	-----