

# M18 BOS125-502B

## M18™ 125 MM RANDOM ORBITAL SANDER

High performance motor delivers 14,000 to 24,000 sanding strokes per minute for faster material removal

REDLINK™ overload protection electronics in tool and battery pack deliver best in class system durability

Variable speed wheel with 6 speed settings allows the correct speed to be set for different types of material

Dust extraction box with internal filter keeps dust contained and managed

Universal hook and loop sanding pad allows easy changing of sanding discs

Lightweight - 1.6 kg

Vacuum adaptor supplied fits directly to all MILWAUKEE® dust extractors

REDLITHIUM™ battery pack provides superior pack construction, electronics and fade-free performance to deliver more run time and more work over pack life

Flexible battery system: works with all MILWAUKEE® M18™ batteries



**REDLITHIUM™**



|                                      |                                                      |
|--------------------------------------|------------------------------------------------------|
| No load speed (rpm)                  | 12,000                                               |
| Oscillation rate (opm)               | 14,000 - 24,000                                      |
| Oscillation diameter (mm)            | 2.4                                                  |
| Sanding pad size (mm)                | 125                                                  |
| Weight with battery pack (EPTA) (kg) | 1.6 (M18 B5)                                         |
| Kit included                         | 2 x M18 B5 Battery packs, M12-18 C Charger, Tool bag |
| Article Number                       | 4933464230                                           |