

Features

- Provides high vacuum flow.
- Evacuates large volumes of air, liquid and small materials quickly.
- Ideal for dirty environments.
- Can be used for lifting/positioning of porous products.

RS PRO Vacuum Generator

RS Stock No.: 0765416



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is

rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- G 1/8 Inlet Connections
- 1/4 in. NPTF Outlet Connections
- Provides high vacuum flow
- Evacuates large volumes of air, liquid and small materials quickly
- Ideal for dirty environments
- Can be used for lifting/positioning of porous products

General Specifications

Nozzle Diameter	19.1mm
Maximum Suction Flow	3398L/min
Maximum Vacuum Pressure	847mbar
Maximum Operating Temperature	+204°C
Minimum Operating Temperature	-73°C
Evacuation Time (1 Litre)	3.4s
Operating Pressure	3.5bar
Features	Silencer
Manufacturer Series	S80
Orifice	6.4mm

Other Specifications

