



PRODUCT-DETAILS

BVWV-P090
COND FTNG 90D PG9 NW10 IP68 CSA BLK



General Information	
Extended Product Type:	BVWV-P090
Product ID:	7TAA292150R0444
EAN:	7630030228285
Catalog Description:	COND FTNG 90D PG9 NW10 IP68 CSA BLK
Long Description:	VW Connector 90 Degree Elbow, PG Thread for IP68 - Thread PG 9, Fits to Conduit Size NW/Metric 10/12, Color Black
Display Name:	BVWV-P090

Additional Information	
Product Main Type:	PMA Flexible Cable Protection
Application:	For Cable Protection Systems In a Wide Range of Applications
Product Type:	Fittings for Nylon Flexible Conduits

Ordering

EAN:	7630030228285
UPC:	786209954015

Technical

Number of Batteries:	0
Color:	Black
Material:	High-Grade Specially Formulated Polyamide/Nylon 6
Size:	PG09

Environmental

WEEE Category:	Product Not in WEEE Scope
----------------	---------------------------

Container Information

Package Level 1 Units:	500 EA
Package Level 1 EAN:	7630030228285
Package Level 1 Height:	200 mm 7.874 in
Package Level 1 Depth / Length:	399.999 mm 15.748 in
Package Level 1 Width:	299.999 mm 11.811 in

Certificates and Declarations

Data Sheet, Technical Information:	BVWV-P090
Instructions and Manuals:	BVWV-P090
Declaration of Conformity - CE:	9AKK107680A0674

External Classifications and Standards

ETIM 8:	EC001176 - Screw connection for corrugated plastic hose
ETIM 9:	EC001176 - Screw connection for corrugated plastic hose
UNSPSC:	39131717

Categories

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems

