


Hook 8 R30, black similar to RAL 9005



REACH RoHS

The hooks for when things get a little shaky: Curved and sheathed in PVC, the stainless steel loop of Hook 8 R30 provides the best hold. The two prongs of Hook 8 R30 are ideal for holding hammers, screwdrivers and pliers close to hand ready for their next use. A gap of 60 mm between the non-slip loops is big enough to ensure tools can be removed and returned with the greatest of ease. The sheathing provides a soft contact surface and a secure hold for tools.

Scope of Delivery

- 1 Wire, St, stainless
- 1 PVC sheathing, anthracite
- 1 Wire mount, PA-GF
- 1 Hexagon Socket Head Cap Screw DIN 912-M6x20, St, bright zinc-plated
- 1 Washer DIN 433-6.4, St, bright zinc-plated
- 1 Automatic T-Slot Nut V 8 St M6, stainless

Technical note

[0.0.654.32](#) Please click here for further information!

Properties	
Article number	0.0.654.32
Colour	black similar to RAL 9005
Delivery unit	1 set
Weight	71.0 g
Max. load-carrying capacity	12,5 kg

Accessoires	
0.0.645.27	Hook and Holder Adapter D30, black
0.0.654.54	Label Backplate, Hook and Holder System, black similar to RAL 9005
0.0.654.53	Label Backplate, Hook and Holder System, grey similar to RAL 7042
0.0.655.91	Hook D30/D4-60
0.0.026.29	Key with T-Handle 5 A/F