



SET OF 150 TOOLS IN FOAM MODULE + ETAB 120 CM **CPP-150-ET**

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:58:23





DESCRIPTION

SET OF 150 TOOLS IN FOAM MODULE + ETAB 120 CM

3 GOOD REASONS TO ORDER

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:58:23



1. CLOSE TO YOUR WORKSTATION
2. ERGONOMIC, ROBUST AND MODULAR
3. SELECTION OF 150 INTEGRATED PROFESSIONAL TOOLS

550 kg per shelf

Foot protection to prevent marks on floors

Wall mounting plate

Easy assembly

Adjustable shelf height:

Adjustable in increments of 7.6 cm.

Sliding storage drawer:

Capacity of approximately 35 kg with ball bearing slides.

Adjustable perforated steel panel:

Standard spacing of 112 cm wide and 38 cm high.

Can hold most perforated panel accessories.

Professional-grade adjustment and finish.

SPECIFIC DATA

Designation	120 CM WORK BENCH WITH 150 TOOLS
Sales reference	CPP-150-ET
Weight (kg)	60
Width (mm)	450
Length (mm)	1250
Height (mm)	1220
Guarantee	O SAM TOOL guarantee.

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:58:23



Guarantee applied

O | SAM TOOL guarantee.

Guarantee without time limit on the tools used under normal conditions.

[>> Find out more](#)

Toolset

	x 1	120 CM WORKBENCH WITH DRAWER AND TOOL PANEL ETAB-120M1
	x 12	Combination wrenches in mm 50A-... Ref : 8 - 9 - 10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 19 - 21 mm
	x 18	1/2" short hexagonal sockets in mm SH-... Ref : 10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 20 - 21 - 22 - 23 - 24 - 27 - 30 - 32 mm
	x 1	Straight 1/2" extensions S-2... Ref : S-210
	x 1	1/2" sliding locking handle S-120
	x 1	1/2" site ratchet with lever reversion S-157B
	x 1	Site 1/4" ratchet R-157B
	x 1	1/4" sliding handle R-120
	x 1	1/4" joint R-240
	x 1	Straight 1/4" extensions R-21... Ref : R-210
	x 1	Fitted 1/4" extension R-225

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:58:23



	x 1	Fitted 1/4" extension R-225C
	x 1	1/4" bit holder socket RD-1
	x 10	1/4" short hexagonal key socket (mm) R-...Douilles_1/4_MM Ref : 4 - 5 - 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 mm
	x 6	1/4" single-piece screwdriver sockets for hollow hexagonal screws RS-... Ref : 3 - 4 - 5 - 6 - 7 - 8 mm
	x 5	1/4" sockets for Torx® head RTX-... Ref : 4 - 5 - 6 - 7 - 8 mm
	x 8	One-piece screwdriver socket 1/4" for Torx® mark RT-... Ref : T9 - T10 - T15 - T20 - T25 - T27 - T30 - T40
	x 1	1/4" adapter R-232
	x 1	1/2" adapter S-232
	x 1	1/2" reducer S-230
	x 1	31-piece screwdriver bit set E900-J30B
	x 1	Flexible rules 781-... Ref : 781-2
	x 5	Long drift punches 7-...A Ref : 7-25A - 7-35A - 7-50A - 7-70A - 7-90A
	x 1	Punch 10 mm 8N-...A Ref : 8N-3A
	x 1	Satin-finish adjustable wrenches 54-C... Ref : 54-C10

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:58:23



	x 1	Rack of 9 Resistorx® male keys 59-R9A
	x 9	ResisTorx® elbow hexagonal keys 59-... Ref : T8 - T9 - T10 - T15 - T20 - T25 - T27 - T30 - T40
	x 1	Polished burnished finish stacked-branch multigrip pliers 209-25PA
	x 1	Chrome-plated polished diagonal cutting pliers 232-...G Ref : 232-16G
	x 1	Riveting hammers 310-...N Ref : 310-32N
	x 1	Bodyworker's chisel 1-... Ref : 1-B
	x 1	Self-retracting blade knife 378-40
	x 1	Pen light 1396-LS
	x 1	Crimping pliers 241-42
	x 1	Thickness gauges 770-... Ref : 770-E
	x 1	Universal hand shears 331-16
	x 1	Mallets with interchangeable tips 320-...D Ref : 320-35D
	x 1	Spare tips for mallets 320-...d and 322 320-C-...N / 322-C...
	x 6	Torx® screwdriver TA-...X Ref : T10 - T15 - T20 - T25 - T30 - T40

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:58:23



	x 2	Electrician's slotted screwdriver TA-...E Ref : 3x50 - 6.5x150 mm
	x 1	Mechanic's slotted screwdriver TA-...M Ref : 5.5x150 mm
	x 3	Phillips® screwdriver TA-...P Ref : N°0 - N°1 - N°2

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:58:23

