



Hinge 8 40x40, heavy-duty



REACH RoHS

For connecting profiles at various angles up to 180° and for use as heavy-duty hinges (adjustment range $\pm 90^\circ$).
When used in conjunction with the spacer rings, they can be used as freely movable hinges. If the spacer rings are removed, they can be used as rigid angle elements, e.g. bracing, and can also be pinned.



Scope of Delivery

2 hinge halves, die-cast zinc, RAL9006 white aluminium
4 fixing elements, die-cast zinc, bright zinc-plated
2 thread bushes M8, St, zinc-plated
2 spacer rings, St, stainless
2 Countersunk Screws DIN 7991-M8x10, St

Technical note

[0.0.265.31](#) For more information, please click here!

Properties	
Article number	0.0.265.31
Delivery unit	1 pce.
Weight	320.0 g

Accessoires	
8.0.000.19	Button-Head Screw M8x16, bright zinc-plated
0.0.026.18	T-Slot Nut 8 St M8, bright zinc-plated