


Parker Product Datasheet



Quick coupling system with nominal diameter 7.2 for pneumatic applications up to 35 bar. Available in brass sleeve or polymer.

PART NUMBER: 26KAKK08MPX

COUPLING HALF: Coupler

CONNECTION TYPE: Tube

BODY MATERIAL: Brass

CONNECTION SIZE: 6x8 MM

FUNCTION: Single Shut-Off

PRODUCT OVERVIEW

Parker's Basic Quick Coupling Series 26 is an industrial brass coupling with European profile. Coupling system with single-hand operation and standard-valve. Small mass size. The ergonomic sleeve (available in Brass or Polymer) design prevents dirt on the valve body.

Markets:

- General Industrial
- Industrial manufacturing equipment

Features/Benefits:

- Industrial coupling with European profile, most representative profile worldwide
- Single-hand operation for easy and fast connection

TECH SPECIFICATIONS

INDUSTRY	General Industrial
BRAND	Rectus
PRODUCT SERIES	Series 26
MAXIMUM OPERATING TEMPERATURE	212 °F
FLOW RATE	1070 L/min (air)
MINIMUM OPERATING TEMPERATURE	-4 °F
FOR FLUID TYPE	Air & Neutral Gases (Industrial compressed, lubricated air)
INDUSTRY	Healthcare & Life Sciences
BRAND	Parker
DIAMETER	7.2 mm (nominal)
LENGTH	132 mm
INTERCHANGE TYPE	European Profile
CONNECTION SIZE	6x8 mm
WEIGHT	0.098 kg
MINIMUM OPERATING TEMPERATURE	-20 °C
INDUSTRY	Transportation
MAXIMUM OPERATING TEMPERATURE	100 °C
COMPATIBLE FITTING	Series 26 Plug
FUNCTION	Single Shut-Off
REGION OF ORIGIN	Germany
OUTSIDE DIAMETER	25 mm
MAXIMUM OPERATING PRESSURE	35 bar
TECHNOLOGY	Pneumatics

QUANTITY PER BOX	10
DIVISION	Low Pressure Connectors Europe Division
APPLICATION	Food & Beverages
OPERATION TYPE	Sleeve
MAXIMUM OPERATING PRESSURE	507 psi
VALVE INCLUDED	Yes
PRODUCT STYLE	Quick-Connect
COUPLING HALF	Coupler
APPLICATION	Mobile & Defence
PRODUCT TYPE	Pneumatic Quick Couplings
VALVE TYPE	Standard Valve
APPLICATION	Safety & Rescue
CONNECTION TYPE	Tube with Spring Guard
DIVISION	Low Pressure Connectors Europe Division
SEAL MATERIAL	NBR
APPLICATION	Industrial Machinery
APPLICATION	Trucks & Trailers
PLATING TYPE	Without Surface Treatment
BODY MATERIAL	Brass
HEX SIZE	21 mm
APPLICATION	Air & Gas Compressor
SLEEVE MATERIAL	Brass