

M12 BLP-402X

M12™ BRUSHLESS PLANER

M12™ Brushless Planer with a 2 mm planing depth and 51 mm planing width allows the tool to perform in the most common user applications

Compact and light weight, comfortable to use in a variety of orientations and allows for one handed usage

Dual-sided dust port for improved chip ejection to the left or right

The drum holds two TCT reversible blades and runs at 14,000 rpm to give a smooth and consistent cut finish

60 metres of continuous planing at 2 mm depth in oak, with 1 x 4.0 Ah battery


Up to 17.5 mm of rebate depth

A kick stand located on the base which protects the work piece from accidental damage

On board blade storage for two additional TCT blades

Brushless motor, REDLITHIUM™ battery pack and REDLINK™ electronic deliver power, run time and durability

Flexible battery system: works with all MILWAUKEE® M12™ batteries



No load speed (rpm)	14,500
Planing depth (mm)	2.0
Planing width (mm)	56
Rebate depth (mm)	17.5
Weight with battery pack (EPTA) (kg)	1.92 (M12 B4)
Kit included	2 x M12 B4 Battery packs, C12 C Charger, HD Box
Article number	4933492851