



MADE IN GERMANY



Product number 9192334210
EAN 4007123687688

DESCRIPTION

- Drum body made of sheet steel, front and back with protective insulation for robust operation.
- Innovative 'cablepilot' carrying handle for perfect cable routing. Swivels on both sides and allows for comfortable carrying and hanging.
- Large, sturdy folding twist grip for effortless winding and unwinding of the cable.
- Resistant to petrol and oils.
- The BREMAXX® PUR cable (BQ cable) is extremely abrasion-resistant, resistant to being driven over, and has an extremely high cut and tear resistance. It is also resistant to acids and oils, weather and microbes. Cold-resistant down to -40 °C.
- 4 protective contact sockets, splash-proof, with self-closing lids.
- With extra robust earthing-pin plug.
- With thermal cut-out protection against overheating.
- With visual readiness display in the socket insert.
- Category 2 equipment (K2 DGUV 203-005): for use in harsh operating conditions with high mechanical, physical and chemical impacts.

TECHNICAL DATA

Cable quality	PUR (polyurethane)	Plug system socket	Type E (FR)
Cable length	33 m	Plug system plug	Type E and F (Protective contact with earth hole)
Cable designation	H07BQ-F 3G2,5	Max. current carrying capacity	16 A
Cable colour	red	Nominal input voltage	230 V
Reel diameter	290 mm	Degree of protection (IP)	IP44
Plug system CEE socket	Without		

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1	Weight of product (including packaging)	7.14 kg
Weight of product (without packaging)	6.74 kg	Dimension LxWxH (incl. packing)	31 cm x 21 cm x 41 cm
Dimension LxWxH (without packing)	20 cm x 30.5 cm x 39 cm		

SCOPE OF DELIVERY

Professional SteelCore Cable Reel SC 3214

Hugo Brennenstuhl GmbH & Co. KG

www.brennenstuhl.com

All products are subject to technical changes.