

Features

- Waterproof IP67 rating guarantees protection against extended immersion under higher pressures
- Cable out diameter 4.6mm
- Voltage rating of 125V
- Current rating of 4A
- Gold-plated brass contacts for corrosion resistance
- Threaded mating type
- Operating temperature range from -25°C to 80°C
- Gold contact plating
- PVC cable jacket
- 2M length

RS PRO Male M9 2 Pin Cable

RS Stock No.: 0783499



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

The 2 pin male M9 cable had been widely used for automotive and sensor application, it's unshielded.

General Specifications

Number of Contacts	2
Shielding	Unshielded
Housing Material	PVC
Contact Material	Brass
Contact Plating	Gold
Pole Format	2P
Contact Gender	Male
Mating Type	Threaded
Body Orientation	Straight
Mating Cycles	500
Cable Jacket	PVC
Color	Black
Application	Marine, Automotive

Mechanical Specifications

Connector Size	Standard
Termination Method	Solder
Mounting Type	Moulded cable
Panel Cut-Out	/
Contact Diameter	24AWG

Electrical Specifications

Current Rating	4A
Voltage Rating	125V
Insulation Resistance	≥100MΩ

Protection Category

IP Rating	IP67(Lock)
-----------	------------

Approvals

Declarations	MFR Declaration of Conformity
Hazardous Area Certification	None
Standards Met	IEC 61076

Similar Products

Stock No.	Brand	Product Name	Attribute 1	Attribute 2	Attribute 3

