



FloorPro Deep Cleaner RM 69 eco!efficiency

Intensive cleaner optimised for use with the eco!efficiency mode of our scrubber driers. Tough on oil and grease stains in logistics and production environments.

pH value 12
in concentrate



Properties

- Powerful ecological deep cleaner for heavily soiled industrial floors
- Loosens heavy oil, grease and mineral-based soiling
- Pleasant, fresh scent
- Rapidly effective
- Quick oil and water separation in the oil separator (easily separable = asf)
- NTA-free

Usage options

- Scrubber driers
- Manual

Application areas

Car dealership and garage	Floor cleaning
Building cleaning	Floor cleaning
Industry	Floor cleaning
Municipal	Floor cleaning
Retail	Floor cleaning
Haulage contractors, bus operators	Floor cleaning
Food and drink industry	Floor cleaning

Technical data

Container sizes	Packaging unit	Part number
2.5 l	4 Piece(s)	6.295-650.0
10 l	1 Piece(s)	6.295-651.0
20 l	1 Piece(s)	6.295-652.0
200 l	1 Piece(s)	6.295-653.0
1000 l	1 Piece(s)	6.296-156.0

Application

Scrubber-driers - deep cleaning

- Remove coarse dirt by sweeping.
- Use appropriate brush/roller/pad and squeegee for scrubber drier as required.
- Combine the product with the appropriate dosage and fresh water.
- Wet surface evenly with product (using brush/roller/pad as required).
- Allow to soak.
- Reaction time 5-10 minutes, depending on the degree of soiling.
- Vacuum the dirty water from the surface in overlapping sections.
- Rinse with plenty of clear water and soak in water until all dirt and cleaning agent residues have been removed.

Scrubber driers - maintenance cleaning

- Remove coarse dirt by sweeping.
- Use appropriate brush/roller/pad and squeegee for scrubber drier as required.
- Combine the product with the appropriate dosage and fresh water.
- On DOSE machines, set the dosing only on the device.
- Clean the surface in overlapping sections.

Manual

- Remove coarse dirt by sweeping.
- Combine the product with the appropriate dosage and fresh water.
- Clean surface manually.

Instructions for use

- Test on an inconspicuous part for material compatibility.
- Do not apply to wood, linoleum or unsealed parquet flooring.
- Do not apply to alkali-sensitive surfaces.
- Do not let the cleaning solution dry out.
- Store away from frost.

Warnings and safety recommendations according to EC Directives

- Danger
- H314 Causes severe skin burns and eye damage
- P280 Wear protective gloves/protective clothing/eye protection/face protection.
- P303 + P361 + P353 IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water [or shower].
- P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
- P310 Immediately call a POISON CENTER/doctor.
- P405 Store locked up.
- P501a Dispose of contents/container in accordance with local/regional/national/international regulations.

Further information

- Material Safety Data Sheet (MSDS)

Dosage and yield

Contents	Cleaning method	Dosage	Soiling	Yield
1000 ml	Machine - maintenance cleaning	0.5 - 3 %	mild-medium	4890 m ²
1000 ml	Manual - maintenance cleaning	0.5 - 3 %	mild	12000 m ²
1000 ml	Machine - intermediate cleaning	3 - 10 %	medium-strong	2000 m ²