

# KERN 316-06

**KERN**

Individual weight, OIML Class E2, 50 g, Compact form, stainless steel polished



Article number for guaranteed plus-deviation 921-336

## Packing & Shipping

|                              |                |
|------------------------------|----------------|
| Delivery time                | 1 d            |
| Dimensions packaging (W×D×H) | 18×18×26 mm    |
| Shipping method              | Parcel service |
| Net weight approx.           | 0,05 kg        |
| Gross weight approx.         | 0,05 kg        |
| Shipping weight              | 0,1 kg         |
| Shipping volume weight       | 0,1 kg         |

## Optional cases

|                                 |             |
|---------------------------------|-------------|
| Case - Plastic article number   | 317-060-400 |
| Case - Aluminium article number | 317-060-600 |
| Case - Wood article number      | 317-060-100 |

## Product information

|                      |                          |
|----------------------|--------------------------|
| GTIN/EAN number      | 4045761094888            |
| Trade number         | 84239090                 |
| REACH classification | no prohibited substances |

## Pictograms

### STANDARD



### OPTION



## Category

|                  |                   |
|------------------|-------------------|
| Brand            | KERN              |
| Product category | Individual weight |
| Product group    | OIML E2           |
| Product family   | 316               |

## Measuring System

|                                                        |        |
|--------------------------------------------------------|--------|
| Test weight - nominal value                            | 50 g   |
| Test weight - volume uncertainty (cm <sup>3</sup> )    | 0,0781 |
| Weight OIML class                                      | E2     |
| Conformity assessment possible                         | no     |
| Test weight - volume (cm <sup>3</sup> )                | 6,25   |
| Permissible tolerance according to OIML (+/-)          | 0,1 mg |
| OIML-compliant                                         | ✓      |
| Test weight - Density [Min] (OIML)                     | 7740   |
| Test weight - Density [Max] (OIML)                     | 8280   |
| Test weight - Density (kg/m <sup>3</sup> )             | 7950   |
| Test weight - Density uncertainty (kg/m <sup>3</sup> ) | 140    |

## Construction

|                   |                          |
|-------------------|--------------------------|
| Shape weight      | Compact form             |
| Dimensions (Ø×H)  | 18×26,8 mm               |
| Material          | stainless steel polished |
| Adjustment method | Polishing                |

## Services (optional)

|                                      |         |
|--------------------------------------|---------|
| Article number for DAkkS calibration | 962-336 |
|--------------------------------------|---------|