

# BW 5000S/3M



## Service trolley with three drawers and assortment of 189 tools

- Thermoplastic worktop
- 3 drawers 588x367 mm height 70 mm, with ball bearing slides
- Drawer bases protected by foamed rubber mats
- Front centralized safety lock
- Practical side screwdriver holder included
- Two side screwdriver holders integrated in the structure
- Large lower shelf protected with oil and petrol-proof rubber mat
- Four castors Ø 125 mm:  
2 fixed and 2 steering (one with brake)
- Static load capacity: 400 kg
- Static load capacity: 15 kg evenly distributed



|           | Art.          |
|-----------|---------------|
| 050006341 | BW 5000S/3M-O |
| 050006342 | BW 5000S/3M-A |
| 050006343 | BW 5000S/3M-R |

- n. 22 42: □  
6-7-8-9-10-11-12-13-14-15-16-17-18-19-20-21-22-23-24-27-30-32 mm
- n. 6 1201E: 2,5x50-3x75-4x100-5,5x125-6,5x150-8x200 mm
- n. 4 1202E: PH0x60-PH1x80-PH2x100-PH3x150 mm
- n. 1 1201EN: 4x30 mm
- n. 1 1202EN: PH1x30 mm
- n. 1 BW 32: Centre punches Ø 4 mm
- n. 1 BW 34: Flat chisels 150 mm
- n. 1 BW 36: Cape chisels 150 mm
- n. 1 BW 1048: Slip joint pliers, boxed joints 250 mm
- n. 1 BW 1082BM: Diagonal cutting nippers □ 160 mm
- n. 1 BW 1150BM: Heavy-duty combination pliers □ 180 mm
- n. 1 BW 1166BM: Extra-long needle knurled nose pliers □ 200 mm
- n. 1 BW 1370: Engineer's hammers 500 g
- n. 1 BW 1390: Soft face hammer, plastic faces Ø 35 mm
- n. 1 1032: 180 mm
- n. 1 1034: 170 mm
- n. 1 1036: 175 mm
- n. 1 1038: 175 mm
- n. 9 BW 96BPC/SC9: Set of 9 ball head offset hexagon key wrenches □  
1,5-2-2,5-3-4-5-6-8-10 mm
- n. 1 BW 111: Adjustable wrenches 250 mm
- n. 61 BW 861/C61: Set of 60 bits with magnetic bit holder, in pocket-size case □ □ □ □
- n. 1 BW 895/1: Socket holders for items BW 861, BW 862, BW 866  
□ 1/4" - E1/4"
- n. 13 BW 900: Hexagon hand sockets, 1/4" □  
4-4,5-5-5,5-6-7-8-9-10-11-12-13-14 mm
- n. 6 BW 900ME: Socket drivers for hexagon screws, 1/4" □ 3-4-5-6-7-8 mm
- n. 8 BW 900TX: Socket drivers for Torx® head screws, 1/4" □  
T06-T07-T08-T09-T10-T15-T20-T25
- n. 1 BW 900/20: Extension cords - 1/4" 50 mm
- n. 1 BW 900/20L: Extension cords - 1/4" 100 mm
- n. 1 BW 900/25: Universal joint - 1/4"
- n. 1 BW 900/30: 1/4" drive spinner handle 150 mm
- n. 1 BW 900/42: 1/4" drive sliding T-handle 115 mm
- n. 1 BW 900/55: Reversible ratchet, 1/4" □ 150 mm
- n. 1 BW 910/16F: Adaptor - F3/8"xM1/2" E 3/8" - B 1/2"
- n. 20 BW 920A: Hexagon hand sockets, 1/2" □  
8-9-10-11-12-13-14-15-16-17-18-19-20-21-22-23-24-27-30-32 mm
- n. 8 BW 920PE: Socket drivers for hexagon screws, 1/2" □  
5-6-7-8-9-10-12-14 mm



**Scan the QR Code to access the web tab**  
Specs, media and documentation in one click.

