

3M United Kingdom PLC | 3M Ireland Limited

Product catalogue 2023

Industrial Adhesives and Tapes

Valid from 01.06.2023

The information in this catalogue is current at the date of publication. Products availability may be amended by 3M from time to time. 3M is not liable in case of any errors or omissions.

■ Table of Contents

Packaging Systems

Packaging Tapes	192
Box Sealing Tapes	193
Hang Tags	198



Packaging Systems


Packaging Systems

Packaging Tapes

Scotch® Pouch Tape 8241

Performance document control (pouch) tape on a roll.

- Bright orange border on all four sides and a transparent non-sticky rectangular window
- Safe application of packing slips and other documents to a wide variety of boxes and packaging
- Protects the document and tracks the package



Product ID	Part Number	Product Name	MOQ	Order Unit
7100160307	8241150	Scotch® Pouch Tape 8241, Transparent, 150 mm x 66 m	12	Roll

3M™ Carry Handle Tape 8330

Our 3M™ Carry Handle 8330 transforms almost anything into a convenient, travel-friendly package. A durable plastic strip with adhesive at each end for adhering to both sides of a box or package creates a small loop which can support up to 30 pounds when properly applied.

- Transform bulky purchases into travel-friendly packages
- Carry handles are easily applied at retail checkout and can support up to 30 pounds
- Customize these handles with up to six colors for special promotions or UPC codes to spread the word about your business



Product ID	Part Number	Product Name	MOQ	Order Unit
7100054963	8330W	3M™ Carry Handle 8330, White, 35 mm x 584 mm x 152 mm	1	Case

3M™ Carry Handle 8310

Our 3M™ Carry Handle 8310 transforms almost anything into a convenient, travel-friendly package. A durable plastic strip with adhesive at each end for adhering to both sides of a box or package creates a small loop which can support up to 10 pounds.

- Transform bulky purchases into travel-friendly packages
- Carry handles are easily applied at retail checkout and can support up to 10 pounds
- Customize these handles with up to six colors for special promotions or UPC codes to spread the word about your business



Product ID	Part Number	Product Name	MOQ	Order Unit
7100049685	695826	3M™ Carry Handle 8310 White, 1 in x 17 in x 3 in, 25 handles per pad, 110 pads per case Bulk	1	Case

Packaging Systems

3M™ Carry Handle Tape 8347HP

Mono-axially oriented polypropylene backing with 150 N/CM of tensile strength, 40% elongation, excellent adhesion on most plastic overwraps. Designed to be used after the heat shrinking process to form an adhesive carry handle.

- Its adhesive adheres quickly and strongly on many surfaces including packaging films.
- High shear strength for carrying handle applications
- Unique adhesive construction with polypropylene backing allows you to create handle on automatic equipment



Product ID	Part Number	Product Name	MOQ	Order Unit
7000035384	160986	3M™ Carry Handle Tape 8347HP, Transparent, 25 mm x 5000 m	1	Roll

Box Sealing Tapes

Focus

Scotch® Box Sealing Tape 311+

Scotch® Box Sealing Tape 311+ is a high performance industrial packaging tape for box sealing, splicing, recoupage and other demanding packaging applications. It offers good performance in damp and cold shipping and storage environments, even in below freezing temperatures.

- High performance industrial packaging tape designed for cold and damp temperatures
- Great for box sealing, splicing, recoupage and demanding packaging applications
- Good performance over broad temperature ranges



Product ID	Part Number	Product Name	MOQ	Order Unit
7100220442	311+48X66C	Scotch® Box Sealing Tape 311+, Transparent, 48 mm x 66 m	36	Roll
7100220358	311+48X990C	Scotch® Box Sealing Tape 311+, Transparent, 48 mm x 990 m	6	Roll

Scotch® Box Sealing Tape 313

Scotch® Box Sealing Tape 313 closes a wide variety of medium weight box materials securely, including recycled liner paper and fibreboard. The backing of this value performance tape is crafted from polypropylene making it easy to handle and conformable around edges and on rough surfaces for a tight seal. The tape withstands cold temperatures and works well on boxes weighing up to 70 lbs.

- High adhesion and holding power resists popping for a secure seal
- Suitable for hard to stick to surfaces and cold temperature applications
- Available with custom printing for security and/or branding



Product ID	Part Number	Product Name	MOQ	Order Unit
7000095541	xxx	Scotch® Box Sealing Tape 313, Brown, 50 mm x 100 m	36	Roll
7000095540	xxx	Scotch® Box Sealing Tape 313, Clear, 50 mm x 100 m	864	Roll

Packaging Systems

Scotch® Box Sealing Tape 371

Scotch® Box Sealing Tape 371 securely closes a wide variety of box and carton materials, including corrugated fibreboard. The moisture-resistant polypropylene backing resists abrasion, chemicals, and scuffing to hold strong throughout the shipping process. It easily conforms around edges and on rough surfaces to provide a lasting hold.



- Rubber resin adhesive sticks quickly to a variety of materials, including fiberboard
- Tape resists nicks, abrasions, moisture and scuffing for long lasting hold
- Backing conforms around edges and rough areas for a tight seal

Product ID	Part Number	Product Name	MOQ	Order Unit
7000095346	371B2566	Scotch® Box Sealing Tape 371, Brown, 25 mm x 66 m	72	Roll
7000095343	371B3866	Scotch® Box Sealing Tape 371, Brown, 38 mm x 66 m	48	Roll
7000095475	BP1081	Scotch® Box Sealing Tape 371, Brown, 50 mm x 66 m	36	Roll
7000095375	37175990	Scotch® Box Sealing Tape 371, Brown, 75 mm x 990 m	4	Roll
7100135750	371T4866N	Scotch® Box Sealing Tape 371, Clear, 48 mm x 66 m	36	Roll
7100196532	371TORREDA35066T	Scotch® Box Sealing Tape 371, Clear, 50 mm x 66 m, 3 R/T 12 /B	1188	Roll
7100144123	371T2566N	Scotch® Box Sealing Tape 371, Transparent, 25 mm x 66 m	72	Roll
7000035373	371T3866	Scotch® Box Sealing Tape 371, Transparent, 38 mm x 66 m	48	Roll
7000095476	BP1082	Scotch® Box Sealing Tape 371, Transparent, 50 mm x 66 m	36	Roll
7100135321	xxx	Scotch® Box Sealing Tape 371, Transparent, 50 mm x 100 m	36	Roll
7000095737	371T7566	Scotch® Box Sealing Tape 371, Transparent, 75 mm x 66 m	792	Roll
7100144124	371T759	Scotch® Box Sealing Tape 371, Transparent, 75 mm x 990 m	4	Roll
7000035377	206395	Scotch® Box Sealing Tape 371, White, 50 mm x 66 m	36	Roll

Scotch® High Performance Box Sealing Tape 3705

Make your boxes and packages even more secure with Scotch® High Performance Box Sealing Tape 3705. Our super strength box sealing tape features an extremely strong bi-axially oriented polypropylene strong film backing and a very high shear/tack solvent based natural rubber resin adhesive.



- Protect your valuable and fragile goods
- Use in a wide range of demanding packaging applications
- Reduce the risk of product damage or box sealing failures

Product ID	Part Number	Product Name	MOQ	Order Unit
7000095271	3705T50	Scotch® High Performance Box Sealing Tape 3705, Transparent, 50 mm x 66 m	36	Roll

Packaging Systems

Scotch® High Performance Box Sealing Tape 3739

Re-seal and package heavy weights of valuable goods with Scotch® Box Sealing Tape 3739. Our tape is made of a high strength polypropylene film backing and hot melt synthetic rubber-resin adhesive, and can used for single strip closure of fibreboard boxes.




- Re-seal and package heavy weights of valuable goods
- Use for single strip closure of fibreboard boxes
- Performs well at all temperatures typically encountered by packaged products in shipping and storage environments

Product ID	Part Number	Product Name	MOQ	Order Unit
7000095394	3739B759	Scotch® High Performance Box Sealing Tape 3739, Brown, 75 mm x 990 m	144	Roll
7100146490	xxx	Scotch® High Performance Box Sealing Tape 3739, Transparent, 50 mm x 990 m	6	Roll
7000095395	3739T75	Scotch® High Performance Box Sealing Tape 3739, Transparent, 75 mm x 66 m	24	Roll
7000095396	3739T759	Scotch® High Performance Box Sealing Tape 3739, Transparent, 75 mm x 990 m	4	Roll
7000095412	138132	Scotch® High Performance Box Sealing Tape 3739, Transparent, 150 mm x 990 m	72	Roll

Scotch® High Performance Box Sealing Tape 375E

Seal a variety of boxes and cartons, including those with high recycled content using Scotch® High Performance Box Sealing Tape 375E. Our tape has hot melt solvent free (synthetic rubber resin) adhesive and polypropylene film backing that resists splitting and absorbs impact shock, when subjected to rough handling.



- Absorbs impact shock
- Get high moisture, abrasion and split resistance
- Use on over-packed and heavy-weight packages for a tight seal

Product ID	Part Number	Product Name	MOQ	Order Unit
7000095715	375E50	Scotch® High Performance Box Sealing Tape 375E, Brown, 50 mm x 66 m	36	Roll
7000095896	375E75	Scotch® High Performance Box Sealing Tape 375E, Brown, 75 mm x 66 m	24	Roll
7000095434	375T5099	Scotch® High Performance Box Sealing Tape 375E, Transparent, 50 mm x 990 m	6	Roll
7000095437	375T7566	Scotch® High Performance Box Sealing Tape 375E, Transparent, 75 mm x 66 m	648	Roll

Packaging Systems

Focus

Scotch® High Tack Box Sealing Tape 375+

Scotch® High Tack Box Sealing Tape 375+ is a high-performance packaging tape that securely closes a variety of heavy weight box materials, including recycled fiberboard. The strong adhesive securely seals packages to help prevent tampering and tape failure during moving, shipping and delivery. The polypropylene film backing is easy to unwind and resists abrasion, moisture, scuffing and edge tear.



- High-performance hot melt packaging tape for heavy duty applications
- Strong adhesive helps prevent tampering and tape failure during shipping and delivery
- High edge tear and split resistance for e-commerce and single-parcel shipments

Product ID	Part Number	Product Name	MOQ	Order Unit
7100216187	xxx	Scotch® High Tack Box Sealing Tape 375+, Clear, 72 mm x 914 m	4	Roll
7100215092	xxx	Scotch® High Tack Box Sealing Tape 375+, Transparent, 48 mm x 50 m	36	Roll
7100215511	xxx	Scotch® High Tack Box Sealing Tape 375+, Transparent, 48 mm x 914 m	6	Roll
7100215467	xxx	Scotch® High Tack Box Sealing Tape 375+, Transparent, 72 mm x 50 m	24	Roll

Scotch® Performance Box Sealing Tape 3444

Seal cartons by using Scotch® Performance Box Sealing Tape 3444. Our sealing tape is made from non-silicone flat back impregnated paper, coated with a natural rubber adhesive. It sticks to a wide variety of surfaces.




- Apply to carton sealing applications
- Use as a single strip closure of lightweight boxes, repaired and miscellaneous packaging
- Get non-silicone flat-back impregnated paper, coated with a high tack, natural rubber adhesive

Product ID	Part Number	Product Name	MOQ	Order Unit
7100146500	34445050N	Scotch® Performance Box Sealing Tape 3444, Brown, 50 mm x 50 m	36	Roll
7100146162	xxx	Scotch® Performance Box Sealing Tape 3444, Brown, 75 mm x 50 m	24	Roll

Scotch® Performance Low Noise Box Sealing Tape 3707

Use Scotch® Performance Low Noise Box Sealing Tape 3707 for its specifically designed adhesive that provides reduced noise during application. Our tape is made with and polypropylene film backing and solvent (natural rubber resin) adhesive. It resists splitting and absorbs impact shock.



- Reduce noise during application
- Get split resistance
- Absorbs impact shock

Product ID	Part Number	Product Name	MOQ	Order Unit
7000095237	3707B506	Scotch® Performance Low Noise Box Sealing Tape 3707, Buff, 50 mm x 66 m	36	Roll
7000095240	3707T506	Scotch® Performance Low Noise Box Sealing Tape 3707, Transparent, 50 mm x 66 m	6	Roll

Packaging Systems

Scotch® Performance PVC Box Sealing Tape 6890

Use Scotch® Performance PVC Box Sealing Tape 6890 for box sealing, combining, attaching, heat shrink sealing and bundling lightweight packages. Our tape is made with a PVC film backing and solvent (natural rubber resin) adhesive and is best applied at room temperature.

- Use for box sealing, combining, attaching, heat shrink sealing and bundling lightweight packages
- Eliminate the need for dispensers when tearing by hand
- Reduce noise level in the work area



Product ID	Part Number	Product Name	MOQ	Order Unit
7000095243	6890W506	Scotch® Performance PVC Box Sealing Tape 6890, White, 50 mm x 66 m	36	Roll

Scotch® Stretchable Tape 8886

Constructed with a specialized, transparent backing, Scotch® Stretchable Tape 8886 is designed to contain and secure pallets for shipping. It is coated with a synthetic rubber adhesive that removes cleanly when stretched over labels.

- Special polypropylene film backing provides 650% stretch factor allowing a 55 meter roll to yield 357 meters of tape
- Easily bolts to case sealer for simple installation
- After stretching, polyethylene backing increases in strength for bundling and strapping applications.



Product ID	Part Number	Product Name	MOQ	Order Unit
7100025020	8886	Scotch® Stretchable Tape 8886, Clear, 36 mm x 55 m, 0.17 mm	24	Roll

Scotch® General Purpose Low Noise Box Sealing Tape 309

Scotch® Box Sealing Tape 309 is a low noise general purpose packing tape suitable for light weight applications specifically in the food and beverage industry. The polypropylene film backing is easy to handle and resists abrasion, moisture and scuffing. The consistent and reliable backing easily conforms around edges and on rough surfaces for a tight seal.

- General purpose packaging tape suitable for light weight and price sensitive applications
- Acrylic adhesive with polypropylene backing delivers dependable, quality performance
- Resists UV rays without yellowing for archival applications



Product ID	Part Number	Product Name	MOQ	Order Unit
7000095477	BP1083	Scotch® General Purpose Low Noise Box Sealing Tape 309, Brown, 50 mm x 66 m	36	Roll
7000095580	309B7566	Scotch® General Purpose Low Noise Box Sealing Tape 309, Brown, 75 mm x 66 m	792	Roll
7000095558	309T7566	Scotch® General Purpose Low Noise Box Sealing Tape 309, Transparent, 75 mm x 66 m	24	Roll
7000095478	S5066T6	Scotch® General Purpose Low Noise Box Sealing Tape 309BC, Transparent, 50 mm x 66 m	36	Roll

Packaging Systems

Tartan™ Box Sealing Tape 369

Close lightweight envelopes, packages mailers, box and carton materials securely with Tartan™ Box Sealing Tape 369. Our tapes moisture-resistant polypropylene backing resists abrasion, chemicals, and scuffing to hold strong throughout the shipping process.



- Seal lightweight envelopes, packages mailers, box and carton materials securely
- Resists abrasion, chemicals, nicks and scuffing to hold strong throughout the shipping process
- Close packages securely without the holes, waste, sharp points and disposal of staples

Product ID	Part Number	Product Name	MOQ	Order Unit
7100135774	369B48X66J	Tartan™ Box Sealing Tape 369, Brown, 44 mm x 66 m	36	Roll
7100135749	369B48X132	Tartan™ Box Sealing Tape 369, Brown, 44 mm x 132 m	36	Roll
7100135752	369T48X66J	Tartan™ Box Sealing Tape 369, Transparent, 44 mm x 66 m	36	Roll
7100135755	369T48X132J	Tartan™ Box Sealing Tape 369, Transparent, 44 mm x 132 m	36	Roll
7100135746	369T48X990	Tartan™ Box Sealing Tape 369, Transparent, 44 mm x 990 m	6	Roll

Hang Tags

3M™ Hang Tab 1074

We designed 3M™ Hang Tab 1074 to quickly stick to a product surface and allow that product to hang from a peg for display. These hang tabs are great for hanging shrink-wrapped packages and for in-store repair of damaged packaging, such as torn punches in chipboard header cards.



- Sticks instantly to shrink-wrapped packages, cartons, and product surfaces
- Polyester backing resists abrasion, splitting and edge tear
- Clear tape lets packaging copy and graphics show through

Product ID	Part Number	Product Name	MOQ	Order Unit
7000051823	3M1074	3M™ Hang Tabs 1074, Transparent, 25 mm x 50 mm	10	Pack

3M™ Hang Tab 1075

Clear sturdy polyester 50,8 mm x 50,8 mm tab with pressure sensitive adhesive backing. Sticks to most product or packaging surfaces so that the item can be displayed. Delta hole for secure holding on retail peg.



- Clear pads do not obscure packaging graphics. Pre-cut, bendable tab format for convenience and ease of use.
- Strong polyester backing resists abrasion, tearing and splitting.
- Clear tape won't obscure packaging copy, brand messaging or graphics

Product ID	Part Number	Product Name	MOQ	Order Unit
7000001899	3M1075	3M™ Hang Tabs 1075, Transparent, 50 mm x 50 mm	10	Pack

■ Packaging Systems

3M™ Hang Tab 1076
















Clear sturdy polyester 50,8 mm x 50,8 mm tab with pressure sensitive adhesive backing. Sticks to most product or packaging surfaces so that the item can be displayed. Round hole for secure holding on retail peg.

- Clear pads do not obscure packaging graphics. Pre-cut, bendable tab format for convenience and ease of use.
- Strong polyester backing resists abrasion, tearing and splitting.
- Aggressive hot melt rubber resin adhesive sticks to a variety of surfaces, including shrink wrapped packages and chipboard header cards.











Product ID	Part Number	Product Name	MOQ	Order Unit
7000051800	3M1076	3M™ Hang Tabs 1076, Transparent, 50 mm x 50 mm	10	Pack

3M™ Box Sealing Tapes

							
Product number	309	313	369	371	6890	3739	375E
Properties/suitable for	Low noise and colder & damper	Low noise and colder & damper	Economical general purpose	Economical general purpose	Recycled cartons	Performance tape	High performance tape
Key features (info box)							

Physical and Performance Characteristics, Key Features

Product number	309	313	369	371	6890	3739	375E
Total thickness [mm]	0.050	0.065	0.041	0.045	0.051	0.054	0.073
Adhesive type	Acrylic	Acrylic	Hot melt rubber-resin	Hot melt rubber-resin	Solvent natural rubber resin	Hot melt rubber-resin	Hot melt rubber-resin
Colour	Tan, clear, white	Tan, clear	Tan, clear	Tan, clear	Tan, clear	Tan, clear	Tan, clear
Backing material	BOPP	BOPP	BOPP	BOPP	PVC	BOPP	BOPP
Peel strength [Newton/25 mm] 	6.5	8.8	10.5	11.75	5.5	11	15
Tensile strength [Newton/25 mm] 	125	153	118 *	132.5	143	118	200
Elongation at break 	160%	125%	162%	165%	70%	165%	140%
Light weight packaging 	•		•	•			
Medium weight packaging 		•			•		
Medium to heavy weight packaging 						•	•
Low noise 	•	•			•		
Meets BRC requirements 	•	•	•*	•*		•	•

* Not all items are certified

Suggested Applications

Product number	309	313	369	371	6890	3739	375E
Lightweight box sealing	•			•			
Reduce noise level in the work area with a slow, low noise unwind	•	•			•		
Lightweight to medium-weight box sealing		•			•		
Non-critical lightweight box sealing	•		•				
Best performance application range for slotted boxes weighing up to 70 lbs / 30 kg				•			
Heat shrink sealing and bundling lightweight packages					•		
Single strip closure of fibreboard boxes						•	
Medium- to heavy-weight box sealing						•	•
Seal boxes with high recycled content							•
Product number	309	313	369	371	6890	3739	375E

Product Use

All statements, technical information, and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluates the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method or application. All questions of liability relating to this product are governed by the terms of the sale subject, where applicable, to the prevailing law.

3M TERMS OF SALE

1. Application

1.1 These conditions apply to all contracts between 3M and the Buyer referred to in the order and override all conditions stipulated by the Buyer (even if submitted in a later document); any other agreements between the parties relating to the subject matter of this order are terminated (except an agreement into which these conditions are incorporated).

1.2 No variation of these conditions is permitted unless agreed in writing by an authorised officer of 3M. Lead times for delivery shall be as set out in 3M's quotation or proposal or if none is specified 3M's standard lead times shall apply.

2. Description

2.1 The description of the goods or services to be supplied by 3M shall be as set out in 3M's quotation, as modified by any written specification supplied by 3M, or otherwise agreed in writing by an authorised officer of 3M.

2.2 3M may amend any specification if required by any applicable statute or regulation, or by notification to the Buyer following which the applicable specification shall be that as so amended.

2.3 All samples, drawings, images, descriptive matter and advertising materials produced by 3M and any descriptions or illustrations contained in 3M's literature, digital media or emails are produced solely to describe the goods or services approximately and do not form part of the agreement into which these conditions are incorporated.

3. Price

3.1 Save where expressly stated otherwise by 3M the price to be paid for the goods or the services will be 3M's price at the date when the goods are dispatched or the services are provided.

3.2 The price of goods includes the cost of 3M's standard packaging and standard delivery within the UK and Ireland by 3M's normal transportation; the price does not include VAT. Where the price is based on pallets and/or packaging being returned to 3M, then failure to do so by the Buyer will result in a surcharge at 3M's standard rate.

4. Payment

4.1 Unless otherwise specified on 3M's invoice, payment for the goods or services must be received in cleared funds no later than thirty days of the date of invoice.

4.2 3M reserves the right to charge interest on overdue sums at the rate of 4% per annum above the Base Rate for the time being of Lloyds Bank plc calculated on a daily basis from the due date of payment in Clause 4.1 until the date upon which payment is made.

4.3 3M may at any time require the Buyer to make payment in advance of delivery or require security for payment.

4.4 If the Buyer fails to make payment by the due date or when required, 3M may (without prejudice to any other remedy which it may have) cancel this contract and/or any other contract between the Buyer and 3M and/or suspend delivery under this or any other contract until payment is made.

4.5 The Buyer will have no statutory or other right of set off.

5. Delivery

5.1 Delivery dates are approximate only and 3M shall not be responsible for any loss or damage arising from any delay in delivering all or part of any goods ordered or delay in the provision of any services.

5.2 Without prejudice to Clause 5.1, 3M will not be liable for any delay in delivery or non-delivery of goods or services or any other breach of these conditions caused by any circumstances beyond 3M's reasonable control including without limitation, any Act of God, explosion, fire, flood, war, hostilities, accident, delay in delivery or non-delivery by 3M's suppliers, breakdowns or accidents to machinery, labour strike or dispute, order or decree of any court or action of any governmental authority, or any other causes or any circumstances beyond 3M's control; on the occurrence of any of the above events 3M reserves the right to cancel or suspend the whole or part of any delivery or service provision.

5.3 In the case of any order for goods of a type or description not normally held in stock by 3M, and therefore specially made ordered or imported by 3M to meet such order, the Buyer will accept goods 10% more or 10% less than ordered, the total price of the order being correspondingly adjusted.

5.4 Where 3M references the international rules for the interpretation of trade terms prepared by the International Chamber of Commerce (Incoterms) in the relevant contract or proposal, such terms shall apply to delivery save that where they conflict with these conditions, these conditions shall prevail. For deliveries outside of the UK mainland the term of sale shall be FCA 3M UK warehouse unless otherwise mutually agreed in writing by 3M and Buyer.

5.5 Goods supplied may be subject to export controls. The Buyer should refer to 3M's packing list accompanying the goods for any export control status.

6. Risk

Risk in all goods supplied to the Buyer will pass to the Buyer on delivery. Unloading shall be at the Buyer's risk.

7. Inspection

7.1 If the goods or any of them are damaged or lost while in the custody of a carrier, 3M will (at its option) either replace such goods or refund to the Buyer the price paid for them, but 3M's liability in connection with any such goods will not exceed the cost of replacement or the price paid by the Buyer.

7.2 3M will not be under any liability under 7.1 above unless the following conditions are strictly complied with:

7.2:1 In the event of non-delivery of a whole consignment of goods the Buyer must inform 3M in writing within ten days of the date of the invoice.

7.2:2 In the case of damage to goods or loss of part of a consignment, the consignment must be inspected in the presence of the carrier. If any goods are damaged or lost the consignment note must be endorsed accordingly and the Buyer must notify 3M within forty-eight hours of delivery, such notification to be confirmed in writing within the following five days. 3M shall have no further liability for such damage or loss.

8. Liabilities and Warranties

8.1 Nothing in this clause will be deemed to exclude or restrict 3M's liability for (i) death or personal injury resulting from its negligence; (ii) fraud or fraudulent misrepresentation; (iii) breach of any obligation as to title implied by section 12 of the Sale of Goods Act 1979; and/or (iv) any act, omission or matter, liability for which may not be legally excluded or limited.

8.2 If any goods supplied or any services supplied or provided by or on behalf of 3M prove on inspection to be defective in material or workmanship, 3M will (at its option) replace the same (or the defective part) or refund to the Buyer the price of the goods or services (or a pro-rated amount of the price if not all the goods are defective).

8.3 The Buyer will determine the suitability of the goods for its intended use and will not rely upon any representations made by or on behalf of 3M.

8.4 3M's liability under these conditions shall never exceed the cost of replacement or the price paid by the Buyer for the goods or services.

8.5 3M will not be liable for any consequential or indirect loss or damage (whether for loss of profit, loss of business, depletion of goodwill or otherwise) costs, expenses or other claims for consequential compensation whatsoever suffered by the Buyer whether this loss or damage arises from a breach of duty, in contract or in tort or in any other way (including loss or damage arising from 3M's negligence).

8.6 The Buyer shall at all times comply with standards of business conduct that are consistent with 3M's Code of Conduct located at www.3m.com/businessconduct and all applicable laws, statutes, regulations and codes relating to anti-bribery including but not limited to the US Foreign Corrupt Practices Act and the UK Bribery Act 2010 ("Bribery Laws") and shall maintain in place its own policies and adequate procedures, to ensure full compliance with the Bribery Laws. The Buyer shall promptly report to 3M any request or demand for any undue financial or other advantage of any kind received by or offered to the Buyer in connection with 3M's goods or services.

8.7 Except as set out in these conditions, all other warranties and conditions, whether express or implied, statutory or otherwise are excluded to the fullest extent permissible at law.

9. Assignment

9.1 3M may assign, or deal in any other manner with, any contract between 3M and Buyer or any part of them, including sub-contracting any of its obligations under such contracts to any third party or agent.

9.2 The Buyer shall not be entitled to assign, or deal in any other manner with, any contracts between 3M and Buyer or any part of them, including sub-contracting any of its obligations under such contracts, without the prior written consent of 3M.

10. Termination

If there is appointed a Receiver, Administrator or Administrative Receiver of the Buyer's property or assets or any part of them, or a court order is made or a resolution is passed for the winding-up of the Buyer (except for the purpose of amalgamation or reconstruction) or if the Buyer commits any act of bankruptcy, or any bankruptcy petition is presented against the Buyer (or any analogous proceedings under the law of any country outside the United Kingdom are commenced), 3M may by notice in writing to the Buyer cancel all orders and contracts between 3M and the Buyer or any part of them remaining unfulfilled.

11. General

11.1 If any provision, or part of a provision, of these conditions is found by any court or administrative body of competent jurisdiction to be invalid, illegal or unenforceable (a "void provision") such invalidity, illegality or unenforceability shall not affect the other provisions of the conditions, which shall remain in full force and effect. If a void provision would be valid, legal and enforceable if some part of it were deleted, that void provision shall apply with such modification as may be necessary to make it valid, legal and enforceable and if it cannot be made valid, legal and enforceable it shall be deemed to be deleted.

11.2 No provision of the conditions shall be enforceable under the Contracts (Rights of Third Parties) Act 1999 by any person who is not a party to the contract between 3M and Buyer.

11.3 A failure to exercise, or delay in exercising a right, power or remedy provided to 3M by these conditions or by law does not constitute a waiver of that, or any other, right, power or remedy and shall not (and nor shall any single or partial exercise of any such right, power or remedy) preclude the further exercise of that, or any other, right, power or remedy.

12. Jurisdiction

12.1 All contracts between 3M and the Buyer where the goods are shipped to or services are provided in the Republic of Ireland shall be governed by and construed in accordance with the Laws of the Republic of Ireland, and the Buyer agrees to submit to the jurisdiction of the Courts of law in the Republic of Ireland in respect of them.


12.2 Except as provided above, all contracts between 3M and the Buyer shall be governed by and construed in accordance with the Laws of England, and the Buyer agrees to submit to the jurisdiction of the Courts of law in England in respect of them.

Effective 1 January 2017



3M United Kingdom PLC
3M Centre Cain Road,
Bracknell,
Berkshire, RG12 8HT
Tel: 0870 6080050
www.3M.co.uk

3M Ireland Limited
The Iveagh Building
The Park 18, Carrickmines,
D18 X015, Ireland
Tel: +353-1-2803555
www.3m.ie



**Please scan the QR
code for additional
product information.**