

RS PRO Standard Steel Lockers

Features

- Riveted and welded steel construction.
- Durable epoxy powder coated finish in five door colours.
- Door stiffeners provide added strength and security.
- Supplied with Camlocks as standard.
- Compartment clear opening = locker
- ActiveCoat antimicrobial technology
- Standard colours to chose



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Standard Steel Lockers

A range of steel lockers are available in various sizes, but all share the same footprint; making them ideal for fitting into runs under windows (or obstructions), in order to maximise space.

Standard Steel lockers All standard steel lockers are the ideal choice for schools and colleges as well as general workplace personal storage. Versatile, hard-wearing and reliable, our lockers provide quality, choice and security as standard.

Lockers have been tested and conform to the requirements of the British Standard for Clothes Lockers BS 4680: 1996 'Standard Duty'.

ActiveCoat antimicrobial technology is incorporated into all our locker products at the time of manufacture, offering constant protection against a wide range of bacteria.



General Specifications

Product Name	Standard Steel Lockers
Number of Doors	See details below
Body Colour	Light Grey
Door Colours	See details below
External Height	See details below
External Width	See details below
External Depth	See details below

Stock No.	Brand	Product Name	No of Doors	Door Colours	Dimension (H x W x D mm)
213601	RS PRO	Full height Locker w/ Sloping Top	1	 Blue	1800 x 300 x 300
213602	RS PRO	Full height Locker w/ Sloping Top	1	 Light Grey	1800 x 300 x 300
213604	RS PRO	Full height Locker w/ Sloping Top	1	 Red	1800 x 300 x 300
213605	RS PRO	Full height Locker w/ Sloping Top	1	 Green	1800 x 300 x 300
213606	RS PRO	Full height Locker w/ Sloping Top	1	 Yellow	1800 x 300 x 300
213608	RS PRO	Full height Locker w/ Sloping Top	1	 Dark Grey	1800 x 300 x 300
213617	RS PRO	Full height Locker w/ Sloping Top	2	 Blue	1800 x 300 x 300
213618	RS PRO	Full height Locker w/ Sloping Top	2	 Light Grey	1800 x 300 x 300
213620	RS PRO	Full height Locker w/ Sloping Top	2	 Red	1800 x 300 x 300
213526	RS PRO	Full height Locker w/ Sloping Top	2	 Green	1800 x 300 x 300
213527	RS PRO	Full height Locker w/ Sloping Top	2	 Yellow	1800 x 300 x 300
213529	RS PRO	Full height Locker w/ Sloping Top	2	 Dark Grey	1800 x 300 x 300
213539	RS PRO	Full height Locker w/ Sloping Top	3	 Blue	1800 x 300 x 300
213541	RS PRO	Full height Locker w/ Sloping Top	3	 Light Grey	1800 x 300 x 300
213542	RS PRO	Full height Locker w/ Sloping Top	3	 Red	1800 x 300 x 300
213544	RS PRO	Full height Locker w/ Sloping Top	3	 Green	1800 x 300 x 300
213545	RS PRO	Full height Locker w/ Sloping Top	3	 Yellow	1800 x 300 x 300
213547	RS PRO	Full height Locker w/ Sloping Top	3	 Dark Grey	1800 x 300 x 300
213555	RS PRO	Full height Locker w/ Sloping Top	4	 Blue	1800 x 300 x 300
213557	RS PRO	Full height Locker w/ Sloping Top	4	 Light Grey	1800 x 300 x 300
213558	RS PRO	Full height Locker w/ Sloping Top	4	 Red	1800 x 300 x 300
213560	RS PRO	Full height Locker w/ Sloping Top	4	 Green	1800 x 300 x 300
213561	RS PRO	Full height Locker w/ Sloping Top	4	 Yellow	1800 x 300 x 300
213563	RS PRO	Full height Locker w/ Sloping Top	4	 Dark Grey	1800 x 300 x 300
213660	RS PRO	Full height Locker w/ Sloping Top	6	 Blue	1800 x 300 x 300
213569	RS PRO	Full height Locker w/ Sloping Top	6	 Light Grey	1800 x 300 x 300
214618	RS PRO	Full height Locker w/ Sloping Top	6	 Red	1800 x 300 x 300
214620	RS PRO	Full height Locker w/ Sloping Top	6	 Green	1800 x 300 x 300
214621	RS PRO	Full height Locker w/ Sloping Top	6	 Yellow	1800 x 300 x 300
214623	RS PRO	Full height Locker w/ Sloping Top	6	 Dark Grey	1800 x 300 x 300
213915	RS PRO	Full height Locker	10	 Blue	1800 x 300 x 300
213917	RS PRO	Full height Locker	10	 Light Grey	1800 x 300 x 300
213918	RS PRO	Full height Locker	10	 Red	1800 x 300 x 300
213920	RS PRO	Full height Locker	10	 Green	1800 x 300 x 300
213921	RS PRO	Full height Locker	10	 Yellow	1800 x 300 x 300
213923	RS PRO	Full height Locker	10	 Dark Grey	1800 x 300 x 300
213924	RS PRO	Full height Locker w/ Sloping Top	10	 Blue	1800 x 300 x 300
213926	RS PRO	Full height Locker w/ Sloping Top	10	 Light Grey	1800 x 300 x 300
213927	RS PRO	Full height Locker w/ Sloping Top	10	 Red	1800 x 300 x 300

Stock No.	Brand	Product Name	No of Doors	Door Colours	Dimension (H x W x D mm)
213929	RS PRO	Full height Locker w/ Sloping Top	10	 Green	1800 x 300 x 300
213930	RS PRO	Full height Locker w/ Sloping Top	10	 Yellow	1800 x 300 x 300
213932	RS PRO	Full height Locker w/ Sloping Top	10	 Dark Grey	1800 x 300 x 300
213942	RS PRO	Full height Locker	1	 Blue	1800 x 300 x 380
213943	RS PRO	Full height Locker	1	 Light Grey	1800 x 300 x 380
213945	RS PRO	Full height Locker	1	 Red	1800 x 300 x 380
213946	RS PRO	Full height Locker	1	 Green	1800 x 300 x 380
213948	RS PRO	Full height Locker	1	 Yellow	1800 x 300 x 380
213949	RS PRO	Full height Locker	1	 Dark Grey	1800 x 300 x 380
214658	RS PRO	Full height Locker w/ Sloping Top	1	 Blue	1800 x 300 x 380
214659	RS PRO	Full height Locker w/ Sloping Top	1	 Light Grey	1800 x 300 x 380
214660	RS PRO	Full height Locker w/ Sloping Top	1	 Red	1800 x 300 x 380
214661	RS PRO	Full height Locker w/ Sloping Top	1	 Green	1800 x 300 x 380
214663	RS PRO	Full height Locker w/ Sloping Top	1	 Yellow	1800 x 300 x 380
214664	RS PRO	Full height Locker w/ Sloping Top	1	 Dark Grey	1800 x 300 x 380
214665	RS PRO	Full height Locker	2	 Blue	1800 x 300 x 380
214667	RS PRO	Full height Locker	2	 Light Grey	1800 x 300 x 380
214668	RS PRO	Full height Locker	2	 Red	1800 x 300 x 380
214670	RS PRO	Full height Locker	2	 Green	1800 x 300 x 380
214671	RS PRO	Full height Locker	2	 Yellow	1800 x 300 x 380
214673	RS PRO	Full height Locker	2	 Dark Grey	1800 x 300 x 380
214674	RS PRO	Full height Locker w/ Sloping Top	2	 Blue	1800 x 300 x 380
214676	RS PRO	Full height Locker w/ Sloping Top	2	 Light Grey	1800 x 300 x 380
213785	RS PRO	Full height Locker w/ Sloping Top	2	 Red	1800 x 300 x 380
213787	RS PRO	Full height Locker w/ Sloping Top	2	 Green	1800 x 300 x 380
213788	RS PRO	Full height Locker w/ Sloping Top	2	 Yellow	1800 x 300 x 380
213790	RS PRO	Full height Locker w/ Sloping Top	2	 Dark Grey	1800 x 300 x 380
213791	RS PRO	Full height Locker	3	 Blue	1800 x 300 x 380
213793	RS PRO	Full height Locker	3	 Light Grey	1800 x 300 x 380
213794	RS PRO	Full height Locker	3	 Red	1800 x 300 x 380
213796	RS PRO	Full height Locker	3	 Green	1800 x 300 x 380
213797	RS PRO	Full height Locker	3	 Yellow	1800 x 300 x 380
213798	RS PRO	Full height Locker	3	 Dark Grey	1800 x 300 x 380
213799	RS PRO	Full height Locker w/ Sloping Top	3	 Blue	1800 x 300 x 380
213800	RS PRO	Full height Locker w/ Sloping Top	3	 Light Grey	1800 x 300 x 380
213801	RS PRO	Full height Locker w/ Sloping Top	3	 Red	1800 x 300 x 380
213803	RS PRO	Full height Locker w/ Sloping Top	3	 Green	1800 x 300 x 380
213804	RS PRO	Full height Locker w/ Sloping Top	3	 Yellow	1800 x 300 x 380
213805	RS PRO	Full height Locker w/ Sloping Top	3	 Dark Grey	1800 x 300 x 380

Stock No.	Brand	Product Name	No of Doors	Door Colours	Dimension (H x W x D mm)
213806	RS PRO	Full height Locker	4	 Blue	1800 x 300 x 380
213807	RS PRO	Full height Locker	4	 Light Grey	1800 x 300 x 380
213808	RS PRO	Full height Locker	4	 Red	1800 x 300 x 380
213810	RS PRO	Full height Locker	4	 Green	1800 x 300 x 380
213811	RS PRO	Full height Locker	4	 Yellow	1800 x 300 x 380
213812	RS PRO	Full height Locker	4	 Dark Grey	1800 x 300 x 380
213813	RS PRO	Full height Locker w/ Sloping Top	4	 Blue	1800 x 300 x 380
213814	RS PRO	Full height Locker w/ Sloping Top	4	 Light Grey	1800 x 300 x 380
213816	RS PRO	Full height Locker w/ Sloping Top	4	 Red	1800 x 300 x 380
213817	RS PRO	Full height Locker w/ Sloping Top	4	 Green	1800 x 300 x 380
213819	RS PRO	Full height Locker w/ Sloping Top	4	 Yellow	1800 x 300 x 380
213820	RS PRO	Full height Locker w/ Sloping Top	4	 Dark Grey	1800 x 300 x 380
214539	RS PRO	Full height Locker	6	 Blue	1800 x 300 x 380
214540	RS PRO	Full height Locker	6	 Light Grey	1800 x 300 x 380
214541	RS PRO	Full height Locker	6	 Red	1800 x 300 x 380
214542	RS PRO	Full height Locker	6	 Green	1800 x 300 x 380
214544	RS PRO	Full height Locker	6	 Yellow	1800 x 300 x 380
214545	RS PRO	Full height Locker	6	 Dark Grey	1800 x 300 x 380
214556	RS PRO	Full height Locker w/ Sloping Top	6	 Blue	1800 x 300 x 380
214557	RS PRO	Full height Locker w/ Sloping Top	6	 Light Grey	1800 x 300 x 380
214558	RS PRO	Full height Locker w/ Sloping Top	6	 Red	1800 x 300 x 380
214560	RS PRO	Full height Locker w/ Sloping Top	6	 Green	1800 x 300 x 380
214562	RS PRO	Full height Locker w/ Sloping Top	6	 Yellow	1800 x 300 x 380
214563	RS PRO	Full height Locker w/ Sloping Top	6	 Dark Grey	1800 x 300 x 380
214564	RS PRO	Full height Locker	10	 Blue	1800 x 300 x 380
214566	RS PRO	Full height Locker	10	 Light Grey	1800 x 300 x 380
214567	RS PRO	Full height Locker	10	 Red	1800 x 300 x 380
214569	RS PRO	Full height Locker	10	 Green	1800 x 300 x 380
214570	RS PRO	Full height Locker	10	 Yellow	1800 x 300 x 380
214572	RS PRO	Full height Locker	10	 Dark Grey	1800 x 300 x 380
214573	RS PRO	Full height Locker w/ Sloping Top	10	 Blue	1800 x 300 x 380
214575	RS PRO	Full height Locker w/ Sloping Top	10	 Light Grey	1800 x 300 x 380
214576	RS PRO	Full height Locker w/ Sloping Top	10	 Red	1800 x 300 x 380
214578	RS PRO	Full height Locker w/ Sloping Top	10	 Green	1800 x 300 x 380
213822	RS PRO	Full height Locker w/ Sloping Top	10	 Yellow	1800 x 300 x 380
213823	RS PRO	Full height Locker w/ Sloping Top	10	 Dark Grey	1800 x 300 x 380
213825	RS PRO	Full height Locker w/ Sloping Top	1	 Blue	1800 x 300 x 450
213826	RS PRO	Full height Locker w/ Sloping Top	1	 Light Grey	1800 x 300 x 450
213828	RS PRO	Full height Locker w/ Sloping Top	1	 Red	1800 x 300 x 450

Stock No.	Brand	Product Name	No of Doors	Door Colours	Dimension (H x W x D mm)
213829	RS PRO	Full height Locker w/ Sloping Top	1	 Green	1800 x 300 x 450
213831	RS PRO	Full height Locker w/ Sloping Top	1	 Yellow	1800 x 300 x 450
213832	RS PRO	Full height Locker w/ Sloping Top	1	 Dark Grey	1800 x 300 x 450
213841	RS PRO	Full height Locker w/ Sloping Top	2	 Blue	1800 x 300 x 450
213842	RS PRO	Full height Locker w/ Sloping Top	2	 Light Grey	1800 x 300 x 450
214251	RS PRO	Full height Locker w/ Sloping Top	2	 Red	1800 x 300 x 450
214253	RS PRO	Full height Locker w/ Sloping Top	2	 Green	1800 x 300 x 450
214254	RS PRO	Full height Locker w/ Sloping Top	2	 Yellow	1800 x 300 x 450
214255	RS PRO	Full height Locker w/ Sloping Top	2	 Dark Grey	1800 x 300 x 450
214266	RS PRO	Full height Locker w/ Sloping Top	3	 Blue	1800 x 300 x 450
214267	RS PRO	Full height Locker w/ Sloping Top	3	 Light Grey	1800 x 300 x 450
214269	RS PRO	Full height Locker w/ Sloping Top	3	 Red	1800 x 300 x 450
213320	RS PRO	Full height Locker w/ Sloping Top	3	 Green	1800 x 300 x 450
213321	RS PRO	Full height Locker w/ Sloping Top	3	 Yellow	1800 x 300 x 450
213322	RS PRO	Full height Locker w/ Sloping Top	3	 Dark Grey	1800 x 300 x 450
213331	RS PRO	Full height Locker w/ Sloping Top	4	 Blue	1800 x 300 x 450
213333	RS PRO	Full height Locker w/ Sloping Top	4	 Light Grey	1800 x 300 x 450
213334	RS PRO	Full height Locker w/ Sloping Top	4	 Red	1800 x 300 x 450
213336	RS PRO	Full height Locker w/ Sloping Top	4	 Green	1800 x 300 x 450
213337	RS PRO	Full height Locker w/ Sloping Top	4	 Yellow	1800 x 300 x 450
213338	RS PRO	Full height Locker w/ Sloping Top	4	 Dark Grey	1800 x 300 x 450
214283	RS PRO	Full height Locker w/ Sloping Top	6	 Blue	1800 x 300 x 450
214285	RS PRO	Full height Locker w/ Sloping Top	6	 Light Grey	1800 x 300 x 450
214286	RS PRO	Full height Locker w/ Sloping Top	6	 Red	1800 x 300 x 450
214288	RS PRO	Full height Locker w/ Sloping Top	6	 Green	1800 x 300 x 450
214289	RS PRO	Full height Locker w/ Sloping Top	6	 Yellow	1800 x 300 x 450
214291	RS PRO	Full height Locker w/ Sloping Top	6	 Dark Grey	1800 x 300 x 450
214351	RS PRO	Full height Locker	10	 Blue	1800 x 300 x 450
214352	RS PRO	Full height Locker	10	 Light Grey	1800 x 300 x 450
214354	RS PRO	Full height Locker	10	 Red	1800 x 300 x 450
214355	RS PRO	Full height Locker	10	 Green	1800 x 300 x 450
214356	RS PRO	Full height Locker	10	 Yellow	1800 x 300 x 450
214358	RS PRO	Full height Locker	10	 Dark Grey	1800 x 300 x 450
214359	RS PRO	Full height Locker w/ Sloping Top	10	 Blue	1800 x 300 x 450
214360	RS PRO	Full height Locker w/ Sloping Top	10	 Light Grey	1800 x 300 x 450
214361	RS PRO	Full height Locker w/ Sloping Top	10	 Red	1800 x 300 x 450
214362	RS PRO	Full height Locker w/ Sloping Top	10	 Green	1800 x 300 x 450
214364	RS PRO	Full height Locker w/ Sloping Top	10	 Yellow	1800 x 300 x 450
214365	RS PRO	Full height Locker w/ Sloping Top	10	 Dark Grey	1800 x 300 x 450

Stock No.	Brand	Product Name	No of Doors	Door Colours	Dimension (H x W x D mm)
214366	RS PRO	Full height Locker	1	 Blue	1800 x 380 x 450
214367	RS PRO	Full height Locker	1	 Light Grey	1800 x 380 x 450
214368	RS PRO	Full height Locker	1	 Red	1800 x 380 x 450
214370	RS PRO	Full height Locker	1	 Green	1800 x 380 x 450
214371	RS PRO	Full height Locker	1	 Yellow	1800 x 380 x 450
214373	RS PRO	Full height Locker	1	 Dark Grey	1800 x 380 x 450
214374	RS PRO	Full height Locker w/ Sloping Top	1	 Blue	1800 x 380 x 450
214376	RS PRO	Full height Locker w/ Sloping Top	1	 Light Grey	1800 x 380 x 450
214377	RS PRO	Full height Locker w/ Sloping Top	1	 Red	1800 x 380 x 450
214378	RS PRO	Full height Locker w/ Sloping Top	1	 Green	1800 x 380 x 450
214380	RS PRO	Full height Locker w/ Sloping Top	1	 Yellow	1800 x 380 x 450
214382	RS PRO	Full height Locker w/ Sloping Top	1	 Dark Grey	1800 x 380 x 450
214383	RS PRO	Full height Locker	2	 Blue	1800 x 380 x 450
214384	RS PRO	Full height Locker	2	 Light Grey	1800 x 380 x 450
214386	RS PRO	Full height Locker	2	 Red	1800 x 380 x 450
214387	RS PRO	Full height Locker	2	 Green	1800 x 380 x 450
213443	RS PRO	Full height Locker	2	 Yellow	1800 x 380 x 450
213444	RS PRO	Full height Locker	2	 Dark Grey	1800 x 380 x 450
213445	RS PRO	Full height Locker w/ Sloping Top	2	 Blue	1800 x 380 x 450
213446	RS PRO	Full height Locker w/ Sloping Top	2	 Light Grey	1800 x 380 x 450
213447	RS PRO	Full height Locker w/ Sloping Top	2	 Red	1800 x 380 x 450
213448	RS PRO	Full height Locker w/ Sloping Top	2	 Green	1800 x 380 x 450
213450	RS PRO	Full height Locker w/ Sloping Top	2	 Yellow	1800 x 380 x 450
213451	RS PRO	Full height Locker w/ Sloping Top	2	 Dark Grey	1800 x 380 x 450
213452	RS PRO	Full height Locker	3	 Blue	1800 x 380 x 450
213453	RS PRO	Full height Locker	3	 Light Grey	1800 x 380 x 450
213454	RS PRO	Full height Locker	3	 Red	1800 x 380 x 450
213456	RS PRO	Full height Locker	3	 Green	1800 x 380 x 450
213457	RS PRO	Full height Locker	3	 Yellow	1800 x 380 x 450
213459	RS PRO	Full height Locker	3	 Dark Grey	1800 x 380 x 450
213460	RS PRO	Full height Locker w/ Sloping Top	3	 Blue	1800 x 380 x 450
213462	RS PRO	Full height Locker w/ Sloping Top	3	 Light Grey	1800 x 380 x 450
213463	RS PRO	Full height Locker w/ Sloping Top	3	 Red	1800 x 380 x 450
213465	RS PRO	Full height Locker w/ Sloping Top	3	 Green	1800 x 380 x 450
213466	RS PRO	Full height Locker w/ Sloping Top	3	 Yellow	1800 x 380 x 450
213468	RS PRO	Full height Locker w/ Sloping Top	3	 Dark Grey	1800 x 380 x 450
213469	RS PRO	Full height Locker	4	 Blue	1800 x 380 x 450
213471	RS PRO	Full height Locker	4	 Light Grey	1800 x 380 x 450
213472	RS PRO	Full height Locker	4	 Red	1800 x 380 x 450

Stock No.	Brand	Product Name	No of Doors	Door Colours	Dimension (H x W x D mm)
213474	RS PRO	Full height Locker	4	 Green	1800 x 380 x 450
213475	RS PRO	Full height Locker	4	 Yellow	1800 x 380 x 450
213476	RS PRO	Full height Locker	4	 Dark Grey	1800 x 380 x 450
213238	RS PRO	Full height Locker w/ Sloping Top	4	 Blue	1800 x 380 x 450
213239	RS PRO	Full height Locker w/ Sloping Top	4	 Light Grey	1800 x 380 x 450
213241	RS PRO	Full height Locker w/ Sloping Top	4	 Red	1800 x 380 x 450
213242	RS PRO	Full height Locker w/ Sloping Top	4	 Green	1800 x 380 x 450
213244	RS PRO	Full height Locker w/ Sloping Top	4	 Yellow	1800 x 380 x 450
213245	RS PRO	Full height Locker w/ Sloping Top	4	 Dark Grey	1800 x 380 x 450
213246	RS PRO	Full height Locker	6	 Blue	1800 x 380 x 450
213248	RS PRO	Full height Locker	6	 Light Grey	1800 x 380 x 450
213249	RS PRO	Full height Locker	6	 Red	1800 x 380 x 450
213250	RS PRO	Full height Locker	6	 Green	1800 x 380 x 450
213251	RS PRO	Full height Locker	6	 Yellow	1800 x 380 x 450
213252	RS PRO	Full height Locker	6	 Dark Grey	1800 x 380 x 450
213254	RS PRO	Full height Locker	10	 Blue	1800 x 380 x 450
213255	RS PRO	Full height Locker	10	 Light Grey	1800 x 380 x 450
213703	RS PRO	Full height Locker	10	 Red	1800 x 380 x 450
213705	RS PRO	Full height Locker	10	 Green	1800 x 380 x 450
213706	RS PRO	Full height Locker	10	 Yellow	1800 x 380 x 450
213707	RS PRO	Full height Locker	10	 Dark Grey	1800 x 380 x 450
213709	RS PRO	Full height Locker w/ Sloping Top	10	 Blue	1800 x 380 x 450
213711	RS PRO	Full height Locker w/ Sloping Top	10	 Light Grey	1800 x 380 x 450
213712	RS PRO	Full height Locker w/ Sloping Top	10	 Red	1800 x 380 x 450
213713	RS PRO	Full height Locker w/ Sloping Top	10	 Green	1800 x 380 x 450
213715	RS PRO	Full height Locker w/ Sloping Top	10	 Yellow	1800 x 380 x 450
213716	RS PRO	Full height Locker w/ Sloping Top	10	 Dark Grey	1800 x 380 x 450
213718	RS PRO	Full height Locker	1	 Blue	1800 x 450 x 450
213719	RS PRO	Full height Locker	1	 Light Grey	1800 x 450 x 450
213721	RS PRO	Full height Locker	1	 Red	1800 x 450 x 450
213722	RS PRO	Full height Locker	1	 Green	1800 x 450 x 450
213724	RS PRO	Full height Locker	1	 Yellow	1800 x 450 x 450
213725	RS PRO	Full height Locker	1	 Dark Grey	1800 x 450 x 450
213258	RS PRO	Full height Locker w/ Sloping Top	1	 Blue	1800 x 450 x 450
213260	RS PRO	Full height Locker w/ Sloping Top	1	 Light Grey	1800 x 450 x 450
213263	RS PRO	Full height Locker w/ Sloping Top	1	 Red	1800 x 450 x 450
213264	RS PRO	Full height Locker w/ Sloping Top	1	 Green	1800 x 450 x 450
213266	RS PRO	Full height Locker w/ Sloping Top	1	 Yellow	1800 x 450 x 450
213267	RS PRO	Full height Locker w/ Sloping Top	1	 Dark Grey	1800 x 450 x 450

Stock No.	Brand	Product Name	No of Doors	Door Colours	Dimension (H x W x D mm)
213268	RS PRO	Full height Locker	2	 Blue	1800 x 450 x 450
213270	RS PRO	Full height Locker	2	 Light Grey	1800 x 450 x 450
213272	RS PRO	Full height Locker	2	 Red	1800 x 450 x 450
213273	RS PRO	Full height Locker	2	 Green	1800 x 450 x 450
213274	RS PRO	Full height Locker	2	 Yellow	1800 x 450 x 450
213276	RS PRO	Full height Locker	2	 Dark Grey	1800 x 450 x 450
213277	RS PRO	Full height Locker w/ Sloping Top	2	 Blue	1800 x 450 x 450
213279	RS PRO	Full height Locker w/ Sloping Top	2	 Light Grey	1800 x 450 x 450
213280	RS PRO	Full height Locker w/ Sloping Top	2	 Red	1800 x 450 x 450
213282	RS PRO	Full height Locker w/ Sloping Top	2	 Green	1800 x 450 x 450
213283	RS PRO	Full height Locker w/ Sloping Top	2	 Yellow	1800 x 450 x 450
213718	RS PRO	Full height Locker w/ Sloping Top	2	 Dark Grey	1800 x 450 x 450
213285	RS PRO	Full height Locker	3	 Blue	1800 x 450 x 450
213286	RS PRO	Full height Locker	3	 Light Grey	1800 x 450 x 450
213288	RS PRO	Full height Locker	3	 Red	1800 x 450 x 450
213289	RS PRO	Full height Locker	3	 Green	1800 x 450 x 450
213291	RS PRO	Full height Locker	3	 Yellow	1800 x 450 x 450
213292	RS PRO	Full height Locker	3	 Dark Grey	1800 x 450 x 450
213294	RS PRO	Full height Locker w/ Sloping Top	3	 Blue	1800 x 450 x 450
213295	RS PRO	Full height Locker w/ Sloping Top	3	 Light Grey	1800 x 450 x 450
213296	RS PRO	Full height Locker w/ Sloping Top	3	 Red	1800 x 450 x 450
213298	RS PRO	Full height Locker w/ Sloping Top	3	 Green	1800 x 450 x 450
213299	RS PRO	Full height Locker w/ Sloping Top	3	 Yellow	1800 x 450 x 450
213570	RS PRO	Full height Locker w/ Sloping Top	3	 Dark Grey	1800 x 450 x 450
213572	RS PRO	Full height Locker	4	 Blue	1800 x 450 x 450
213573	RS PRO	Full height Locker	4	 Light Grey	1800 x 450 x 450
213575	RS PRO	Full height Locker	4	 Red	1800 x 450 x 450
213179	RS PRO	Full height Locker	4	 Green	1800 x 450 x 450
213181	RS PRO	Full height Locker	4	 Yellow	1800 x 450 x 450
213182	RS PRO	Full height Locker	4	 Dark Grey	1800 x 450 x 450
213184	RS PRO	Full height Locker w/ Sloping Top	4	 Blue	1800 x 450 x 450
213185	RS PRO	Full height Locker w/ Sloping Top	4	 Light Grey	1800 x 450 x 450
213187	RS PRO	Full height Locker w/ Sloping Top	4	 Red	1800 x 450 x 450
213188	RS PRO	Full height Locker w/ Sloping Top	4	 Green	1800 x 450 x 450
213189	RS PRO	Full height Locker w/ Sloping Top	4	 Yellow	1800 x 450 x 450
213190	RS PRO	Full height Locker w/ Sloping Top	4	 Dark Grey	1800 x 450 x 450
213191	RS PRO	Full height Locker	6	 Blue	1800 x 450 x 450
213193	RS PRO	Full height Locker	6	 Light Grey	1800 x 450 x 450
213194	RS PRO	Full height Locker	6	 Red	1800 x 450 x 450

Stock No.	Brand	Product Name	No of Doors	Door Colours	Dimension (H x W x D mm)
213195	RS PRO	Full height Locker	6	 Green	1800 x 450 x 450
213197	RS PRO	Full height Locker	6	 Yellow	1800 x 450 x 450
213198	RS PRO	Full height Locker	6	 Dark Grey	1800 x 450 x 450
213200	RS PRO	Full height Locker w/ Sloping Top	6	 Blue	1800 x 450 x 450
213201	RS PRO	Full height Locker w/ Sloping Top	6	 Light Grey	1800 x 450 x 450
213202	RS PRO	Full height Locker w/ Sloping Top	6	 Red	1800 x 450 x 450
213204	RS PRO	Full height Locker w/ Sloping Top	6	 Green	1800 x 450 x 450
213205	RS PRO	Full height Locker w/ Sloping Top	6	 Yellow	1800 x 450 x 450
213207	RS PRO	Full height Locker w/ Sloping Top	6	 Dark Grey	1800 x 450 x 450
213208	RS PRO	Full height Locker	10	 Blue	1800 x 450 x 450
213210	RS PRO	Full height Locker	10	 Light Grey	1800 x 450 x 450
213211	RS PRO	Full height Locker	10	 Red	1800 x 450 x 450
213213	RS PRO	Full height Locker	10	 Green	1800 x 450 x 450
213661	RS PRO	Full height Locker	10	 Yellow	1800 x 450 x 450
213662	RS PRO	Full height Locker	10	 Dark Grey	1800 x 450 x 450
213674	RS PRO	Full height Locker w/ Sloping Top	10	 Blue	1800 x 450 x 450
213676	RS PRO	Full height Locker w/ Sloping Top	10	 Light Grey	1800 x 450 x 450
213677	RS PRO	Full height Locker w/ Sloping Top	10	 Red	1800 x 450 x 450
213678	RS PRO	Full height Locker w/ Sloping Top	10	 Green	1800 x 450 x 450
213680	RS PRO	Full height Locker w/ Sloping Top	10	 Yellow	1800 x 450 x 450
213682	RS PRO	Full height Locker w/ Sloping Top	10	 Dark Grey	1800 x 450 x 450
213974	RS PRO	Cube Locker	1	 Blue	300 x 300 x 300
213976	RS PRO	Cube Locker	1	 Light Grey	300 x 300 x 300
213977	RS PRO	Cube Locker	1	 Red	300 x 300 x 300
213979	RS PRO	Cube Locker	1	 Green	300 x 300 x 300
213980	RS PRO	Cube Locker	1	 Yellow	300 x 300 x 300
213982	RS PRO	Cube Locker	1	 Dark Grey	300 x 300 x 300
213983	RS PRO	Cube Locker	1	 Blue	380 x 380 x 380
213985	RS PRO	Cube Locker	1	 Light Grey	380 x 380 x 380
213986	RS PRO	Cube Locker	1	 Red	380 x 380 x 380
213987	RS PRO	Cube Locker	1	 Green	380 x 380 x 380
213989	RS PRO	Cube Locker	1	 Yellow	380 x 380 x 380
213991	RS PRO	Cube Locker	1	 Dark Grey	380 x 380 x 380
213992	RS PRO	Cube Locker	1	 Blue	450 x 450 x 450
214441	RS PRO	Cube Locker	1	 Light Grey	450 x 450 x 450
214443	RS PRO	Cube Locker	1	 Red	450 x 450 x 450
214444	RS PRO	Cube Locker	1	 Green	450 x 450 x 450
214446	RS PRO	Cube Locker	1	 Yellow	450 x 450 x 450
214447	RS PRO	Cube Locker	1	 Dark Grey	450 x 450 x 450

Stock No.	Brand	Product Name	No of Doors	Door Colours	Dimension (H x W x D mm)
213585	RS PRO	Support Frame w/ Seat	N/A	 Light Grey (Frame)	600 x 300
213586	RS PRO	Support Frame w/ Seat	N/A	 Light Grey (Frame)	750 x 300
213588	RS PRO	Support Frame w/ Seat	N/A	 Light Grey (Frame)	800 x 300
213589	RS PRO	Support Frame w/ Seat	N/A	 Light Grey (Frame)	750 x 380
213591	RS PRO	Support Frame w/ Seat	N/A	 Light Grey (Frame)	750 x 450
213592	RS PRO	Support Frame w/ Seat	N/A	 Light Grey (Frame)	800 x 450
213594	RS PRO	Locker Support Frame	N/A	 Light Grey (Frame)	150 x 300 x 300
213595	RS PRO	Locker Support Frame	N/A	 Light Grey (Frame)	150 x 300 x 450
213597	RS PRO	Locker Support Frame	N/A	 Light Grey (Frame)	150 x 380 x 450
213598	RS PRO	Locker Support Frame	N/A	 Light Grey (Frame)	150 x 450 x 450
213599	RS PRO	Locker Support Frame	N/A	 Light Grey (Frame)	150 x 915 x 505

Important note regarding locker installations

Wherever possible lockers should be secured to ensure stability. Single lockers should ideally be fixed back to a wall. Runs of lockers should be fixed together side-to-side and either fixed back to a wall or fixed back-to-back to another run of lockers.

Approvals

Standards Met	BS 4680: 1996
---------------	---------------




Full height lockers

Our full height 1800mm metal lockers are available in a wide range of sizes, door configurations, locking options and colours.

- Single door lockers have a fixed top shelf, with a garment hanging rail (except 300mm deep) with two coat hooks.
- Two door lockers have a garment hanging rail (except 300mm deep) and two coat hooks in each compartment.

Height - 1800mm	
Width	Depth
300	300
300	380
300	450
380	450
450	450



Cube Lockers

Cubes- as the name suggests- have an equal height, width and depth; allowing combined stacking of units on the floor or on support frames.

- Versatile and compact all steel single door cube lockers; popular for personal effects and bags.

Height	Width	Depth
300mm	300mm	300mm
380mm	380mm	380mm
450mm	450mm	450mm



Can be stacked and mounted onto frames to create blocks of lockers.

Accessories

Customise our lockers to meet your requirements..



Sloping tops are essential in hygiene sensitive locations (such as hospitals and the food industry). The slope prevents items and litter being left on locker tops and makes cleaning easier. Sloping tops increase the overall height of the locker.



Locker support frames raise lockers off the floor, reducing impact damage and improving hygiene standards.

Supplied with adjustable feet to allow for uneven floors. Inset rear legs to clear pipes and skirting. Standard height is 150mm.



Support frame with seat. Seat units are incorporated into the locker frame, as well as slatted seats to the front.

They can include a mesh shelf for footwear.