

RS PRO Cupboard Range

Features

- Finished with antibacterial technology
- Vertical door stiffener for added strength.
- 3-point locking as standard.
- Adjustable shelves on a 25mm vertical pitch.
- Shelves carry a maximum of 78kg UDL.
- Semi-concealed hinges.
- Standard colours to chose
- Lock options may be available, depending on the design of cupboard chosen.
- Cupboard options:
 - Standard Cupboard
 - Security Cupboard
 - Slimline Cupboard
 - Large Volume Cupboard
 - Tool Cabinet



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Steel Cupboard Range

Valuable goods and equipment used in any work environment can be safely locked away in RS PRO secure industrial storage cupboards. A versatile and robust range of steel cupboards providing secure storage in the workplace; meeting the stringent requirements of BS EN 14073:2004 (Parts 1, 2 & 3) and BS EN 14074:2004.

Cupboards are all available with a range of internal configurations, dependant on whether you require a small amount of larger compartments or several smaller compartments; we have the storage cabinet to meet your needs.

ActiveCoat antimicrobial technology is incorporated into all our locker products at the time of manufacture, offering constant protection against a wide range of bacteria.



General Specifications

Product Name	Steel Cupboard
Number of Doors	See details below
Body Colour	Light Grey
Door Colours	See details below
Cupboard Internals	See details below
External Height	See details below
External Width	See details below
External Depth	See details below

Stock No.	Brand	Product Name	Door Colours	Dimension (H x W x D mm)	Cupboard Internals
213844	RS PRO	Tool Cabinet	 Blue	1820 x 477 x 505	S31
213845	RS PRO	Tool Cabinet	 Light Grey	1820 x 477 x 505	S31
213847	RS PRO	Tool Cabinet	 Red	1820 x 477 x 505	S31
213848	RS PRO	Tool Cabinet	 Green	1820 x 477 x 505	S31
213850	RS PRO	Tool Cabinet	 Yellow	1820 x 477 x 505	S31
213851	RS PRO	Tool Cabinet	 Dark Grey	1820 x 477 x 505	S31
213853	RS PRO	Tool Cabinet	 Blue	1820 x 477 x 505	S35
213854	RS PRO	Tool Cabinet	 Light Grey	1820 x 477 x 505	S35
213856	RS PRO	Tool Cabinet	 Red	1820 x 477 x 505	S35
213857	RS PRO	Tool Cabinet	 Green	1820 x 477 x 505	S35
213858	RS PRO	Tool Cabinet	 Yellow	1820 x 477 x 505	S35
213860	RS PRO	Tool Cabinet	 Dark Grey	1820 x 477 x 505	S35
213862	RS PRO	Tool Cabinet	 Blue	1820 x 477 x 505	S41
213863	RS PRO	Tool Cabinet	 Light Grey	1820 x 477 x 505	S41
214579	RS PRO	Tool Cabinet	 Red	1820 x 477 x 505	S41
214581	RS PRO	Tool Cabinet	 Green	1820 x 477 x 505	S41
214582	RS PRO	Tool Cabinet	 Yellow	1820 x 477 x 505	S41
214584	RS PRO	Tool Cabinet	 Dark Grey	1820 x 477 x 505	S41
214585	RS PRO	Slimline Cupboard	 Blue	1820 x 615 x 505	S00
214586	RS PRO	Slimline Cupboard	 Light Grey	1820 x 615 x 505	S00
214588	RS PRO	Slimline Cupboard	 Red	1820 x 615 x 505	S00
214589	RS PRO	Slimline Cupboard	 Green	1820 x 615 x 505	S00
214590	RS PRO	Slimline Cupboard	 Yellow	1820 x 615 x 505	S00
214591	RS PRO	Slimline Cupboard	 Dark Grey	1820 x 615 x 505	S00
214592	RS PRO	Slimline Cupboard	 Blue	1820 x 615 x 505	S01
214594	RS PRO	Slimline Cupboard	 Light Grey	1820 x 615 x 505	S01
214595	RS PRO	Slimline Cupboard	 Red	1820 x 615 x 505	S01
214597	RS PRO	Slimline Cupboard	 Green	1820 x 615 x 505	S01
214598	RS PRO	Slimline Cupboard	 Yellow	1820 x 615 x 505	S01
214601	RS PRO	Slimline Cupboard	 Dark Grey	1820 x 615 x 505	S01
214602	RS PRO	Slimline Cupboard	 Blue	1820 x 615 x 505	S02
214604	RS PRO	Slimline Cupboard	 Light Grey	1820 x 615 x 505	S02
214605	RS PRO	Slimline Cupboard	 Red	1820 x 615 x 505	S02
214607	RS PRO	Slimline Cupboard	 Green	1820 x 615 x 505	S02
214608	RS PRO	Slimline Cupboard	 Yellow	1820 x 615 x 505	S02
214609	RS PRO	Slimline Cupboard	 Dark Grey	1820 x 615 x 505	S02
214610	RS PRO	Slimline Cupboard	 Blue	1820 x 615 x 505	S08
214611	RS PRO	Slimline Cupboard	 Light Grey	1820 x 615 x 505	S08

Stock No.	Brand	Product Name	Door Colours	Dimension (H x W x D mm)	Cupboard Internals
214613	RS PRO	Slimline Cupboard	 Red	1820 x 615 x 505	S08
214614	RS PRO	Slimline Cupboard	 Green	1820 x 615 x 505	S08
214615	RS PRO	Slimline Cupboard	 Yellow	1820 x 615 x 505	S08
214617	RS PRO	Slimline Cupboard	 Dark Grey	1820 x 615 x 505	S08
213864	RS PRO	Slimline Cupboard	 Blue	1820 x 615 x 505	S09
213866	RS PRO	Slimline Cupboard	 Light Grey	1820 x 615 x 505	S09
213867	RS PRO	Slimline Cupboard	 Red	1820 x 615 x 505	S09
213869	RS PRO	Slimline Cupboard	 Green	1820 x 615 x 505	S09
213870	RS PRO	Slimline Cupboard	 Yellow	1820 x 615 x 505	S09
213872	RS PRO	Slimline Cupboard	 Dark Grey	1820 x 615 x 505	S09
213873	RS PRO	Slimline Cupboard	 Blue	1820 x 615 x 505	S10
213875	RS PRO	Slimline Cupboard	 Light Grey	1820 x 615 x 505	S10
213876	RS PRO	Slimline Cupboard	 Red	1820 x 615 x 505	S10
213878	RS PRO	Slimline Cupboard	 Green	1820 x 615 x 505	S10
213879	RS PRO	Slimline Cupboard	 Yellow	1820 x 615 x 505	S10
213881	RS PRO	Slimline Cupboard	 Dark Grey	1820 x 615 x 505	S10
213882	RS PRO	Slimline Cupboard	 Blue	1820 x 615 x 505	S11
213884	RS PRO	Slimline Cupboard	 Light Grey	1820 x 615 x 505	S11
213885	RS PRO	Slimline Cupboard	 Red	1820 x 615 x 505	S11
213886	RS PRO	Slimline Cupboard	 Green	1820 x 615 x 505	S11
213888	RS PRO	Slimline Cupboard	 Yellow	1820 x 615 x 505	S11
213889	RS PRO	Slimline Cupboard	 Dark Grey	1820 x 615 x 505	S11
213890	RS PRO	Slimline Cupboard	 Blue	1820 x 615 x 505	S12
213891	RS PRO	Slimline Cupboard	 Light Grey	1820 x 615 x 505	S12
213892	RS PRO	Slimline Cupboard	 Red	1820 x 615 x 505	S12
213894	RS PRO	Slimline Cupboard	 Green	1820 x 615 x 505	S12
213895	RS PRO	Slimline Cupboard	 Yellow	1820 x 615 x 505	S12
213897	RS PRO	Slimline Cupboard	 Dark Grey	1820 x 615 x 505	S12
213898	RS PRO	Slimline Cupboard	 Blue	1820 x 615 x 505	S13
213901	RS PRO	Slimline Cupboard	 Light Grey	1820 x 615 x 505	S13
213902	RS PRO	Slimline Cupboard	 Red	1820 x 615 x 505	S13
213904	RS PRO	Slimline Cupboard	 Green	1820 x 615 x 505	S13
213905	RS PRO	Slimline Cupboard	 Yellow	1820 x 615 x 505	S13
213907	RS PRO	Slimline Cupboard	 Dark Grey	1820 x 615 x 505	S13
214481	RS PRO	Slimline Cupboard	 Blue	1820 x 615 x 505	S14
214483	RS PRO	Slimline Cupboard	 Light Grey	1820 x 615 x 505	S14
214484	RS PRO	Slimline Cupboard	 Red	1820 x 615 x 505	S14
214485	RS PRO	Slimline Cupboard	 Green	1820 x 615 x 505	S14
214487	RS PRO	Slimline Cupboard	 Yellow	1820 x 615 x 505	S14

Stock No.	Brand	Product Name	Door Colours	Dimension (H x W x D mm)	Cupboard Internals
214488	RS PRO	Slimline Cupboard	 Dark Grey	1820 x 615 x 505	S14
21449	RS PRO	Standard Cupboard	 Blue	1820 x 915 x 505	S00
214491	RS PRO	Standard Cupboard	 Light Grey	1820 x 915 x 505	S00
214493	RS PRO	Standard Cupboard	 Red	1820 x 915 x 505	S00
214494	RS PRO	Standard Cupboard	 Green	1820 x 915 x 505	S00
214496	RS PRO	Standard Cupboard	 Yellow	1820 x 915 x 505	S00
214497	RS PRO	Standard Cupboard	 Dark Grey	1820 x 915 x 505	S00
213741	RS PRO	Standard Cupboard	 Blue	1820 x 915 x 505	S02
213743	RS PRO	Standard Cupboard	 Light Grey	1820 x 915 x 505	S02
213744	RS PRO	Standard Cupboard	 Red	1820 x 915 x 505	S02
213746	RS PRO	Standard Cupboard	 Green	1820 x 915 x 505	S02
213747	RS PRO	Standard Cupboard	 Yellow	1820 x 915 x 505	S02
213749	RS PRO	Standard Cupboard	 Dark Grey	1820 x 915 x 505	S02
213750	RS PRO	Standard Cupboard	 Blue	1820 x 915 x 505	S08
213752	RS PRO	Standard Cupboard	 Light Grey	1820 x 915 x 505	S08
213753	RS PRO	Standard Cupboard	 Red	1820 x 915 x 505	S08
213755	RS PRO	Standard Cupboard	 Green	1820 x 915 x 505	S08
213756	RS PRO	Standard Cupboard	 Yellow	1820 x 915 x 505	S08
213757	RS PRO	Standard Cupboard	 Dark Grey	1820 x 915 x 505	S08
213759	RS PRO	Standard Cupboard	 Blue	1820 x 915 x 505	S09
213761	RS PRO	Standard Cupboard	 Light Grey	1820 x 915 x 505	S09
213762	RS PRO	Standard Cupboard	 Red	1820 x 915 x 505	S09
213763	RS PRO	Standard Cupboard	 Green	1820 x 915 x 505	S09
213765	RS PRO	Standard Cupboard	 Yellow	1820 x 915 x 505	S09
213766	RS PRO	Standard Cupboard	 Dark Grey	1820 x 915 x 505	S09
213768	RS PRO	Standard Cupboard	 Blue	1820 x 915 x 505	S10
213769	RS PRO	Standard Cupboard	 Light Grey	1820 x 915 x 505	S10
213771	RS PRO	Standard Cupboard	 Red	1820 x 915 x 505	S10
213772	RS PRO	Standard Cupboard	 Green	1820 x 915 x 505	S10
213774	RS PRO	Standard Cupboard	 Yellow	1820 x 915 x 505	S10
213775	RS PRO	Standard Cupboard	 Dark Grey	1820 x 915 x 505	S10
213777	RS PRO	Standard Cupboard	 Blue	1820 x 915 x 505	S11
213778	RS PRO	Standard Cupboard	 Light Grey	1820 x 915 x 505	S11
213779	RS PRO	Standard Cupboard	 Red	1820 x 915 x 505	S11
21378	RS PRO	Standard Cupboard	 Green	1820 x 915 x 505	S11
213781	RS PRO	Standard Cupboard	 Yellow	1820 x 915 x 505	S11
213782	RS PRO	Standard Cupboard	 Dark Grey	1820 x 915 x 505	S11
214499	RS PRO	Standard Cupboard	 Blue	1820 x 915 x 505	S12

Stock No.	Brand	Product Name	Door Colours	Dimension (H x W x D mm)	Cupboard Internals
214500	RS PRO	Standard Cupboard	Light Grey	1820 x 915 x 505	S12
214501	RS PRO	Standard Cupboard	Red	1820 x 915 x 505	S12
214503	RS PRO	Standard Cupboard	Green	1820 x 915 x 505	S12
214504	RS PRO	Standard Cupboard	Yellow	1820 x 915 x 505	S12
214506	RS PRO	Standard Cupboard	Dark Grey	1820 x 915 x 505	S12
214507	RS PRO	Standard Cupboard	Blue	1820 x 915 x 505	S13
214508	RS PRO	Standard Cupboard	Light Grey	1820 x 915 x 505	S13
214510	RS PRO	Standard Cupboard	Red	1820 x 915 x 505	S13
214512	RS PRO	Standard Cupboard	Green	1820 x 915 x 505	S13
214513	RS PRO	Standard Cupboard	Yellow	1820 x 915 x 505	S13
214514	RS PRO	Standard Cupboard	Dark Grey	1820 x 915 x 505	S13
214516	RS PRO	Standard Cupboard	Blue	1820 x 915 x 505	S14
214517	RS PRO	Standard Cupboard	Light Grey	1820 x 915 x 505	S14
214519	RS PRO	Standard Cupboard	Red	1820 x 915 x 505	S14
214520	RS PRO	Standard Cupboard	Green	1820 x 915 x 505	S14
214522	RS PRO	Standard Cupboard	Yellow	1820 x 915 x 505	S14
214523	RS PRO	Standard Cupboard	Dark Grey	1820 x 915 x 505	S14
214525	RS PRO	Standard Cupboard	Blue	1820 x 915 x 505	S20
214526	RS PRO	Standard Cupboard	Light Grey	1820 x 915 x 505	S20
214528	RS PRO	Standard Cupboard	Red	1820 x 915 x 505	S20
214529	RS PRO	Standard Cupboard	Green	1820 x 915 x 505	S20
214531	RS PRO	Standard Cupboard	Yellow	1820 x 915 x 505	S20
214532	RS PRO	Standard Cupboard	Dark Grey	1820 x 915 x 505	S20
214534	RS PRO	Standard Cupboard	Blue	1820 x 915 x 505	S21
214535	RS PRO	Standard Cupboard	Light Grey	1820 x 915 x 505	S21
214536	RS PRO	Standard Cupboard	Red	1820 x 915 x 505	S21
214538	RS PRO	Standard Cupboard	Green	1820 x 915 x 505	S21
213783	RS PRO	Standard Cupboard	Yellow	1820 x 915 x 505	S21
213784	RS PRO	Standard Cupboard	Dark Grey	1820 x 915 x 505	S21
213998	RS PRO	Standard Cupboard	Blue	1820 x 915 x 505	S22
213999	RS PRO	Standard Cupboard	Light Grey	1820 x 915 x 505	S22
214001	RS PRO	Standard Cupboard	Red	1820 x 915 x 505	S22
214002	RS PRO	Standard Cupboard	Green	1820 x 915 x 505	S22
214003	RS PRO	Standard Cupboard	Yellow	1820 x 915 x 505	S22
214005	RS PRO	Standard Cupboard	Dark Grey	1820 x 915 x 505	S22
214006	RS PRO	Standard Cupboard	Blue	1820 x 915 x 505	S25
214008	RS PRO	Standard Cupboard	Light Grey	1820 x 915 x 505	S25
214009	RS PRO	Standard Cupboard	Red	1820 x 915 x 505	S25
21411	RS PRO	Standard Cupboard	Green	1820 x 915 x 505	S25

Stock No.	Brand	Product Name	Door Colours	Dimension (H x W x D mm)	Cupboard Internals
21412	RS PRO	Standard Cupboard	 Yellow	1820 x 915 x 505	S25
21414	RS PRO	Standard Cupboard	 Dark Grey	1820 x 915 x 505	S25
214015	RS PRO	Insight Cupboard	 Blue	1820 x 915 x 505	S13
214017	RS PRO	Insight Cupboard	 Light Grey	1820 x 915 x 505	S13
214018	RS PRO	Insight Cupboard	 Red	1820 x 915 x 505	S13
214019	RS PRO	Insight Cupboard	 Green	1820 x 915 x 505	S13
214020	RS PRO	Insight Cupboard	 Yellow	1820 x 915 x 505	S13
214021	RS PRO	Insight Cupboard	 Dark Grey	1820 x 915 x 505	S13
214023	RS PRO	Security Cupboard	 Blue	1820 x 915 x 505	S02
214024	RS PRO	Security Cupboard	 Light Grey	1820 x 915 x 505	S02
214025	RS PRO	Security Cupboard	 Red	1820 x 915 x 505	S02
214027	RS PRO	Security Cupboard	 Green	1820 x 915 x 505	S02
214028	RS PRO	Security Cupboard	 Yellow	1820 x 915 x 505	S02
214030	RS PRO	Security Cupboard	 Dark Grey	1820 x 915 x 505	S02
214031	RS PRO	Security Cupboard	 Blue	1820 x 915 x 505	S11
214033	RS PRO	Security Cupboard	 Light Grey	1820 x 915 x 505	S11
214034	RS PRO	Security Cupboard	 Red	1820 x 915 x 505	S11
214698	RS PRO	Security Cupboard	 Green	1820 x 915 x 505	S11
214699	RS PRO	Security Cupboard	 Yellow	1820 x 915 x 505	S11
214700	RS PRO	Security Cupboard	 Dark Grey	1820 x 915 x 505	S11
214702	RS PRO	Security Cupboard	 Blue	1820 x 915 x 505	S12
214703	RS PRO	Security Cupboard	 Light Grey	1820 x 915 x 505	S12
214705	RS PRO	Security Cupboard	 Red	1820 x 915 x 505	S12
214706	RS PRO	Security Cupboard	 Green	1820 x 915 x 505	S12
214708	RS PRO	Security Cupboard	 Yellow	1820 x 915 x 505	S12
214709	RS PRO	Security Cupboard	 Dark Grey	1820 x 915 x 505	S12
214711	RS PRO	Security Cupboard	 Blue	1820 x 915 x 505	S13
214712	RS PRO	Security Cupboard	 Light Grey	1820 x 915 x 505	S13
214714	RS PRO	Security Cupboard	 Red	1820 x 915 x 505	S13
214715	RS PRO	Security Cupboard	 Green	1820 x 915 x 505	S13
214716	RS PRO	Security Cupboard	 Yellow	1820 x 915 x 505	S13
214718	RS PRO	Security Cupboard	 Dark Grey	1820 x 915 x 505	S13
214719	RS PRO	Security Cupboard	 Blue	1820 x 915 x 505	S14
214720	RS PRO	Security Cupboard	 Light Grey	1820 x 915 x 505	S14
214721	RS PRO	Security Cupboard	 Red	1820 x 915 x 505	S14
214722	RS PRO	Security Cupboard	 Green	1820 x 915 x 505	S14
214724	RS PRO	Security Cupboard	 Yellow	1820 x 915 x 505	S14
214138	RS PRO	Security Cupboard	 Dark Grey	1820 x 915 x 505	S14
214140	RS PRO	Security Cupboard	 Blue	1820 x 915 x 505	S25

Stock No.	Brand	Product Name	Door Colours	Dimension (H x W x D mm)	Cupboard Internals
214141	RS PRO	Security Cupboard	 Light Grey	1820 x 915 x 505	S25
214143	RS PRO	Security Cupboard	 Red	1820 x 915 x 505	S25
214144	RS PRO	Security Cupboard	 Green	1820 x 915 x 505	S25
214146	RS PRO	Security Cupboard	 Yellow	1820 x 915 x 505	S25
214147	RS PRO	Security Cupboard	 Dark Grey	1820 x 915 x 505	S25
214148	RS PRO	Tool Cabinet	 Blue	1820 x 915 x 505	S32
214036	RS PRO	Tool Cabinet	 Light Grey	1820 x 915 x 505	S32
214037	RS PRO	Tool Cabinet	 Red	1820 x 915 x 505	S32
214039	RS PRO	Tool Cabinet	 Green	1820 x 915 x 505	S32
214040	RS PRO	Tool Cabinet	 Yellow	1820 x 915 x 505	S32
214042	RS PRO	Tool Cabinet	 Dark Grey	1820 x 915 x 505	S32
214043	RS PRO	Tool Cabinet	 Blue	1820 x 915 x 505	S38
214045	RS PRO	Tool Cabinet	 Light Grey	1820 x 915 x 505	S38
214046	RS PRO	Tool Cabinet	 Red	1820 x 915 x 505	S38
214047	RS PRO	Tool Cabinet	 Green	1820 x 915 x 505	S38
214049	RS PRO	Tool Cabinet	 Yellow	1820 x 915 x 505	S38
214051	RS PRO	Tool Cabinet	 Dark Grey	1820 x 915 x 505	S38
214052	RS PRO	Tool Cabinet	 Blue	1820 x 915 x 505	S40
214053	RS PRO	Tool Cabinet	 Light Grey	1820 x 915 x 505	S40
214055	RS PRO	Tool Cabinet	 Red	1820 x 915 x 505	S40
214056	RS PRO	Tool Cabinet	 Green	1820 x 915 x 505	S40
214058	RS PRO	Tool Cabinet	 Yellow	1820 x 915 x 505	S40
214059	RS PRO	Tool Cabinet	 Dark Grey	1820 x 915 x 505	S40
214191	RS PRO	Tool Cabinet	 Blue	1820 x 915 x 505	S44
214193	RS PRO	Tool Cabinet	 Light Grey	1820 x 915 x 505	S44
214194	RS PRO	Tool Cabinet	 Red	1820 x 915 x 505	S44
214196	RS PRO	Tool Cabinet	 Green	1820 x 915 x 505	S44
214197	RS PRO	Tool Cabinet	 Yellow	1820 x 915 x 505	S44
214198	RS PRO	Tool Cabinet	 Dark Grey	1820 x 915 x 505	S44
214200	RS PRO	Large Volume Cupboards	 Blue	1830 x 1219 x 457	S00
214201	RS PRO	Large Volume Cupboards	 Light Grey	1830 x 1219 x 457	S00
214203	RS PRO	Large Volume Cupboards	 Red	1830 x 1219 x 457	S00
214204	RS PRO	Large Volume Cupboards	 Green	1830 x 1219 x 457	S00
214205	RS PRO	Large Volume Cupboards	 Yellow	1830 x 1219 x 457	S00
214207	RS PRO	Large Volume Cupboards	 Dark Grey	1830 x 1219 x 457	S00
214208	RS PRO	Large Volume Cupboards	 Blue	1830 x 1219 x 457	S02
214210	RS PRO	Large Volume Cupboards	 Light Grey	1830 x 1219 x 457	S02
214211	RS PRO	Large Volume Cupboards	 Red	1830 x 1219 x 457	S02
214213	RS PRO	Large Volume Cupboards	 Green	1830 x 1219 x 457	S02

Stock No.	Brand	Product Name	Door Colours	Dimension (H x W x D mm)	Cupboard Internals
214214	RS PRO	Large Volume Cupboards	 Yellow	1830 x 1219 x 457	S02
214216	RS PRO	Large Volume Cupboards	 Dark Grey	1830 x 1219 x 457	S02
214217	RS PRO	Large Volume Cupboards	 Blue	1830 x 1219 x 457	S08
214219	RS PRO	Large Volume Cupboards	 Light Grey	1830 x 1219 x 457	S08
214220	RS PRO	Large Volume Cupboards	 Red	1830 x 1219 x 457	S08
214222	RS PRO	Large Volume Cupboards	 Green	1830 x 1219 x 457	S08
214223	RS PRO	Large Volume Cupboards	 Yellow	1830 x 1219 x 457	S08
214225	RS PRO	Large Volume Cupboards	 Dark Grey	1830 x 1219 x 457	S08
214226	RS PRO	Large Volume Cupboards	 Blue	1830 x 1219 x 457	S09
214227	RS PRO	Large Volume Cupboards	 Light Grey	1830 x 1219 x 457	S09
214229	RS PRO	Large Volume Cupboards	 Red	1830 x 1219 x 457	S09
214119	RS PRO	Large Volume Cupboards	 Green	1830 x 1219 x 457	S09
214121	RS PRO	Large Volume Cupboards	 Yellow	1830 x 1219 x 457	S09
214122	RS PRO	Large Volume Cupboards	 Dark Grey	1830 x 1219 x 457	S09
214124	RS PRO	Large Volume Cupboards	 Blue	1830 x 1219 x 457	S10
214125	RS PRO	Large Volume Cupboards	 Light Grey	1830 x 1219 x 457	S10
214126	RS PRO	Large Volume Cupboards	 Red	1830 x 1219 x 457	S10
214128	RS PRO	Large Volume Cupboards	 Green	1830 x 1219 x 457	S10
214129	RS PRO	Large Volume Cupboards	 Yellow	1830 x 1219 x 457	S10
214130	RS PRO	Large Volume Cupboards	 Dark Grey	1830 x 1219 x 457	S10
214131	RS PRO	Large Volume Cupboards	 Blue	1830 x 1219 x 457	S11
214132	RS PRO	Large Volume Cupboards	 Light Grey	1830 x 1219 x 457	S11
214134	RS PRO	Large Volume Cupboards	 Red	1830 x 1219 x 457	S11
214135	RS PRO	Large Volume Cupboards	 Green	1830 x 1219 x 457	S11
214136	RS PRO	Large Volume Cupboards	 Yellow	1830 x 1219 x 457	S11
214137	RS PRO	Large Volume Cupboards	 Dark Grey	1830 x 1219 x 457	S11
213301	RS PRO	Large Volume Cupboards	 Blue	1830 x 1219 x 457	S12
213302	RS PRO	Large Volume Cupboards	 Light Grey	1830 x 1219 x 457	S12
213303	RS PRO	Large Volume Cupboards	 Red	1830 x 1219 x 457	S12
213305	RS PRO	Large Volume Cupboards	 Green	1830 x 1219 x 457	S12
213306	RS PRO	Large Volume Cupboards	 Yellow	1830 x 1219 x 457	S12
213308	RS PRO	Large Volume Cupboards	 Dark Grey	1830 x 1219 x 457	S12
213309	RS PRO	Large Volume Cupboards	 Blue	1830 x 1219 x 457	S13
213311	RS PRO	Large Volume Cupboards	 Light Grey	1830 x 1219 x 457	S13
213312	RS PRO	Large Volume Cupboards	 Red	1830 x 1219 x 457	S13
213314	RS PRO	Large Volume Cupboards	 Green	1830 x 1219 x 457	S13
213315	RS PRO	Large Volume Cupboards	 Yellow	1830 x 1219 x 457	S13
213316	RS PRO	Large Volume Cupboards	 Dark Grey	1830 x 1219 x 457	S13
213317	RS PRO	Large Volume Cupboards	 Blue	1830 x 1219 x 457	S20

Stock No.	Brand	Product Name	Door Colours	Dimension (H x W x D mm)	Cupboard Internals
213318	RS PRO	Large Volume Cupboards	 Light Grey	1830 x 1219 x 457	S20
213319	RS PRO	Large Volume Cupboards	 Red	1830 x 1219 x 457	S20
214231	RS PRO	Large Volume Cupboards	 Green	1830 x 1219 x 457	S20
214232	RS PRO	Large Volume Cupboards	 Yellow	1830 x 1219 x 457	S20
214233	RS PRO	Large Volume Cupboards	 Dark Grey	1830 x 1219 x 457	S20
214235	RS PRO	Large Volume Cupboards	 Blue	1830 x 1219 x 457	S22
214236	RS PRO	Large Volume Cupboards	 Light Grey	1830 x 1219 x 457	S22
214238	RS PRO	Large Volume Cupboards	 Red	1830 x 1219 x 457	S22
214239	RS PRO	Large Volume Cupboards	 Green	1830 x 1219 x 457	S22
214241	RS PRO	Large Volume Cupboards	 Yellow	1830 x 1219 x 457	S22
214242	RS PRO	Large Volume Cupboards	 Dark Grey	1830 x 1219 x 457	S22
214244	RS PRO	STANDARD CUPBOARD SHELF CLIP	N/A	N/A	N/A
214245	RS PRO	48 X 18 CUPB.SHELF	 Light Grey	N/A	N/A
213369	RS PRO	Tool Cabinet	 Blue	984 X 477 X 505	S30
213370	RS PRO	Tool Cabinet	 Light Grey	984 X 477 X 505	S30
213371	RS PRO	Tool Cabinet	 Red	984 X 477 X 505	S30
213373	RS PRO	Tool Cabinet	 Green	984 X 477 X 505	S30
213374	RS PRO	Tool Cabinet	 Yellow	984 X 477 X 505	S30
213375	RS PRO	Tool Cabinet	 Dark Grey	984 X 477 X 505	S30
213377	RS PRO	Tool Cabinet	 Blue	984 X 477 X 505	S33
213378	RS PRO	Tool Cabinet	 Light Grey	984 X 477 X 505	S33
213380	RS PRO	Tool Cabinet	 Red	984 X 477 X 505	S33
213381	RS PRO	Tool Cabinet	 Green	984 X 477 X 505	S33
213383	RS PRO	Tool Cabinet	 Yellow	984 X 477 X 505	S33
213384	RS PRO	Tool Cabinet	 Dark Grey	984 X 477 X 505	S33
213386	RS PRO	Tool Cabinet	 Blue	984 X 477 X 505	S34
213387	RS PRO	Tool Cabinet	 Light Grey	984 X 477 X 505	S34
213389	RS PRO	Tool Cabinet	 Red	984 X 477 X 505	S34
213390	RS PRO	Tool Cabinet	 Green	984 X 477 X 505	S34
213392	RS PRO	Tool Cabinet	 Yellow	984 X 477 X 505	S34
213393	RS PRO	Tool Cabinet	 Dark Grey	984 X 477 X 505	S34
213395	RS PRO	Tool Cabinet	 Blue	984 X 477 X 505	S39
213396	RS PRO	Tool Cabinet	 Light Grey	984 X 477 X 505	S39
213397	RS PRO	Tool Cabinet	 Red	984 X 477 X 505	S39
213399	RS PRO	Tool Cabinet	 Green	984 X 477 X 505	S39
213400	RS PRO	Tool Cabinet	 Yellow	984 X 477 X 505	S39
213402	RS PRO	Tool Cabinet	 Dark Grey	984 X 477 X 505	S39
214310	RS PRO	Tool Cabinet	 Blue	984 X 477 X 505	S42
214311	RS PRO	Tool Cabinet	 Light Grey	984 X 477 X 505	S42

Stock No.	Brand	Product Name	Door Colours	Dimension (H x W x D mm)	Cupboard Internals
214312	RS PRO	Tool Cabinet	 Red	984 X 477 X 505	S42
214314	RS PRO	Tool Cabinet	 Green	984 X 477 X 505	S42
214315	RS PRO	Tool Cabinet	 Yellow	984 X 477 X 505	S42
214317	RS PRO	Tool Cabinet	 Dark Grey	984 X 477 X 505	S42
214318	RS PRO	Tool Cabinet	 Blue	984 X 477 X 505	S45
214320	RS PRO	Tool Cabinet	 Light Grey	984 X 477 X 505	S45
214321	RS PRO	Tool Cabinet	 Red	984 X 477 X 505	S45
214323	RS PRO	Tool Cabinet	 Green	984 X 477 X 505	S45
214324	RS PRO	Tool Cabinet	 Yellow	984 X 477 X 505	S45
214326	RS PRO	Tool Cabinet	 Dark Grey	984 X 477 X 505	S45
214327	RS PRO	Low Slimline Cupboard	 Blue	984 X 615 X 505	S12
214328	RS PRO	Low Slimline Cupboard	 Light Grey	984 X 615 X 505	S12
214330	RS PRO	Low Slimline Cupboard	 Red	984 X 615 X 505	S12
214332	RS PRO	Low Slimline Cupboard	 Green	984 X 615 X 505	S12
214333	RS PRO	Low Slimline Cupboard	 Yellow	984 X 615 X 505	S12
214334	RS PRO	Low Slimline Cupboard	 Dark Grey	984 X 615 X 505	S12
214336	RS PRO	Standard Cupboard	 Blue	984 X 915 X 505	S12
214337	RS PRO	Standard Cupboard	 Light Grey	984 X 915 X 505	S12
214339	RS PRO	Standard Cupboard	 Red	984 X 915 X 505	S12
214340	RS PRO	Standard Cupboard	 Green	984 X 915 X 505	S12
214342	RS PRO	Standard Cupboard	 Yellow	984 X 915 X 505	S12
214343	RS PRO	Standard Cupboard	 Dark Grey	984 X 915 X 505	S12
213415	RS PRO	Security Cupboard	 Blue	984 X 915 X 505	S12
213416	RS PRO	Security Cupboard	 Light Grey	984 X 915 X 505	S12
213418	RS PRO	Security Cupboard	 Red	984 X 915 X 505	S12
213419	RS PRO	Security Cupboard	 Green	984 X 915 X 505	S12
213421	RS PRO	Security Cupboard	 Yellow	984 X 915 X 505	S12
213422	RS PRO	Security Cupboard	 Dark Grey	984 X 915 X 505	S12
213423	RS PRO	Tool Cabinet	 Blue	984 X 915 X 505	S35
213424	RS PRO	Tool Cabinet	 Light Grey	984 X 915 X 505	S35
213425	RS PRO	Tool Cabinet	 Red	984 X 915 X 505	S35
213426	RS PRO	Tool Cabinet	 Green	984 X 915 X 505	S35
214390	RS PRO	Tool Cabinet	 Yellow	984 X 915 X 505	S35
214392	RS PRO	Tool Cabinet	 Dark Grey	984 X 915 X 505	S35
214393	RS PRO	Tool Cabinet	 Blue	984 X 915 X 505	S36
214395	RS PRO	Tool Cabinet	 Light Grey	984 X 915 X 505	S36
214396	RS PRO	Tool Cabinet	 Red	984 X 915 X 505	S36
214398	RS PRO	Tool Cabinet	 Green	984 X 915 X 505	S36
214399	RS PRO	Tool Cabinet	 Yellow	984 X 915 X 505	S36

Stock No.	Brand	Product Name	Door Colours	Dimension (H x W x D mm)	Cupboard Internals
214400	RS PRO	Tool Cabinet	 Dark Grey	984 X 915 X 505	S36
214402	RS PRO	Tool Cabinet	 Blue	984 X 915 X 505	S37
214403	RS PRO	Tool Cabinet	 Light Grey	984 X 915 X 505	S37
214405	RS PRO	Tool Cabinet	 Red	984 X 915 X 505	S37
214406	RS PRO	Tool Cabinet	 Green	984 X 915 X 505	S37
214407	RS PRO	Tool Cabinet	 Yellow	984 X 915 X 505	S37
214409	RS PRO	Tool Cabinet	 Dark Grey	984 X 915 X 505	S37
214411	RS PRO	Tool Cabinet	 Blue	984 X 915 X 505	S43
214412	RS PRO	Tool Cabinet	 Light Grey	984 X 915 X 505	S43
214413	RS PRO	Tool Cabinet	 Red	984 X 915 X 505	S43
214415	RS PRO	Tool Cabinet	 Green	984 X 915 X 505	S43
214416	RS PRO	Tool Cabinet	 Yellow	984 X 915 X 505	S43
214418	RS PRO	Tool Cabinet	 Dark Grey	984 X 915 X 505	S43
214419	RS PRO	SHELF CLIP FOR LARGE VOLUME CUPBOARD	N/A	N/A	N/A
214421	RS PRO	Cupboard Shelf	 Light Grey	300 x 505	N/A
214422	RS PRO	Cupboard Shelf	 Light Grey	450 x 505	N/A
213576	RS PRO	Single Cupboard Adj Shelf	 Yellow	477 x 505	N/A
213577	RS PRO	Tool Cabinet Shelf, Single (Galvanised)	 Light Grey	477 x 505	N/A
213579	RS PRO	Slimline Cupboard Shelf	 Light Grey	615 x 505	N/A
213581	RS PRO	Standard Cupboard Shelf	 Light Grey	915 x 505	N/A
213482	RS PRO	Tool Cabinet Shelf, Double (Galvanised)	 Light Grey	477 x 505	N/A
213484	RS PRO	SLOPING TOP FOR 915x505mm CUPBOARD	 Light Grey	N/A	N/A

Important note regarding locker installations

Wherever possible lockers should be secured to ensure stability. Single lockers should ideally be fixed back to a wall. Runs of lockers should be fixed together side-to-side and either fixed back to a wall or fixed back-to-back to another run of lockers.

Tool Cabinet




Cupboard Internals




4 shelves

S31




2 drawers,
2 shelves

S35




7 drawers,
1 shelf

S41




6 drawers,
6 shelves

S40




8 shelves

S32




4 drawers,
4 shelves

S38




14 drawers,
2 shelves

S44




1 drawer,
1 shelf

S33




1 drawer,
2 shelves

S34



2 drawers,
1 shelf

S45



2 shelves

S30



6 drawers

S39



8 drawers

S42

Slimline Cupboards




The practical solution where storage space is limited. Slimline cupboards provide secure storage in a compact 'footprint' of only 615 x 505mm.

■ Extra shelf 615 x 505mm

Cupboard Internals

Standard, Security, Vision, Slimline and Large Volume cupboards are all available in the internal configurations illustrated. These offer a range of solutions to meet workplace requirements.



Standard Cupboards



These strong, robust steel cupboards provide excellent durability and capacity for storage of items within a workplace environment.

Whether for use as an office or a factory cupboard; the product is designed to meet your requirements.

■ Extra shelf 915 x 505mm

Height - 984 or 1820mm	
Width	Depth
915mm	505mm

Security Cupboards

Where valuable and potentially vulnerable materials or equipment are used in the workplace; the need for storage equipment with enhanced security becomes a necessity. Security cupboards benefit from an additional hasp and staple fitting.

■ Extra shelf 915 x 505mm

Height - 984 or 1820mm	
Width	Depth
915mm	505mm



Security cupboards benefit from an additional hasp and staple fitting, for use with a padlock (not supplied), as well as the standard 3 point locking.



Insight Cupboard

Vision cupboards show visible items, but do not compromise on security.

Based on the standard all-steel cupboards; with the addition of toughened polycarbonate view panels, set within a steel door (which has an all-round strengthened edge).

■ Extra shelf 915 x 505mm



Large Volume Cupboards

As the name suggests, these are the largest of our cupboard range; offering spacious storage for awkward and bulky items.

- Extra shelf 1291 x 457mm

Height - 1830mm	
Width	Depth
1219mm	457mm




High quality metal lock operates the 3 point locking system.



Cupboard Internals

Standard, Security, Vision, Slimline and Large Volume cupboards are all available in the internal configurations illustrated. These offer a range of solutions to meet workplace requirements.



Low Slimline Cupboard



Low slim tool cupboard

Cupboards Internals



S12

- Two adjustable full width shelves.

