

BMP[®]41 LABEL PRINTER



Print it once, print it all, get it done!

The BMP[™]41 label printer is the rugged, portable solution that gives you the versatility to create your own length or already-sized die-cut and continuous labels anywhere, anytime! The BMP[™]41 label printer is designed with you in mind. Get your labelling done easier and faster so you can get on with your day. You only need one printer to print everything you need.



Order Reference	Description	Width (mm)	Length (m)	Height (mm)	Manufacturer Part Number	Printer Compatibility
B-595 Vinyl Tape, General Industrial Identification; Pipe Marking						
7753619	Red/White Permanent Vinyl Tape	12.7 mm	7.62 m		MC-500-595-WT-RD	BMP41; BMP51; BMP53
7753663	Red/White Permanent Vinyl Tape	19.5 mm	7.62 m		MC-750-595-WT-RD	BMP41; BMP51; BMP53
7934262	Red/White Permanent Vinyl Tape 7.62m	25.4 mm	7.62 m		MC1-1000-595-WT-RD	BMP41; BMP51; BMP53
7753584	White/Black Permanent Vinyl Tape	12.7 mm	7.62 m		MC-500-595-BK-WT	BMP41; BMP51; BMP53
7753644	White/Black Permanent Vinyl Tape	19.5 mm	7.62 m		MC-750-595-BK-WT	BMP41; BMP51; BMP53
7934234	White/Black Permanent Vinyl Tape 7.62m	25.4 mm	7.62 m		MC1-1000-595-BK-WT	BMP41; BMP51; BMP53
7753593	White/Blue Permanent Vinyl Tape	12.7 mm	7.62 m		MC-500-595-BL-WT	BMP41; BMP51; BMP53
7753647	White/Blue Permanent Vinyl Tape	19.5 mm	7.62 m		MC-750-595-BL-WT	BMP41; BMP51; BMP53
7934238	White/Blue Permanent Vinyl Tape 7.62m	25.4 mm	7.62 m		MC1-1000-595-BL-WT	BMP41; BMP51; BMP53
7753590	White/Clear Permanent Vinyl Tape	12.7 mm	6.1 m		MC-500-595-CL-WT	BMP41; BMP51; BMP53
7753650	White/Clear Permanent Vinyl Tape	19.5 mm	6.1 m		MC-750-595-CL-WT	BMP41; BMP51; BMP53
7934240	White/Clear Permanent Vinyl Tape 6.09m	25.4 mm	6.1 m		MC1-1000-595-CL-WT	BMP41; BMP51; BMP53
7753600	White/Green Permanent Vinyl Tape	12.7 mm	7.62 m		MC-500-595-GN-WT	BMP41; BMP51; BMP53
7753653	White/Green Permanent Vinyl Tape	19.5 mm	7.62 m		MC-750-595-GN-WT	BMP41; BMP51; BMP53
7934244	White/Green Permanent Vinyl Tape 7.62m	25.4 mm	7.62 m		MC1-1000-595-GN-WT	BMP41; BMP51; BMP53
7753607	White/Red Permanent Vinyl Tape	12.7 mm	7.62 m		MC-500-595-RD-WT	BMP41; BMP51; BMP53
7753666	White/Red Permanent Vinyl Tape	19.5 mm	7.62 m		MC-750-595-RD-WT	BMP41; BMP51; BMP53
7934256	White/Red Permanent Vinyl Tape 7.62m	25.4 mm	7.62 m		MC1-1000-595-RD-WT	BMP41; BMP51; BMP53
7753596	Black/Clear Permanent Vinyl Tape	12.7 mm	6.1 m		MC-500-595-CL-BK	BMP41; BMP51; BMP53
7753641	Black/Clear Permanent Vinyl Tape	19.5 mm	6.1 m		MC-750-595-CL-BK	BMP41; BMP51; BMP53
7934247	Black/Clear Permanent Vinyl Tape 6.09m	25.4 mm	6.1 m		MC1-1000-595-CL-BK	BMP41; BMP51; BMP53
7753603	Black/Orange Permanent Vinyl Tape	12.7 mm	7.62 m		MC-500-595-OR-BK	BMP41; BMP51; BMP53
7753657	Black/Orange Permanent Vinyl Tape	19.5 mm	7.62 m		MC-750-595-OR-BK	BMP41; BMP51; BMP53
7934253	Black/Orange Permanent Vinyl Tape 7.62m	25.4 mm	7.62 m		MC1-1000-595-OR-BK	BMP41; BMP51; BMP53
7753616	Black/White Permanent Vinyl Tape	12.7 mm	7.62 m		MC-500-595-WT-BK	BMP41; BMP51; BMP53
7753669	Black/White Permanent Vinyl Tape	19.5 mm	7.62 m		MC-750-595-WT-BK	BMP41; BMP51; BMP53
7934250	Black/White Permanent Vinyl Tape 7.62m	25.4 mm	7.62 m		MC1-1000-595-WT-BK	BMP41; BMP51; BMP53
7753613	Black/Yellow Permanent Vinyl Tape	12.7 mm	7.62 m		MC-500-595-YL-BK	BMP41; BMP51; BMP53
7753672	Black/Yellow Permanent Vinyl Tape	19.5 mm	7.62 m		MC-750-595-YL-BK	BMP41; BMP51; BMP53
7934269	Black/Yellow Permanent Vinyl Tape 7.62m	25.4 mm	7.62 m		MC1-1000-595-YL-BK	BMP41; BMP51; BMP53
B-584 Reflective Tap, General & Industrial Identification						
7753580	Black/Yellow Reflective Vinyl Tape	12.7 mm	6.1 m		MC-500-584-YL	BMP41; BMP51; BMP53
7753635	Black/Yellow Reflective Vinyl Tape	19.5 mm	6.1 m		MC-750-584-YL	BMP41; BMP51; BMP53
B-422 Gloss Polyester Tape, General & Industrial Identification; Rating & Nameplate Labels; Voice & Data Communication						
7753565	Black/White Glossy Polyester Tape	9.53 mm	7.62 m		MC-375-422	BMP41; BMP51; BMP53
7753571	Black/White Glossy Polyester Tape	12.7 mm	7.62 m		MC-475-422	BMP41; BMP51; BMP53
7753574	Black/White Glossy Polyester Tape	12.7 mm	7.62 m		MC-500-422	BMP41; BMP51; BMP53
7753625	Black/White Glossy Polyester Tape	15.88 mm	7.62 m		MC-625-422	BMP41; BMP51; BMP53
7934231	Black/White Glossy Polyester Tape 7.62m	25.4 mm	7.62 m		MC1-1000-422	BMP41; BMP51; BMP53
B-499 Matt Nylon Cloth Tape, Wire & Cable Marking; Laboratory Identification						
7753568	Black/White Nylon Cloth Printer Tape	9.53 mm	4.88 m		MC-375-499	BMP41; BMP51; BMP53
7753578	Black/White Nylon Cloth Printer Tape	12.7 mm	4.88 m		MC-500-499	BMP41; BMP51; BMP53
7753638	Black/White Nylon Cloth Tape	19.5 mm	4.88 m		MC-750-499	BMP41; BMP51; BMP53
B-498 Semi Gloss Vinyl Cloth Tape, Wire & Cable Marking; Laboratory Identification; Removable						
8011654	MC-240-498 Terminal markers black /white	6.1 mm	4.88 m		MC-240-498	BMP41; BMP51; BMP53
8011657	MC-318-498 Terminal markers black /white	8.8 mm	4.88 m		MC-318-498	BMP41; BMP51; BMP53
8011660	MC-375-498 Terminal marker black/white	9.53 mm	6.1 m		MC-375-498	BMP41; BMP51; BMP53
B-422 Gloss Polyester Labels, General & Industrial Identification; Product Identification; Voice & Data Communication						
7934137	Black/White Polyester Printer Labels	25.4 mm		12.7 mm	M-47-422	BMP41; BMP51; BMP53
7934143	Black/White Polyester Printer Labels	25.4 mm		25.4 mm	M-49-422	BMP41; BMP51; BMP53
7934165	Black/White Polyester Printer Labels	12.7 mm		38.1 mm	M-89-422	BMP41; BMP51; BMP53

7934177	Black/White Polyester Printer Labels	19.5 mm	38.1 mm	M-90-422	BMP41; BMP51; BMP53
7753391	Black/White Polyester Printer Labels	12.7 mm	12.7 mm	M-7-422	BMP41; BMP51; BMP53
B-499 Matt Nylon Cloth Labels, Wire & Cable Marking; Laboratory Identification					
7753414	Black/Orange Nylon Cloth Printer Labels 9.53 mm Dia			M-82-499-OR-BK	BMP41; BMP51; BMP53
7753423	Black/Orange Nylon Cloth Printer Labels 12.70 mm Dia			M-83-499-OR-BK	BMP41; BMP51; BMP53
7753417	Black/Red Nylon Cloth Printer Labels 9.53 mm Dia			M-82-499-RD-BK	BMP41; BMP51; BMP53
7753427	Black/Red Nylon Cloth Printer Labels 12.70 mm Dia			M-83-499-RD-BK	BMP41; BMP51; BMP53
7753411	Black/Yellow Nylon Cloth Printer Labels 9.53 mm Dia			M-82-499-YL-BK	BMP41; BMP51; BMP53
7753436	Black/Yellow Nylon Cloth Printer Labels 12.70 mm Dia			M-83-499-YL-BK	BMP41; BMP51; BMP53
7753405	Black/White Nylon Cloth Printer Labels 9.53 mm Dia			M-82-499	BMP41; BMP51; BMP53
7753420	Black/White Nylon Cloth Printer Labels 12.70 mm Dia			M-83-499	BMP41; BMP51; BMP53
7753265	Black/White Nylon Cloth Printer Labels	12.7 mm	25.4 mm	M-131-499	BMP41; BMP51; BMP53
7934193	Black/White Nylon Cloth Printer Labels	25.4 mm	57.15 mm	M-141-499	BMP41; BMP51; BMP53
7934228	Black/White Nylon Cloth Printer Labels	25.4 mm	48.26 mm	M-128-499	BMP41; BMP51; BMP53
8011645	M-11-499 Nylon cloth black on white	19.5 mm	12.7 mm	M-11-499	BMP41; BMP51; BMP53
B-428 Matt Polyester Labels, Rating & Nameplate Labels					
7934146	Black/Silver Metallised Polyester Labels	25.4 mm	12.7 mm	M-47-428	BMP41; BMP51; BMP53
7934155	Black/Silver Metallised Polyester Labels	25.4 mm	5.8 mm	M-60-428	BMP41; BMP51; BMP53
8011676	M-92-428-BB Metallised poly black/silver	12.7 mm	33.2 mm	M-92-428-BB	BMP41; BMP51; BMP53
B-483 Gloss Polyester, General & Industrial Identification; Rating & Nameplate Labels; Voice & Data Communication					
7753382	Black/White Polyester Printer Labels	12.7 mm	5.8 mm	M-61-483	BMP41; BMP51; BMP53
7934149	Black/White Polyester Printer Labels	25.4 mm	12.7 mm	M-47-483	BMP41; BMP51; BMP53
7934159	Black/White Polyester Printer Labels	25.4 mm	5.8 mm	M-60-483	BMP41; BMP51; BMP53
B-427 Self Laminating Vinyl, Wire & Cable Marking					
7753243	Black/White Self-Laminating Vinyl Labels	12.7 mm	19.5 mm	M-11-427	BMP41; BMP51; BMP53
7753231	Black/White Self-Laminating Vinyl Labels	12.7 mm	31.75 mm	M-102-427	BMP41; BMP51; BMP53
7934152	Black/White Self-Laminating Vinyl Labels	25.4 mm	25.4 mm	M-49-427	BMP41; BMP51; BMP53
7934168	Black/White Self-Laminating Vinyl Labels	25.4 mm	63.5 mm	M-51-427	BMP41; BMP51; BMP53
7934171	Black/White Self-Laminating Vinyl Labels	19.5 mm	38.1 mm	M-90-427	BMP41; BMP51; BMP53
7934174	Black/White Self-Laminating Vinyl Labels	12.7 mm	38.1 mm	M-89-427	BMP41; BMP51; BMP53
7934180	Black/White Self-Laminating Vinyl Labels	25.4 mm	38.1 mm	M-91-427	BMP41; BMP51; BMP53
7934196	Black/White Self-Laminating Vinyl Labels	25.4 mm	19.5 mm	M-136-427	BMP41; BMP51; BMP53
7934199	Black/White Self-Laminating Vinyl Labels	25.4 mm	31.75 mm	M-143-427	BMP41; BMP51; BMP53
7934203	Black/White Self-Laminating Vinyl Labels	12.7 mm	25.4 mm	M-47-427	BMP41; BMP51; BMP53
7934206	Black/White Self-Laminating Vinyl Labels	19.5 mm	25.4 mm	M-48-427	BMP41; BMP51; BMP53
7934212	Black/White Self-Laminating Vinyl Labels	25.4 mm	11.6 mm	M-53-427	BMP41; BMP51; BMP53
7753629	Black/White Self-Laminating Vinyl Tape	19.5 mm	7.62 m	MC-750-427	BMP41; BMP51; BMP53
7934216	Black/Yellow Self-Laminating Vinyl Labels	25.4 mm	11.6 mm	M-53-427-YL	BMP41; BMP51; BMP53
7934161	Black/Yellow Self-Laminating Vinyl Label	25.4 mm	63.5 mm	M-51-427-YL	BMP41; BMP51; BMP53
7934183	Black/Yellow Self-Laminating Vinyl Label	25.4 mm	38.1 mm	M-91-427-YL	BMP41; BMP51; BMP53
B-342 Heat Shrink Polyolefin Sleeve, Wire & Cable Marking; Heat-shrinkable; Self-Extinguishing.					
7753492	Blk/White Heatshrink Wire Marker Sleeve	2.13 m	6. mm	MC-125-342	BMP41; BMP51; BMP53
7753540	Blk/White Heatshrink Wire Marker Sleeve	2.13 m	11.15 mm	MC-250-342	BMP41; BMP51; BMP53
7753543	Blk/White Heatshrink Wire Marker Sleeve	2.13 m	8.5 mm	MC-187-342	BMP41; BMP51; BMP53
7753495	Blk/Yellow Heatshrink Wire Marker Sleeve	2.13 m	6. mm	MC-125-342-YL	BMP41; BMP51; BMP53
7753546	Blk/Yellow Heatshrink Wire Marker Sleeve	2.13 m	8.5 mm	MC-187-342-YL	BMP41; BMP51; BMP53
7753559	Blk/Yellow Heatshrink Wire Marker Sleeve	2.13 m	11.15 mm	MC-250-342-YL	BMP41; BMP51; BMP53
8011682	M-125-075-342 heatshrink black/white	19.5 mm	6. mm	M-125-075-342	BMP41; BMP51; BMP53
8011679	M-187-075-342 heatshrink black/white	19.5 mm	8.5 mm	M-187-075-342	BMP41; BMP51; BMP53
8011673	M-250-075-342 heatshrink black/white	19.5 mm	11.15 mm	M-250-075-342	BMP41; BMP51; BMP53
8011685	M-375-075-342 heatshrink black/white	19.5 mm	16.4 mm	M-375-075-342	BMP41; BMP51; BMP53
B-498 Semi Gloss Vinyl Cloth Labels, Wire & Cable Marking; Laboratory Identification; Removable					
7753262	Black/White Vinyl Cloth Printer Labels	12.7 mm	25.4 mm	M-131-498	BMP41; BMP51; BMP53
7753394	Black/White Vinyl Cloth Printer Labels	12.7 mm	12.7 mm	M-7-498	BMP41; BMP51; BMP53
7934187	Black/White Vinyl Cloth Printer Labels	25.4 mm	38.1 mm	M-91-498	BMP41; BMP51; BMP53
7934200	Black/White Vinyl Cloth Printer Labels	25.4 mm	19.5 mm	M-48-498	BMP41; BMP51; BMP53
7934219	Black/White Vinyl Cloth Printer Labels	25.4 mm	25.4 mm	M-49-498	BMP41; BMP51; BMP53
7934225	Black/White Vinyl Cloth Printer Labels	25.4 mm	48.26 mm	M-128-498	BMP41; BMP51; BMP53
8011641	M-11-498 Vinyl cloth labels black/white	19.5 mm	12.7 mm	M-11-498	BMP41; BMP51; BMP53
B-412 Polypropylene Tags, Voice & Data Communication					
8011663	MC-475-412 Polyprop taglabel black/white	12.7 mm	6.1 m	MC-475-412	BMP41; BMP51; BMP53
7753556	Black/White Polypropylene Tags	9.53 mm	6.1 m	MC-375-412	BMP41; BMP51; BMP53
7753622	Black/White Polypropylene Tags	15.88 mm	6.1 m	MC-625-412	BMP41; BMP51; BMP53
Accessories					
8011613	BMP41 Battery			BMP41-BATT	BMP41; BMP61
8011635	BMP41 EU External Battery Quick Charger			BMP41-QC-EU	BMP41
8011639	BMP41 UK External Battery Quick Charger			BMP41-QC-UK	BMP41
8011617	BMP41 Hard Case			BMP41-HC	BMP41
7117590	BMP71 AC Adaptor UK			M41/50/61/71-AC-BC-UK	BMP41; BMP51; BMP53; BMP71

* BMP53 Now discontinued 2017

** Additional BMP51/53 labels are available, see printer product page for full range